Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360728

Luminaire Tested: **GSS-SB5B-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360728
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB5B-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 5SQUARE 184W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(130) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	25125.4 lumens
Efficiency:	N/A
Efficacy:	136.6 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	184
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	11.1%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360728
CATALOG NUMBER: GSS-SB5B-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 12.4 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360728
CATALOG NUMBER: GSS-SB5B-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360728
CATALOG NUMBER: GSS-SB5B-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	12562.7	0.0	12562.7
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	12562.7	0.0	12562.7
	% Fixture	50.0	0.0	50.0
Total	Lumens	25125.4	0.0	25125.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	479.2	1.9
10°-20°	1460.4	5.8
20°-30°	2440.9	9.7
30°-40°	3366.2	13.4
40°-50°	4126.5	16.4
50°-60°	4835.7	19.2
60°-70°	5369.9	21.4
70°-80°	2920.2	11.6
80°-90°	126.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	25125.4	100.0
0°-180°	25125.4	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360728
CATALOG NUMBER: GSS-SB5B-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2190.2	8.7			
FM	(30°-60°)	6164.2	24.5			
FH	(60°-80°)	4145.0	16.5			G2/5000
FVH	(80°-90°)	63.3	0.3			G1/100
BL	(0°-30°)	2190.2	8.7	B3/2500		
BM	(30°-60°)	6164.2	24.5	B4/8500		
BH	(60°-80°)	4145.0	16.5	B4/5000		G4/5000
BVH	(80°-90°)	63.3	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360728
CATALOG NUMBER: GSS-SB5B-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	4950.3	4950.3	4950.3	4950.3	4950.3	4950.3	4950.3	4950.3	4950.3	4950.3	4950.3
2.5°	4955.8	4955.8	4939.3	4961.3	4950.3	4955.8	4961.3	4955.8	4950.3	4955.8	4961.3
5°	4983.3	4972.3	4983.3	4994.3	4977.8	4988.8	4983.3	4955.8	4972.3	4972.3	4972.3
7.5°	5032.8	5043.8	5032.8	5060.3	5043.8	5076.8	5043.8	5021.8	5016.3	5010.8	5010.8
10°	5054.8	5054.8	5049.3	5098.8	5109.8	5142.8	5120.8	5087.8	5071.3	5049.3	5027.3
12.5°	4994.3	5005.3	5032.8	5126.3	5170.4	5236.4	5219.9	5153.8	5104.3	5087.8	5054.8
15°	4928.3	4939.3	4994.3	5109.8	5214.4	5313.4	5307.9	5225.4	5164.8	5120.8	5071.3
17.5°	4823.8	4840.3	4917.3	5093.3	5280.4	5390.4	5423.4	5340.9	5274.9	5203.4	5137.3
20°	4647.8	4647.8	4785.3	5010.8	5269.4	5516.9	5604.9	5538.9	5461.9	5346.4	5258.4
22.5°	4449.8	4460.8	4598.3	4895.3	5263.9	5626.9	5797.4	5725.9	5648.9	5522.4	5390.4
25°	4251.8	4251.8	4405.8	4741.3	5192.4	5703.9	6022.9	5984.4	5830.4	5714.9	5544.4
27.5°	4070.3	4070.3	4235.3	4587.3	5071.3	5725.9	6248.4	6248.4	6077.9	5907.4	5720.4
30°	3855.8	3910.8	4097.8	4466.3	4961.3	5687.4	6413.4	6517.9	6363.9	6143.9	5868.9
32.5°	3674.2	3712.8	3905.3	4295.8	4801.8	5643.4	6600.4	6859.0	6699.5	6396.9	6088.9
35°	3459.7	3454.2	3674.2	4059.3	4576.3	5544.4	6749.0	7266.0	7112.0	6787.5	6369.4
37.5°	3179.2	3179.2	3404.7	3778.8	4361.8	5373.9	6870.0	7717.0	7601.5	7233.0	6787.5
40°	2876.7	2909.7	3107.7	3487.2	4103.3	5170.4	6870.0	8085.5	8146.1	7766.5	7304.5
42.5°	2656.7	2667.7	2849.2	3206.7	3817.3	4906.3	6782.0	8404.6	8586.1	8267.1	7667.5
45°	2425.7	2453.2	2607.2	2937.2	3520.2	4592.8	6627.9	8762.1	9053.6	8833.6	8047.0
47.5°	2145.1	2172.6	2348.7	2684.2	3239.7	4251.8	6369.4	9136.1	9746.7	9587.1	8723.6
50°	1820.6	1842.6	2007.6	2365.2	2926.2	3861.3	6044.9	9416.6	10439.7	10599.2	9746.7
52.5°	1424.6	1441.1	1617.1	1963.6	2552.2	3487.2	5588.4	9587.1	11138.3	11699.3	11116.3
55°	1023.1	1050.6	1204.6	1490.6	2057.1	2986.7	5043.8	9675.2	11902.8	13002.9	12815.9
57.5°	737.0	748.1	852.6	1072.6	1529.1	2398.2	4345.3	9526.6	12590.4	14559.5	14950.0
60°	610.5	610.5	627.0	731.5	1045.1	1694.1	3509.2	8976.6	13178.9	16132.6	17337.2
62.5°	561.0	561.0	572.0	588.5	687.5	1100.1	2508.2	7860.0	13244.9	17645.2	19955.4
65°	511.5	511.5	522.5	533.5	555.5	715.0	1512.6	5753.4	11952.3	17661.7	21363.4
67.5°	467.5	467.5	473.0	478.5	489.5	522.5	830.6	3487.2	9565.1	17194.2	21902.5
70°	423.5	423.5	423.5	418.0	434.5	440.0	550.0	1771.1	6396.9	15527.6	21644.0
72.5°	*374.0*	*374.0*	*368.5*	*357.5*	*363.0*	*363.0*	*407.0*	*869.1*	*3322.2*	*12342.8*	*19542.8*
75°	319.0	324.5	302.5	291.5	286.0	291.5	324.5	495.0	1485.1	7486.0	14603.5
77.5°	269.5	280.5	247.5	225.5	220.0	220.0	253.0	308.0	638.0	2717.2	6545.4
80°	203.5	209.0	181.5	159.5	159.5	154.0	187.0	225.5	302.5	808.6	1468.6
82.5°	115.5	115.5	104.5	93.5	88.0	93.5	126.5	154.0	187.0	286.0	401.5
85°	27.5	27.5	33.0	38.5	38.5	49.5	71.5	82.5	99.0	115.5	154.0
87.5°	5.5	5.5	5.5	11.0	16.5	16.5	27.5	38.5	49.5	60.5	66.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360728
CATALOG NUMBER: GSS-SB5B-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	4950.3	4950.3	*4950.3*
2.5°	4961.3	4966.8	*4961.3*
5°	4994.3	4983.3	*4966.8*
7.5°	4999.8	5005.3	*5010.8*
10°	5021.8	5043.8	*5010.8*
12.5°	5043.8	5027.3	*5016.3*
15°	5060.3	5054.8	*5021.8*
17.5°	5120.8	5098.8	*5093.3*
20°	5214.4	5208.9	*5192.4*
22.5°	5324.4	5313.4	*5307.9*
25°	5483.9	5445.4	*5423.4*
27.5°	5615.9	5582.9	*5571.9*
30°	5747.9	5681.9	*5681.9*
32.5°	5863.4	5846.9	*5835.9*
35°	6138.4	6055.9	*6066.9*
37.5°	6473.9	6391.4	*6319.9*
40°	6947.0	6837.0	*6793.0*
42.5°	7249.5	7139.5	*7150.5*
45°	7420.0	7227.5	*7178.0*
47.5°	7882.0	7640.0	*7574.0*
50°	8630.1	8333.1	*8250.6*
52.5°	9840.2	9361.6	*9251.6*
55°	11358.3	10769.7	*10659.7*
57.5°	13437.4	12656.4	*12419.8*
60°	15967.6	14999.5	*14642.0*
62.5°	19009.3	17815.7	*17474.7*
65°	21297.4	20301.9	*19773.8*
67.5°	23129.1	22309.5	*22056.5*
70°	24218.1	24256.6	*24322.6*
72.5°	*22958.6*	*24014.6*	*24520.7*
75°	16825.6	17645.2	*18431.7*
77.5°	6501.4	5863.4	*5676.4*
80°	1050.6	984.6	*1017.6*
82.5°	473.0	500.5	*528.0*
85°	308.0	357.5	*379.5*
87.5°	71.5	71.5	*71.5*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)