Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360723

Luminaire Tested: **GSS-SB4A-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360723
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4A-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 114W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(104) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	15963.3 lumens
Efficiency:	N/A
Efficacy:	140.0 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	114
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.2%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360723
CATALOG NUMBER: GSS-SB4A-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 7.9 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360723
CATALOG NUMBER: GSS-SB4A-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360723
CATALOG NUMBER: GSS-SB4A-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	7981.7	0.0	7981.7
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	7981.7	0.0	7981.7
	% Fixture	50.0	0.0	50.0
Total	Lumens	15963.3	0.0	15963.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	304.4	1.9
10°-20°	927.8	5.8
20°-30°	1550.8	9.7
30°-40°	2138.7	13.4
40°-50°	2621.8	16.4
50°-60°	3072.3	19.2
60°-70°	3411.8	21.4
70°-80°	1855.3	11.6
80°-90°	80.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	15963.3	100.0
0°-180°	15963.3	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360723
CATALOG NUMBER: GSS-SB4A-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1391.5	8.7			
FM	(30°-60°)	3916.4	24.5			
FH	(60°-80°)	2633.5	16.5			G2/5000
FVH	(80°-90°)	40.2	0.3			G1/100
BL	(0°-30°)	1391.5	8.7	B3/2500		
BM	(30°-60°)	3916.4	24.5	B3/5000		
BH	(60°-80°)	2633.5	16.5	B4/5000		G4/5000
BVH	(80°-90°)	40.2	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360723
CATALOG NUMBER: GSS-SB4A-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3145.2	3145.2	3145.2	3145.2	3145.2	3145.2	3145.2	3145.2	3145.2	3145.2	3145.2
2.5°	3148.7	3148.7	3138.2	3152.2	3145.2	3148.7	3152.2	3148.7	3145.2	3148.7	3152.2
5°	3166.1	3159.2	3166.1	3173.1	3162.6	3169.6	3166.1	3148.7	3159.2	3159.2	3159.2
7.5°	3197.6	3204.6	3197.6	3215.1	3204.6	3225.6	3204.6	3190.6	3187.1	3183.6	3183.6
10°	3211.6	3211.6	3208.1	3239.5	3246.5	3267.5	3253.5	3232.5	3222.1	3208.1	3194.1
12.5°	3173.1	3180.1	3197.6	3257.0	3285.0	3326.9	3316.4	3274.5	3243.0	3232.5	3211.6
15°	3131.2	3138.2	3173.1	3246.5	3312.9	3375.8	3372.3	3319.9	3281.5	3253.5	3222.1
17.5°	3064.8	3075.3	3124.2	3236.0	3354.9	3424.7	3445.7	3393.3	3351.4	3305.9	3264.0
20°	2953.0	2953.0	3040.3	3183.6	3347.9	3505.1	3561.0	3519.1	3470.2	3396.8	3340.9
22.5°	2827.2	2834.2	2921.5	3110.2	3344.4	3575.0	3683.3	3637.9	3589.0	3508.6	3424.7
25°	2701.4	2701.4	2799.2	3012.4	3298.9	3623.9	3826.6	3802.2	3704.3	3630.9	3522.6
27.5°	2586.0	2586.0	2690.9	2914.5	3222.1	3637.9	3969.9	3969.9	3861.6	3753.2	3634.4
30°	2449.7	2484.7	2603.5	2837.6	3152.2	3613.5	4074.7	4141.1	4043.3	3903.5	3728.8
32.5°	2334.4	2358.9	2481.2	2729.3	3050.8	3585.5	4193.6	4357.8	4256.5	4064.3	3868.6
35°	2198.1	2194.6	2334.4	2579.0	2907.5	3522.6	4287.9	4616.4	4518.6	4312.4	4046.8
37.5°	2019.9	2019.9	2163.2	2400.8	2771.2	3414.3	4364.8	4903.0	4829.6	4595.4	4312.4
40°	1827.7	1848.7	1974.5	2215.6	2607.0	3285.0	4364.8	5137.1	5175.6	4934.4	4640.9
42.5°	1687.9	1694.9	1810.2	2037.4	2425.3	3117.2	4308.9	5339.8	5455.1	5252.4	4871.5
45°	1541.1	1558.6	1656.5	1866.1	2236.6	2918.0	4211.0	5567.0	5752.2	5612.4	5112.7
47.5°	1362.9	1380.4	1492.2	1705.4	2058.3	2701.4	4046.8	5804.6	6192.5	6091.2	5542.5
50°	1156.7	1170.7	1275.5	1502.7	1859.1	2453.2	3840.6	5982.8	6632.8	6734.2	6192.5
52.5°	905.1	915.6	1027.4	1247.6	1621.5	2215.6	3550.6	6091.2	7076.6	7433.1	7062.7
55°	650.0	667.5	765.3	947.0	1307.0	1897.6	3204.6	6147.1	7562.4	8261.3	8142.5
57.5°	468.3	475.3	541.7	681.5	971.5	1523.7	2760.8	6052.7	7999.2	9250.3	9498.4
60°	387.9	387.9	398.4	464.8	664.0	1076.3	2229.6	5703.2	8373.2	10249.8	11015.1
62.5°	356.5	356.5	363.4	373.9	436.8	698.9	1593.6	4993.8	8415.1	11210.8	12678.5
65°	325.0	325.0	332.0	339.0	353.0	454.3	961.0	3655.4	7593.8	11221.3	13573.2
67.5°	297.0	297.0	300.5	304.0	311.0	332.0	527.7	2215.6	6077.2	10924.2	13915.6
70°	269.1	269.1	269.1	265.6	276.1	279.6	349.5	1125.3	4064.3	9865.4	13751.4
72.5°	*237.6*	*237.6*	*234.1*	*227.2*	*230.6*	*230.6*	*258.6*	*552.2*	*2110.8*	*7842.0*	*12416.4*
75°	202.7	206.2	192.2	185.2	181.7	185.2	206.2	314.5	943.6	4756.2	9278.3
77.5°	171.2	178.2	157.3	143.3	139.8	139.8	160.8	195.7	405.4	1726.4	4158.6
80°	129.3	132.8	115.3	101.3	101.3	97.8	118.8	143.3	192.2	513.7	933.1
82.5°	73.4	73.4	66.4	59.4	55.9	59.4	80.4	97.8	118.8	181.7	255.1
85°	17.5	17.5	21.0	24.5	24.5	31.5	45.4	52.4	62.9	73.4	97.8
87.5°	3.5	3.5	3.5	7.0	10.5	10.5	17.5	24.5	31.5	38.4	41.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360723
CATALOG NUMBER: GSS-SB4A-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3145.2	3145.2	*3145.2*
2.5°	3152.2	3155.7	*3152.2*
5°	3173.1	3166.1	*3155.7*
7.5°	3176.6	3180.1	*3183.6*
10°	3190.6	3204.6	*3183.6*
12.5°	3204.6	3194.1	*3187.1*
15°	3215.1	3211.6	*3190.6*
17.5°	3253.5	3239.5	*3236.0*
20°	3312.9	3309.4	*3298.9*
22.5°	3382.8	3375.8	*3372.3*
25°	3484.2	3459.7	*3445.7*
27.5°	3568.0	3547.1	*3540.1*
30°	3651.9	3610.0	*3610.0*
32.5°	3725.3	3714.8	*3707.8*
35°	3900.0	3847.6	*3854.6*
37.5°	4113.2	4060.8	*4015.3*
40°	4413.7	4343.8	*4315.9*
42.5°	4605.9	4536.0	*4543.0*
45°	4714.3	4592.0	*4560.5*
47.5°	5007.8	4854.1	*4812.1*
50°	5483.1	5294.4	*5242.0*
52.5°	6251.9	5947.9	*5878.0*
55°	7216.4	6842.5	*6772.6*
57.5°	8537.4	8041.2	*7890.9*
60°	10144.9	9529.9	*9302.7*
62.5°	12077.5	11319.1	*11102.5*
65°	13531.2	12898.7	*12563.2*
67.5°	14695.0	14174.3	*14013.5*
70°	15386.9	15411.4	*15453.3*
72.5°	*14586.6*	*15257.6*	*15579.1*
75°	10690.1	11210.8	*11710.5*
77.5°	4130.7	3725.3	*3606.5*
80°	667.5	625.5	*646.5*
82.5°	300.5	318.0	*335.5*
85°	195.7	227.2	*241.1*
87.5°	45.4	45.4	*45.4*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)