Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360732

Luminaire Tested: **GSS-SB6B-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360732
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6B-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 219W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(156) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	30166.1 lumens
Efficiency:	N/A
Efficacy:	137.7 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	219
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360732
CATALOG NUMBER: GSS-SB6B-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 14.9 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360732
CATALOG NUMBER: GSS-SB6B-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360732
CATALOG NUMBER: GSS-SB6B-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	15083.0	0.0	15083.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	15083.0	0.0	15083.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	30166.1	0.0	30166.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	575.3	1.9
10°-20°	1753.4	5.8
20°-30°	2930.6	9.7
30°-40°	4041.5	13.4
40°-50°	4954.3	16.4
50°-60°	5805.8	19.2
60°-70°	6447.3	21.4
70°-80°	3506.0	11.6
80°-90°	151.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	30166.1	100.0
0°-180°	30166.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360732
CATALOG NUMBER: GSS-SB6B-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2629.6	8.7			
FM	(30°-60°)	7400.8	24.5			
FH	(60°-80°)	4976.6	16.5			G2/5000
FVH	(80°-90°)	76.0	0.3			G1/100
BL	(0°-30°)	2629.6	8.7	B4/5000		
BM	(30°-60°)	7400.8	24.5	B4/8500		
BH	(60°-80°)	4976.6	16.5	B4/5000		G4/5000
BVH	(80°-90°)	76.0	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360732
CATALOG NUMBER: GSS-SB6B-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	5943.5	5943.5	5943.5	5943.5	5943.5	5943.5	5943.5	5943.5	5943.5	5943.5	5943.5
2.5°	5950.1	5950.1	5930.3	5956.7	5943.5	5950.1	5956.7	5950.1	5943.5	5950.1	5956.7
5°	5983.1	5969.9	5983.1	5996.3	5976.5	5989.7	5983.1	5950.1	5969.9	5969.9	5969.9
7.5°	6042.5	6055.7	6042.5	6075.5	6055.7	6095.4	6055.7	6029.3	6022.7	6016.1	6016.1
10°	6068.9	6068.9	6062.3	6121.8	6135.0	6174.6	6148.2	6108.6	6088.8	6062.3	6035.9
12.5°	5996.3	6009.5	6042.5	6154.8	6207.6	6286.9	6267.1	6187.8	6128.4	6108.6	6068.9
15°	5917.1	5930.3	5996.3	6135.0	6260.5	6379.3	6372.7	6273.7	6201.0	6148.2	6088.8
17.5°	5791.6	5811.4	5903.8	6115.2	6339.7	6471.8	6511.4	6412.3	6333.1	6247.2	6168.0
20°	5580.3	5580.3	5745.4	6016.1	6326.5	6623.7	6729.3	6650.1	6557.6	6418.9	6313.3
22.5°	5342.5	5355.7	5520.8	5877.4	6319.9	6755.7	6960.5	6874.6	6782.2	6630.3	6471.8
25°	5104.8	5104.8	5289.7	5692.5	6234.0	6848.2	7231.2	7185.0	7000.1	6861.4	6656.7
27.5°	4886.9	4886.9	5085.0	5507.6	6088.8	6874.6	7502.0	7502.0	7297.3	7092.5	6868.0
30°	4629.3	4695.3	4919.9	5362.3	5956.7	6828.4	7700.1	7825.6	7640.7	7376.5	7046.3
32.5°	4411.4	4457.6	4688.7	5157.6	5765.2	6775.6	7924.6	8235.0	8043.5	7680.3	7310.5
35°	4153.8	4147.2	4411.4	4873.6	5494.4	6656.7	8102.9	8723.7	8538.8	8149.2	7647.3
37.5°	3817.0	3817.0	4087.8	4536.8	5236.9	6452.0	8248.2	9265.2	9126.5	8684.1	8149.2
40°	3453.8	3493.4	3731.2	4186.8	4926.5	6207.6	8248.2	9707.7	9780.3	9324.6	8769.9
42.5°	3189.7	3202.9	3420.8	3850.0	4583.1	5890.6	8142.5	10090.7	10308.6	9925.6	9205.8
45°	2912.3	2945.3	3130.2	3526.5	4226.5	5514.2	7957.6	10519.9	10869.9	10605.8	9661.4
47.5°	2575.5	2608.5	2819.8	3222.7	3889.7	5104.8	7647.3	10969.0	11702.0	11510.5	10473.7
50°	2185.9	2212.3	2410.4	2839.7	3513.2	4635.9	7257.6	11305.8	12534.1	12725.6	11702.0
52.5°	1710.4	1730.2	1941.5	2357.6	3064.2	4186.8	6709.5	11510.5	13372.8	14046.4	13346.4
55°	1228.3	1261.3	1446.2	1789.6	2469.8	3585.9	6055.7	11616.2	14290.7	15611.5	15387.0
57.5°	884.9	898.1	1023.6	1287.8	1835.9	2879.3	5217.0	11437.9	15116.2	17480.4	17949.3
60°	733.0	733.0	752.8	878.3	1254.7	2034.0	4213.3	10777.5	15822.8	19369.1	20815.3
62.5°	673.6	673.6	686.8	706.6	825.5	1320.8	3011.4	9436.9	15902.1	21185.2	23958.8
65°	614.2	614.2	627.4	640.6	667.0	858.5	1816.1	6907.6	14350.2	21205.0	25649.4
67.5°	561.3	561.3	567.9	574.5	587.7	627.4	997.2	4186.8	11484.1	20643.6	26296.5
70°	508.5	508.5	508.5	501.9	521.7	528.3	660.4	2126.4	7680.3	18642.7	25986.2
72.5°	*449.1*	*449.1*	*442.5*	*429.3*	*435.9*	*435.9*	*488.7*	*1043.4*	*3988.7*	*14819.0*	*23463.5*
75°	383.0	389.6	363.2	350.0	343.4	350.0	389.6	594.3	1783.0	8987.8	17533.2
77.5°	323.6	336.8	297.2	270.8	264.2	264.2	303.8	369.8	766.0	3262.3	7858.6
80°	244.3	250.9	217.9	191.5	191.5	184.9	224.5	270.8	363.2	970.8	1763.2
82.5°	138.7	138.7	125.5	112.3	105.7	112.3	151.9	184.9	224.5	343.4	482.1
85°	33.0	33.0	39.6	46.2	46.2	59.4	85.9	99.1	118.9	138.7	184.9
87.5°	6.6	6.6	6.6	13.2	19.8	19.8	33.0	46.2	59.4	72.6	79.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360732
CATALOG NUMBER: GSS-SB6B-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	5943.5	5943.5	*5943.5*
2.5°	5956.7	5963.3	*5956.7*
5°	5996.3	5983.1	*5963.3*
7.5°	6002.9	6009.5	*6016.1*
10°	6029.3	6055.7	*6016.1*
12.5°	6055.7	6035.9	*6022.7*
15°	6075.5	6068.9	*6029.3*
17.5°	6148.2	6121.8	*6115.2*
20°	6260.5	6253.8	*6234.0*
22.5°	6392.5	6379.3	*6372.7*
25°	6584.0	6537.8	*6511.4*
27.5°	6742.5	6702.9	*6689.7*
30°	6901.0	6821.8	*6821.8*
32.5°	7039.7	7019.9	*7006.7*
35°	7369.9	7270.8	*7284.0*
37.5°	7772.7	7673.7	*7587.8*
40°	8340.7	8208.6	*8155.8*
42.5°	8703.9	8571.8	*8585.0*
45°	8908.6	8677.5	*8618.0*
47.5°	9463.3	9172.8	*9093.5*
50°	10361.4	10004.8	*9905.8*
52.5°	11814.3	11239.8	*11107.7*
55°	13637.0	12930.3	*12798.3*
57.5°	16133.2	15195.5	*14911.5*
60°	19171.0	18008.7	*17579.5*
62.5°	22822.9	21389.9	*20980.4*
65°	25570.1	24374.8	*23740.8*
67.5°	27769.2	26785.2	*26481.4*
70°	29076.8	29123.0	*29202.2*
72.5°	*27564.5*	*28832.4*	*29440.0*
75°	20201.2	21185.2	*22129.5*
77.5°	7805.8	7039.7	*6815.2*
80°	1261.3	1182.1	*1221.7*
82.5°	567.9	601.0	*634.0*
85°	369.8	429.3	*455.7*
87.5°	85.9	85.9	*85.9*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)