Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360713

Luminaire Tested: **GSS-SB1C-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360713
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB1C-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 1SQUARE 52W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(26) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	6202.7 lumens
Efficiency:	N/A
Efficacy:	119.3 lumens/watt
Luminous Opening:	Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	52
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	10.1%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360713
CATALOG NUMBER: GSS-SB1C-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 3.1 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360713
CATALOG NUMBER: GSS-SB1C-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360713
CATALOG NUMBER: GSS-SB1C-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3101.4	0.0	3101.4
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3101.4	0.0	3101.4
	% Fixture	50.0	0.0	50.0
Total	Lumens	6202.7	0.0	6202.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.3	1.9
10°-20°	360.5	5.8
20°-30°	602.6	9.7
30°-40°	831.0	13.4
40°-50°	1018.7	16.4
50°-60°	1193.8	19.2
60°-70°	1325.7	21.4
70°-80°	720.9	11.6
80°-90°	31.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6202.7	100.0
0°-180°	6202.7	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360713
CATALOG NUMBER: GSS-SB1C-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	540.7	8.7			
FM	(30°-60°)	1521.8	24.5			
FH	(60°-80°)	1023.3	16.5			G1/1800
FVH	(80°-90°)	15.6	0.3			G1/100
BL	(0°-30°)	540.7	8.7	B2/1000		
BM	(30°-60°)	1521.8	24.5	B2/2500		
BH	(60°-80°)	1023.3	16.5	B3/2500		G3/2500
BVH	(80°-90°)	15.6	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360713
CATALOG NUMBER: GSS-SB1C-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1222.1	1222.1	1222.1	1222.1	1222.1	1222.1	1222.1	1222.1	1222.1	1222.1	1222.1
2.5°	1223.4	1223.4	1219.4	1224.8	1222.1	1223.4	1224.8	1223.4	1222.1	1223.4	1224.8
5°	1230.2	1227.5	1230.2	1233.0	1228.9	1231.6	1230.2	1223.4	1227.5	1227.5	1227.5
7.5°	1242.5	1245.2	1242.5	1249.2	1245.2	1253.3	1245.2	1239.7	1238.4	1237.0	1237.0
10°	1247.9	1247.9	1246.5	1258.8	1261.5	1269.6	1264.2	1256.0	1252.0	1246.5	1241.1
12.5°	1233.0	1235.7	1242.5	1265.5	1276.4	1292.7	1288.6	1272.3	1260.1	1256.0	1247.9
15°	1216.7	1219.4	1233.0	1261.5	1287.3	1311.7	1310.4	1290.0	1275.0	1264.2	1252.0
17.5°	1190.9	1194.9	1213.9	1257.4	1303.6	1330.7	1338.9	1318.5	1302.2	1284.6	1268.3
20°	1147.4	1147.4	1181.4	1237.0	1300.8	1362.0	1383.7	1367.4	1348.4	1319.9	1298.1
22.5°	1098.5	1101.2	1135.2	1208.5	1299.5	1389.1	1431.2	1413.6	1394.5	1363.3	1330.7
25°	1049.6	1049.6	1087.7	1170.5	1281.8	1408.1	1486.9	1477.4	1439.4	1410.8	1368.7
27.5°	1004.8	1004.8	1045.6	1132.5	1252.0	1413.6	1542.5	1542.5	1500.5	1458.4	1412.2
30°	951.9	965.5	1011.6	1102.6	1224.8	1404.0	1583.3	1609.1	1571.1	1516.7	1448.9
32.5°	907.1	916.6	964.1	1060.5	1185.4	1393.2	1629.5	1693.3	1653.9	1579.2	1503.2
35°	854.1	852.7	907.1	1002.1	1129.8	1368.7	1666.1	1793.8	1755.7	1675.6	1572.4
37.5°	784.9	784.9	840.5	932.9	1076.8	1326.6	1696.0	1905.1	1876.6	1785.6	1675.6
40°	710.2	718.3	767.2	860.9	1013.0	1276.4	1696.0	1996.1	2011.0	1917.3	1803.3
42.5°	655.9	658.6	703.4	791.6	942.4	1211.2	1674.3	2074.8	2119.6	2040.9	1892.9
45°	598.8	605.6	643.6	725.1	869.0	1133.8	1636.2	2163.1	2235.1	2180.8	1986.6
47.5°	529.6	536.4	579.8	662.6	799.8	1049.6	1572.4	2255.4	2406.2	2366.8	2153.6
50°	449.5	454.9	495.6	583.9	722.4	953.2	1492.3	2324.7	2577.3	2616.6	2406.2
52.5°	351.7	355.8	399.2	484.8	630.1	860.9	1379.6	2366.8	2749.7	2888.2	2744.3
55°	252.6	259.4	297.4	368.0	507.8	737.3	1245.2	2388.5	2938.4	3210.0	3163.9
57.5°	182.0	184.7	210.5	264.8	377.5	592.0	1072.7	2351.8	3108.2	3594.3	3690.7
60°	150.7	150.7	154.8	180.6	258.0	418.2	866.3	2216.1	3253.5	3982.7	4280.0
62.5°	138.5	138.5	141.2	145.3	169.7	271.6	619.2	1940.4	3269.8	4356.1	4926.4
65°	126.3	126.3	129.0	131.7	137.1	176.5	373.4	1420.3	2950.7	4360.1	5274.0
67.5°	115.4	115.4	116.8	118.1	120.9	129.0	205.0	860.9	2361.4	4244.7	5407.1
70°	104.6	104.6	104.6	103.2	107.3	108.6	135.8	437.2	1579.2	3833.3	5343.3
72.5°	*92.3*	*92.3*	*91.0*	*88.3*	*89.6*	*89.6*	*100.5*	*214.5*	*820.2*	*3047.1*	*4824.5*
75°	78.8	80.1	74.7	72.0	70.6	72.0	80.1	122.2	366.6	1848.1	3605.2
77.5°	66.5	69.3	61.1	55.7	54.3	54.3	62.5	76.0	157.5	670.8	1615.9
80°	50.2	51.6	44.8	39.4	39.4	38.0	46.2	55.7	74.7	199.6	362.6
82.5°	28.5	28.5	25.8	23.1	21.7	23.1	31.2	38.0	46.2	70.6	99.1
85°	6.8	6.8	8.1	9.5	9.5	12.2	17.7	20.4	24.4	28.5	38.0
87.5°	1.4	1.4	1.4	2.7	4.1	4.1	6.8	9.5	12.2	14.9	16.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360713
CATALOG NUMBER: GSS-SB1C-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1222.1	1222.1	*1222.1*
2.5°	1224.8	1226.2	*1224.8*
5°	1233.0	1230.2	*1226.2*
7.5°	1234.3	1235.7	*1237.0*
10°	1239.7	1245.2	*1237.0*
12.5°	1245.2	1241.1	*1238.4*
15°	1249.2	1247.9	*1239.7*
17.5°	1264.2	1258.8	*1257.4*
20°	1287.3	1285.9	*1281.8*
22.5°	1314.4	1311.7	*1310.4*
25°	1353.8	1344.3	*1338.9*
27.5°	1386.4	1378.2	*1375.5*
30°	1419.0	1402.7	*1402.7*
32.5°	1447.5	1443.4	*1440.7*
35°	1515.4	1495.0	*1497.7*
37.5°	1598.2	1577.9	*1560.2*
40°	1715.0	1687.8	*1677.0*
42.5°	1789.7	1762.5	*1765.2*
45°	1831.8	1784.3	*1772.0*
47.5°	1945.8	1886.1	*1869.8*
50°	2130.5	2057.2	*2036.8*
52.5°	2429.2	2311.1	*2284.0*
55°	2804.0	2658.7	*2631.6*
57.5°	3317.3	3124.5	*3066.1*
60°	3941.9	3702.9	*3614.7*
62.5°	4692.8	4398.2	*4314.0*
65°	5257.7	5011.9	*4881.6*
67.5°	5709.9	5507.6	*5445.1*
70°	5978.7	5988.2	*6004.5*
72.5°	*5667.8*	*5928.5*	*6053.4*
75°	4153.7	4356.1	*4550.2*
77.5°	1605.0	1447.5	*1401.3*
80°	259.4	243.1	*251.2*
82.5°	116.8	123.6	*130.4*
85°	76.0	88.3	*93.7*
87.5°	17.7	17.7	*17.7*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)