Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360721

Luminaire Tested: **GSS-SB3C-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360721
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB3C-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 3SQUARE 150W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(78) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	19077.4 lumens
Efficiency:	N/A
Efficacy:	127.2 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	150
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.3%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360721
CATALOG NUMBER: GSS-SB3C-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 9.4 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360721
CATALOG NUMBER: GSS-SB3C-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360721
CATALOG NUMBER: GSS-SB3C-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	9538.7	0.0	9538.7
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	9538.7	0.0	9538.7
	% Fixture	50.0	0.0	50.0
Total	Lumens	19077.4	0.0	19077.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	363.8	1.9
10°-20°	1108.8	5.8
20°-30°	1853.3	9.7
30°-40°	2555.9	13.4
40°-50°	3133.2	16.4
50°-60°	3671.7	19.2
60°-70°	4077.3	21.4
70°-80°	2217.2	11.6
80°-90°	96.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	19077.4	100.0
0°-180°	19077.4	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360721
CATALOG NUMBER: GSS-SB3C-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1663.0	8.7			
FM	(30°-60°)	4680.4	24.5			
FH	(60°-80°)	3147.3	16.5			G2/5000
FVH	(80°-90°)	48.0	0.3			G1/100
BL	(0°-30°)	1663.0	8.7	B3/2500		
BM	(30°-60°)	4680.4	24.5	B3/5000		
BH	(60°-80°)	3147.3	16.5	B4/5000		G4/5000
BVH	(80°-90°)	48.0	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360721
CATALOG NUMBER: GSS-SB3C-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3758.7	3758.7	3758.7	3758.7	3758.7	3758.7	3758.7	3758.7	3758.7	3758.7	3758.7
2.5°	3762.9	3762.9	3750.4	3767.1	3758.7	3762.9	3767.1	3762.9	3758.7	3762.9	3767.1
5°	3783.8	3775.4	3783.8	3792.1	3779.6	3787.9	3783.8	3762.9	3775.4	3775.4	3775.4
7.5°	3821.4	3829.7	3821.4	3842.2	3829.7	3854.8	3829.7	3813.0	3808.8	3804.7	3804.7
10°	3838.1	3838.1	3833.9	3871.5	3879.8	3904.9	3888.2	3863.1	3850.6	3833.9	3817.2
12.5°	3792.1	3800.5	3821.4	3892.4	3925.8	3975.9	3963.4	3913.2	3875.7	3863.1	3838.1
15°	3742.0	3750.4	3792.1	3879.8	3959.2	4034.4	4030.2	3967.5	3921.6	3888.2	3850.6
17.5°	3662.7	3675.2	3733.7	3867.3	4009.3	4092.8	4117.9	4055.2	4005.1	3950.8	3900.7
20°	3529.0	3529.0	3633.4	3804.7	4000.9	4188.9	4255.7	4205.6	4147.1	4059.4	3992.6
22.5°	3378.7	3387.0	3491.4	3717.0	3996.8	4272.4	4401.9	4347.6	4289.1	4193.1	4092.8
25°	3228.3	3228.3	3345.3	3600.0	3942.5	4330.9	4573.1	4543.9	4426.9	4339.2	4209.8
27.5°	3090.5	3090.5	3215.8	3483.1	3850.6	4347.6	4744.3	4744.3	4614.9	4485.4	4343.4
30°	2927.6	2969.4	3111.4	3391.2	3767.1	4318.3	4869.6	4949.0	4832.0	4665.0	4456.2
32.5°	2789.8	2819.0	2965.2	3261.7	3646.0	4284.9	5011.6	5207.9	5086.8	4857.1	4623.2
35°	2626.9	2622.7	2789.8	3082.1	3474.7	4209.8	5124.4	5517.0	5400.0	5153.6	4836.2
37.5°	2413.9	2413.9	2585.2	2869.2	3311.8	4080.3	5216.3	5859.4	5771.7	5491.9	5153.6
40°	2184.2	2209.3	2359.6	2647.8	3115.6	3925.8	5216.3	6139.2	6185.2	5897.0	5546.2
42.5°	2017.2	2025.5	2163.3	2434.8	2898.4	3725.3	5149.4	6381.5	6519.3	6277.1	5821.8
45°	1841.8	1862.7	1979.6	2230.2	2672.9	3487.3	5032.5	6652.9	6874.3	6707.2	6110.0
47.5°	1628.8	1649.7	1783.3	2038.1	2459.9	3228.3	4836.2	6936.9	7400.5	7279.4	6623.7
50°	1382.4	1399.1	1524.4	1795.8	2221.8	2931.8	4589.8	7149.9	7926.7	8047.8	7400.5
52.5°	1081.7	1094.2	1227.8	1491.0	1937.8	2647.8	4243.2	7279.4	8457.1	8883.1	8440.4
55°	776.8	797.7	914.6	1131.8	1562.0	2267.8	3829.7	7346.2	9037.6	9872.9	9730.9
57.5°	559.6	568.0	647.3	814.4	1161.0	1820.9	3299.3	7233.4	9559.7	11054.8	11351.3
60°	463.6	463.6	476.1	555.5	793.5	1286.3	2664.5	6815.8	10006.5	12249.2	13163.9
62.5°	426.0	426.0	434.3	446.9	522.0	835.3	1904.4	5968.0	10056.7	13397.7	15151.8
65°	388.4	388.4	396.8	405.1	421.8	542.9	1148.5	4368.5	9075.2	13410.3	16220.9
67.5°	355.0	355.0	359.2	363.3	371.7	396.8	630.6	2647.8	7262.7	13055.3	16630.2
70°	321.6	321.6	321.6	317.4	329.9	334.1	417.6	1344.8	4857.1	11789.8	16433.9
72.5°	*284.0*	*284.0*	*279.8*	*271.5*	*275.6*	*275.6*	*309.0*	*659.9*	*2522.5*	*9371.7*	*14838.6*
75°	242.2	246.4	229.7	221.3	217.2	221.3	246.4	375.9	1127.6	5684.0	11088.2
77.5°	204.6	213.0	187.9	171.2	167.1	167.1	192.1	233.9	484.5	2063.1	4969.9
80°	154.5	158.7	137.8	121.1	121.1	116.9	142.0	171.2	229.7	613.9	1115.1
82.5°	87.7	87.7	79.4	71.0	66.8	71.0	96.1	116.9	142.0	217.2	304.9
85°	20.9	20.9	25.1	29.2	29.2	37.6	54.3	62.6	75.2	87.7	116.9
87.5°	4.2	4.2	4.2	8.4	12.5	12.5	20.9	29.2	37.6	45.9	50.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360721
CATALOG NUMBER: GSS-SB3C-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3758.7	3758.7	*3758.7*
2.5°	3767.1	3771.2	*3767.1*
5°	3792.1	3783.8	*3771.2*
7.5°	3796.3	3800.5	*3804.7*
10°	3813.0	3829.7	*3804.7*
12.5°	3829.7	3817.2	*3808.8*
15°	3842.2	3838.1	*3813.0*
17.5°	3888.2	3871.5	*3867.3*
20°	3959.2	3955.0	*3942.5*
22.5°	4042.7	4034.4	*4030.2*
25°	4163.8	4134.6	*4117.9*
27.5°	4264.1	4239.0	*4230.6*
30°	4364.3	4314.2	*4314.2*
32.5°	4452.0	4439.5	*4431.1*
35°	4660.8	4598.2	*4606.5*
37.5°	4915.6	4852.9	*4798.6*
40°	5274.7	5191.2	*5157.8*
42.5°	5504.4	5420.9	*5429.3*
45°	5633.9	5487.7	*5450.1*
47.5°	5984.7	5801.0	*5750.8*
50°	6552.7	6327.2	*6264.5*
52.5°	7471.5	7108.1	*7024.6*
55°	8624.2	8177.3	*8093.8*
57.5°	10202.8	9609.8	*9430.2*
60°	12123.9	11388.9	*11117.4*
62.5°	14433.5	13527.2	*13268.3*
65°	16170.8	15414.9	*15014.0*
67.5°	17561.6	16939.3	*16747.2*
70°	18388.5	18417.7	*18467.8*
72.5°	*17432.1*	*18233.9*	*18618.2*
75°	12775.5	13397.7	*13995.0*
77.5°	4936.4	4452.0	*4310.0*
80°	797.7	747.6	*772.6*
82.5°	359.2	380.0	*400.9*
85°	233.9	271.5	*288.2*
87.5°	54.3	54.3	*54.3*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)