Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360716

Luminaire Tested: **GSS-SB2B-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360716
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2B-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 74W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(52) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	9603.3 lumens
Efficiency:	N/A
Efficacy:	129.8 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	74
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	13.6%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360716
CATALOG NUMBER: GSS-SB2B-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 4.7 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360716
CATALOG NUMBER: GSS-SB2B-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360716
CATALOG NUMBER: GSS-SB2B-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4801.7	0.0	4801.7
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	4801.7	0.0	4801.7
	% Fixture	50.0	0.0	50.0
Total	Lumens	9603.3	0.0	9603.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.1	1.9
10°-20°	558.2	5.8
20°-30°	933.0	9.7
30°-40°	1286.6	13.4
40°-50°	1577.2	16.4
50°-60°	1848.3	19.2
60°-70°	2052.5	21.4
70°-80°	1116.1	11.6
80°-90°	48.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9603.3	100.0
0°-180°	9603.3	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360716
CATALOG NUMBER: GSS-SB2B-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	837.1	8.7			
FM	(30°-60°)	2356.0	24.5			
FH	(60°-80°)	1584.3	16.5			G1/1800
FVH	(80°-90°)	24.2	0.3			G1/100
BL	(0°-30°)	837.1	8.7	B2/1000		
BM	(30°-60°)	2356.0	24.5	B2/2500		
BH	(60°-80°)	1584.3	16.5	B3/2500		G3/2500
BVH	(80°-90°)	24.2	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360716
CATALOG NUMBER: GSS-SB2B-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1892.1	1892.1	1892.1	1892.1	1892.1	1892.1	1892.1	1892.1	1892.1	1892.1	1892.1
2.5°	1894.2	1894.2	1887.9	1896.3	1892.1	1894.2	1896.3	1894.2	1892.1	1894.2	1896.3
5°	1904.7	1900.5	1904.7	1908.9	1902.6	1906.8	1904.7	1894.2	1900.5	1900.5	1900.5
7.5°	1923.6	1927.8	1923.6	1934.1	1927.8	1940.5	1927.8	1919.4	1917.3	1915.2	1915.2
10°	1932.0	1932.0	1929.9	1948.9	1953.1	1965.7	1957.3	1944.7	1938.3	1929.9	1921.5
12.5°	1908.9	1913.1	1923.6	1959.4	1976.2	2001.4	1995.1	1969.9	1951.0	1944.7	1932.0
15°	1883.7	1887.9	1908.9	1953.1	1993.0	2030.9	2028.7	1997.2	1974.1	1957.3	1938.3
17.5°	1843.7	1850.1	1879.5	1946.8	2018.2	2060.3	2072.9	2041.4	2016.1	1988.8	1963.6
20°	1776.5	1776.5	1829.0	1915.2	2014.0	2108.6	2142.3	2117.0	2087.6	2043.5	2009.8
22.5°	1700.8	1705.0	1757.5	1871.1	2011.9	2150.7	2215.9	2188.5	2159.1	2110.7	2060.3
25°	1625.1	1625.1	1684.0	1812.2	1984.6	2180.1	2302.1	2287.3	2228.5	2184.3	2119.1
27.5°	1555.7	1555.7	1618.8	1753.3	1938.3	2188.5	2388.2	2388.2	2323.1	2257.9	2186.4
30°	1473.7	1494.8	1566.2	1707.1	1896.3	2173.8	2451.3	2491.3	2432.4	2348.3	2243.2
32.5°	1404.4	1419.1	1492.7	1641.9	1835.3	2157.0	2522.8	2621.6	2560.6	2445.0	2327.3
35°	1322.4	1320.3	1404.4	1551.5	1749.1	2119.1	2579.6	2777.2	2718.3	2594.3	2434.5
37.5°	1215.1	1215.1	1301.3	1444.3	1667.1	2054.0	2625.8	2949.6	2905.4	2764.6	2594.3
40°	1099.5	1112.1	1187.8	1332.9	1568.3	1976.2	2625.8	3090.4	3113.6	2968.5	2791.9
42.5°	1015.4	1019.6	1089.0	1225.7	1459.0	1875.3	2592.2	3212.4	3281.7	3159.8	2930.6
45°	927.1	937.6	996.5	1122.6	1345.5	1755.4	2533.3	3349.0	3460.4	3376.3	3075.7
47.5°	819.9	830.4	897.7	1025.9	1238.3	1625.1	2434.5	3492.0	3725.3	3664.4	3334.3
50°	695.9	704.3	767.4	904.0	1118.4	1475.8	2310.5	3599.2	3990.2	4051.2	3725.3
52.5°	544.5	550.8	618.1	750.5	975.5	1332.9	2136.0	3664.4	4257.2	4471.7	4248.8
55°	391.0	401.5	460.4	569.7	786.3	1141.6	1927.8	3698.0	4549.4	4969.9	4898.4
57.5°	281.7	285.9	325.9	410.0	584.4	916.6	1660.8	3641.2	4812.2	5564.9	5714.1
60°	233.4	233.4	239.7	279.6	399.4	647.5	1341.3	3431.0	5037.2	6166.1	6626.5
62.5°	214.4	214.4	218.6	224.9	262.8	420.5	958.7	3004.2	5062.4	6744.3	7627.3
65°	195.5	195.5	199.7	203.9	212.3	273.3	578.1	2199.0	4568.4	6750.6	8165.4
67.5°	178.7	178.7	180.8	182.9	187.1	199.7	317.5	1332.9	3656.0	6571.9	8371.5
70°	161.9	161.9	161.9	159.8	166.1	168.2	210.2	677.0	2445.0	5934.9	8272.7
72.5°	*143.0*	*143.0*	*140.9*	*136.7*	*138.8*	*138.8*	*155.6*	*332.2*	*1269.8*	*4717.6*	*7469.6*
75°	121.9	124.0	115.6	111.4	109.3	111.4	124.0	189.2	567.6	2861.3	5581.7
77.5°	103.0	107.2	94.6	86.2	84.1	84.1	96.7	117.7	243.9	1038.6	2501.8
80°	77.8	79.9	69.4	61.0	61.0	58.9	71.5	86.2	115.6	309.0	561.3
82.5°	44.1	44.1	39.9	35.7	33.6	35.7	48.4	58.9	71.5	109.3	153.5
85°	10.5	10.5	12.6	14.7	14.7	18.9	27.3	31.5	37.8	44.1	58.9
87.5°	2.1	2.1	2.1	4.2	6.3	6.3	10.5	14.7	18.9	23.1	25.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360716
CATALOG NUMBER: GSS-SB2B-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1892.1	1892.1	*1892.1*
2.5°	1896.3	1898.4	*1896.3*
5°	1908.9	1904.7	*1898.4*
7.5°	1911.0	1913.1	*1915.2*
10°	1919.4	1927.8	*1915.2*
12.5°	1927.8	1921.5	*1917.3*
15°	1934.1	1932.0	*1919.4*
17.5°	1957.3	1948.9	*1946.8*
20°	1993.0	1990.9	*1984.6*
22.5°	2035.1	2030.9	*2028.7*
25°	2096.0	2081.3	*2072.9*
27.5°	2146.5	2133.9	*2129.7*
30°	2196.9	2171.7	*2171.7*
32.5°	2241.1	2234.8	*2230.6*
35°	2346.2	2314.7	*2318.9*
37.5°	2474.4	2442.9	*2415.6*
40°	2655.2	2613.2	*2596.4*
42.5°	2770.9	2728.8	*2733.0*
45°	2836.0	2762.5	*2743.5*
47.5°	3012.6	2920.1	*2894.9*
50°	3298.6	3185.0	*3153.5*
52.5°	3761.1	3578.2	*3536.1*
55°	4341.3	4116.4	*4074.3*
57.5°	5136.0	4837.5	*4747.1*
60°	6103.1	5733.1	*5596.4*
62.5°	7265.7	6809.4	*6679.1*
65°	8140.2	7759.7	*7557.9*
67.5°	8840.3	8527.0	*8430.3*
70°	9256.6	9271.3	*9296.5*
72.5°	*8775.1*	*9178.8*	*9372.2*
75°	6431.0	6744.3	*7044.9*
77.5°	2485.0	2241.1	*2169.6*
80°	401.5	376.3	*388.9*
82.5°	180.8	191.3	*201.8*
85°	117.7	136.7	*145.1*
87.5°	27.3	27.3	*27.3*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)