Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360720

Luminaire Tested: **GSS-SB3B-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360720
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB3B-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 3SQUARE 109W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(78) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	14466.6 lumens
Efficiency:	N/A
Efficacy:	132.7 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	109
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360720
CATALOG NUMBER: GSS-SB3B-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 7.1 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360720
CATALOG NUMBER: GSS-SB3B-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360720
CATALOG NUMBER: GSS-SB3B-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	7233.3	0.0	7233.3
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	7233.3	0.0	7233.3
	% Fixture	50.0	0.0	50.0
Total	Lumens	14466.6	0.0	14466.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.9	1.9
10°-20°	840.9	5.8
20°-30°	1405.4	9.7
30°-40°	1938.2	13.4
40°-50°	2375.9	16.4
50°-60°	2784.3	19.2
60°-70°	3091.9	21.4
70°-80°	1681.4	11.6
80°-90°	72.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	14466.6	100.0
0°-180°	14466.6	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360720
CATALOG NUMBER: GSS-SB3B-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1261.1	8.7			
FM	(30°-60°)	3549.2	24.5			
FH	(60°-80°)	2386.6	16.5			G2/5000
FVH	(80°-90°)	36.4	0.3			G1/100
BL	(0°-30°)	1261.1	8.7	B3/2500		
BM	(30°-60°)	3549.2	24.5	B3/5000		
BH	(60°-80°)	2386.6	16.5	B3/2500		G3/2500
BVH	(80°-90°)	36.4	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360720
CATALOG NUMBER: GSS-SB3B-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	2850.3	2850.3	2850.3	2850.3	2850.3	2850.3	2850.3	2850.3	2850.3	2850.3	2850.3
2.5°	2853.4	2853.4	2843.9	2856.6	2850.3	2853.4	2856.6	2853.4	2850.3	2853.4	2856.6
5°	2869.3	2862.9	2869.3	2875.6	2866.1	2872.5	2869.3	2853.4	2862.9	2862.9	2862.9
7.5°	2897.8	2904.1	2897.8	2913.6	2904.1	2923.1	2904.1	2891.5	2888.3	2885.1	2885.1
10°	2910.5	2910.5	2907.3	2935.8	2942.1	2961.1	2948.5	2929.5	2920.0	2907.3	2894.6
12.5°	2875.6	2882.0	2897.8	2951.6	2977.0	3015.0	3005.5	2967.5	2939.0	2929.5	2910.5
15°	2837.6	2843.9	2875.6	2942.1	3002.3	3059.3	3056.1	3008.6	2973.8	2948.5	2920.0
17.5°	2777.4	2786.9	2831.3	2932.6	3040.3	3103.6	3122.6	3075.1	3037.1	2996.0	2958.0
20°	2676.1	2676.1	2755.3	2885.1	3034.0	3176.5	3227.2	3189.1	3144.8	3078.3	3027.6
22.5°	2562.1	2568.4	2647.6	2818.6	3030.8	3239.8	3338.0	3296.8	3252.5	3179.6	3103.6
25°	2448.1	2448.1	2536.8	2729.9	2989.6	3284.2	3467.8	3445.7	3357.0	3290.5	3192.3
27.5°	2343.6	2343.6	2438.6	2641.3	2920.0	3296.8	3597.7	3597.7	3499.5	3401.3	3293.7
30°	2220.1	2251.7	2359.4	2571.6	2856.6	3274.7	3692.7	3752.9	3664.2	3537.5	3379.2
32.5°	2115.5	2137.7	2248.6	2473.4	2764.8	3249.3	3800.4	3949.2	3857.4	3683.2	3505.8
35°	1992.0	1988.9	2115.5	2337.2	2634.9	3192.3	3885.9	4183.6	4094.9	3908.1	3667.4
37.5°	1830.5	1830.5	1960.4	2175.7	2511.4	3094.1	3955.6	4443.3	4376.8	4164.6	3908.1
40°	1656.3	1675.3	1789.3	2007.9	2362.6	2977.0	3955.6	4655.5	4690.3	4471.8	4205.7
42.5°	1529.7	1536.0	1640.5	1846.3	2197.9	2824.9	3904.9	4839.1	4943.7	4760.0	4414.8
45°	1396.6	1412.5	1501.1	1691.2	2026.9	2644.4	3816.2	5045.0	5212.8	5086.2	4633.3
47.5°	1235.1	1251.0	1352.3	1545.5	1865.4	2448.1	3667.4	5260.4	5611.9	5520.0	5022.8
50°	1048.3	1060.9	1155.9	1361.8	1684.8	2223.2	3480.5	5421.9	6010.9	6102.8	5611.9
52.5°	820.2	829.7	931.1	1130.6	1469.5	2007.9	3217.7	5520.0	6413.1	6736.2	6400.5
55°	589.1	604.9	693.6	858.3	1184.5	1719.7	2904.1	5570.7	6853.3	7486.7	7379.1
57.5°	424.4	430.7	490.9	617.6	880.4	1380.8	2501.9	5485.2	7249.2	8383.0	8607.9
60°	351.5	351.5	361.0	421.2	601.7	975.4	2020.5	5168.5	7588.1	9288.8	9982.3
62.5°	323.0	323.0	329.4	338.9	395.9	633.4	1444.1	4525.6	7626.1	10159.7	11489.8
65°	294.5	294.5	300.9	307.2	319.9	411.7	870.9	3312.7	6881.8	10169.2	12300.5
67.5°	269.2	269.2	272.4	275.5	281.9	300.9	478.2	2007.9	5507.4	9900.0	12610.9
70°	243.9	243.9	243.9	240.7	250.2	253.4	316.7	1019.8	3683.2	8940.4	12462.1
72.5°	*215.4*	*215.4*	*212.2*	*205.9*	*209.0*	*209.0*	*234.4*	*500.4*	*1912.9*	*7106.7*	*11252.3*
75°	183.7	186.9	174.2	167.8	164.7	167.8	186.9	285.0	855.1	4310.3	8408.3
77.5°	155.2	161.5	142.5	129.8	126.7	126.7	145.7	177.4	367.4	1564.5	3768.7
80°	117.2	120.3	104.5	91.8	91.8	88.7	107.7	129.8	174.2	465.5	845.6
82.5°	66.5	66.5	60.2	53.8	50.7	53.8	72.8	88.7	107.7	164.7	231.2
85°	15.8	15.8	19.0	22.2	22.2	28.5	41.2	47.5	57.0	66.5	88.7
87.5°	3.2	3.2	3.2	6.3	9.5	9.5	15.8	22.2	28.5	34.8	38.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360720
CATALOG NUMBER: GSS-SB3B-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	2850.3	2850.3	*2850.3*
2.5°	2856.6	2859.8	*2856.6*
5°	2875.6	2869.3	*2859.8*
7.5°	2878.8	2882.0	*2885.1*
10°	2891.5	2904.1	*2885.1*
12.5°	2904.1	2894.6	*2888.3*
15°	2913.6	2910.5	*2891.5*
17.5°	2948.5	2935.8	*2932.6*
20°	3002.3	2999.1	*2989.6*
22.5°	3065.6	3059.3	*3056.1*
25°	3157.5	3135.3	*3122.6*
27.5°	3233.5	3214.5	*3208.2*
30°	3309.5	3271.5	*3271.5*
32.5°	3376.0	3366.5	*3360.2*
35°	3534.3	3486.8	*3493.2*
37.5°	3727.5	3680.0	*3638.9*
40°	3999.9	3936.6	*3911.2*
42.5°	4174.1	4110.7	*4117.1*
45°	4272.3	4161.4	*4132.9*
47.5°	4538.3	4398.9	*4360.9*
50°	4969.0	4798.0	*4750.5*
52.5°	5665.7	5390.2	*5326.9*
55°	6539.8	6200.9	*6137.6*
57.5°	7736.9	7287.2	*7151.0*
60°	9193.7	8636.4	*8430.5*
62.5°	10945.1	10257.8	*10061.5*
65°	12262.5	11689.3	*11385.3*
67.5°	13317.1	12845.3	*12699.6*
70°	13944.2	13966.4	*14004.4*
72.5°	*13219.0*	*13827.0*	*14118.4*
75°	9687.8	10159.7	*10612.5*
77.5°	3743.4	3376.0	*3268.3*
80°	604.9	566.9	*585.9*
82.5°	272.4	288.2	*304.0*
85°	177.4	205.9	*218.5*
87.5°	41.2	41.2	*41.2*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)