Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360724

Luminaire Tested: **GSS-SB4B-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360724
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4B-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 148W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(104) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	20111.9 lumens
Efficiency:	N/A
Efficacy:	135.9 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	148
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	13.6%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360724
CATALOG NUMBER: GSS-SB4B-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 9.9 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360724
CATALOG NUMBER: GSS-SB4B-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360724
CATALOG NUMBER: GSS-SB4B-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	10055.9	0.0	10055.9
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	10055.9	0.0	10055.9
	% Fixture	50.0	0.0	50.0
Total	Lumens	20111.9	0.0	20111.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	383.5	1.9
10°-20°	1169.0	5.8
20°-30°	1953.8	9.7
30°-40°	2694.5	13.4
40°-50°	3303.1	16.4
50°-60°	3870.8	19.2
60°-70°	4298.4	21.4
70°-80°	2337.5	11.6
80°-90°	101.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	20111.9	100.0
0°-180°	20111.9	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360724
CATALOG NUMBER: GSS-SB4B-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1753.2	8.7			
FM	(30°-60°)	4934.2	24.5			
FH	(60°-80°)	3317.9	16.5			G2/5000
FVH	(80°-90°)	50.6	0.3			G1/100
BL	(0°-30°)	1753.2	8.7	B3/2500		
BM	(30°-60°)	4934.2	24.5	B3/5000		
BH	(60°-80°)	3317.9	16.5	B4/5000		G4/5000
BVH	(80°-90°)	50.6	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360724
CATALOG NUMBER: GSS-SB4B-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3962.5	3962.5	3962.5	3962.5	3962.5	3962.5	3962.5	3962.5	3962.5	3962.5	3962.5
2.5°	3966.9	3966.9	3953.7	3971.3	3962.5	3966.9	3971.3	3966.9	3962.5	3966.9	3971.3
5°	3989.0	3980.2	3989.0	3997.8	3984.6	3993.4	3989.0	3966.9	3980.2	3980.2	3980.2
7.5°	4028.6	4037.4	4028.6	4050.6	4037.4	4063.8	4037.4	4019.8	4015.4	4011.0	4011.0
10°	4046.2	4046.2	4041.8	4081.4	4090.2	4116.6	4099.0	4072.6	4059.4	4041.8	4024.2
12.5°	3997.8	4006.6	4028.6	4103.4	4138.7	4191.5	4178.3	4125.4	4085.8	4072.6	4046.2
15°	3944.9	3953.7	3997.8	4090.2	4173.9	4253.1	4248.7	4182.7	4134.3	4099.0	4059.4
17.5°	3861.3	3874.5	3936.1	4077.0	4226.7	4314.8	4341.2	4275.1	4222.3	4165.1	4112.2
20°	3720.4	3720.4	3830.5	4011.0	4217.9	4416.0	4486.5	4433.6	4372.0	4279.5	4209.1
22.5°	3561.9	3570.7	3680.8	3918.5	4213.5	4504.1	4640.6	4583.3	4521.7	4420.4	4314.8
25°	3403.4	3403.4	3526.7	3795.2	4156.3	4565.7	4821.1	4790.3	4667.0	4574.5	4438.0
27.5°	3258.1	3258.1	3390.2	3672.0	4059.4	4583.3	5001.6	5001.6	4865.1	4728.6	4578.9
30°	3086.4	3130.4	3280.1	3575.1	3971.3	4552.5	5133.7	5217.3	5094.1	4918.0	4697.8
32.5°	2941.1	2971.9	3126.0	3438.6	3843.7	4517.3	5283.4	5490.3	5362.6	5120.5	4873.9
35°	2769.4	2765.0	2941.1	3249.3	3663.1	4438.0	5402.3	5816.1	5692.8	5433.1	5098.5
37.5°	2544.8	2544.8	2725.3	3024.7	3491.4	4301.6	5499.1	6177.2	6084.7	5789.7	5433.1
40°	2302.7	2329.1	2487.6	2791.4	3284.5	4138.7	5499.1	6472.1	6520.6	6216.8	5846.9
42.5°	2126.6	2135.4	2280.7	2566.8	3055.6	3927.3	5428.7	6727.5	6872.8	6617.4	6137.5
45°	1941.6	1963.7	2086.9	2351.1	2817.8	3676.4	5305.4	7013.7	7247.0	7070.9	6441.3
47.5°	1717.1	1739.1	1880.0	2148.6	2593.3	3403.4	5098.5	7313.1	7801.8	7674.1	6982.9
50°	1457.3	1474.9	1607.0	1893.2	2342.3	3090.8	4838.7	7537.6	8356.6	8484.2	7801.8
52.5°	1140.3	1153.5	1294.4	1571.8	2042.9	2791.4	4473.3	7674.1	8915.7	9364.8	8898.1
55°	818.9	840.9	964.2	1193.2	1646.7	2390.7	4037.4	7744.6	9527.7	10408.3	10258.6
57.5°	590.0	598.8	682.4	858.6	1224.0	1919.6	3478.2	7625.7	10078.1	11654.3	11966.9
60°	488.7	488.7	501.9	585.6	836.5	1356.1	2809.0	7185.4	10549.2	12913.5	13877.7
62.5°	449.1	449.1	457.9	471.1	550.4	880.6	2007.7	6291.6	10602.0	14124.3	15973.4
65°	409.5	409.5	418.3	427.1	444.7	572.4	1210.8	4605.4	9567.3	14137.5	17100.6
67.5°	374.2	374.2	378.6	383.0	391.9	418.3	664.8	2791.4	7656.5	13763.2	17532.0
70°	339.0	339.0	339.0	334.6	347.8	352.2	440.3	1417.7	5120.5	12429.2	17325.1
72.5°	*299.4*	*299.4*	*295.0*	*286.2*	*290.6*	*290.6*	*325.8*	*695.6*	*2659.3*	*9879.9*	*15643.2*
75°	255.4	259.8	242.2	233.3	228.9	233.3	259.8	396.3	1188.8	5992.2	11689.5
77.5°	215.7	224.5	198.1	180.5	176.1	176.1	202.5	246.6	510.7	2175.0	5239.4
80°	162.9	167.3	145.3	127.7	127.7	123.3	149.7	180.5	242.2	647.2	1175.6
82.5°	92.5	92.5	83.7	74.8	70.4	74.8	101.3	123.3	149.7	228.9	321.4
85°	22.0	22.0	26.4	30.8	30.8	39.6	57.2	66.0	79.3	92.5	123.3
87.5°	4.4	4.4	4.4	8.8	13.2	13.2	22.0	30.8	39.6	48.4	52.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360724
CATALOG NUMBER: GSS-SB4B-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3962.5	3962.5	*3962.5*
2.5°	3971.3	3975.7	*3971.3*
5°	3997.8	3989.0	*3975.7*
7.5°	4002.2	4006.6	*4011.0*
10°	4019.8	4037.4	*4011.0*
12.5°	4037.4	4024.2	*4015.4*
15°	4050.6	4046.2	*4019.8*
17.5°	4099.0	4081.4	*4077.0*
20°	4173.9	4169.5	*4156.3*
22.5°	4261.9	4253.1	*4248.7*
25°	4389.6	4358.8	*4341.2*
27.5°	4495.3	4468.9	*4460.1*
30°	4600.9	4548.1	*4548.1*
32.5°	4693.4	4680.2	*4671.4*
35°	4913.6	4847.5	*4856.3*
37.5°	5182.1	5116.1	*5058.8*
40°	5560.8	5472.7	*5437.5*
42.5°	5802.9	5714.9	*5723.7*
45°	5939.4	5785.3	*5745.7*
47.5°	6309.2	6115.5	*6062.7*
50°	6908.0	6670.3	*6604.2*
52.5°	7876.7	7493.6	*7405.5*
55°	9091.8	8620.7	*8532.7*
57.5°	10756.1	10130.9	*9941.6*
60°	12781.4	12006.5	*11720.3*
62.5°	15216.2	14260.7	*13987.8*
65°	17047.7	16250.8	*15828.1*
67.5°	18513.9	17857.8	*17655.3*
70°	19385.6	19416.4	*19469.3*
72.5°	*18377.4*	*19222.7*	*19627.8*
75°	13468.2	14124.3	*14753.9*
77.5°	5204.1	4693.4	*4543.7*
80°	840.9	788.1	*814.5*
82.5°	378.6	400.7	*422.7*
85°	246.6	286.2	*303.8*
87.5°	57.2	57.2	*57.2*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)