Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360733

Luminaire Tested: **GSS-SB6C-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360733
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6C-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 300W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(156) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	39780.8 lumens
Efficiency:	N/A
Efficacy:	132.6 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B5 - U0 - G5


Input Watts (W):	300
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.3%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360733
CATALOG NUMBER: GSS-SB6C-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 19.6 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360733
CATALOG NUMBER: GSS-SB6C-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360733
CATALOG NUMBER: GSS-SB6C-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	19890.4	0.0	19890.4
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	19890.4	0.0	19890.4
	% Fixture	50.0	0.0	50.0
Total	Lumens	39780.8	0.0	39780.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	758.6	1.9
10°-20°	2312.2	5.8
20°-30°	3864.7	9.7
30°-40°	5329.6	13.4
40°-50°	6533.4	16.4
50°-60°	7656.3	19.2
60°-70°	8502.2	21.4
70°-80°	4623.5	11.6
80°-90°	200.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	39780.8	100.0
0°-180°	39780.8	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360733
CATALOG NUMBER: GSS-SB6C-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	3467.8	8.7			
FM	(30°-60°)	9759.6	24.5			
FH	(60°-80°)	6562.8	16.5			G3/7500
FVH	(80°-90°)	100.2	0.3			G2/225
BL	(0°-30°)	3467.8	8.7	B4/5000		
BM	(30°-60°)	9759.6	24.5	B5		
BH	(60°-80°)	6562.8	16.5	B5		G5
BVH	(80°-90°)	100.2	0.3			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G5
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360733
CATALOG NUMBER: GSS-SB6C-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	7837.8	7837.8	7837.8	7837.8	7837.8	7837.8	7837.8	7837.8	7837.8	7837.8	7837.8
2.5°	7846.5	7846.5	7820.4	7855.2	7837.8	7846.5	7855.2	7846.5	7837.8	7846.5	7855.2
5°	7890.1	7872.6	7890.1	7907.5	7881.3	7898.8	7890.1	7846.5	7872.6	7872.6	7872.6
7.5°	7968.4	7985.8	7968.4	8012.0	7985.8	8038.1	7985.8	7951.0	7942.3	7933.6	7933.6
10°	8003.3	8003.3	7994.6	8072.9	8090.4	8142.6	8107.8	8055.5	8029.4	7994.6	7959.7
12.5°	7907.5	7924.9	7968.4	8116.5	8186.1	8290.7	8264.5	8160.0	8081.6	8055.5	8003.3
15°	7803.0	7820.4	7907.5	8090.4	8255.8	8412.6	8403.9	8273.2	8177.4	8107.8	8029.4
17.5°	7637.5	7663.6	7785.5	8064.2	8360.3	8534.5	8586.7	8456.1	8351.6	8238.4	8133.9
20°	7358.8	7358.8	7576.5	7933.6	8342.9	8734.8	8874.1	8769.6	8647.7	8464.8	8325.5
22.5°	7045.3	7062.7	7280.4	7750.7	8334.2	8909.0	9178.9	9065.7	8943.8	8743.5	8534.5
25°	6731.8	6731.8	6975.6	7506.9	8221.0	9030.9	9536.0	9475.0	9231.2	9048.3	8778.3
27.5°	6444.4	6444.4	6705.7	7263.0	8029.4	9065.7	9893.0	9893.0	9623.1	9353.1	9057.0
30°	6104.8	6191.9	6488.0	7071.4	7855.2	9004.8	10154.3	10319.8	10075.9	9727.6	9292.1
32.5°	5817.4	5878.4	6183.2	6801.5	7602.7	8935.1	10450.4	10859.7	10607.2	10128.2	9640.5
35°	5477.8	5469.0	5817.4	6427.0	7245.6	8778.3	10685.5	11504.2	11260.3	10746.5	10084.6
37.5°	5033.6	5033.6	5390.7	5982.9	6906.0	8508.4	10877.1	12218.3	12035.4	11451.9	10746.5
40°	4554.6	4606.9	4920.4	5521.3	6496.7	8186.1	10877.1	12801.7	12897.5	12296.6	11565.1
42.5°	4206.3	4223.7	4511.1	5077.2	6043.8	7768.1	10737.8	13306.8	13594.2	13089.1	12139.9
45°	3840.5	3884.1	4127.9	4650.4	5573.5	7271.7	10493.9	13872.9	14334.5	13986.1	12740.8
47.5°	3396.4	3439.9	3718.6	4249.8	5129.4	6731.8	10084.6	14465.1	15431.8	15179.2	13811.9
50°	2882.6	2917.4	3178.7	3744.7	4633.0	6113.5	9570.8	14909.2	16529.1	16781.6	15431.8
52.5°	2255.5	2281.7	2560.3	3109.0	4040.8	5521.3	8848.0	15179.2	17635.1	18523.3	17600.2
55°	1619.8	1663.4	1907.2	2360.0	3257.0	4728.8	7985.8	15318.5	18845.6	20587.3	20291.2
57.5°	1167.0	1184.4	1349.8	1698.2	2421.0	3797.0	6879.8	15083.4	19934.1	23051.8	23670.2
60°	966.7	966.7	992.8	1158.3	1654.6	2682.3	5556.1	14212.5	20866.0	25542.5	27449.7
62.5°	888.3	888.3	905.7	931.8	1088.6	1741.7	3971.2	12444.7	20970.5	27937.4	31595.0
65°	809.9	809.9	827.3	844.7	879.6	1132.1	2394.9	9109.3	18923.9	27963.5	33824.5
67.5°	740.2	740.2	748.9	757.7	775.1	827.3	1315.0	5521.3	15144.4	27223.3	34677.9
70°	670.6	670.6	670.6	661.9	688.0	696.7	870.9	2804.2	10128.2	24584.6	34268.6
72.5°	*592.2*	*592.2*	*583.5*	*566.1*	*574.8*	*574.8*	*644.4*	*1376.0*	*5260.0*	*19542.3*	*30941.9*
75°	505.1	513.8	479.0	461.6	452.9	461.6	513.8	783.8	2351.3	11852.5	23121.5
77.5°	426.7	444.1	391.9	357.1	348.3	348.3	400.6	487.7	1010.2	4302.1	10363.3
80°	322.2	330.9	287.4	252.6	252.6	243.8	296.1	357.1	479.0	1280.2	2325.2
82.5°	182.9	182.9	165.5	148.0	139.3	148.0	200.3	243.8	296.1	452.9	635.7
85°	43.5	43.5	52.3	61.0	61.0	78.4	113.2	130.6	156.8	182.9	243.8
87.5°	8.7	8.7	8.7	17.4	26.1	26.1	43.5	61.0	78.4	95.8	104.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360733
CATALOG NUMBER: GSS-SB6C-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	7837.8	7837.8	*7837.8*
2.5°	7855.2	7863.9	*7855.2*
5°	7907.5	7890.1	*7863.9*
7.5°	7916.2	7924.9	*7933.6*
10°	7951.0	7985.8	*7933.6*
12.5°	7985.8	7959.7	*7942.3*
15°	8012.0	8003.3	*7951.0*
17.5°	8107.8	8072.9	*8064.2*
20°	8255.8	8247.1	*8221.0*
22.5°	8430.0	8412.6	*8403.9*
25°	8682.5	8621.6	*8586.7*
27.5°	8891.6	8839.3	*8821.9*
30°	9100.6	8996.1	*8996.1*
32.5°	9283.4	9257.3	*9239.9*
35°	9718.9	9588.2	*9605.7*
37.5°	10250.1	10119.5	*10006.3*
40°	10999.0	10824.9	*10755.2*
42.5°	11478.0	11303.9	*11321.3*
45°	11748.0	11443.2	*11364.8*
47.5°	12479.5	12096.3	*11991.8*
50°	13663.9	13193.6	*13063.0*
52.5°	15579.8	14822.2	*14648.0*
55°	17983.4	17051.6	*16877.4*
57.5°	21275.3	20038.6	*19664.2*
60°	25281.3	23748.5	*23182.5*
62.5°	30097.2	28207.4	*27667.4*
65°	33720.0	32143.7	*31307.7*
67.5°	36619.9	35322.4	*34921.8*
70°	38344.3	38405.2	*38509.7*
72.5°	*36350.0*	*38022.0*	*38823.2*
75°	26639.8	27937.4	*29182.7*
77.5°	10293.6	9283.4	*8987.3*
80°	1663.4	1558.9	*1611.1*
82.5°	748.9	792.5	*836.0*
85°	487.7	566.1	*600.9*
87.5°	113.2	113.2	*113.2*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)