Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1367260

Luminaire Tested: **GSS-SB6B-727-U-T4W**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1367260
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6B-727-U-T4W
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 219W 70CRI 2700K FIXTURE w/ TYPE IV WIDE DISTRIBUTION OPTIC
Light Source:	(156) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	29205.3 lumens
Efficiency:	N/A
Efficacy:	133.4 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type IV - Short
BUG Rating:	B3 - U0 - G4


Input Watts (W):	219
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1367260
CATALOG NUMBER: GSS-SB6B-727-U-T4W

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 10.6 fc
Type IV - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1367260
CATALOG NUMBER: GSS-SB6B-727-U-T4W

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1367260
CATALOG NUMBER: GSS-SB6B-727-U-T4W

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	7317.9	0.0	7317.9
	% Fixture	25.1	0.0	25.1
Street Side	Lumens	21887.4	0.0	21887.4
	% Fixture	74.9	0.0	74.9
Total	Lumens	29205.3	0.0	29205.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.3	1.2
10°-20°	1143.3	3.9
20°-30°	1967.4	6.7
30°-40°	2773.4	9.5
40°-50°	3837.8	13.1
50°-60°	5699.5	19.5
60°-70°	7617.2	26.1
70°-80°	5373.4	18.4
80°-90°	445.0	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	29205.3	100.0
0°-180°	29205.3	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1367260
CATALOG NUMBER: GSS-SB6B-727-U-T4W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1848.3	6.3			
FM	(30°-60°)	8702.5	29.8			
FH	(60°-80°)	11007.3	37.7			G4/12000
FVH	(80°-90°)	329.3	1.1			G3/500
BL	(0°-30°)	1610.7	5.5	B3/2500		
BM	(30°-60°)	3608.2	12.4	B3/5000		
BH	(60°-80°)	1983.3	6.8	B3/2500		G3/2500
BVH	(80°-90°)	115.7	0.4			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4
Type IV Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1367260
CATALOG NUMBER: GSS-SB6B-727-U-T4W

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
0°	3451.1	3451.1	3451.1	3451.1	3451.1	*3451.1*	3451.1	3451.1	3451.1	3451.1	3451.1
2.5°	3706.2	3685.0	3663.7	3656.6	3628.3	*3585.8*	3585.8	3571.6	3536.2	3507.8	3486.6
5°	3947.2	3954.3	3918.8	3890.5	3848.0	*3777.1*	3784.2	3720.4	3649.6	3571.6	3514.9
7.5°	4181.0	4181.0	4138.5	4103.1	4046.4	*3961.4*	3961.4	3862.2	3777.1	3670.8	3592.9
10°	4393.6	4379.5	4322.8	4280.3	4202.3	*4110.2*	4103.1	4003.9	3897.6	3777.1	3670.8
12.5°	4556.6	4556.6	4499.9	4429.1	4344.0	*4244.8*	4237.7	4131.4	4025.1	3897.6	3770.0
15°	4712.5	4677.1	4627.5	4535.4	4436.2	*4358.2*	4344.0	4251.9	4145.6	4032.2	3890.5
17.5°	4769.2	4755.1	4691.3	4599.2	4507.0	*4422.0*	4422.0	4336.9	4259.0	4145.6	4003.9
20°	4755.1	4733.8	4677.1	4599.2	4528.3	*4457.4*	4457.4	4393.6	4351.1	4244.8	4117.3
22.5°	4684.2	4662.9	4627.5	4556.6	4521.2	*4478.7*	4478.7	4443.2	4429.1	4365.3	4244.8
25°	4662.9	4648.8	4599.2	4535.4	4499.9	*4492.9*	4499.9	4507.0	4521.2	4471.6	4372.4
27.5°	4677.1	4677.1	4634.6	4570.8	4528.3	*4535.4*	4542.5	4585.0	4627.5	4599.2	4514.1
30°	4769.2	4748.0	4719.6	4655.8	4606.2	*4613.3*	4613.3	4698.4	4740.9	4705.4	4641.7
32.5°	4925.1	4903.9	4861.4	4726.7	4677.1	*4712.5*	4726.7	4797.6	4825.9	4790.5	4762.1
35°	5286.5	5307.8	5166.1	4925.1	4790.5	*4818.8*	4833.0	4882.6	4918.0	4903.9	4875.5
37.5°	5945.6	5952.7	5775.5	5343.2	5031.4	*4946.4*	4953.5	5024.3	5066.9	5017.3	4996.0
40°	6767.6	6774.7	6526.7	5938.5	5414.1	*5201.5*	5194.4	5208.6	5272.4	5187.3	5173.2
42.5°	7660.5	7561.3	7348.7	6675.5	5981.0	*5626.7*	5562.9	5520.4	5598.3	5492.1	5421.2
45°	8510.9	8440.0	8149.5	7455.0	6661.3	*6186.5*	6122.8	5910.2	6037.7	5952.7	5825.1
47.5°	9219.6	9162.9	8943.2	8298.3	7433.8	*6859.7*	6760.5	6427.5	6654.2	6611.7	6455.8
50°	9744.0	9687.3	9538.5	9141.6	8411.7	*7610.9*	7518.8	7114.9	7348.7	7426.7	7306.2
52.5°	10126.6	10112.5	10055.8	9992.0	9403.8	*8482.6*	8376.3	7873.1	8255.8	8404.6	8369.2
55°	10707.7	10679.4	10700.6	10806.9	10466.8	*9410.9*	9255.0	8666.8	9191.2	9467.6	9524.3
57.5°	11260.5	11260.5	11444.7	11721.1	11678.6	*10410.1*	10225.8	9595.1	10325.1	10459.7	10729.0
60°	11777.8	11827.4	12082.5	12692.0	12812.4	*11494.3*	11274.7	10665.2	11402.2	11551.0	12040.0
62.5°	11558.1	11678.6	12493.5	13478.6	13875.4	*12656.5*	12436.8	11841.6	12614.0	12436.8	12876.2
65°	10438.4	10622.7	11884.1	13528.2	14910.0	*13932.1*	13747.8	13166.8	13280.1	12571.5	13343.9
67.5°	9262.1	9531.4	10998.3	12925.8	15179.3	*15236.0*	15073.0	13981.7	13273.0	12713.2	13818.7
70°	*8206.2*	*8425.9*	*10155.0*	*12819.5*	*14775.4*	*16079.3*	*16043.9*	*14102.2*	*13655.7*	*12840.8*	*13521.1*
72.5°	5754.3	6059.0	7830.6	11834.5	14895.9	*14704.5*	14626.6	14945.5	13939.2	12373.1	11983.3
75°	2069.3	2189.7	4060.6	8007.8	11841.6	*13925.0*	13988.8	13847.1	13662.8	11083.3	9007.0
77.5°	616.5	659.0	1155.1	3174.8	6640.1	*11175.4*	11281.7	10906.2	10268.4	6682.6	3408.6
80°	333.1	361.4	545.7	928.3	2487.4	*6307.0*	6597.5	5584.2	3699.2	1764.5	765.3
82.5°	163.0	177.2	283.5	453.5	1070.1	*2005.5*	2012.6	1785.8	1204.7	531.5	283.5
85°	56.7	63.8	92.1	170.1	368.5	*411.0*	411.0	382.7	354.3	262.2	127.6
87.5°	14.2	14.2	21.3	28.3	35.4	*42.5*	42.5	49.6	56.7	63.8	63.8
90°	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1367260
CATALOG NUMBER: GSS-SB6B-727-U-T4W

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3451.1	3451.1	3451.1	3451.1	3451.1	3451.1	3451.1	3451.1	3451.1	3451.1	3451.1
2.5°	3472.4	3444.0	3422.8	3401.5	3387.4	3359.0	3351.9	3351.9	3344.8	3351.9	3344.8
5°	3493.7	3451.1	3415.7	3387.4	3373.2	3359.0	3359.0	3366.1	3359.0	3366.1	3359.0
7.5°	3536.2	3507.8	3472.4	3429.9	3422.8	3415.7	3422.8	3437.0	3444.0	3451.1	3437.0
10°	3621.2	3578.7	3529.1	3507.8	3493.7	3486.6	3507.8	3536.2	3543.3	3557.4	3543.3
12.5°	3720.4	3670.8	3635.4	3585.8	3585.8	3592.9	3614.1	3649.6	3670.8	3692.1	3670.8
15°	3833.8	3784.2	3734.6	3692.1	3685.0	3699.2	3734.6	3770.0	3777.1	3784.2	3770.0
17.5°	3947.2	3897.6	3833.8	3784.2	3777.1	3812.5	3826.7	3826.7	3812.5	3812.5	3791.3
20°	4060.6	4025.1	3961.4	3869.2	3897.6	3911.8	3869.2	3833.8	3812.5	3805.5	3784.2
22.5°	4195.2	4138.5	4067.7	3968.5	3989.7	3933.0	3855.1	3840.9	3819.6	3826.7	3805.5
25°	4322.8	4287.3	4174.0	4046.4	3989.7	3897.6	3848.0	3848.0	3826.7	3840.9	3833.8
27.5°	4471.6	4429.1	4273.2	4088.9	3940.1	3840.9	3833.8	3833.8	3798.4	3805.5	3798.4
30°	4620.4	4556.6	4351.1	4053.5	3819.6	3755.9	3777.1	3770.0	3755.9	3777.1	3791.3
32.5°	4748.0	4698.4	4393.6	3968.5	3670.8	3642.5	3656.6	3692.1	3727.5	3748.8	3777.1
35°	4882.6	4825.9	4429.1	3819.6	3507.8	3465.3	3458.2	3564.5	3628.3	3663.7	3685.0
37.5°	5024.3	4953.5	4450.3	3656.6	3351.9	3224.4	3245.6	3330.7	3401.5	3465.3	3514.9
40°	5215.7	5144.8	4478.7	3479.5	3188.9	3018.9	2990.5	3011.8	3061.4	3153.5	3203.1
42.5°	5499.1	5385.8	4478.7	3252.7	2955.1	2834.6	2735.4	2657.4	2629.1	2685.8	2714.1
45°	5888.9	5718.8	4450.3	3018.9	2685.8	2600.8	2437.8	2310.2	2196.8	2140.1	2126.0
47.5°	6533.8	6236.1	4422.0	2792.1	2430.7	2324.4	2126.0	1977.1	1814.1	1665.3	1629.9
50°	7398.3	6923.5	4429.1	2565.3	2175.6	2033.8	1856.7	1700.8	1509.4	1367.7	1346.4
52.5°	8539.3	7887.3	4471.6	2317.3	1927.5	1800.0	1651.2	1495.3	1303.9	1197.6	1190.5
55°	9864.4	9049.5	4620.4	2040.9	1700.8	1601.6	1495.3	1346.4	1183.4	1091.3	1077.2
57.5°	11409.3	10395.9	4918.0	1750.4	1495.3	1459.8	1374.8	1233.1	1098.4	1006.3	992.1
60°	12932.9	11699.8	5144.8	1495.3	1332.3	1332.3	1254.3	1148.0	963.8	885.8	871.6
62.5°	13641.5	12103.8	4712.5	1289.7	1204.7	1226.0	1176.4	1027.5	970.9	935.4	914.2
65°	13811.6	11877.0	3543.3	1133.8	1098.4	1169.3	1091.3	1098.4	1048.8	1013.4	992.1
67.5°	13606.1	11232.1	2267.7	999.2	1020.5	1098.4	1204.7	1211.8	1048.8	970.9	956.7
70°	*12401.4*	*9850.3*	*1396.0*	*885.8*	*914.2*	*1084.2*	*1339.4*	*1140.9*	*992.1*	*928.3*	*900.0*
72.5°	10346.3	8128.2	977.9	779.5	779.5	1027.5	1204.7	1070.1	914.2	878.7	843.3
75°	7263.7	5499.1	715.7	652.0	652.0	800.8	1112.6	977.9	857.5	871.6	857.5
77.5°	2473.2	1785.8	517.3	503.1	481.9	687.4	992.1	935.4	793.7	751.2	694.5
80°	729.9	574.0	382.7	354.3	347.2	552.7	836.2	687.4	566.9	517.3	481.9
82.5°	283.5	255.1	248.0	226.8	219.7	368.5	552.7	474.8	425.2	354.3	347.2
85°	113.4	113.4	127.6	127.6	113.4	198.4	333.1	262.2	248.0	219.7	212.6
87.5°	56.7	56.7	49.6	35.4	35.4	42.5	35.4	35.4	35.4	35.4	35.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)