Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360718

Luminaire Tested: **GSS-SB2D-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360718
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2D-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 147W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(52) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	17406.8 lumens
Efficiency:	N/A
Efficacy:	118.4 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	147
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	3.1%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360718
CATALOG NUMBER: GSS-SB2D-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 8.6 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360718
CATALOG NUMBER: GSS-SB2D-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360718
CATALOG NUMBER: GSS-SB2D-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	8703.4	0.0	8703.4
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	8703.4	0.0	8703.4
	% Fixture	50.0	0.0	50.0
Total	Lumens	17406.8	0.0	17406.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.0	1.9
10°-20°	1011.7	5.8
20°-30°	1691.1	9.7
30°-40°	2332.1	13.4
40°-50°	2858.8	16.4
50°-60°	3350.1	19.2
60°-70°	3720.3	21.4
70°-80°	2023.1	11.6
80°-90°	87.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	17406.8	100.0
0°-180°	17406.8	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360718
CATALOG NUMBER: GSS-SB2D-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1517.4	8.7			
FM	(30°-60°)	4270.5	24.5			
FH	(60°-80°)	2871.7	16.5			G2/5000
FVH	(80°-90°)	43.8	0.3			G1/100
BL	(0°-30°)	1517.4	8.7	B3/2500		
BM	(30°-60°)	4270.5	24.5	B3/5000		
BH	(60°-80°)	2871.7	16.5	B4/5000		G4/5000
BVH	(80°-90°)	43.8	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360718
CATALOG NUMBER: GSS-SB2D-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3429.6	3429.6	3429.6	3429.6	3429.6	3429.6	3429.6	3429.6	3429.6	3429.6	3429.6
2.5°	3433.4	3433.4	3421.9	3437.2	3429.6	3433.4	3437.2	3433.4	3429.6	3433.4	3437.2
5°	3452.4	3444.8	3452.4	3460.1	3448.6	3456.2	3452.4	3433.4	3444.8	3444.8	3444.8
7.5°	3486.7	3494.3	3486.7	3505.8	3494.3	3517.2	3494.3	3479.1	3475.3	3471.5	3471.5
10°	3502.0	3502.0	3498.2	3532.5	3540.1	3562.9	3547.7	3524.8	3513.4	3498.2	3482.9
12.5°	3460.1	3467.7	3486.7	3551.5	3582.0	3627.7	3616.3	3570.6	3536.3	3524.8	3502.0
15°	3414.3	3421.9	3460.1	3540.1	3612.5	3681.1	3677.3	3620.1	3578.2	3547.7	3513.4
17.5°	3341.9	3353.4	3406.7	3528.6	3658.2	3734.4	3757.3	3700.1	3654.4	3604.9	3559.1
20°	3220.0	3220.0	3315.2	3471.5	3650.6	3822.1	3883.0	3837.3	3784.0	3703.9	3643.0
22.5°	3082.8	3090.4	3185.7	3391.5	3646.8	3898.3	4016.4	3966.9	3913.5	3825.9	3734.4
25°	2945.6	2945.6	3052.3	3284.8	3597.2	3951.6	4172.6	4146.0	4039.3	3959.2	3841.1
27.5°	2819.9	2819.9	2934.2	3178.1	3513.4	3966.9	4328.9	4328.9	4210.7	4092.6	3963.1
30°	2671.3	2709.4	2838.9	3094.2	3437.2	3940.2	4443.2	4515.6	4408.9	4256.5	4065.9
32.5°	2545.5	2572.2	2705.5	2976.1	3326.7	3909.7	4572.8	4751.9	4641.3	4431.8	4218.4
35°	2396.9	2393.1	2545.5	2812.2	3170.4	3841.1	4675.6	5033.8	4927.1	4702.3	4412.7
37.5°	2202.5	2202.5	2358.8	2617.9	3021.8	3723.0	4759.5	5346.3	5266.3	5011.0	4702.3
40°	1993.0	2015.8	2153.0	2415.9	2842.7	3582.0	4759.5	5601.6	5643.5	5380.6	5060.5
42.5°	1840.5	1848.2	1973.9	2221.6	2644.6	3399.1	4698.5	5822.6	5948.4	5727.4	5312.0
45°	1680.5	1699.5	1806.2	2034.9	2438.8	3181.9	4591.8	6070.3	6272.3	6119.9	5574.9
47.5°	1486.1	1505.2	1627.1	1859.6	2244.5	2945.6	4412.7	6329.5	6752.4	6641.9	6043.7
50°	1261.3	1276.6	1390.9	1638.6	2027.3	2675.1	4187.9	6523.8	7232.6	7343.1	6752.4
52.5°	987.0	998.4	1120.3	1360.4	1768.1	2415.9	3871.6	6641.9	7716.5	8105.2	7701.3
55°	708.8	727.8	834.5	1032.7	1425.2	2069.2	3494.3	6702.9	8246.2	9008.3	8878.8
57.5°	510.6	518.2	590.6	743.1	1059.4	1661.4	3010.4	6600.0	8722.5	10086.7	10357.3
60°	423.0	423.0	434.4	506.8	724.0	1173.7	2431.2	6218.9	9130.3	11176.6	12011.1
62.5°	388.7	388.7	396.3	407.7	476.3	762.1	1737.6	5445.4	9176.0	12224.5	13825.0
65°	354.4	354.4	362.0	369.6	384.9	495.4	1047.9	3985.9	8280.5	12235.9	14800.5
67.5°	323.9	323.9	327.7	331.5	339.1	362.0	575.4	2415.9	6626.7	11912.0	15173.9
70°	293.4	293.4	293.4	289.6	301.0	304.9	381.1	1227.0	4431.8	10757.4	14994.8
72.5°	*259.1*	*259.1*	*255.3*	*247.7*	*251.5*	*251.5*	*282.0*	*602.1*	*2301.6*	*8551.0*	*13539.2*
75°	221.0	224.8	209.6	202.0	198.2	202.0	224.8	343.0	1028.9	5186.3	10117.2
77.5°	186.7	194.3	171.5	156.2	152.4	152.4	175.3	213.4	442.0	1882.5	4534.6
80°	141.0	144.8	125.8	110.5	110.5	106.7	129.6	156.2	209.6	560.2	1017.4
82.5°	80.0	80.0	72.4	64.8	61.0	64.8	87.6	106.7	129.6	198.2	278.2
85°	19.1	19.1	22.9	26.7	26.7	34.3	49.5	57.2	68.6	80.0	106.7
87.5°	3.8	3.8	3.8	7.6	11.4	11.4	19.1	26.7	34.3	41.9	45.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360718
CATALOG NUMBER: GSS-SB2D-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3429.6	3429.6	*3429.6*
2.5°	3437.2	3441.0	*3437.2*
5°	3460.1	3452.4	*3441.0*
7.5°	3463.9	3467.7	*3471.5*
10°	3479.1	3494.3	*3471.5*
12.5°	3494.3	3482.9	*3475.3*
15°	3505.8	3502.0	*3479.1*
17.5°	3547.7	3532.5	*3528.6*
20°	3612.5	3608.7	*3597.2*
22.5°	3688.7	3681.1	*3677.3*
25°	3799.2	3772.5	*3757.3*
27.5°	3890.7	3867.8	*3860.2*
30°	3982.1	3936.4	*3936.4*
32.5°	4062.1	4050.7	*4043.1*
35°	4252.7	4195.5	*4203.1*
37.5°	4485.1	4427.9	*4378.4*
40°	4812.8	4736.6	*4706.1*
42.5°	5022.4	4946.2	*4953.8*
45°	5140.5	5007.2	*4972.9*
47.5°	5460.6	5293.0	*5247.2*
50°	5978.9	5773.1	*5715.9*
52.5°	6817.2	6485.7	*6409.5*
55°	7868.9	7461.2	*7385.0*
57.5°	9309.4	8768.3	*8604.4*
60°	11062.3	10391.6	*10143.9*
62.5°	13169.5	12342.6	*12106.4*
65°	14754.8	14065.0	*13699.2*
67.5°	16023.7	15455.9	*15280.6*
70°	16778.2	16804.9	*16850.6*
72.5°	*15905.6*	*16637.2*	*16987.8*
75°	11656.7	12224.5	*12769.4*
77.5°	4504.2	4062.1	*3932.6*
80°	727.8	682.1	*705.0*
82.5°	327.7	346.8	*365.8*
85°	213.4	247.7	*262.9*
87.5°	49.5	49.5	*49.5*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)