Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360722

Luminaire Tested: **GSS-SB3D-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360722
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB3D-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 3SQUARE 219W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(78) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	26221.1 lumens
Efficiency:	N/A
Efficacy:	119.7 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	219
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	2.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360722
CATALOG NUMBER: GSS-SB3D-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 12.9 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360722
CATALOG NUMBER: GSS-SB3D-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360722
CATALOG NUMBER: GSS-SB3D-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	13110.6	0.0	13110.6
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	13110.6	0.0	13110.6
	% Fixture	50.0	0.0	50.0
Total	Lumens	26221.1	0.0	26221.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	500.1	1.9
10°-20°	1524.1	5.8
20°-30°	2547.4	9.7
30°-40°	3513.0	13.4
40°-50°	4306.4	16.4
50°-60°	5046.5	19.2
60°-70°	5604.1	21.4
70°-80°	3047.5	11.6
80°-90°	132.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	26221.1	100.0
0°-180°	26221.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360722
CATALOG NUMBER: GSS-SB3D-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2285.7	8.7			
FM	(30°-60°)	6433.0	24.5			
FH	(60°-80°)	4325.8	16.5			G2/5000
FVH	(80°-90°)	66.0	0.3			G1/100
BL	(0°-30°)	2285.7	8.7	B3/2500		
BM	(30°-60°)	6433.0	24.5	B4/8500		
BH	(60°-80°)	4325.8	16.5	B4/5000		G4/5000
BVH	(80°-90°)	66.0	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360722
CATALOG NUMBER: GSS-SB3D-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	5166.2	5166.2	5166.2	5166.2	5166.2	5166.2	5166.2	5166.2	5166.2	5166.2	5166.2
2.5°	5172.0	5172.0	5154.7	5177.7	5166.2	5172.0	5177.7	5172.0	5166.2	5172.0	5177.7
5°	5200.7	5189.2	5200.7	5212.1	5194.9	5206.4	5200.7	5172.0	5189.2	5189.2	5189.2
7.5°	5252.3	5263.8	5252.3	5281.0	5263.8	5298.2	5263.8	5240.8	5235.1	5229.4	5229.4
10°	5275.3	5275.3	5269.5	5321.2	5332.7	5367.1	5344.2	5309.7	5292.5	5269.5	5246.6
12.5°	5212.1	5223.6	5252.3	5349.9	5395.8	5464.7	5447.5	5378.6	5326.9	5309.7	5275.3
15°	5143.2	5154.7	5212.1	5332.7	5441.7	5545.1	5539.3	5453.2	5390.1	5344.2	5292.5
17.5°	5034.2	5051.4	5131.8	5315.5	5510.6	5625.4	5659.9	5573.8	5504.9	5430.3	5361.4
20°	4850.5	4850.5	4994.0	5229.4	5499.1	5757.5	5849.3	5780.4	5700.1	5579.5	5487.7
22.5°	4643.8	4655.3	4798.8	5108.8	5493.4	5872.3	6050.2	5975.6	5895.2	5763.2	5625.4
25°	4437.2	4437.2	4597.9	4948.1	5418.8	5952.6	6285.6	6245.4	6084.6	5964.1	5786.2
27.5°	4247.8	4247.8	4420.0	4787.4	5292.5	5975.6	6520.9	6520.9	6343.0	6165.0	5969.8
30°	4023.9	4081.3	4276.5	4661.1	5177.7	5935.4	6693.1	6802.2	6641.5	6411.8	6124.8
32.5°	3834.5	3874.7	4075.6	4483.1	5011.2	5889.5	6888.3	7158.1	6991.6	6675.9	6354.4
35°	3610.6	3604.9	3834.5	4236.3	4775.9	5786.2	7043.3	7582.8	7422.1	7083.4	6647.2
37.5°	3317.9	3317.9	3553.2	3943.5	4552.0	5608.2	7169.6	8053.5	7933.0	7548.4	7083.4
40°	3002.1	3036.6	3243.2	3639.3	4282.2	5395.8	7169.6	8438.1	8501.3	8105.2	7623.0
42.5°	2772.5	2784.0	2973.4	3346.6	3983.7	5120.3	7077.7	8771.1	8960.5	8627.6	8001.9
45°	2531.4	2560.1	2720.9	3065.3	3673.7	4793.1	6917.0	9144.2	9448.4	9218.8	8398.0
47.5°	2238.7	2267.4	2451.1	2801.2	3381.0	4437.2	6647.2	9534.5	10171.7	10005.2	9104.0
50°	1900.0	1923.0	2095.2	2468.3	3053.8	4029.6	6308.5	9827.3	10895.0	11061.4	10171.7
52.5°	1486.7	1503.9	1687.6	2049.3	2663.5	3639.3	5832.1	10005.2	11624.0	12209.5	11601.0
55°	1067.7	1096.4	1257.1	1555.6	2146.8	3116.9	5263.8	10097.1	12421.9	13569.9	13374.7
57.5°	769.2	780.7	889.7	1119.3	1595.8	2502.7	4534.8	9942.1	13139.4	15194.4	15602.0
60°	637.2	637.2	654.4	763.5	1090.6	1768.0	3662.3	9368.1	13753.6	16836.1	18093.2
62.5°	585.5	585.5	597.0	614.2	717.5	1148.0	2617.5	8202.8	13822.5	18414.7	20825.6
65°	533.8	533.8	545.3	556.8	579.8	746.2	1578.6	6004.3	12473.5	18431.9	22295.1
67.5°	487.9	487.9	493.7	499.4	510.9	545.3	866.8	3639.3	9982.3	17944.0	22857.6
70°	442.0	442.0	442.0	436.3	453.5	459.2	574.0	1848.4	6675.9	16204.7	22587.8
72.5°	*390.3*	*390.3*	*384.6*	*373.1*	*378.9*	*378.9*	*424.8*	*907.0*	*3467.1*	*12881.1*	*20395.1*
75°	332.9	338.7	315.7	304.2	298.5	304.2	338.7	516.6	1549.9	7812.5	15240.3
77.5°	281.3	292.8	258.3	235.3	229.6	229.6	264.1	321.5	665.9	2835.7	6830.9
80°	212.4	218.1	189.4	166.5	166.5	160.7	195.2	235.3	315.7	843.8	1532.6
82.5°	120.5	120.5	109.1	97.6	91.8	97.6	132.0	160.7	195.2	298.5	419.0
85°	28.7	28.7	34.4	40.2	40.2	51.7	74.6	86.1	103.3	120.5	160.7
87.5°	5.7	5.7	5.7	11.5	17.2	17.2	28.7	40.2	51.7	63.1	68.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360722
CATALOG NUMBER: GSS-SB3D-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	5166.2	5166.2	*5166.2*
2.5°	5177.7	5183.4	*5177.7*
5°	5212.1	5200.7	*5183.4*
7.5°	5217.9	5223.6	*5229.4*
10°	5240.8	5263.8	*5229.4*
12.5°	5263.8	5246.6	*5235.1*
15°	5281.0	5275.3	*5240.8*
17.5°	5344.2	5321.2	*5315.5*
20°	5441.7	5436.0	*5418.8*
22.5°	5556.5	5545.1	*5539.3*
25°	5723.0	5682.8	*5659.9*
27.5°	5860.8	5826.3	*5814.9*
30°	5998.5	5929.7	*5929.7*
32.5°	6119.1	6101.9	*6090.4*
35°	6406.1	6320.0	*6331.5*
37.5°	6756.3	6670.2	*6595.5*
40°	7249.9	7135.1	*7089.2*
42.5°	7565.6	7450.8	*7462.3*
45°	7743.6	7542.7	*7491.0*
47.5°	8225.8	7973.2	*7904.3*
50°	9006.4	8696.5	*8610.4*
52.5°	10269.3	9769.9	*9655.1*
55°	11853.6	11239.4	*11124.6*
57.5°	14023.4	13208.3	*12961.4*
60°	16663.9	15653.6	*15280.5*
62.5°	19838.2	18592.6	*18236.7*
65°	22226.2	21187.2	*20636.1*
67.5°	24137.7	23282.4	*23018.3*
70°	25274.3	25314.4	*25383.3*
72.5°	*23959.7*	*25061.9*	*25590.0*
75°	17559.4	18414.7	*19235.5*
77.5°	6785.0	6119.1	*5923.9*
80°	1096.4	1027.5	*1061.9*
82.5°	493.7	522.4	*551.1*
85°	321.5	373.1	*396.1*
87.5°	74.6	74.6	*74.6*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)