Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360726

Luminaire Tested: **GSS-SB4D-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360726
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4D-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 238W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(104) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	29354.4 lumens
Efficiency:	N/A
Efficacy:	123.3 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	238
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	--
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360726
CATALOG NUMBER: GSS-SB4D-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 14.5 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360726
CATALOG NUMBER: GSS-SB4D-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360726
CATALOG NUMBER: GSS-SB4D-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	14677.2	0.0	14677.2
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	14677.2	0.0	14677.2
	% Fixture	50.0	0.0	50.0
Total	Lumens	29354.4	0.0	29354.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	559.8	1.9
10°-20°	1706.2	5.8
20°-30°	2851.7	9.7
30°-40°	3932.7	13.4
40°-50°	4821.0	16.4
50°-60°	5649.6	19.2
60°-70°	6273.8	21.4
70°-80°	3411.7	11.6
80°-90°	147.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	29354.4	100.0
0°-180°	29354.4	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360726
CATALOG NUMBER: GSS-SB4D-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2558.9	8.7			
FM	(30°-60°)	7201.7	24.5			
FH	(60°-80°)	4842.7	16.5			G2/5000
FVH	(80°-90°)	73.9	0.3			G1/100
BL	(0°-30°)	2558.9	8.7	B4/5000		
BM	(30°-60°)	7201.7	24.5	B4/8500		
BH	(60°-80°)	4842.7	16.5	B4/5000		G4/5000
BVH	(80°-90°)	73.9	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360726
CATALOG NUMBER: GSS-SB4D-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	5783.5	5783.5	5783.5	5783.5	5783.5	5783.5	5783.5	5783.5	5783.5	5783.5	5783.5
2.5°	5790.0	5790.0	5770.7	5796.4	5783.5	5790.0	5796.4	5790.0	5783.5	5790.0	5796.4
5°	5822.1	5809.2	5822.1	5834.9	5815.7	5828.5	5822.1	5790.0	5809.2	5809.2	5809.2
7.5°	5879.9	5892.8	5879.9	5912.1	5892.8	5931.3	5892.8	5867.1	5860.7	5854.2	5854.2
10°	5905.6	5905.6	5899.2	5957.0	5969.9	6008.5	5982.8	5944.2	5924.9	5899.2	5873.5
12.5°	5834.9	5847.8	5879.9	5989.2	6040.6	6117.7	6098.4	6021.3	5963.5	5944.2	5905.6
15°	5757.8	5770.7	5834.9	5969.9	6092.0	6207.7	6201.2	6104.8	6034.2	5982.8	5924.9
17.5°	5635.7	5655.0	5745.0	5950.6	6169.1	6297.6	6336.2	6239.8	6162.7	6079.1	6002.0
20°	5430.1	5430.1	5590.8	5854.2	6156.3	6445.4	6548.3	6471.1	6381.2	6246.2	6143.4
22.5°	5198.8	5211.6	5372.3	5719.3	6149.8	6574.0	6773.2	6689.6	6599.7	6451.9	6297.6
25°	4967.4	4967.4	5147.4	5539.3	6066.3	6663.9	7036.6	6991.7	6811.7	6676.8	6477.6
27.5°	4755.4	4755.4	4948.1	5359.4	5924.9	6689.6	7300.1	7300.1	7100.9	6901.7	6683.2
30°	4504.7	4569.0	4787.5	5218.0	5796.4	6644.6	7492.9	7615.0	7435.1	7178.0	6856.7
32.5°	4292.7	4337.7	4562.6	5018.8	5610.0	6593.2	7711.4	8013.4	7827.1	7473.6	7113.8
35°	4042.1	4035.6	4292.7	4742.5	5346.6	6477.6	7884.9	8489.0	8309.0	7929.9	7441.5
37.5°	3714.3	3714.3	3977.8	4414.8	5095.9	6278.4	8026.3	9015.9	8880.9	8450.4	7929.9
40°	3360.9	3399.4	3630.8	4074.2	4793.9	6040.6	8026.3	9446.4	9517.1	9073.7	8533.9
42.5°	3103.8	3116.7	3328.7	3746.4	4459.8	5732.1	7923.4	9819.2	10031.2	9658.5	8958.1
45°	2833.9	2866.1	3046.0	3431.6	4112.7	5365.8	7743.5	10236.9	10577.5	10320.4	9401.5
47.5°	2506.2	2538.3	2744.0	3136.0	3785.0	4967.4	7441.5	10673.8	11387.1	11200.8	10191.9
50°	2127.1	2152.8	2345.5	2763.2	3418.7	4511.2	7062.3	11001.6	12196.8	12383.2	11387.1
52.5°	1664.4	1683.7	1889.3	2294.1	2981.7	4074.2	6529.0	11200.8	13013.0	13668.4	12987.3
55°	1195.3	1227.4	1407.3	1741.5	2403.4	3489.4	5892.8	11303.6	13906.2	15191.4	14972.9
57.5°	861.1	874.0	996.1	1253.1	1786.5	2801.8	5076.7	11130.1	14709.5	17010.0	17466.3
60°	713.3	713.3	732.6	854.7	1221.0	1979.3	4099.9	10487.5	15397.1	18847.9	20255.2
62.5°	655.5	655.5	668.3	687.6	803.3	1285.2	2930.3	9183.0	15474.2	20615.1	23314.1
65°	597.6	597.6	610.5	623.3	649.0	835.4	1767.2	6721.8	13964.0	20634.4	24959.2
67.5°	546.2	546.2	552.6	559.1	571.9	610.5	970.3	4074.2	11175.1	20088.2	25588.9
70°	494.8	494.8	494.8	488.4	507.7	514.1	642.6	2069.2	7473.6	18141.0	25286.9
72.5°	*437.0*	*437.0*	*430.6*	*417.7*	*424.1*	*424.1*	*475.5*	*1015.3*	*3881.4*	*14420.3*	*22832.1*
75°	372.7	379.1	353.4	340.6	334.2	340.6	379.1	578.4	1735.1	8746.0	17061.4
77.5°	314.9	327.7	289.2	263.5	257.0	257.0	295.6	359.9	745.4	3174.5	7647.1
80°	237.8	244.2	212.1	186.4	186.4	179.9	218.5	263.5	353.4	944.6	1715.8
82.5°	134.9	134.9	122.1	109.2	102.8	109.2	147.8	179.9	218.5	334.2	469.1
85°	32.1	32.1	38.6	45.0	45.0	57.8	83.5	96.4	115.7	134.9	179.9
87.5°	6.4	6.4	6.4	12.9	19.3	19.3	32.1	45.0	57.8	70.7	77.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360726
CATALOG NUMBER: GSS-SB4D-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	5783.5	5783.5	*5783.5*
2.5°	5796.4	5802.8	*5796.4*
5°	5834.9	5822.1	*5802.8*
7.5°	5841.4	5847.8	*5854.2*
10°	5867.1	5892.8	*5854.2*
12.5°	5892.8	5873.5	*5860.7*
15°	5912.1	5905.6	*5867.1*
17.5°	5982.8	5957.0	*5950.6*
20°	6092.0	6085.6	*6066.3*
22.5°	6220.5	6207.7	*6201.2*
25°	6406.9	6361.9	*6336.2*
27.5°	6561.1	6522.5	*6509.7*
30°	6715.3	6638.2	*6638.2*
32.5°	6850.3	6831.0	*6818.2*
35°	7171.6	7075.2	*7088.0*
37.5°	7563.6	7467.2	*7383.7*
40°	8116.2	7987.7	*7936.3*
42.5°	8469.7	8341.1	*8354.0*
45°	8668.9	8444.0	*8386.1*
47.5°	9208.7	8925.9	*8848.8*
50°	10082.6	9735.6	*9639.2*
52.5°	11496.4	10937.3	*10808.8*
55°	13270.0	12582.4	*12453.9*
57.5°	15699.1	14786.6	*14510.3*
60°	18655.1	17524.1	*17106.4*
62.5°	22208.8	20814.3	*20415.9*
65°	24882.1	23718.9	*23102.0*
67.5°	27022.0	26064.5	*25768.9*
70°	28294.4	28339.3	*28416.5*
72.5°	*26822.8*	*28056.6*	*28647.8*
75°	19657.6	20615.1	*21534.0*
77.5°	7595.7	6850.3	*6631.8*
80°	1227.4	1150.3	*1188.8*
82.5°	552.6	584.8	*616.9*
85°	359.9	417.7	*443.4*
87.5°	83.5	83.5	*83.5*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)