Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360717

Luminaire Tested: **GSS-SB2C-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360717
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2C-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 102W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(52) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	12664.1 lumens
Efficiency:	N/A
Efficacy:	124.2 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	102
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360717
CATALOG NUMBER: GSS-SB2C-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 6.2 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360717
CATALOG NUMBER: GSS-SB2C-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360717
CATALOG NUMBER: GSS-SB2C-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6332.0	0.0	6332.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	6332.0	0.0	6332.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	12664.1	0.0	12664.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.5	1.9
10°-20°	736.1	5.8
20°-30°	1230.3	9.7
30°-40°	1696.7	13.4
40°-50°	2079.9	16.4
50°-60°	2437.3	19.2
60°-70°	2706.6	21.4
70°-80°	1471.9	11.6
80°-90°	63.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12664.1	100.0
0°-180°	12664.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360717
CATALOG NUMBER: GSS-SB2C-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1103.9	8.7			
FM	(30°-60°)	3106.9	24.5			
FH	(60°-80°)	2089.2	16.5			G2/5000
FVH	(80°-90°)	31.9	0.3			G1/100
BL	(0°-30°)	1103.9	8.7	B3/2500		
BM	(30°-60°)	3106.9	24.5	B3/5000		
BH	(60°-80°)	2089.2	16.5	B3/2500		G3/2500
BVH	(80°-90°)	31.9	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360717
CATALOG NUMBER: GSS-SB2C-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	2495.1	2495.1	2495.1	2495.1	2495.1	2495.1	2495.1	2495.1	2495.1	2495.1	2495.1
2.5°	2497.9	2497.9	2489.6	2500.7	2495.1	2497.9	2500.7	2497.9	2495.1	2497.9	2500.7
5°	2511.8	2506.2	2511.8	2517.3	2509.0	2514.5	2511.8	2497.9	2506.2	2506.2	2506.2
7.5°	2536.7	2542.3	2536.7	2550.6	2542.3	2558.9	2542.3	2531.2	2528.4	2525.6	2525.6
10°	2547.8	2547.8	2545.0	2570.0	2575.5	2592.2	2581.1	2564.4	2556.1	2545.0	2534.0
12.5°	2517.3	2522.9	2536.7	2583.9	2606.0	2639.3	2631.0	2597.7	2572.8	2564.4	2547.8
15°	2484.0	2489.6	2517.3	2575.5	2628.2	2678.1	2675.3	2633.8	2603.3	2581.1	2556.1
17.5°	2431.4	2439.7	2478.5	2567.2	2661.5	2716.9	2733.6	2692.0	2658.7	2622.7	2589.4
20°	2342.7	2342.7	2412.0	2525.6	2655.9	2780.7	2825.0	2791.8	2753.0	2694.7	2650.4
22.5°	2242.9	2248.4	2317.7	2467.4	2653.2	2836.1	2922.1	2886.0	2847.2	2783.5	2716.9
25°	2143.0	2143.0	2220.7	2389.8	2617.1	2875.0	3035.8	3016.3	2938.7	2880.5	2794.6
27.5°	2051.6	2051.6	2134.7	2312.2	2556.1	2886.0	3149.4	3149.4	3063.5	2977.5	2883.3
30°	1943.4	1971.2	2065.4	2251.2	2500.7	2866.6	3232.6	3285.3	3207.6	3096.7	2958.1
32.5°	1851.9	1871.4	1968.4	2165.2	2420.3	2844.5	3326.8	3457.2	3376.8	3224.3	3069.0
35°	1743.8	1741.1	1851.9	2046.0	2306.6	2794.6	3401.7	3662.3	3584.7	3421.1	3210.4
37.5°	1602.4	1602.4	1716.1	1904.6	2198.5	2708.6	3462.7	3889.6	3831.4	3645.7	3421.1
40°	1450.0	1466.6	1566.4	1757.7	2068.2	2606.0	3462.7	4075.4	4105.9	3914.6	3681.7
42.5°	1339.1	1344.6	1436.1	1616.3	1924.0	2473.0	3418.3	4236.2	4327.7	4166.9	3864.7
45°	1222.6	1236.5	1314.1	1480.4	1774.3	2314.9	3340.7	4416.4	4563.3	4452.4	4056.0
47.5°	1081.2	1095.1	1183.8	1352.9	1632.9	2143.0	3210.4	4604.9	4912.6	4832.2	4397.0
50°	917.7	928.7	1011.9	1192.1	1474.9	1946.2	3046.8	4746.3	5262.0	5342.4	4912.6
52.5°	718.0	726.4	815.1	989.7	1286.4	1757.7	2816.7	4832.2	5614.1	5896.8	5603.0
55°	515.7	529.5	607.2	751.3	1036.9	1505.4	2542.3	4876.6	5999.4	6553.9	6459.6
57.5°	371.5	377.0	429.7	540.6	770.7	1208.8	2190.2	4801.8	6346.0	7338.5	7535.3
60°	307.7	307.7	316.1	368.7	526.8	853.9	1768.8	4524.5	6642.6	8131.4	8738.5
62.5°	282.8	282.8	288.3	296.6	346.5	554.5	1264.2	3961.7	6675.9	8893.8	10058.2
65°	257.8	257.8	263.4	268.9	280.0	360.4	762.4	2899.9	6024.4	8902.1	10767.9
67.5°	235.7	235.7	238.4	241.2	246.7	263.4	418.6	1757.7	4821.2	8666.4	11039.6
70°	213.5	213.5	213.5	210.7	219.0	221.8	277.2	892.7	3224.3	7826.4	10909.3
72.5°	*188.5*	*188.5*	*185.7*	*180.2*	*183.0*	*183.0*	*205.2*	*438.0*	*1674.5*	*6221.2*	*9850.2*
75°	160.8	163.6	152.5	146.9	144.2	146.9	163.6	249.5	748.5	3773.2	7360.7
77.5°	135.8	141.4	124.8	113.7	110.9	110.9	127.5	155.3	321.6	1369.6	3299.1
80°	102.6	105.4	91.5	80.4	80.4	77.6	94.3	113.7	152.5	407.5	740.2
82.5°	58.2	58.2	52.7	47.1	44.4	47.1	63.8	77.6	94.3	144.2	202.4
85°	13.9	13.9	16.6	19.4	19.4	25.0	36.0	41.6	49.9	58.2	77.6
87.5°	2.8	2.8	2.8	5.5	8.3	8.3	13.9	19.4	25.0	30.5	33.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360717
CATALOG NUMBER: GSS-SB2C-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	2495.1	2495.1	*2495.1*
2.5°	2500.7	2503.5	*2500.7*
5°	2517.3	2511.8	*2503.5*
7.5°	2520.1	2522.9	*2525.6*
10°	2531.2	2542.3	*2525.6*
12.5°	2542.3	2534.0	*2528.4*
15°	2550.6	2547.8	*2531.2*
17.5°	2581.1	2570.0	*2567.2*
20°	2628.2	2625.4	*2617.1*
22.5°	2683.7	2678.1	*2675.3*
25°	2764.1	2744.7	*2733.6*
27.5°	2830.6	2814.0	*2808.4*
30°	2897.1	2863.9	*2863.9*
32.5°	2955.4	2947.0	*2941.5*
35°	3094.0	3052.4	*3057.9*
37.5°	3263.1	3221.5	*3185.5*
40°	3501.5	3446.1	*3423.9*
42.5°	3654.0	3598.5	*3604.1*
45°	3739.9	3642.9	*3617.9*
47.5°	3972.8	3850.8	*3817.6*
50°	4349.9	4200.1	*4158.6*
52.5°	4959.8	4718.6	*4663.1*
55°	5725.0	5428.3	*5372.9*
57.5°	6772.9	6379.2	*6260.0*
60°	8048.2	7560.3	*7380.1*
62.5°	9581.3	8979.7	*8807.8*
65°	10734.6	10232.8	*9966.7*
67.5°	11657.8	11244.8	*11117.2*
70°	12206.8	12226.2	*12259.4*
72.5°	*11571.9*	*12104.2*	*12359.2*
75°	8480.7	8893.8	*9290.2*
77.5°	3276.9	2955.4	*2861.1*
80°	529.5	496.3	*512.9*
82.5°	238.4	252.3	*266.1*
85°	155.3	180.2	*191.3*
87.5°	36.0	36.0	*36.0*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)