Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360725

Luminaire Tested: **GSS-SB4C-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360725
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4C-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 204W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(104) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	26521.7 lumens
Efficiency:	N/A
Efficacy:	130.0 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	204
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360725
CATALOG NUMBER: GSS-SB4C-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 13.1 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360725
CATALOG NUMBER: GSS-SB4C-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360725
CATALOG NUMBER: GSS-SB4C-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	13260.8	0.0	13260.8
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	13260.8	0.0	13260.8
	% Fixture	50.0	0.0	50.0
Total	Lumens	26521.7	0.0	26521.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	505.8	1.9
10°-20°	1541.5	5.8
20°-30°	2576.6	9.7
30°-40°	3553.2	13.4
40°-50°	4355.8	16.4
50°-60°	5104.4	19.2
60°-70°	5668.4	21.4
70°-80°	3082.4	11.6
80°-90°	133.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	26521.7	100.0
0°-180°	26521.7	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360725
CATALOG NUMBER: GSS-SB4C-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2311.9	8.7			
FM	(30°-60°)	6506.7	24.5			
FH	(60°-80°)	4375.4	16.5			G2/5000
FVH	(80°-90°)	66.8	0.3			G1/100
BL	(0°-30°)	2311.9	8.7	B3/2500		
BM	(30°-60°)	6506.7	24.5	B4/8500		
BH	(60°-80°)	4375.4	16.5	B4/5000		G4/5000
BVH	(80°-90°)	66.8	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360725
CATALOG NUMBER: GSS-SB4C-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	5225.4	5225.4	5225.4	5225.4	5225.4	5225.4	5225.4	5225.4	5225.4	5225.4	5225.4
2.5°	5231.2	5231.2	5213.8	5237.0	5225.4	5231.2	5237.0	5231.2	5225.4	5231.2	5237.0
5°	5260.3	5248.7	5260.3	5271.9	5254.5	5266.1	5260.3	5231.2	5248.7	5248.7	5248.7
7.5°	5312.5	5324.1	5312.5	5341.6	5324.1	5359.0	5324.1	5300.9	5295.1	5289.3	5289.3
10°	5335.7	5335.7	5329.9	5382.2	5393.8	5428.6	5405.4	5370.6	5353.2	5329.9	5306.7
12.5°	5271.9	5283.5	5312.5	5411.2	5457.7	5527.3	5509.9	5440.3	5388.0	5370.6	5335.7
15°	5202.2	5213.8	5271.9	5393.8	5504.1	5608.6	5602.8	5515.7	5451.9	5405.4	5353.2
17.5°	5091.9	5109.3	5190.6	5376.4	5573.8	5689.9	5724.7	5637.7	5568.0	5492.5	5422.8
20°	4906.1	4906.1	5051.2	5289.3	5562.2	5823.5	5916.3	5846.7	5765.4	5643.5	5550.6
22.5°	4697.1	4708.7	4853.8	5167.4	5556.4	5939.6	6119.6	6044.1	5962.8	5829.3	5689.9
25°	4488.1	4488.1	4650.6	5004.8	5480.9	6020.9	6357.6	6317.0	6154.4	6032.5	5852.5
27.5°	4296.5	4296.5	4470.6	4842.2	5353.2	6044.1	6595.7	6595.7	6415.7	6235.7	6038.3
30°	4070.0	4128.1	4325.5	4714.5	5237.0	6003.4	6769.8	6880.2	6717.6	6485.3	6195.0
32.5°	3878.4	3919.1	4122.3	4534.5	5068.7	5957.0	6967.2	7240.1	7071.7	6752.4	6427.3
35°	3652.0	3646.2	3878.4	4284.9	4830.6	5852.5	7124.0	7669.8	7507.2	7164.6	6723.4
37.5°	3355.9	3355.9	3593.9	3988.7	4604.2	5672.5	7251.7	8145.9	8023.9	7634.9	7164.6
40°	3036.6	3071.4	3280.4	3681.0	4331.3	5457.7	7251.7	8534.9	8598.7	8198.1	7710.4
42.5°	2804.3	2815.9	3007.5	3384.9	4029.4	5179.0	7158.8	8871.6	9063.2	8726.5	8093.6
45°	2560.5	2589.5	2752.1	3100.4	3715.9	4848.0	6996.3	9249.0	9556.7	9324.5	8494.2
47.5°	2264.4	2293.4	2479.2	2833.3	3419.8	4488.1	6723.4	9643.8	10288.3	10119.9	9208.4
50°	1921.8	1945.0	2119.2	2496.6	3088.8	4075.8	6380.8	9939.9	11019.9	11188.2	10288.3
52.5°	1503.8	1521.2	1707.0	2072.8	2694.0	3681.0	5898.9	10119.9	11757.2	12349.4	11734.0
55°	1079.9	1109.0	1271.5	1573.4	2171.5	3152.7	5324.1	10212.8	12564.3	13725.5	13528.1
57.5°	778.0	789.6	899.9	1132.2	1614.1	2531.4	4586.8	10056.1	13290.0	15368.6	15780.8
60°	644.5	644.5	661.9	772.2	1103.1	1788.3	3704.2	9475.4	13911.3	17029.1	18300.6
62.5°	592.2	592.2	603.8	621.2	725.8	1161.2	2647.6	8296.8	13980.9	18625.8	21064.3
65°	540.0	540.0	551.6	563.2	586.4	754.8	1596.7	6073.1	12616.5	18643.2	22550.6
67.5°	493.5	493.5	499.3	505.1	516.7	551.6	876.7	3681.0	10096.7	18149.7	23119.6
70°	447.1	447.1	447.1	441.3	458.7	464.5	580.6	1869.5	6752.4	16390.4	22846.7
72.5°	*394.8*	*394.8*	*389.0*	*377.4*	*383.2*	*383.2*	*429.6*	*917.4*	*3506.8*	*13028.7*	*20628.8*
75°	336.7	342.6	319.3	307.7	301.9	307.7	342.6	522.5	1567.6	7902.0	15415.0
77.5°	284.5	296.1	261.3	238.0	232.2	232.2	267.1	325.1	673.5	2868.2	6909.2
80°	214.8	220.6	191.6	168.4	168.4	162.6	197.4	238.0	319.3	853.5	1550.2
82.5°	121.9	121.9	110.3	98.7	92.9	98.7	133.5	162.6	197.4	301.9	423.8
85°	29.0	29.0	34.8	40.6	40.6	52.3	75.5	87.1	104.5	121.9	162.6
87.5°	5.8	5.8	5.8	11.6	17.4	17.4	29.0	40.6	52.3	63.9	69.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360725
CATALOG NUMBER: GSS-SB4C-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	5225.4	5225.4	*5225.4*
2.5°	5237.0	5242.8	*5237.0*
5°	5271.9	5260.3	*5242.8*
7.5°	5277.7	5283.5	*5289.3*
10°	5300.9	5324.1	*5289.3*
12.5°	5324.1	5306.7	*5295.1*
15°	5341.6	5335.7	*5300.9*
17.5°	5405.4	5382.2	*5376.4*
20°	5504.1	5498.3	*5480.9*
22.5°	5620.2	5608.6	*5602.8*
25°	5788.6	5748.0	*5724.7*
27.5°	5928.0	5893.1	*5881.5*
30°	6067.3	5997.6	*5997.6*
32.5°	6189.2	6171.8	*6160.2*
35°	6479.5	6392.4	*6404.1*
37.5°	6833.7	6746.6	*6671.1*
40°	7333.0	7216.9	*7170.5*
42.5°	7652.4	7536.2	*7547.8*
45°	7832.3	7629.1	*7576.9*
47.5°	8320.0	8064.6	*7994.9*
50°	9109.7	8796.1	*8709.1*
52.5°	10387.0	9881.9	*9765.7*
55°	11989.5	11368.2	*11252.1*
57.5°	14184.1	13359.7	*13110.0*
60°	16854.9	15833.1	*15455.7*
62.5°	20065.7	18805.7	*18445.8*
65°	22481.0	21430.1	*20872.7*
67.5°	24414.4	23549.3	*23282.2*
70°	25564.0	25604.6	*25674.3*
72.5°	*24234.4*	*25349.1*	*25883.3*
75°	17760.7	18625.8	*19456.0*
77.5°	6862.7	6189.2	*5991.8*
80°	1109.0	1039.3	*1074.1*
82.5°	499.3	528.3	*557.4*
85°	325.1	377.4	*400.6*
87.5°	75.5	75.5	*75.5*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)