Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360743

Luminaire Tested: **GSS-SB3A-730-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360743
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB3A-730-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 3SQUARE 85W 70CRI 3000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(78) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	12373.1 lumens
Efficiency:	N/A
Efficacy:	145.6 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	85
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	11.0%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360743
CATALOG NUMBER: GSS-SB3A-730-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 6.1 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360743
CATALOG NUMBER: GSS-SB3A-730-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360743
CATALOG NUMBER: GSS-SB3A-730-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6186.6	0.0	6186.6
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	6186.6	0.0	6186.6
	% Fixture	50.0	0.0	50.0
Total	Lumens	12373.1	0.0	12373.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.0	1.9
10°-20°	719.2	5.8
20°-30°	1202.0	9.7
30°-40°	1657.7	13.4
40°-50°	2032.1	16.4
50°-60°	2381.3	19.2
60°-70°	2644.4	21.4
70°-80°	1438.1	11.6
80°-90°	62.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12373.1	100.0
0°-180°	12373.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360743
CATALOG NUMBER: GSS-SB3A-730-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1078.6	8.7			
FM	(30°-60°)	3035.6	24.5			
FH	(60°-80°)	2041.3	16.5			G2/5000
FVH	(80°-90°)	31.2	0.3			G1/100
BL	(0°-30°)	1078.6	8.7	B3/2500		
BM	(30°-60°)	3035.6	24.5	B3/5000		
BH	(60°-80°)	2041.3	16.5	B3/2500		G3/2500
BVH	(80°-90°)	31.2	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360743
CATALOG NUMBER: GSS-SB3A-730-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	2437.8	2437.8	2437.8	2437.8	2437.8	2437.8	2437.8	2437.8	2437.8	2437.8	2437.8
2.5°	2440.5	2440.5	2432.4	2443.2	2437.8	2440.5	2443.2	2440.5	2437.8	2440.5	2443.2
5°	2454.1	2448.6	2454.1	2459.5	2451.4	2456.8	2454.1	2440.5	2448.6	2448.6	2448.6
7.5°	2478.4	2483.9	2478.4	2492.0	2483.9	2500.1	2483.9	2473.0	2470.3	2467.6	2467.6
10°	2489.3	2489.3	2486.6	2510.9	2516.4	2532.6	2521.8	2505.5	2497.4	2486.6	2475.7
12.5°	2459.5	2464.9	2478.4	2524.5	2546.2	2578.7	2570.5	2538.0	2513.7	2505.5	2489.3
15°	2427.0	2432.4	2459.5	2516.4	2567.8	2616.6	2613.9	2573.2	2543.4	2521.8	2497.4
17.5°	2375.5	2383.6	2421.6	2508.2	2600.3	2654.5	2670.8	2630.1	2597.6	2562.4	2529.9
20°	2288.8	2288.8	2356.5	2467.6	2594.9	2716.8	2760.1	2727.6	2689.7	2632.8	2589.5
22.5°	2191.3	2196.7	2264.5	2410.7	2592.2	2771.0	2854.9	2819.7	2781.8	2719.5	2654.5
25°	2093.8	2093.8	2169.7	2334.9	2557.0	2808.9	2966.0	2947.0	2871.2	2814.3	2730.3
27.5°	2004.4	2004.4	2085.7	2259.0	2497.4	2819.7	3077.1	3077.1	2993.1	2909.1	2817.0
30°	1898.8	1925.9	2018.0	2199.4	2443.2	2800.8	3158.3	3209.8	3133.9	3025.6	2890.2
32.5°	1809.4	1828.4	1923.2	2115.5	2364.7	2779.1	3250.4	3377.7	3299.2	3150.2	2998.5
35°	1703.8	1701.0	1809.4	1999.0	2253.6	2730.3	3323.5	3578.2	3502.3	3342.5	3136.6
37.5°	1565.6	1565.6	1676.7	1860.9	2148.0	2646.4	3383.1	3800.3	3743.4	3561.9	3342.5
40°	1416.6	1432.9	1530.4	1717.3	2020.7	2546.2	3383.1	3981.8	4011.6	3824.7	3597.1
42.5°	1308.3	1313.7	1403.1	1579.2	1879.8	2416.1	3339.8	4138.9	4228.2	4071.1	3775.9
45°	1194.5	1208.1	1283.9	1446.4	1733.6	2261.7	3264.0	4314.9	4458.5	4350.1	3962.8
47.5°	1056.4	1069.9	1156.6	1321.8	1595.4	2093.8	3136.6	4499.1	4799.8	4721.2	4296.0
50°	896.6	907.4	988.7	1164.7	1441.0	1901.5	2976.8	4637.3	5141.1	5219.6	4799.8
52.5°	701.5	709.7	796.4	967.0	1256.8	1717.3	2752.0	4721.2	5485.1	5761.4	5474.2
55°	503.8	517.4	593.2	734.1	1013.0	1470.8	2483.9	4764.6	5861.6	6403.3	6311.2
57.5°	363.0	368.4	419.8	528.2	753.0	1181.0	2139.9	4691.4	6200.2	7169.9	7362.2
60°	300.7	300.7	308.8	360.3	514.6	834.3	1728.1	4420.6	6490.0	7944.6	8537.8
62.5°	276.3	276.3	281.7	289.8	338.6	541.7	1235.2	3870.7	6522.5	8689.4	9827.1
65°	251.9	251.9	257.3	262.7	273.6	352.1	744.9	2833.3	5886.0	8697.6	10520.5
67.5°	230.2	230.2	232.9	235.7	241.1	257.3	409.0	1717.3	4710.4	8467.3	10786.0
70°	208.6	208.6	208.6	205.9	214.0	216.7	270.9	872.2	3150.2	7646.6	10658.6
72.5°	*184.2*	*184.2*	*181.5*	*176.1*	*178.8*	*178.8*	*200.4*	*428.0*	*1636.0*	*6078.3*	*9623.9*
75°	157.1	159.8	149.0	143.6	140.9	143.6	159.8	243.8	731.3	3686.5	7191.5
77.5°	132.7	138.1	121.9	111.1	108.3	108.3	124.6	151.7	314.2	1338.1	3223.3
80°	100.2	102.9	89.4	78.6	78.6	75.8	92.1	111.1	149.0	398.2	723.2
82.5°	56.9	56.9	51.5	46.0	43.3	46.0	62.3	75.8	92.1	140.9	197.7
85°	13.5	13.5	16.3	19.0	19.0	24.4	35.2	40.6	48.8	56.9	75.8
87.5°	2.7	2.7	2.7	5.4	8.1	8.1	13.5	19.0	24.4	29.8	32.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360743
CATALOG NUMBER: GSS-SB3A-730-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	2437.8	2437.8	*2437.8*
2.5°	2443.2	2445.9	*2443.2*
5°	2459.5	2454.1	*2445.9*
7.5°	2462.2	2464.9	*2467.6*
10°	2473.0	2483.9	*2467.6*
12.5°	2483.9	2475.7	*2470.3*
15°	2492.0	2489.3	*2473.0*
17.5°	2521.8	2510.9	*2508.2*
20°	2567.8	2565.1	*2557.0*
22.5°	2622.0	2616.6	*2613.9*
25°	2700.6	2681.6	*2670.8*
27.5°	2765.6	2749.3	*2743.9*
30°	2830.6	2798.1	*2798.1*
32.5°	2887.5	2879.3	*2873.9*
35°	3022.9	2982.3	*2987.7*
37.5°	3188.1	3147.5	*3112.3*
40°	3421.1	3366.9	*3345.2*
42.5°	3570.0	3515.9	*3521.3*
45°	3654.0	3559.2	*3534.8*
47.5°	3881.5	3762.4	*3729.8*
50°	4249.9	4103.6	*4063.0*
52.5°	4845.8	4610.2	*4556.0*
55°	5593.4	5303.6	*5249.4*
57.5°	6617.3	6232.7	*6116.2*
60°	7863.3	7386.6	*7210.5*
62.5°	9361.2	8773.4	*8605.5*
65°	10488.0	9997.7	*9737.7*
67.5°	11390.0	10986.4	*10861.8*
70°	11926.3	11945.3	*11977.8*
72.5°	*11306.0*	*11826.1*	*12075.3*
75°	8285.8	8689.4	*9076.8*
77.5°	3201.7	2887.5	*2795.4*
80°	517.4	484.9	*501.1*
82.5°	232.9	246.5	*260.0*
85°	151.7	176.1	*186.9*
87.5°	35.2	35.2	*35.2*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)