Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360729

Luminaire Tested: **GSS-SB5C-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360729
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB5C-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 5SQUARE 252W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(130) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	33134.2 lumens
Efficiency:	N/A
Efficacy:	131.5 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B5 - U0 - G5


Input Watts (W):	252
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	7.9%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360729
CATALOG NUMBER: GSS-SB5C-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 16.3 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360729
CATALOG NUMBER: GSS-SB5C-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360729
CATALOG NUMBER: GSS-SB5C-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	16567.1	0.0	16567.1
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	16567.1	0.0	16567.1
	% Fixture	50.0	0.0	50.0
Total	Lumens	33134.2	0.0	33134.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	631.9	1.9
10°-20°	1925.9	5.8
20°-30°	3218.9	9.7
30°-40°	4439.1	13.4
40°-50°	5441.8	16.4
50°-60°	6377.0	19.2
60°-70°	7081.6	21.4
70°-80°	3851.0	11.6
80°-90°	166.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	33134.2	100.0
0°-180°	33134.2	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360729
CATALOG NUMBER: GSS-SB5C-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2888.4	8.7			
FM	(30°-60°)	8129.0	24.5			
FH	(60°-80°)	5466.3	16.5			G3/7500
FVH	(80°-90°)	83.4	0.3			G1/100
BL	(0°-30°)	2888.4	8.7	B4/5000		
BM	(30°-60°)	8129.0	24.5	B4/8500		
BH	(60°-80°)	5466.3	16.5	B5		G5
BVH	(80°-90°)	83.4	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G5
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360729
CATALOG NUMBER: GSS-SB5C-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	6528.3	6528.3	6528.3	6528.3	6528.3	6528.3	6528.3	6528.3	6528.3	6528.3	6528.3
2.5°	6535.5	6535.5	6513.8	6542.8	6528.3	6535.5	6542.8	6535.5	6528.3	6535.5	6542.8
5°	6571.8	6557.3	6571.8	6586.3	6564.5	6579.0	6571.8	6535.5	6557.3	6557.3	6557.3
7.5°	6637.1	6651.6	6637.1	6673.3	6651.6	6695.1	6651.6	6622.6	6615.3	6608.0	6608.0
10°	6666.1	6666.1	6658.8	6724.1	6738.6	6782.1	6753.1	6709.6	6687.8	6658.8	6629.8
12.5°	6586.3	6600.8	6637.1	6760.4	6818.4	6905.4	6883.7	6796.6	6731.4	6709.6	6666.1
15°	6499.2	6513.8	6586.3	6738.6	6876.4	7007.0	6999.7	6890.9	6811.2	6753.1	6687.8
17.5°	6361.4	6383.2	6484.7	6716.9	6963.5	7108.5	7152.1	7043.3	6956.2	6861.9	6774.9
20°	6129.3	6129.3	6310.7	6608.0	6949.0	7275.4	7391.4	7304.4	7202.8	7050.5	6934.5
22.5°	5868.2	5882.7	6064.0	6455.7	6941.7	7420.5	7645.3	7551.0	7449.5	7282.6	7108.5
25°	5607.0	5607.0	5810.2	6252.6	6847.4	7522.0	7942.7	7891.9	7688.8	7536.5	7311.7
27.5°	5367.7	5367.7	5585.3	6049.5	6687.8	7551.0	8240.1	8240.1	8015.3	7790.4	7543.8
30°	5084.8	5157.3	5403.9	5889.9	6542.8	7500.2	8457.7	8595.5	8392.4	8102.3	7739.6
32.5°	4845.4	4896.2	5150.1	5665.1	6332.4	7442.2	8704.3	9045.3	8834.9	8436.0	8029.8
35°	4562.5	4555.3	4845.4	5353.2	6035.0	7311.7	8900.2	9582.0	9378.9	8951.0	8399.7
37.5°	4192.6	4192.6	4490.0	4983.2	5752.1	7086.8	9059.8	10176.8	10024.5	9538.5	8951.0
40°	3793.6	3837.2	4098.3	4598.8	5411.2	6818.4	9059.8	10662.8	10742.6	10242.1	9632.8
42.5°	3503.5	3518.0	3757.4	4228.9	5034.0	6470.2	8943.7	11083.5	11322.9	10902.2	10111.5
45°	3198.8	3235.1	3438.2	3873.4	4642.3	6056.8	8740.6	11555.0	11939.5	11649.3	10612.0
47.5°	2828.9	2865.2	3097.3	3539.8	4272.4	5607.0	8399.7	12048.3	12853.4	12643.1	11504.2
50°	2400.9	2430.0	2647.6	3119.1	3858.9	5092.0	7971.7	12418.2	13767.4	13977.7	12853.4
52.5°	1878.7	1900.4	2132.6	2589.5	3365.7	4598.8	7369.7	12643.1	14688.6	15428.5	14659.6
55°	1349.2	1385.4	1588.5	1965.7	2712.9	3938.7	6651.6	12759.1	15696.8	17147.6	16900.9
57.5°	972.0	986.5	1124.3	1414.5	2016.5	3162.6	5730.4	12563.3	16603.5	19200.3	19715.3
60°	805.2	805.2	826.9	964.7	1378.2	2234.1	4627.8	11837.9	17379.7	21274.9	22863.4
62.5°	739.9	739.9	754.4	776.1	906.7	1450.7	3307.7	10365.4	17466.7	23269.6	26316.1
65°	674.6	674.6	689.1	703.6	732.6	943.0	1994.7	7587.3	15762.1	23291.4	28173.1
67.5°	616.6	616.6	623.8	631.1	645.6	689.1	1095.3	4598.8	12614.0	22674.8	28883.9
70°	558.5	558.5	558.5	551.3	573.0	580.3	725.4	2335.7	8436.0	20477.0	28543.0
72.5°	*493.2*	*493.2*	*486.0*	*471.5*	*478.7*	*478.7*	*536.8*	*1146.1*	*4381.2*	*16277.1*	*25772.1*
75°	420.7	428.0	398.9	384.4	377.2	384.4	428.0	652.8	1958.5	9872.2	19258.4
77.5°	355.4	369.9	326.4	297.4	290.1	290.1	333.7	406.2	841.4	3583.3	8631.8
80°	268.4	275.6	239.4	210.4	210.4	203.1	246.6	297.4	398.9	1066.3	1936.7
82.5°	152.3	152.3	137.8	123.3	116.1	123.3	166.8	203.1	246.6	377.2	529.5
85°	36.3	36.3	43.5	50.8	50.8	65.3	94.3	108.8	130.6	152.3	203.1
87.5°	7.3	7.3	7.3	14.5	21.8	21.8	36.3	50.8	65.3	79.8	87.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360729
CATALOG NUMBER: GSS-SB5C-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	6528.3	6528.3	*6528.3*
2.5°	6542.8	6550.0	*6542.8*
5°	6586.3	6571.8	*6550.0*
7.5°	6593.5	6600.8	*6608.0*
10°	6622.6	6651.6	*6608.0*
12.5°	6651.6	6629.8	*6615.3*
15°	6673.3	6666.1	*6622.6*
17.5°	6753.1	6724.1	*6716.9*
20°	6876.4	6869.2	*6847.4*
22.5°	7021.5	7007.0	*6999.7*
25°	7231.9	7181.1	*7152.1*
27.5°	7405.9	7362.4	*7347.9*
30°	7580.0	7493.0	*7493.0*
32.5°	7732.4	7710.6	*7696.1*
35°	8095.0	7986.2	*8000.7*
37.5°	8537.5	8428.7	*8334.4*
40°	9161.3	9016.3	*8958.2*
42.5°	9560.3	9415.2	*9429.7*
45°	9785.1	9531.3	*9466.0*
47.5°	10394.4	10075.3	*9988.2*
50°	11380.9	10989.2	*10880.4*
52.5°	12976.7	12345.7	*12200.6*
55°	14978.7	14202.6	*14057.5*
57.5°	17720.6	16690.6	*16378.7*
60°	21057.3	19780.6	*19309.1*
62.5°	25068.5	23494.5	*23044.8*
65°	28086.0	26773.1	*26076.8*
67.5°	30501.5	29420.7	*29087.0*
70°	31937.7	31988.5	*32075.5*
72.5°	*30276.6*	*31669.3*	*32336.6*
75°	22188.8	23269.6	*24306.9*
77.5°	8573.8	7732.4	*7485.7*
80°	1385.4	1298.4	*1341.9*
82.5°	623.8	660.1	*696.3*
85°	406.2	471.5	*500.5*
87.5°	94.3	94.3	*94.3*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)