Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1361119

Luminaire Tested: **GSS-SB1A-730-U-5WQ**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

**Test Information**

| | |
|---|---|
| Test Method: | LM-79-08 |
| Report Number: | P1361119 |
| Test Lab: | INNOVATION CENTER(G3) |
| Issue Date: | 02/18/2026 |
| Manufacturer: | COOPER LIGHTING SOLUTIONS (FORMERLY EATON) |
| Product Line: | McGRAW-EDISON |
| Catalog Number: | GSS-SB1A-730-U-5WQ |
| Description: | GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 1SQUARE 31W 70CRI 3000K FIXTURE w/ TYPE V SQUARE WIDE DISTRIBUTION OPTIC |
| Light Source: | (26) 3000K CCT, 70 CRI LEDS |
| Ballast/Driver: | ELECTRONIC DRIVER |

**Summary**

| | |
|---|---|
| Lumens per Lamp: | N/A |
| Luminaire Lumens: | 4038 lumens |
| Efficiency: | N/A |
| Efficacy: | 130.3 lumens/watt |
| Luminous Opening: | Rectangular (W 0.5' x L: 0.5' x H: 0') |
| IES Classification: | Type V - Short |
| BUG Rating: | B2 - U0 - G1 |


| | |
|---|---|
| Input Watts (W): | 31 |
| Input Voltage (V): | 120 |
| Input Current (Ain): | NR |
| Voltage Rise (V): | NR |
| Power Factor: | 0.98 |
| Total Harmonic Distortion (THDi): | 6.4% |
| Frequency (hertz): | 60 |
| Stabilization Time: | NR |
| Operation Time: | NR |
| Ambient Temperature (°C): | NR |
| Test Distance: | 28.75 FT |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1361119
CATALOG NUMBER: GSS-SB1A-730-U-5WQ

## Iso-Footcandle Lines of Horizontal Illumination





Based on 20 foot mounting height. Maximum calculated value = 1 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1361119
CATALOG NUMBER: GSS-SB1A-730-U-5WQ

## Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1361119
CATALOG NUMBER: GSS-SB1A-730-U-5WQ

**FLUX DISTRIBUTION:**

| | | Downward | Upward | Total |
|---|---|---|---|---|
| **House Side** | Lumens | 2019.0 | 0.0 | 2019.0 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| **Street Side** | Lumens | 2019.0 | 0.0 | 2019.0 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| **Total** | Lumens | 4038.0 | 0.0 | 4038.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

**ZONAL LUMENS:**

| Zone | Lumens | % Fixture |
|---|---|---|
| 0°-10° | 36.2 | 0.9 |
| 10°-20° | 107.3 | 2.7 |
| 20°-30° | 180.5 | 4.5 |
| 30°-40° | 276.7 | 6.9 |
| 40°-50° | 480.0 | 11.9 |
| 50°-60° | 960.3 | 23.8 |
| 60°-70° | 1426.7 | 35.3 |
| 70°-80° | 550.3 | 13.6 |
| 80°-90° | 20.1 | 0.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 4038.0 | 100.0 |
| 0°-180° | 4038.0 | 100.0 |



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1361119
CATALOG NUMBER: GSS-SB1A-730-U-5WQ

## LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | | Lumens | % Fixture | Zone Rating/Lumen Limit B | U | G |
|---|---|---|---|---|---|---|
| FL | (0°-30°) | 162.0 | 4.0 | | | |
| FM | (30°-60°) | 858.5 | 21.3 | | | |
| FH | (60°-80°) | 988.5 | 24.5 | | | G1/1800 |
| FVH | (80°-90°) | 10.0 | 0.2 | | | G1/100 |
| BL | (0°-30°) | 162.0 | 4.0 | B1/500 | | |
| BM | (30°-60°) | 858.5 | 21.3 | B1/1000 | | |
| BH | (60°-80°) | 988.5 | 24.5 | B2/1000 | | G1/1800 |
| BVH | (80°-90°) | 10.0 | 0.2 | | | G1/100 |
| UL | (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH | (100°-180°) | 0.0 | 0.0 | | U0/0 | |

**BUG Rating: B2-U0-G1**
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1361119
CATALOG NUMBER: GSS-SB1A-730-U-5WQ

**CANDELA DISTRIBUTION (FULL):**

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|---|---|---|---|---|---|---|---|---|---|---|---|
| 0° | 384.3 | 384.3 | 384.3 | 384.3 | 384.3 | *384.3* | 384.3 | 384.3 | 384.3 | 384.3 | 384.3 |
| 2.5° | 384.3 | 384.3 | 384.3 | 382.5 | 383.4 | *383.4* | 383.4 | 383.4 | 382.5 | 384.3 | 382.5 |
| 5° | 383.4 | 381.7 | 380.8 | 380.8 | 379.9 | *379.9* | 379.0 | 379.0 | 379.0 | 381.7 | 380.8 |
| 7.5° | 380.8 | 379.9 | 378.1 | 377.2 | 378.1 | *377.2* | 377.2 | 377.2 | 376.3 | 376.3 | 378.1 |
| 10° | 379.0 | 379.0 | 379.0 | 377.2 | 378.1 | *377.2* | 376.3 | 376.3 | 377.2 | 377.2 | 378.1 |
| 12.5° | 379.9 | 379.9 | 379.0 | 377.2 | 377.2 | *376.3* | 376.3 | 375.5 | 377.2 | 378.1 | 377.2 |
| 15° | 379.9 | 379.9 | 379.9 | 378.1 | 378.1 | *377.2* | 376.3 | 376.3 | 377.2 | 379.9 | 379.9 |
| 17.5° | 381.7 | 381.7 | 381.7 | 378.1 | 377.2 | *377.2* | 377.2 | 377.2 | 379.0 | 382.5 | 381.7 |
| 20° | 385.2 | 385.2 | 382.5 | 380.8 | 379.9 | *378.1* | 377.2 | 379.9 | 383.4 | 386.1 | 387.0 |
| 22.5° | 388.7 | 387.0 | 386.1 | 382.5 | 384.3 | *384.3* | 383.4 | 384.3 | 384.3 | 389.6 | 387.9 |
| 25° | 390.5 | 390.5 | 388.7 | 387.0 | 389.6 | *387.9* | 388.7 | 387.0 | 389.6 | 390.5 | 391.4 |
| 27.5° | 394.9 | 394.1 | 394.1 | 391.4 | 393.2 | *391.4* | 392.3 | 392.3 | 393.2 | 394.9 | 395.8 |
| 30° | 402.9 | 402.0 | 401.1 | 400.3 | 398.5 | *395.8* | 399.4 | 398.5 | 400.3 | 402.0 | 402.0 |
| 32.5° | 415.3 | 415.3 | 416.2 | 411.8 | 410.0 | *408.2* | 410.0 | 413.5 | 416.2 | 416.2 | 416.2 |
| 35° | 441.0 | 440.1 | 437.4 | 429.5 | 425.1 | *423.3* | 425.9 | 432.1 | 436.6 | 439.2 | 438.3 |
| 37.5° | 472.0 | 472.0 | 467.6 | 460.5 | 451.6 | *449.8* | 453.4 | 456.0 | 463.1 | 468.4 | 472.9 |
| 40° | 507.4 | 510.9 | 505.6 | 496.8 | 488.8 | *487.9* | 491.5 | 491.5 | 496.8 | 506.5 | 508.3 |
| 42.5° | 562.3 | 558.8 | 550.8 | 539.3 | 535.7 | *536.6* | 534.9 | 536.6 | 541.1 | 550.8 | 551.7 |
| 45° | 619.9 | 621.6 | 613.7 | 601.3 | 596.0 | *600.4* | 596.8 | 594.2 | 599.5 | 609.2 | 606.6 |
| 47.5° | 695.1 | 694.3 | 686.3 | 681.0 | 681.0 | *680.1* | 673.0 | 666.8 | 672.1 | 679.2 | 674.8 |
| 50° | 782.8 | 783.7 | 781.9 | 784.6 | 784.6 | *796.1* | 787.2 | 767.7 | 762.4 | 766.9 | 764.2 |
| 52.5° | 886.4 | 890.0 | 896.1 | 905.0 | 929.8 | *949.3* | 927.1 | 901.5 | 882.0 | 879.3 | 872.2 |
| 55° | 1011.3 | 1013.0 | 1026.3 | 1044.9 | 1099.8 | *1145.9* | 1116.6 | 1046.7 | 1010.4 | 996.2 | 986.5 |
| 57.5° | 1142.3 | 1150.3 | 1167.1 | 1208.7 | 1287.6 | *1364.6* | 1304.4 | 1202.5 | 1146.8 | 1123.7 | 1126.4 |
| 60° | 1281.4 | 1287.6 | 1315.9 | 1360.2 | 1482.4 | *1564.7* | 1493.0 | 1354.0 | 1293.7 | 1268.1 | 1266.3 |
| 62.5° | 1340.7 | 1354.9 | 1404.4 | 1496.5 | 1633.8 | *1723.2* | 1641.8 | 1501.0 | 1416.0 | 1368.1 | 1363.7 |
| 65° | 1294.6 | 1302.6 | 1354.0 | 1487.7 | 1712.6 | *1846.3* | 1748.9 | 1536.4 | 1410.6 | 1357.5 | 1346.0 |
| 67.5° | *1193.7* | *1207.0* | *1233.5* | *1340.7* | *1604.6* | *1906.5* | *1682.5* | *1406.2* | *1273.4* | *1220.3* | *1206.1* |
| 70° | 996.2 | 1012.2 | 1041.4 | 1167.1 | 1384.1 | *1648.0* | 1456.7 | 1156.5 | 1009.5 | 954.6 | 964.3 |
| 72.5° | 627.0 | 651.7 | 716.4 | 877.6 | 1128.2 | *1157.4* | 1119.3 | 824.4 | 656.2 | 594.2 | 575.6 |
| 75° | 178.0 | 195.7 | 270.1 | 498.5 | 655.3 | *753.6* | 596.8 | 449.0 | 293.1 | 231.1 | 224.0 |
| 77.5° | 53.1 | 56.7 | 74.4 | 139.0 | 256.8 | *416.2* | 262.1 | 168.2 | 98.3 | 73.5 | 75.3 |
| 80° | 32.8 | 33.6 | 40.7 | 49.6 | 70.0 | *158.5* | 79.7 | 47.8 | 44.3 | 33.6 | 34.5 |
| 82.5° | 21.3 | 20.4 | 24.8 | 27.5 | 30.1 | *32.8* | 28.3 | 27.5 | 26.6 | 20.4 | 19.5 |
| 85° | 8.9 | 8.9 | 10.6 | 12.4 | 11.5 | *11.5* | 12.4 | 13.3 | 12.4 | 10.6 | 10.6 |
| 87.5° | 3.5 | 3.5 | 5.3 | 4.4 | 4.4 | *4.4* | 5.3 | 5.3 | 5.3 | 5.3 | 5.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | *0.0* | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

# LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


## Test Information

| | |
|---|---|
| Test Method: | LM-79-2019 |
| Report Number: | SP1-2407-184-4 |
| Test Lab: | COOPER LIGHTING SOLUTIONS |
| Photometer: | SP1 - 76IN SPHERE |
| Measurement Geometry: | 4π |
| Issue Date: | 10/15/2024 |
| Manufacturer: | COOPER LIGHTING SOLUTIONS |
| Product Line: | McGraw-Edison |
| Catalog Number: | **GSS-SB1A-730-U-5WQ** |
| Description: | GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS |

## Spectral Parameters

| | |
|---|---|
| CCT (K): | 2985 |
| CIE u': | 0.2504 |
| CIE v': | 0.5243 |
| Duv: | 0.0019 |
| CIE x: | 0.4408 |
| CIE y: | 0.4101 |
| CIE z: | 0.1491 |
| Peak Wavelength (nm): | 595 |
| Dominant Wavelength (nm): | 582 |
| Purity: | 55.41818 |
| Rf: | 73.8 |
| Rg: | 94.4 |

| | |
|---|---|
| CRI (Ra): | 70.8 |
| R1: | 66.3 |
| R2: | 80.6 |
| R3: | 94.5 |
| R4: | 68.2 |
| R5: | 66.5 |
| R6: | 74.7 |
| R7: | 76.2 |
| R8: | 39.6 |
| R9: | -43.2 |
| R10: | 57.6 |
| R11: | 64.8 |
| R12: | 53.5 |
| R13: | 68.7 |
| R14: | 97.0 |
| R15: | 56.4 |




## Test Conditions


| | |
|---|---|
| Stabilization Time: | 36M |
| Operation Time: | 1H 36M |
| Sphere Temperature (°C): | 25.2 |

REPORT NUMBER: SP1-2407-184-4


| Measurement and Test Equipment | | | |
|---|---|---|---|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-184-4

## CIE 1931 Chromaticity Diagram




## CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles





CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

## Photopic Flux vs. Wavelength





## Photopic Lumens: NR

| λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 360 | 0 | NR | 490 | 142 | NR | 620 | 803 | NR | 750 | 17 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 189 | NR | 625 | 734 | NR | 755 | 15 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 240 | NR | 630 | 670 | NR | 760 | 13 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 290 | NR | 635 | 600 | NR | 765 | 11 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 335 | NR | 640 | 535 | NR | 770 | 9 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 375 | NR | 645 | 473 | NR | 775 | 8 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 408 | NR | 650 | 415 | NR | 780 | 7 | NR | 910 | 0 | NR |
| 395 | 2 | NR | 525 | 434 | NR | 655 | 362 | NR | 785 | 6 | NR | 915 | 0 | NR |
| 400 | 4 | NR | 530 | 461 | NR | 660 | 313 | NR | 790 | 5 | NR | 920 | 0 | NR |
| 405 | 8 | NR | 535 | 486 | NR | 665 | 271 | NR | 795 | 4 | NR | 925 | 0 | NR |
| 410 | 16 | NR | 540 | 514 | NR | 670 | 231 | NR | 800 | 4 | NR | 930 | 0 | NR |
| 415 | 33 | NR | 545 | 549 | NR | 675 | 198 | NR | 805 | 3 | NR | 935 | 0 | NR |
| 420 | 69 | NR | 550 | 591 | NR | 680 | 169 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 131 | NR | 555 | 640 | NR | 685 | 144 | NR | 815 | 2 | NR | 945 | 0 | NR |
| 430 | 227 | NR | 560 | 695 | NR | 690 | 123 | NR | 820 | 2 | NR | 950 | 0 | NR |
| 435 | 369 | NR | 565 | 757 | NR | 695 | 104 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 517 | NR | 570 | 822 | NR | 700 | 88 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 498 | NR | 575 | 882 | NR | 705 | 75 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 315 | NR | 580 | 935 | NR | 710 | 63 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 204 | NR | 585 | 972 | NR | 715 | 54 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 145 | NR | 590 | 996 | NR | 720 | 46 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 100 | NR | 595 | 1000 | NR | 725 | 39 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 78 | NR | 600 | 989 | NR | 730 | 33 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 76 | NR | 605 | 960 | NR | 735 | 28 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 83 | NR | 610 | 918 | NR | 740 | 24 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 105 | NR | 615 | 864 | NR | 745 | 20 | NR | 875 | 1 | NR | | | |

REPORT NUMBER: SP1-2407-184-4

## Scotopic Flux vs. Wavelength





**Scotopic Lumens: NR** **S/P: 1.19**

| λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 360 | 0 | NR | 490 | 142 | NR | 620 | 803 | NR | 750 | 17 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 189 | NR | 625 | 734 | NR | 755 | 15 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 240 | NR | 630 | 670 | NR | 760 | 13 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 290 | NR | 635 | 600 | NR | 765 | 11 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 335 | NR | 640 | 535 | NR | 770 | 9 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 375 | NR | 645 | 473 | NR | 775 | 8 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 408 | NR | 650 | 415 | NR | 780 | 7 | NR | 910 | 0 | NR |
| 395 | 2 | NR | 525 | 434 | NR | 655 | 362 | NR | 785 | 6 | NR | 915 | 0 | NR |
| 400 | 4 | NR | 530 | 461 | NR | 660 | 313 | NR | 790 | 5 | NR | 920 | 0 | NR |
| 405 | 8 | NR | 535 | 486 | NR | 665 | 271 | NR | 795 | 4 | NR | 925 | 0 | NR |
| 410 | 16 | NR | 540 | 514 | NR | 670 | 231 | NR | 800 | 4 | NR | 930 | 0 | NR |
| 415 | 33 | NR | 545 | 549 | NR | 675 | 198 | NR | 805 | 3 | NR | 935 | 0 | NR |
| 420 | 69 | NR | 550 | 591 | NR | 680 | 169 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 131 | NR | 555 | 640 | NR | 685 | 144 | NR | 815 | 2 | NR | 945 | 0 | NR |
| 430 | 227 | NR | 560 | 695 | NR | 690 | 123 | NR | 820 | 2 | NR | 950 | 0 | NR |
| 435 | 369 | NR | 565 | 757 | NR | 695 | 104 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 517 | NR | 570 | 822 | NR | 700 | 88 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 498 | NR | 575 | 882 | NR | 705 | 75 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 315 | NR | 580 | 935 | NR | 710 | 63 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 204 | NR | 585 | 972 | NR | 715 | 54 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 145 | NR | 590 | 996 | NR | 720 | 46 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 100 | NR | 595 | 1000 | NR | 725 | 39 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 78 | NR | 600 | 989 | NR | 730 | 33 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 76 | NR | 605 | 960 | NR | 735 | 28 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 83 | NR | 610 | 918 | NR | 740 | 24 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 105 | NR | 615 | 864 | NR | 745 | 20 | NR | 875 | 1 | NR | | | |

REPORT NUMBER: SP1-2407-184-4

## Melanopic Flux vs. Wavelength




**Melanopic Lumens: NR** **M/P: 2.13**

| λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 360 | 0 | NR | 490 | 142 | NR | 620 | 803 | NR | 750 | 17 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 189 | NR | 625 | 734 | NR | 755 | 15 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 240 | NR | 630 | 670 | NR | 760 | 13 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 290 | NR | 635 | 600 | NR | 765 | 11 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 335 | NR | 640 | 535 | NR | 770 | 9 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 375 | NR | 645 | 473 | NR | 775 | 8 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 408 | NR | 650 | 415 | NR | 780 | 7 | NR | 910 | 0 | NR |
| 395 | 2 | NR | 525 | 434 | NR | 655 | 362 | NR | 785 | 6 | NR | 915 | 0 | NR |
| 400 | 4 | NR | 530 | 461 | NR | 660 | 313 | NR | 790 | 5 | NR | 920 | 0 | NR |
| 405 | 8 | NR | 535 | 486 | NR | 665 | 271 | NR | 795 | 4 | NR | 925 | 0 | NR |
| 410 | 16 | NR | 540 | 514 | NR | 670 | 231 | NR | 800 | 4 | NR | 930 | 0 | NR |
| 415 | 33 | NR | 545 | 549 | NR | 675 | 198 | NR | 805 | 3 | NR | 935 | 0 | NR |
| 420 | 69 | NR | 550 | 591 | NR | 680 | 169 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 131 | NR | 555 | 640 | NR | 685 | 144 | NR | 815 | 2 | NR | 945 | 0 | NR |
| 430 | 227 | NR | 560 | 695 | NR | 690 | 123 | NR | 820 | 2 | NR | 950 | 0 | NR |
| 435 | 369 | NR | 565 | 757 | NR | 695 | 104 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 517 | NR | 570 | 822 | NR | 700 | 88 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 498 | NR | 575 | 882 | NR | 705 | 75 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 315 | NR | 580 | 935 | NR | 710 | 63 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 204 | NR | 585 | 972 | NR | 715 | 54 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 145 | NR | 590 | 996 | NR | 720 | 46 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 100 | NR | 595 | 1000 | NR | 725 | 39 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 78 | NR | 600 | 989 | NR | 730 | 33 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 76 | NR | 605 | 960 | NR | 735 | 28 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 83 | NR | 610 | 918 | NR | 740 | 24 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 105 | NR | 615 | 864 | NR | 745 | 20 | NR | 875 | 1 | NR | | | |


REPORT NUMBER: SP1-2407-184-4

# TM-30-18


## Summary


$R_f$ = 73.8
$R_g$ = 94.4
CIE $R_a$ = 70.8
$R_9$ = -43.2


## Spectral Power Distribution Comparison





## Color Vector Graphics







REPORT NUMBER: SP1-2407-184-4

# TM-30-18

**Individual Sample Fidelity Index ($R_{f,i}$)**


| | | | |
|---|---|---|---|
| CES01 = 86 | CES26 = 63 | CES51 = 86 | CES76 = 61 |
| CES02 = 62 | CES27 = 83 | CES52 = 86 | CES77 = 81 |
| CES03 = 31 | CES28 = 86 | CES53 = 75 | CES78 = 64 |
| CES04 = 71 | CES29 = 58 | CES54 = 81 | CES79 = 86 |
| CES05 = 49 | CES30 = 61 | CES55 = 80 | CES80 = 86 |
| CES06 = 51 | CES31 = 63 | CES56 = 71 | CES81 = 70 |
| CES07 = 41 | CES32 = 61 | CES57 = 69 | CES82 = 94 |
| CES08 = 40 | CES33 = 65 | CES58 = 72 | CES83 = 88 |
| CES09 = 29 | CES34 = 77 | CES59 = 85 | CES84 = 90 |
| CES10 = 76 | CES35 = 88 | CES60 = 93 | CES85 = 80 |
| CES11 = 59 | CES36 = 89 | CES61 = 86 | CES86 = 60 |
| CES12 = 65 | CES37 = 85 | CES62 = 81 | CES87 = 78 |
| CES13 = 43 | CES38 = 69 | CES63 = 73 | CES88 = 75 |
| CES14 = 74 | CES39 = 93 | CES64 = 72 | CES89 = 66 |
| CES15 = 71 | CES40 = 89 | CES65 = 67 | CES90 = 72 |
| CES16 = 47 | CES41 = 83 | CES66 = 70 | CES91 = 95 |
| CES17 = 50 | CES42 = 87 | CES67 = 68 | CES92 = 59 |
| CES18 = 56 | CES43 = 77 | CES68 = 73 | CES93 = 76 |
| CES19 = 73 | CES44 = 99 | CES69 = 83 | CES94 = 48 |
| CES20 = 66 | CES45 = 83 | CES70 = 66 | CES95 = 70 |
| CES21 = 87 | CES46 = 77 | CES71 = 66 | CES96 = 76 |
| CES22 = 79 | CES47 = 74 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 62 | CES73 = 59 | CES98 = 73 |
| CES24 = 91 | CES49 = 77 | CES74 = 93 | CES99 = 60 |
| CES25 = 73 | CES50 = 85 | CES75 = 67 | |





REPORT NUMBER: SP1-2407-184-4

# TM-30-18

## Color Rendition by Hue-Angle Bin











REPORT NUMBER: SP1-2407-184-4

# TM-30-18

## Measure Comparisons




(END OF REPORT)