Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1358819

Luminaire Tested: **GSS-SB2A-730-U-SL4-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1358819
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2A-730-U-SL4-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 58W 70CRI 3000K FIXTURE w/ TYPE IV SPILL CONTROL DISTRIBUTION OPTIC AND HOUSE SIDE SHIELD
Light Source:	(52) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	5296.9 lumens
Efficiency:	N/A
Efficacy:	91.3 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type IV - Short
BUG Rating:	B1 - U0 - G2


Input Watts (W):	58
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.0%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1358819
CATALOG NUMBER: GSS-SB2A-730-U-SL4-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 2.3 fc
Type IV - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1358819
CATALOG NUMBER: GSS-SB2A-730-U-SL4-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1358819
CATALOG NUMBER: GSS-SB2A-730-U-SL4-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	781.9	0.0	781.9
	% Fixture	14.8	0.0	14.8
Street Side	Lumens	4515.0	0.0	4515.0
	% Fixture	85.2	0.0	85.2
Total	Lumens	5296.9	0.0	5296.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.0	1.3
10°-20°	194.1	3.7
20°-30°	327.2	6.2
30°-40°	522.5	9.9
40°-50°	854.0	16.1
50°-60°	1152.2	21.8
60°-70°	1279.7	24.2
70°-80°	847.2	16.0
80°-90°	50.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5296.9	100.0
0°-180°	5296.9	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1358819
CATALOG NUMBER: GSS-SB2A-730-U-SL4-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	405.1	7.6			
FM	(30°-60°)	2038.3	38.5			
FH	(60°-80°)	2028.0	38.3			G2/5000
FVH	(80°-90°)	43.7	0.8			G1/100
BL	(0°-30°)	186.2	3.5	B1/500		
BM	(30°-60°)	490.5	9.3	B1/1000		
BH	(60°-80°)	98.9	1.9	B0/110		G0/110
BVH	(80°-90°)	6.4	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2
Type IV Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1358819
CATALOG NUMBER: GSS-SB2A-730-U-SL4-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	36°	45°	55°	65°	75°	85°
0°	768.3	768.3	768.3	768.3	768.3	768.3	768.3	768.3	768.3	768.3	768.3
2.5°	795.4	788.2	791.8	793.6	788.2	790.0	786.4	784.6	777.4	782.8	775.6
5°	824.4	822.6	820.7	820.7	815.3	813.5	808.1	804.5	797.2	791.8	782.8
7.5°	858.7	847.9	846.1	849.7	838.8	844.2	838.8	833.4	820.7	806.3	791.8
10°	885.8	880.4	873.2	871.4	873.2	869.6	864.1	858.7	851.5	833.4	817.1
12.5°	916.6	912.9	905.7	902.1	889.4	891.3	891.3	884.0	873.2	862.3	844.2
15°	950.9	936.4	932.8	923.8	916.6	911.1	912.9	914.8	902.1	891.3	873.2
17.5°	967.2	963.6	954.5	943.7	943.7	936.4	934.6	934.6	929.2	925.6	903.9
20°	992.5	988.9	972.6	963.6	954.5	952.7	958.1	958.1	949.1	947.3	943.7
22.5°	1030.5	1019.6	997.9	983.4	972.6	970.8	978.0	976.2	976.2	978.0	985.3
25°	1066.6	1054.0	1030.5	1007.0	983.4	987.1	996.1	997.9	990.7	1001.5	1028.6
27.5°	1120.8	1119.0	1082.9	1035.9	1014.2	1012.4	1016.0	1012.4	1005.1	1017.8	1068.4
30°	1263.7	1247.4	1187.7	1101.0	1052.1	1055.8	1050.3	1028.6	1010.6	1025.0	1106.4
32.5°	1402.9	1364.9	1303.4	1204.0	1113.6	1115.4	1077.5	1035.9	1016.0	1032.3	1144.3
35°	1605.3	1565.6	1473.4	1299.8	1207.6	1191.3	1113.6	1063.0	1026.8	1044.9	1187.7
37.5°	1891.0	1833.1	1708.4	1489.6	1290.8	1283.5	1176.9	1086.5	1035.9	1043.1	1245.6
40°	2111.5	2055.5	1954.2	1690.3	1433.6	1419.1	1276.3	1131.7	1037.7	1052.1	1299.8
42.5°	2303.2	2274.2	2138.6	1867.5	1581.8	1551.1	1372.1	1187.7	1075.6	1075.6	1390.2
45°	2559.9	2505.6	2352.0	2033.8	1730.1	1695.7	1498.7	1276.3	1122.7	1102.8	1484.2
47.5°	2785.8	2740.6	2561.7	2191.1	1871.1	1842.2	1619.8	1372.1	1182.3	1151.6	1594.5
50°	3033.5	2986.5	2780.4	2379.1	2010.3	1968.7	1753.6	1460.7	1254.6	1227.5	1726.5
52.5°	3205.2	3165.5	2959.4	2549.0	2144.1	2115.1	1862.0	1551.1	1339.6	1312.5	1853.0
55°	3319.1	3255.9	3055.2	2697.3	2292.3	2256.1	1959.7	1652.3	1435.4	1426.4	1961.5
57.5°	3373.4	3310.1	3140.2	2827.4	2438.7	2399.0	2080.8	1762.6	1560.1	1567.4	2077.2
60°	3344.4	3297.4	3172.7	2950.3	2601.4	2568.9	2196.5	1889.2	1688.5	1719.2	2131.4
62.5°	3131.1	3142.0	3176.3	3132.9	2809.3	2769.6	2364.6	2050.1	1863.9	1869.3	2126.0
65°	2422.5	2467.7	2861.8	3344.4	3100.4	3048.0	2596.0	2252.5	1983.2	1921.7	1985.0
67.5°	1540.3	1636.1	2069.9	3462.0	3507.2	3474.6	2901.5	2418.9	2012.1	1999.4	1856.6
70°	1048.5	1091.9	1368.5	3212.5	3903.1	3908.5	3324.6	2540.0	2102.5	1938.0	1551.1
72.5°	824.4	828.0	967.2	2894.3	3886.8	3906.7	3293.8	2666.5	2039.2	1726.5	1182.3
75°	553.2	567.7	659.9	2361.0	3228.8	3212.5	2690.0	2048.2	1860.2	1364.9	766.5
77.5°	155.5	160.9	274.8	1504.1	2263.4	2332.1	1952.4	703.2	1294.4	625.5	289.2
80°	47.0	50.6	112.1	432.1	1082.9	1240.2	1016.0	211.5	312.8	148.2	57.8
82.5°	19.9	21.7	66.9	99.4	247.7	267.6	238.6	56.0	97.6	47.0	19.9
85°	7.2	9.0	21.7	23.5	38.0	34.3	27.1	18.1	25.3	21.7	10.8
87.5°	0.0	1.8	1.8	3.6	5.4	5.4	7.2	7.2	7.2	7.2	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1358819
CATALOG NUMBER: GSS-SB2A-730-U-SL4-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	768.3	768.3	768.3	768.3	768.3	768.3	768.3	768.3	768.3	768.3	768.3
2.5°	770.1	768.3	761.1	752.0	746.6	744.8	739.4	728.5	732.2	734.0	724.9
5°	777.4	764.7	750.2	732.2	712.3	696.0	674.3	658.0	647.2	645.4	643.6
7.5°	784.6	773.7	748.4	708.7	668.9	627.3	571.3	531.5	502.6	488.1	493.5
10°	808.1	790.0	746.6	685.2	600.2	509.8	428.5	381.4	354.3	341.7	336.3
12.5°	831.6	806.3	746.6	643.6	499.0	385.1	320.0	305.5	305.5	309.1	307.3
15°	862.3	833.4	752.0	580.3	395.9	301.9	291.1	292.9	298.3	301.9	301.9
17.5°	896.7	875.0	752.0	500.8	309.1	280.2	282.0	287.4	292.9	294.7	296.5
20°	945.5	914.8	728.5	408.6	271.2	271.2	274.8	278.4	285.6	289.2	291.1
22.5°	990.7	956.3	685.2	325.4	260.3	262.1	269.4	273.0	280.2	283.8	282.0
25°	1046.7	1014.2	638.2	263.9	249.5	253.1	258.5	263.9	274.8	278.4	278.4
27.5°	1108.2	1079.3	602.0	258.5	238.6	244.1	253.1	260.3	269.4	273.0	273.0
30°	1175.1	1146.2	580.3	278.4	233.2	231.4	242.2	247.7	258.5	267.6	269.4
32.5°	1245.6	1200.4	573.1	318.2	236.8	222.4	231.4	238.6	253.1	263.9	263.9
35°	1346.8	1281.7	573.1	361.6	251.3	213.3	220.6	229.6	245.9	256.7	256.7
37.5°	1471.6	1410.1	629.1	392.3	263.9	206.1	209.7	218.7	231.4	245.9	247.7
40°	1619.8	1590.9	777.4	412.2	271.2	198.9	202.5	206.1	213.3	227.8	231.4
42.5°	1778.9	1748.2	988.9	432.1	267.6	193.4	191.6	191.6	195.2	204.3	206.1
45°	1932.5	1889.2	1178.7	424.8	251.3	182.6	179.0	173.5	173.5	180.8	180.8
47.5°	2068.1	1990.4	1270.9	376.0	231.4	171.7	164.5	155.5	155.5	159.1	159.1
50°	2154.9	1986.8	1213.0	298.3	202.5	160.9	150.0	142.8	141.0	142.8	141.0
52.5°	2167.6	1860.2	997.9	231.4	175.4	148.2	135.6	132.0	130.2	130.2	130.2
55°	2082.6	1627.0	701.4	177.2	153.7	133.8	124.7	122.9	121.1	119.3	117.5
57.5°	1936.2	1289.0	428.5	142.8	139.2	121.1	115.7	113.9	110.3	104.9	103.0
60°	1740.9	949.1	226.0	121.1	121.1	106.7	106.7	106.7	97.6	90.4	86.8
62.5°	1524.0	640.0	126.5	103.0	101.2	95.8	97.6	95.8	86.8	74.1	72.3
65°	1281.7	363.4	85.0	85.0	86.8	83.2	86.8	85.0	72.3	59.7	56.0
67.5°	1106.4	189.8	66.9	72.3	72.3	68.7	74.1	75.9	65.1	52.4	48.8
70°	*865.9*	*95.8*	*54.2*	*59.7*	*59.7*	*54.2*	*65.1*	*70.5*	*59.7*	*45.2*	*43.4*
72.5°	611.0	59.7	45.2	47.0	45.2	41.6	56.0	63.3	52.4	38.0	36.2
75°	372.4	39.8	34.3	38.0	32.5	32.5	48.8	56.0	45.2	30.7	28.9
77.5°	173.5	28.9	25.3	27.1	23.5	25.3	39.8	43.4	32.5	25.3	23.5
80°	43.4	19.9	19.9	18.1	18.1	19.9	28.9	27.1	23.5	21.7	19.9
82.5°	18.1	14.5	12.7	12.7	12.7	14.5	18.1	18.1	19.9	18.1	18.1
85°	9.0	9.0	9.0	9.0	10.8	10.8	14.5	16.3	16.3	16.3	14.5
87.5°	5.4	5.4	5.4	5.4	5.4	7.2	9.0	10.8	12.7	7.2	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)