Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360739

Luminaire Tested: **GSS-SB2A-730-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360739
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2A-730-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 58W 70CRI 3000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(52) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	8213.6 lumens
Efficiency:	N/A
Efficacy:	141.6 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	58
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.0%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360739
CATALOG NUMBER: GSS-SB2A-730-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 4 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360739
CATALOG NUMBER: GSS-SB2A-730-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360739
CATALOG NUMBER: GSS-SB2A-730-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4106.8	0.0	4106.8
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	4106.8	0.0	4106.8
	% Fixture	50.0	0.0	50.0
Total	Lumens	8213.6	0.0	8213.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.6	1.9
10°-20°	477.4	5.8
20°-30°	797.9	9.7
30°-40°	1100.4	13.4
40°-50°	1349.0	16.4
50°-60°	1580.8	19.2
60°-70°	1755.4	21.4
70°-80°	954.6	11.6
80°-90°	41.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8213.6	100.0
0°-180°	8213.6	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360739
CATALOG NUMBER: GSS-SB2A-730-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	716.0	8.7			
FM	(30°-60°)	2015.1	24.5			
FH	(60°-80°)	1355.0	16.5			G1/1800
FVH	(80°-90°)	20.7	0.3			G1/100
BL	(0°-30°)	716.0	8.7	B2/1000		
BM	(30°-60°)	2015.1	24.5	B2/2500		
BH	(60°-80°)	1355.0	16.5	B3/2500		G3/2500
BVH	(80°-90°)	20.7	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360739
CATALOG NUMBER: GSS-SB2A-730-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1618.3	1618.3	1618.3	1618.3	1618.3	1618.3	1618.3	1618.3	1618.3	1618.3	1618.3
2.5°	1620.1	1620.1	1614.7	1621.9	1618.3	1620.1	1621.9	1620.1	1618.3	1620.1	1621.9
5°	1629.1	1625.5	1629.1	1632.7	1627.3	1630.9	1629.1	1620.1	1625.5	1625.5	1625.5
7.5°	1645.3	1648.8	1645.3	1654.2	1648.8	1659.6	1648.8	1641.7	1639.9	1638.1	1638.1
10°	1652.4	1652.4	1650.6	1666.8	1670.4	1681.2	1674.0	1663.2	1657.8	1650.6	1643.5
12.5°	1632.7	1636.3	1645.3	1675.8	1690.2	1711.8	1706.4	1684.8	1668.6	1663.2	1652.4
15°	1611.1	1614.7	1632.7	1670.4	1704.6	1737.0	1735.2	1708.2	1688.4	1674.0	1657.8
17.5°	1576.9	1582.3	1607.5	1665.0	1726.2	1762.1	1772.9	1745.9	1724.4	1701.0	1679.4
20°	1519.4	1519.4	1564.3	1638.1	1722.6	1803.5	1832.3	1810.7	1785.5	1747.7	1719.0
22.5°	1454.7	1458.3	1503.2	1600.3	1720.8	1839.4	1895.2	1871.8	1846.6	1805.3	1762.1
25°	1389.9	1389.9	1440.3	1550.0	1697.4	1864.6	1968.9	1956.3	1906.0	1868.2	1812.5
27.5°	1330.6	1330.6	1384.5	1499.6	1657.8	1871.8	2042.6	2042.6	1986.9	1931.1	1870.0
30°	1260.5	1278.4	1339.6	1460.0	1621.9	1859.2	2096.6	2130.7	2080.4	2008.5	1918.6
32.5°	1201.1	1213.7	1276.6	1404.3	1569.7	1844.8	2157.7	2242.2	2190.1	2091.2	1990.5
35°	1131.0	1129.2	1201.1	1327.0	1496.0	1812.5	2206.3	2375.3	2324.9	2218.8	2082.2
37.5°	1039.3	1039.3	1113.0	1235.3	1425.9	1756.7	2245.8	2522.7	2485.0	2364.5	2218.8
40°	940.4	951.2	1015.9	1140.0	1341.4	1690.2	2245.8	2643.2	2663.0	2538.9	2387.9
42.5°	868.5	872.1	931.4	1048.3	1247.9	1603.9	2217.0	2747.5	2806.8	2702.5	2506.5
45°	793.0	801.9	852.3	960.2	1150.8	1501.4	2166.7	2864.4	2959.7	2887.7	2630.6
47.5°	701.3	710.2	767.8	877.5	1059.1	1389.9	2082.2	2986.6	3186.2	3134.1	2851.8
50°	595.2	602.4	656.3	773.2	956.6	1262.3	1976.1	3078.3	3412.8	3464.9	3186.2
52.5°	465.7	471.1	528.6	641.9	834.3	1140.0	1826.9	3134.1	3641.1	3824.5	3633.9
55°	334.4	343.4	393.8	487.3	672.5	976.4	1648.8	3162.8	3891.1	4250.7	4189.6
57.5°	240.9	244.5	278.7	350.6	499.9	784.0	1420.5	3114.3	4115.8	4759.5	4887.2
60°	199.6	199.6	205.0	239.1	341.6	553.8	1147.2	2934.5	4308.2	5273.8	5667.6
62.5°	183.4	183.4	187.0	192.4	224.8	359.6	819.9	2569.5	4329.8	5768.3	6523.5
65°	167.2	167.2	170.8	174.4	181.6	233.8	494.5	1880.8	3907.3	5773.7	6983.8
67.5°	152.8	152.8	154.6	156.4	160.0	170.8	271.5	1140.0	3126.9	5620.8	7160.0
70°	138.5	138.5	138.5	136.7	142.0	143.8	179.8	579.0	2091.2	5076.0	7075.5
72.5°	*122.3*	*122.3*	*120.5*	*116.9*	*118.7*	*118.7*	*133.1*	*284.1*	*1086.0*	*4034.9*	*6388.6*
75°	104.3	106.1	98.9	95.3	93.5	95.3	106.1	161.8	485.5	2447.2	4773.9
77.5°	88.1	91.7	80.9	73.7	71.9	71.9	82.7	100.7	208.6	888.3	2139.7
80°	66.5	68.3	59.3	52.1	52.1	50.3	61.1	73.7	98.9	264.3	480.1
82.5°	37.8	37.8	34.2	30.6	28.8	30.6	41.4	50.3	61.1	93.5	131.3
85°	9.0	9.0	10.8	12.6	12.6	16.2	23.4	27.0	32.4	37.8	50.3
87.5°	1.8	1.8	1.8	3.6	5.4	5.4	9.0	12.6	16.2	19.8	21.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360739
CATALOG NUMBER: GSS-SB2A-730-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1618.3	1618.3	*1618.3*
2.5°	1621.9	1623.7	*1621.9*
5°	1632.7	1629.1	*1623.7*
7.5°	1634.5	1636.3	*1638.1*
10°	1641.7	1648.8	*1638.1*
12.5°	1648.8	1643.5	*1639.9*
15°	1654.2	1652.4	*1641.7*
17.5°	1674.0	1666.8	*1665.0*
20°	1704.6	1702.8	*1697.4*
22.5°	1740.6	1737.0	*1735.2*
25°	1792.7	1780.1	*1772.9*
27.5°	1835.9	1825.1	*1821.5*
30°	1879.0	1857.4	*1857.4*
32.5°	1916.8	1911.4	*1907.8*
35°	2006.7	1979.7	*1983.3*
37.5°	2116.4	2089.4	*2066.0*
40°	2271.0	2235.0	*2220.6*
42.5°	2369.9	2333.9	*2337.5*
45°	2425.6	2362.7	*2346.5*
47.5°	2576.7	2497.5	*2476.0*
50°	2821.2	2724.1	*2697.1*
52.5°	3216.8	3060.3	*3024.4*
55°	3713.1	3520.7	*3484.7*
57.5°	4392.7	4137.4	*4060.1*
60°	5219.9	4903.4	*4786.5*
62.5°	6214.2	5824.0	*5712.5*
65°	6962.2	6636.8	*6464.1*
67.5°	7561.0	7293.1	*7210.3*
70°	7917.0	7929.6	*7951.2*
72.5°	*7505.2*	*7850.5*	*8015.9*
75°	5500.4	5768.3	*6025.4*
77.5°	2125.3	1916.8	*1855.6*
80°	343.4	321.9	*332.6*
82.5°	154.6	163.6	*172.6*
85°	100.7	116.9	*124.1*
87.5°	23.4	23.4	*23.4*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)