Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1359972

Luminaire Tested: **GSS-SB2B-730-U-T3**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1359972
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2B-730-U-T3
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 74W 70CRI 3000K FIXTURE w/ TYPE III DISTRIBUTION OPTIC
Light Source:	(52) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	10229.9 lumens
Efficiency:	N/A
Efficacy:	138.2 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B2 - U0 - G2


Input Watts (W):	74
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	13.6%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359972
CATALOG NUMBER: GSS-SB2B-730-U-T3

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 4.5 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359972
CATALOG NUMBER: GSS-SB2B-730-U-T3

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1359972
CATALOG NUMBER: GSS-SB2B-730-U-T3

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2420.2	0.0	2420.2
	% Fixture	23.7	0.0	23.7
Street Side	Lumens	7809.7	0.0	7809.7
	% Fixture	76.3	0.0	76.3
Total	Lumens	10229.9	0.0	10229.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.2	1.5
10°-20°	489.6	4.8
20°-30°	837.1	8.2
30°-40°	1214.4	11.9
40°-50°	1577.4	15.4
50°-60°	2137.3	20.9
60°-70°	2493.1	24.4
70°-80°	1229.2	12.0
80°-90°	96.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10229.9	100.0
0°-180°	10229.9	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1359972
CATALOG NUMBER: GSS-SB2B-730-U-T3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	872.7	8.5			
FM	(30°-60°)	3736.3	36.5			
FH	(60°-80°)	3150.0	30.8			G2/5000
FVH	(80°-90°)	50.6	0.5			G1/100
BL	(0°-30°)	609.2	6.0	B2/1000		
BM	(30°-60°)	1192.8	11.7	B2/2500		
BH	(60°-80°)	572.3	5.6	B2/1000		G2/1000
BVH	(80°-90°)	45.8	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359972
CATALOG NUMBER: GSS-SB2B-730-U-T3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	52°	55°	65°	75°	85°
0°	1583.1	1583.1	1583.1	1583.1	1583.1	1583.1	*1583.1*	1583.1	1583.1	1583.1	1583.1
2.5°	1630.9	1628.6	1626.4	1617.2	1617.2	1619.5	*1615.0*	1617.2	1615.0	1603.6	1594.5
5°	1722.0	1701.5	1697.0	1692.4	1697.0	1683.3	*1671.9*	1665.1	1640.0	1633.2	1605.9
7.5°	1760.7	1763.0	1760.7	1751.6	1744.8	1744.8	*1726.6*	1717.5	1701.5	1674.2	1628.6
10°	1815.4	1813.1	1806.3	1810.9	1824.5	1801.8	*1788.1*	1781.2	1753.9	1715.2	1671.9
12.5°	1913.4	1897.4	1892.9	1886.0	1883.8	1870.1	*1854.1*	1856.4	1824.5	1765.3	1719.7
15°	1997.6	1979.4	1999.9	1986.3	1968.0	1947.5	*1931.6*	1917.9	1881.5	1826.8	1769.9
17.5°	2077.4	2068.3	2077.4	2077.4	2075.1	2040.9	*2009.0*	1997.6	1954.4	1892.9	1817.7
20°	2138.9	2138.9	2154.8	2154.8	2148.0	2127.5	*2107.0*	2093.3	2031.8	1952.1	1865.5
22.5°	2218.6	2182.1	2216.3	2218.6	2220.9	2204.9	*2191.3*	2173.0	2109.3	2013.6	1904.3
25°	2293.8	2264.1	2284.6	2271.0	2280.1	2286.9	*2280.1*	2273.3	2202.6	2093.3	1961.2
27.5°	2412.2	2382.6	2396.3	2364.4	2364.4	2357.5	*2368.9*	2378.0	2300.6	2170.8	2011.3
30°	2589.9	2555.7	2544.3	2505.6	2466.9	2450.9	*2455.5*	2471.4	2419.0	2245.9	2061.4
32.5°	2742.5	2724.3	2715.2	2683.3	2635.4	2562.5	*2573.9*	2573.9	2519.3	2300.6	2086.5
35°	2867.8	2863.2	2865.5	2822.2	2813.1	2694.7	*2694.7*	2690.1	2589.9	2373.5	2152.5
37.5°	2949.8	2924.7	2936.1	2952.0	2922.4	2842.7	*2822.2*	2810.8	2687.8	2450.9	2239.1
40°	2931.5	2913.3	2956.6	2986.2	2963.4	2947.5	*2945.2*	2922.4	2785.8	2548.9	2366.6
42.5°	2929.3	2913.3	2965.7	2997.6	2986.2	3011.3	*3018.1*	3034.0	2911.0	2703.8	2548.9
45°	2938.4	2931.5	3018.1	3059.1	3031.8	3065.9	*3104.7*	3118.3	3070.5	2892.8	2776.7
47.5°	3013.5	3004.4	3104.7	3152.5	3175.3	3234.5	*3209.4*	3232.2	3259.6	3161.6	3038.6
50°	3086.4	3095.5	3229.9	3275.5	3387.1	3469.1	*3382.6*	3419.0	3510.1	3473.7	3389.4
52.5°	3202.6	3204.9	3337.0	3450.9	3665.0	3742.4	*3658.2*	3662.7	3785.7	3854.1	3742.4
55°	3232.2	3257.3	3434.9	3671.8	3979.3	4034.0	*3995.3*	3979.3	4125.1	4218.5	4097.8
57.5°	3229.9	3216.3	3437.2	3765.2	4218.5	4412.1	*4434.9*	4391.6	4514.6	4553.3	4487.3
60°	3145.7	3173.0	3414.4	3831.3	4441.7	4872.2	*4926.9*	4870.0	4929.2	4940.6	4756.1
62.5°	2888.3	2897.4	3227.7	3833.6	4617.1	5254.9	*5416.6*	5352.9	5298.2	5157.0	4815.3
65°	2469.1	2453.2	2769.8	3516.9	4649.0	5623.9	*5856.3*	5856.3	5500.9	5229.9	4690.0
67.5°	*2059.1*	*2034.1*	*2271.0*	*2867.8*	*4138.8*	*5785.6*	*6156.9*	*6036.2*	*5544.2*	*5280.0*	*4391.6*
70°	993.1	1063.7	1425.9	2029.5	3163.9	4885.9	*5933.7*	5979.3	5510.0	5122.8	3813.1
72.5°	355.3	339.4	512.5	870.1	1751.6	3188.9	*4967.9*	5368.8	5270.9	4671.8	3122.9
75°	164.0	166.3	214.1	302.9	567.2	1555.7	*3159.3*	3696.9	4514.6	3883.7	2337.0
77.5°	127.6	127.6	145.8	173.1	234.6	503.4	*1615.0*	2075.1	2917.9	2405.4	1113.9
80°	93.4	95.7	97.9	113.9	143.5	189.1	*480.6*	719.8	1063.7	772.2	362.2
82.5°	66.1	66.1	63.8	63.8	77.4	84.3	*129.8*	182.2	312.1	211.8	95.7
85°	27.3	31.9	27.3	27.3	27.3	34.2	*41.0*	47.8	68.3	59.2	41.0
87.5°	4.6	4.6	4.6	6.8	9.1	11.4	*13.7*	15.9	18.2	18.2	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359972
CATALOG NUMBER: GSS-SB2B-730-U-T3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1583.1	1583.1	1583.1	1583.1	1583.1	1583.1	1583.1	1583.1	1583.1	1583.1	1583.1
2.5°	1589.9	1589.9	1583.1	1571.7	1567.1	1560.3	1558.0	1555.7	1551.2	1560.3	1555.7
5°	1599.0	1589.9	1580.8	1562.6	1560.3	1548.9	1537.5	1535.2	1528.4	1535.2	1535.2
7.5°	1619.5	1605.9	1585.4	1567.1	1551.2	1548.9	1528.4	1510.2	1510.2	1512.5	1510.2
10°	1656.0	1640.0	1619.5	1585.4	1555.7	1528.4	1494.2	1471.5	1473.7	1473.7	1469.2
12.5°	1703.8	1681.0	1644.6	1594.5	1548.9	1505.6	1464.6	1457.8	1455.5	1460.1	1446.4
15°	1740.2	1719.7	1660.5	1603.6	1533.0	1489.7	1446.4	1430.5	1432.7	1428.2	1416.8
17.5°	1785.8	1753.9	1681.0	1596.7	1514.7	1473.7	1423.6	1389.5	1371.2	1373.5	1371.2
20°	1829.1	1783.5	1697.0	1596.7	1510.2	1437.3	1373.5	1328.0	1289.2	1282.4	1280.1
22.5°	1861.0	1815.4	1715.2	1599.0	1482.9	1396.3	1302.9	1243.7	1186.7	1177.6	1175.4
25°	1906.5	1847.3	1735.7	1583.1	1446.4	1328.0	1211.8	1145.7	1095.6	1086.5	1086.5
27.5°	1945.3	1881.5	1763.0	1567.1	1387.2	1234.6	1125.2	1059.2	1027.3	1011.3	1011.3
30°	1986.3	1915.6	1785.8	1519.3	1307.5	1141.2	1056.9	1013.6	977.2	961.2	954.4
32.5°	2031.8	1972.6	1790.4	1471.5	1227.7	1079.7	1009.1	972.6	933.9	911.1	908.8
35°	2088.8	2045.5	1774.4	1400.9	1148.0	1031.8	963.5	922.5	883.8	861.0	865.6
37.5°	2179.9	2129.8	1726.6	1300.6	1082.0	1002.2	927.1	867.8	822.3	785.8	788.1
40°	2314.3	2232.3	1656.0	1179.9	1034.1	968.1	883.8	815.5	749.4	694.7	694.7
42.5°	2466.9	2323.4	1569.4	1068.3	997.7	924.8	838.2	751.7	658.3	601.3	599.1
45°	2637.7	2403.1	1469.2	977.2	938.5	872.4	779.0	656.0	594.5	564.9	562.6
47.5°	2865.5	2489.6	1350.7	897.5	870.1	820.0	690.2	601.3	564.9	542.1	539.8
50°	3079.6	2583.0	1252.8	820.0	797.2	758.5	628.7	578.6	549.0	530.7	526.2
52.5°	3327.9	2678.7	1143.5	744.8	715.2	662.8	615.0	567.2	539.8	526.2	521.6
55°	3573.9	2813.1	1022.7	676.5	642.3	619.6	601.3	560.3	533.0	523.9	517.1
57.5°	3854.1	2942.9	874.7	603.6	590.0	587.7	599.1	558.1	535.3	519.3	510.2
60°	3999.8	2999.9	719.8	537.6	539.8	553.5	590.0	558.1	521.6	494.3	482.9
62.5°	3949.7	2883.7	569.5	471.5	492.0	517.1	574.0	537.6	492.0	471.5	457.8
65°	3749.3	2685.5	444.2	414.6	448.7	471.5	535.3	508.0	462.4	441.9	439.6
67.5°	*3460.0*	*2341.6*	*359.9*	*364.5*	*398.6*	*428.2*	*501.1*	*489.7*	*437.3*	*423.7*	*423.7*
70°	2908.8	1881.5	296.1	318.9	348.5	380.4	476.1	460.1	405.5	398.6	398.6
72.5°	2273.3	1328.0	252.8	280.2	289.3	334.8	441.9	426.0	394.1	410.0	412.3
75°	1603.6	808.6	216.4	236.9	246.0	275.6	410.0	416.8	387.2	439.6	448.7
77.5°	728.9	355.3	168.6	186.8	198.2	234.6	353.1	387.2	334.8	334.8	316.6
80°	255.1	150.3	134.4	134.4	143.5	182.2	293.8	318.9	268.8	236.9	227.8
82.5°	93.4	82.0	100.2	100.2	91.1	111.6	195.9	211.8	193.6	168.6	166.3
85°	36.4	38.7	61.5	61.5	45.6	54.7	109.3	113.9	109.3	95.7	95.7
87.5°	15.9	15.9	18.2	18.2	15.9	13.7	20.5	20.5	13.7	9.1	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)