Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360747

Luminaire Tested: **GSS-SB4A-730-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360747
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4A-730-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 114W 70CRI 3000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(104) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	17201.1 lumens
Efficiency:	N/A
Efficacy:	150.9 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	114
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.2%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360747
CATALOG NUMBER: GSS-SB4A-730-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 8.5 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360747
CATALOG NUMBER: GSS-SB4A-730-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360747
CATALOG NUMBER: GSS-SB4A-730-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	8600.5	0.0	8600.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	8600.5	0.0	8600.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	17201.1	0.0	17201.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.0	1.9
10°-20°	999.8	5.8
20°-30°	1671.1	9.7
30°-40°	2304.5	13.4
40°-50°	2825.0	16.4
50°-60°	3310.5	19.2
60°-70°	3676.3	21.4
70°-80°	1999.2	11.6
80°-90°	86.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	17201.1	100.0
0°-180°	17201.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360747
CATALOG NUMBER: GSS-SB4A-730-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1499.4	8.7			
FM	(30°-60°)	4220.0	24.5			
FH	(60°-80°)	2837.7	16.5			G2/5000
FVH	(80°-90°)	43.3	0.3			G1/100
BL	(0°-30°)	1499.4	8.7	B3/2500		
BM	(30°-60°)	4220.0	24.5	B3/5000		
BH	(60°-80°)	2837.7	16.5	B4/5000		G4/5000
BVH	(80°-90°)	43.3	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360747
CATALOG NUMBER: GSS-SB4A-730-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3389.0	3389.0	3389.0	3389.0	3389.0	3389.0	3389.0	3389.0	3389.0	3389.0	3389.0
2.5°	3392.8	3392.8	3381.5	3396.6	3389.0	3392.8	3396.6	3392.8	3389.0	3392.8	3396.6
5°	3411.6	3404.1	3411.6	3419.2	3407.9	3415.4	3411.6	3392.8	3404.1	3404.1	3404.1
7.5°	3445.5	3453.1	3445.5	3464.4	3453.1	3475.7	3453.1	3438.0	3434.2	3430.5	3430.5
10°	3460.6	3460.6	3456.8	3490.7	3498.2	3520.8	3505.8	3483.2	3471.9	3456.8	3441.8
12.5°	3419.2	3426.7	3445.5	3509.5	3539.7	3584.9	3573.6	3528.4	3494.5	3483.2	3460.6
15°	3374.0	3381.5	3419.2	3498.2	3569.8	3637.6	3633.8	3577.3	3535.9	3505.8	3471.9
17.5°	3302.4	3313.7	3366.4	3486.9	3615.0	3690.3	3712.9	3656.4	3611.2	3562.3	3517.1
20°	3181.9	3181.9	3276.1	3430.5	3607.4	3776.9	3837.1	3792.0	3739.2	3660.2	3599.9
22.5°	3046.4	3053.9	3148.0	3351.4	3603.7	3852.2	3968.9	3920.0	3867.3	3780.7	3690.3
25°	2910.8	2910.8	3016.2	3245.9	3554.7	3904.9	4123.3	4097.0	3991.5	3912.5	3795.7
27.5°	2786.5	2786.5	2899.5	3140.5	3471.9	3920.0	4277.7	4277.7	4161.0	4044.3	3916.2
30°	2639.7	2677.3	2805.4	3057.7	3396.6	3893.6	4390.7	4462.2	4356.8	4206.2	4017.9
32.5°	2515.4	2541.8	2673.6	2940.9	3287.4	3863.5	4518.7	4695.7	4586.5	4379.4	4168.5
35°	2368.6	2364.8	2515.4	2779.0	3133.0	3795.7	4620.4	4974.4	4868.9	4646.8	4360.6
37.5°	2176.5	2176.5	2330.9	2587.0	2986.1	3679.0	4703.2	5283.1	5204.1	4951.8	4646.8
40°	1969.4	1992.0	2127.6	2387.4	2809.1	3539.7	4703.2	5535.4	5576.9	5317.0	5000.7
42.5°	1818.8	1826.3	1950.6	2195.3	2613.3	3358.9	4643.0	5753.8	5878.1	5659.7	5249.2
45°	1660.6	1679.5	1784.9	2010.8	2410.0	3144.3	4537.6	5998.6	6198.2	6047.6	5509.1
47.5°	1468.6	1487.4	1607.9	1837.6	2217.9	2910.8	4360.6	6254.7	6672.6	6563.4	5972.2
50°	1246.4	1261.5	1374.4	1619.2	2003.3	2643.5	4138.4	6446.7	7147.1	7256.3	6672.6
52.5°	975.3	986.6	1107.1	1344.3	1747.2	2387.4	3825.9	6563.4	7625.3	8009.4	7610.3
55°	700.4	719.2	824.7	1020.5	1408.3	2044.7	3453.1	6623.7	8148.8	8901.9	8773.9
57.5°	504.6	512.1	583.7	734.3	1046.8	1641.8	2974.8	6522.0	8619.5	9967.5	10234.9
60°	418.0	418.0	429.3	500.8	715.5	1159.8	2402.5	6145.5	9022.4	11044.5	11869.2
62.5°	384.1	384.1	391.6	402.9	470.7	753.1	1717.1	5381.0	9067.6	12080.1	13661.6
65°	350.2	350.2	357.7	365.3	380.3	489.5	1035.5	3938.8	8182.7	12091.3	14625.6
67.5°	320.1	320.1	323.8	327.6	335.1	357.7	568.6	2387.4	6548.4	11771.3	14994.6
70°	290.0	290.0	290.0	286.2	297.5	301.2	376.6	1212.5	4379.4	10630.3	14817.6
72.5°	*256.1*	*256.1*	*252.3*	*244.8*	*248.5*	*248.5*	*278.7*	*595.0*	*2274.4*	*8450.0*	*13379.2*
75°	218.4	222.2	207.1	199.6	195.8	199.6	222.2	338.9	1016.7	5125.0	9997.7
77.5°	184.5	192.0	169.5	154.4	150.6	150.6	173.2	210.9	436.8	1860.2	4481.1
80°	139.3	143.1	124.3	109.2	109.2	105.4	128.0	154.4	207.1	553.5	1005.4
82.5°	79.1	79.1	71.5	64.0	60.2	64.0	86.6	105.4	128.0	195.8	274.9
85°	18.8	18.8	22.6	26.4	26.4	33.9	49.0	56.5	67.8	79.1	105.4
87.5°	3.8	3.8	3.8	7.5	11.3	11.3	18.8	26.4	33.9	41.4	45.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360747
CATALOG NUMBER: GSS-SB4A-730-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3389.0	3389.0	*3389.0*
2.5°	3396.6	3400.3	*3396.6*
5°	3419.2	3411.6	*3400.3*
7.5°	3422.9	3426.7	*3430.5*
10°	3438.0	3453.1	*3430.5*
12.5°	3453.1	3441.8	*3434.2*
15°	3464.4	3460.6	*3438.0*
17.5°	3505.8	3490.7	*3486.9*
20°	3569.8	3566.0	*3554.7*
22.5°	3645.1	3637.6	*3633.8*
25°	3754.3	3727.9	*3712.9*
27.5°	3844.7	3822.1	*3814.6*
30°	3935.1	3889.9	*3889.9*
32.5°	4014.1	4002.8	*3995.3*
35°	4202.4	4145.9	*4153.5*
37.5°	4432.1	4375.6	*4326.7*
40°	4756.0	4680.6	*4650.5*
42.5°	4963.1	4887.8	*4895.3*
45°	5079.8	4948.0	*4914.1*
47.5°	5396.1	5230.4	*5185.2*
50°	5908.2	5704.9	*5648.4*
52.5°	6736.7	6409.1	*6333.7*
55°	7776.0	7373.0	*7297.7*
57.5°	9199.4	8664.6	*8502.7*
60°	10931.5	10268.8	*10024.0*
62.5°	13013.9	12196.8	*11963.3*
65°	14580.4	13898.8	*13537.3*
67.5°	15834.4	15273.3	*15100.1*
70°	16579.9	16606.3	*16651.5*
72.5°	*15717.6*	*16440.6*	*16787.1*
75°	11519.0	12080.1	*12618.5*
77.5°	4450.9	4014.1	*3886.1*
80°	719.2	674.0	*696.6*
82.5°	323.8	342.7	*361.5*
85°	210.9	244.8	*259.8*
87.5°	49.0	49.0	*49.0*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)