Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360736

Luminaire Tested: **GSS-SB1B-730-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360736
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB1B-730-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 1SQUARE 40W 70CRI 3000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(26) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	5068.1 lumens
Efficiency:	N/A
Efficacy:	126.7 lumens/watt
Luminous Opening:	Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B2 - U0 - G2


Input Watts (W):	40
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	5.3%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360736
CATALOG NUMBER: GSS-SB1B-730-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 2.5 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360736
CATALOG NUMBER: GSS-SB1B-730-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360736
CATALOG NUMBER: GSS-SB1B-730-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2534.0	0.0	2534.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2534.0	0.0	2534.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	5068.1	0.0	5068.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.7	1.9
10°-20°	294.6	5.8
20°-30°	492.4	9.7
30°-40°	679.0	13.4
40°-50°	832.4	16.4
50°-60°	975.4	19.2
60°-70°	1083.2	21.4
70°-80°	589.0	11.6
80°-90°	25.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5068.1	100.0
0°-180°	5068.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360736
CATALOG NUMBER: GSS-SB1B-730-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	441.8	8.7			
FM	(30°-60°)	1243.4	24.5			
FH	(60°-80°)	836.1	16.5			G1/1800
FVH	(80°-90°)	12.8	0.3			G1/100
BL	(0°-30°)	441.8	8.7	B1/500		
BM	(30°-60°)	1243.4	24.5	B2/2500		
BH	(60°-80°)	836.1	16.5	B2/1000		G2/1000
BVH	(80°-90°)	12.8	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360736
CATALOG NUMBER: GSS-SB1B-730-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5
2.5°	999.6	999.6	996.3	1000.8	998.5	999.6	1000.8	999.6	998.5	999.6	1000.8
5°	1005.2	1003.0	1005.2	1007.4	1004.1	1006.3	1005.2	999.6	1003.0	1003.0	1003.0
7.5°	1015.2	1017.4	1015.2	1020.7	1017.4	1024.1	1017.4	1013.0	1011.8	1010.7	1010.7
10°	1019.6	1019.6	1018.5	1028.5	1030.7	1037.4	1032.9	1026.3	1022.9	1018.5	1014.1
12.5°	1007.4	1009.6	1015.2	1034.0	1042.9	1056.2	1052.9	1039.6	1029.6	1026.3	1019.6
15°	994.1	996.3	1007.4	1030.7	1051.8	1071.8	1070.7	1054.0	1041.8	1032.9	1022.9
17.5°	973.0	976.3	991.9	1027.4	1065.1	1087.3	1093.9	1077.3	1064.0	1049.6	1036.3
20°	937.5	937.5	965.2	1010.7	1062.9	1112.8	1130.6	1117.2	1101.7	1078.4	1060.7
22.5°	897.6	899.8	927.5	987.4	1061.8	1135.0	1169.4	1155.0	1139.4	1113.9	1087.3
25°	857.6	857.6	888.7	956.4	1047.4	1150.5	1214.9	1207.1	1176.1	1152.8	1118.4
27.5°	821.0	821.0	854.3	925.3	1022.9	1155.0	1260.4	1260.4	1226.0	1191.6	1153.9
30°	777.7	788.8	826.6	900.9	1000.8	1147.2	1293.7	1314.7	1283.7	1239.3	1183.8
32.5°	741.1	748.9	787.7	866.5	968.6	1138.3	1331.4	1383.5	1351.3	1290.3	1228.2
35°	697.9	696.8	741.1	818.8	923.1	1118.4	1361.3	1465.6	1434.6	1369.1	1284.8
37.5°	641.3	641.3	686.8	762.2	879.8	1084.0	1385.7	1556.6	1533.3	1459.0	1369.1
40°	580.3	586.9	626.9	703.4	827.7	1042.9	1385.7	1630.9	1643.1	1566.6	1473.4
42.5°	535.9	538.1	574.7	646.8	770.0	989.7	1368.0	1695.3	1731.9	1667.6	1546.6
45°	489.3	494.8	525.9	592.5	710.1	926.4	1336.9	1767.4	1826.2	1781.8	1623.2
47.5°	432.7	438.2	473.7	541.4	653.5	857.6	1284.8	1842.8	1966.0	1933.8	1759.6
50°	367.2	371.7	405.0	477.1	590.2	778.9	1219.3	1899.4	2105.8	2138.0	1966.0
52.5°	287.4	290.7	326.2	396.1	514.8	703.4	1127.2	1933.8	2246.7	2359.9	2242.3
55°	206.4	211.9	243.0	300.7	414.9	602.4	1017.4	1951.6	2400.9	2622.8	2585.1
57.5°	148.7	150.9	172.0	216.3	308.4	483.7	876.5	1921.6	2539.6	2936.8	3015.6
60°	123.2	123.2	126.5	147.6	210.8	341.7	707.8	1810.7	2658.3	3254.1	3497.1
62.5°	113.2	113.2	115.4	118.7	138.7	221.9	505.9	1585.4	2671.6	3559.2	4025.2
65°	103.2	103.2	105.4	107.6	112.1	144.2	305.1	1160.5	2410.9	3562.5	4309.2
67.5°	94.3	94.3	95.4	96.5	98.7	105.4	167.5	703.4	1929.4	3468.2	4418.0
70°	85.4	85.4	85.4	84.3	87.6	88.8	110.9	357.3	1290.3	3132.1	4365.8
72.5°	*75.4*	*75.4*	*74.3*	*72.1*	*73.2*	*73.2*	*82.1*	*175.3*	*670.1*	*2489.7*	*3942.0*
75°	64.3	65.5	61.0	58.8	57.7	58.8	65.5	99.9	299.6	1510.0	2945.7
77.5°	54.4	56.6	49.9	45.5	44.4	44.4	51.0	62.1	128.7	548.1	1320.3
80°	41.1	42.2	36.6	32.2	32.2	31.1	37.7	45.5	61.0	163.1	296.2
82.5°	23.3	23.3	21.1	18.9	17.8	18.9	25.5	31.1	37.7	57.7	81.0
85°	5.5	5.5	6.7	7.8	7.8	10.0	14.4	16.6	20.0	23.3	31.1
87.5°	1.1	1.1	1.1	2.2	3.3	3.3	5.5	7.8	10.0	12.2	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360736
CATALOG NUMBER: GSS-SB1B-730-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	998.5	998.5	*998.5*
2.5°	1000.8	1001.9	*1000.8*
5°	1007.4	1005.2	*1001.9*
7.5°	1008.5	1009.6	*1010.7*
10°	1013.0	1017.4	*1010.7*
12.5°	1017.4	1014.1	*1011.8*
15°	1020.7	1019.6	*1013.0*
17.5°	1032.9	1028.5	*1027.4*
20°	1051.8	1050.7	*1047.4*
22.5°	1074.0	1071.8	*1070.7*
25°	1106.2	1098.4	*1093.9*
27.5°	1132.8	1126.1	*1123.9*
30°	1159.4	1146.1	*1146.1*
32.5°	1182.7	1179.4	*1177.2*
35°	1238.2	1221.5	*1223.8*
37.5°	1305.9	1289.2	*1274.8*
40°	1401.3	1379.1	*1370.2*
42.5°	1462.3	1440.1	*1442.3*
45°	1496.7	1457.9	*1447.9*
47.5°	1589.9	1541.1	*1527.8*
50°	1740.8	1680.9	*1664.2*
52.5°	1984.9	1888.3	*1866.1*
55°	2291.1	2172.4	*2150.2*
57.5°	2710.5	2552.9	*2505.2*
60°	3220.8	3025.6	*2953.4*
62.5°	3834.4	3593.6	*3524.8*
65°	4295.9	4095.1	*3988.6*
67.5°	4665.4	4500.1	*4449.0*
70°	4885.0	4892.8	*4906.1*
72.5°	*4631.0*	*4844.0*	*4946.1*
75°	3393.9	3559.2	*3717.9*
77.5°	1311.4	1182.7	*1145.0*
80°	211.9	198.6	*205.3*
82.5°	95.4	101.0	*106.5*
85°	62.1	72.1	*76.6*
87.5°	14.4	14.4	*14.4*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)