Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360737

Luminaire Tested: **GSS-SB1C-730-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360737
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB1C-730-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 1SQUARE 52W 70CRI 3000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(26) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	6683.7 lumens
Efficiency:	N/A
Efficacy:	128.5 lumens/watt
Luminous Opening:	Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	52
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	10.1%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360737
CATALOG NUMBER: GSS-SB1C-730-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 3.3 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360737
CATALOG NUMBER: GSS-SB1C-730-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360737
CATALOG NUMBER: GSS-SB1C-730-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3341.8	0.0	3341.8
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3341.8	0.0	3341.8
	% Fixture	50.0	0.0	50.0
Total	Lumens	6683.7	0.0	6683.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.5	1.9
10°-20°	388.5	5.8
20°-30°	649.3	9.7
30°-40°	895.4	13.4
40°-50°	1097.7	16.4
50°-60°	1286.3	19.2
60°-70°	1428.5	21.4
70°-80°	776.8	11.6
80°-90°	33.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6683.7	100.0
0°-180°	6683.7	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360737
CATALOG NUMBER: GSS-SB1C-730-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	582.6	8.7			
FM	(30°-60°)	1639.7	24.5			
FH	(60°-80°)	1102.6	16.5			G1/1800
FVH	(80°-90°)	16.8	0.3			G1/100
BL	(0°-30°)	582.6	8.7	B2/1000		
BM	(30°-60°)	1639.7	24.5	B2/2500		
BH	(60°-80°)	1102.6	16.5	B3/2500		G3/2500
BVH	(80°-90°)	16.8	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360737
CATALOG NUMBER: GSS-SB1C-730-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1316.8	1316.8	1316.8	1316.8	1316.8	1316.8	1316.8	1316.8	1316.8	1316.8	1316.8
2.5°	1318.3	1318.3	1313.9	1319.8	1316.8	1318.3	1319.8	1318.3	1316.8	1318.3	1319.8
5°	1325.6	1322.7	1325.6	1328.6	1324.2	1327.1	1325.6	1318.3	1322.7	1322.7	1322.7
7.5°	1338.8	1341.7	1338.8	1346.1	1341.7	1350.5	1341.7	1335.9	1334.4	1332.9	1332.9
10°	1344.6	1344.6	1343.2	1356.4	1359.3	1368.1	1362.2	1353.4	1349.0	1343.2	1337.3
12.5°	1328.6	1331.5	1338.8	1363.7	1375.4	1392.9	1388.5	1371.0	1357.8	1353.4	1344.6
15°	1311.0	1313.9	1328.6	1359.3	1387.1	1413.4	1412.0	1390.0	1373.9	1362.2	1349.0
17.5°	1283.2	1287.6	1308.1	1354.9	1404.6	1433.9	1442.7	1420.7	1403.2	1384.2	1366.6
20°	1236.4	1236.4	1273.0	1332.9	1401.7	1467.6	1491.0	1473.4	1452.9	1422.2	1398.8
22.5°	1183.7	1186.6	1223.2	1302.2	1400.2	1496.8	1542.2	1523.2	1502.7	1469.0	1433.9
25°	1131.0	1131.0	1172.0	1261.2	1381.2	1517.3	1602.2	1591.9	1551.0	1520.2	1474.9
27.5°	1082.7	1082.7	1126.6	1220.3	1349.0	1523.2	1662.2	1662.2	1616.8	1571.4	1521.7
30°	1025.7	1040.3	1090.1	1188.1	1319.8	1512.9	1706.0	1733.8	1692.9	1634.4	1561.2
32.5°	977.4	987.6	1038.8	1142.7	1277.3	1501.2	1755.8	1824.6	1782.1	1701.7	1619.7
35°	920.3	918.9	977.4	1079.8	1217.4	1474.9	1795.3	1932.8	1891.9	1805.5	1694.3
37.5°	845.7	845.7	905.7	1005.2	1160.3	1429.5	1827.5	2052.8	2022.1	1924.1	1805.5
40°	765.2	774.0	826.7	927.6	1091.5	1375.4	1827.5	2150.9	2166.9	2066.0	1943.1
42.5°	706.7	709.6	757.9	853.0	1015.4	1305.1	1804.1	2235.7	2284.0	2199.1	2039.7
45°	645.3	652.6	693.5	781.3	936.4	1221.7	1763.1	2330.8	2408.4	2349.8	2140.6
47.5°	570.6	577.9	624.8	714.0	861.8	1131.0	1694.3	2430.3	2592.7	2550.3	2320.6
50°	484.3	490.2	534.1	629.2	778.4	1027.1	1608.0	2504.9	2777.1	2819.5	2592.7
52.5°	379.0	383.3	430.2	522.3	678.9	927.6	1486.6	2550.3	2962.9	3112.1	2957.1
55°	272.1	279.5	320.4	396.5	547.2	794.5	1341.7	2573.7	3166.3	3458.9	3409.2
57.5°	196.1	199.0	226.8	285.3	406.8	637.9	1155.9	2534.2	3349.2	3873.0	3976.9
60°	162.4	162.4	166.8	194.6	278.0	450.7	933.5	2387.9	3505.7	4291.5	4611.9
62.5°	149.2	149.2	152.2	156.6	182.9	292.6	667.2	2090.9	3523.3	4693.8	5308.4
65°	136.1	136.1	139.0	141.9	147.8	190.2	402.4	1530.5	3179.5	4698.2	5682.9
67.5°	124.4	124.4	125.8	127.3	130.2	139.0	220.9	927.6	2544.4	4573.9	5826.3
70°	112.7	112.7	112.7	111.2	115.6	117.1	146.3	471.1	1701.7	4130.5	5757.6
72.5°	*99.5*	*99.5*	*98.0*	*95.1*	*96.6*	*96.6*	*108.3*	*231.2*	*883.8*	*3283.3*	*5198.6*
75°	84.9	86.3	80.5	77.5	76.1	77.5	86.3	131.7	395.1	1991.4	3884.7
77.5°	71.7	74.6	65.8	60.0	58.5	58.5	67.3	81.9	169.7	722.8	1741.2
80°	54.1	55.6	48.3	42.4	42.4	41.0	49.7	60.0	80.5	215.1	390.7
82.5°	30.7	30.7	27.8	24.9	23.4	24.9	33.7	41.0	49.7	76.1	106.8
85°	7.3	7.3	8.8	10.2	10.2	13.2	19.0	21.9	26.3	30.7	41.0
87.5°	1.5	1.5	1.5	2.9	4.4	4.4	7.3	10.2	13.2	16.1	17.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360737
CATALOG NUMBER: GSS-SB1C-730-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1316.8	1316.8	*1316.8*
2.5°	1319.8	1321.2	*1319.8*
5°	1328.6	1325.6	*1321.2*
7.5°	1330.0	1331.5	*1332.9*
10°	1335.9	1341.7	*1332.9*
12.5°	1341.7	1337.3	*1334.4*
15°	1346.1	1344.6	*1335.9*
17.5°	1362.2	1356.4	*1354.9*
20°	1387.1	1385.6	*1381.2*
22.5°	1416.3	1413.4	*1412.0*
25°	1458.8	1448.5	*1442.7*
27.5°	1493.9	1485.1	*1482.2*
30°	1529.0	1511.4	*1511.4*
32.5°	1559.7	1555.3	*1552.4*
35°	1632.9	1610.9	*1613.9*
37.5°	1722.1	1700.2	*1681.2*
40°	1848.0	1818.7	*1807.0*
42.5°	1928.5	1899.2	*1902.1*
45°	1973.8	1922.6	*1909.4*
47.5°	2096.7	2032.3	*2014.8*
50°	2295.7	2216.7	*2194.7*
52.5°	2617.6	2490.3	*2461.0*
55°	3021.4	2864.9	*2835.6*
57.5°	3574.5	3366.7	*3303.8*
60°	4247.6	3990.0	*3894.9*
62.5°	5056.7	4739.2	*4648.5*
65°	5665.4	5400.5	*5260.1*
67.5°	6152.6	5934.6	*5867.3*
70°	6442.3	6452.6	*6470.1*
72.5°	*6107.2*	*6388.2*	*6522.8*
75°	4475.8	4693.8	*4903.1*
77.5°	1729.5	1559.7	*1510.0*
80°	279.5	261.9	*270.7*
82.5°	125.8	133.1	*140.5*
85°	81.9	95.1	*101.0*
87.5°	19.0	19.0	*19.0*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)