Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1358821

Luminaire Tested: **GSS-SB2C-730-U-SL4-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1358821
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2C-730-U-SL4-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 102W 70CRI 3000K FIXTURE w/ TYPE IV SPILL CONTROL DISTRIBUTION OPTIC AND HOUSE SIDE SHIELD
Light Source:	(52) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	8800.2 lumens
Efficiency:	N/A
Efficacy:	86.3 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type IV - Short
BUG Rating:	B1 - U0 - G2


Input Watts (W):	102
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1358821
CATALOG NUMBER: GSS-SB2C-730-U-SL4-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 3.9 fc
Type IV - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1358821
CATALOG NUMBER: GSS-SB2C-730-U-SL4-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1358821
CATALOG NUMBER: GSS-SB2C-730-U-SL4-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1299.1	0.0	1299.1
	% Fixture	14.8	0.0	14.8
Street Side	Lumens	7501.2	0.0	7501.2
	% Fixture	85.2	0.0	85.2
Total	Lumens	8800.2	0.0	8800.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.3	1.3
10°-20°	322.5	3.7
20°-30°	543.6	6.2
30°-40°	868.2	9.9
40°-50°	1418.8	16.1
50°-60°	1914.3	21.8
60°-70°	2126.0	24.2
70°-80°	1407.5	16.0
80°-90°	83.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8800.2	100.0
0°-180°	8800.2	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1358821
CATALOG NUMBER: GSS-SB2C-730-U-SL4-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	673.0	7.6			
FM	(30°-60°)	3386.3	38.5			
FH	(60°-80°)	3369.3	38.3			G2/5000
FVH	(80°-90°)	72.5	0.8			G1/100
BL	(0°-30°)	309.3	3.5	B1/500		
BM	(30°-60°)	814.9	9.3	B1/1000		
BH	(60°-80°)	164.2	1.9	B1/500		G1/500
BVH	(80°-90°)	10.6	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2
Type IV Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1358821
CATALOG NUMBER: GSS-SB2C-730-U-SL4-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	36°	45°	55°	65°	75°	85°
0°	1276.5	1276.5	1276.5	1276.5	1276.5	*1276.5*	1276.5	1276.5	1276.5	1276.5	1276.5
2.5°	1321.5	1309.5	1315.5	1318.5	1309.5	*1312.5*	1306.5	1303.5	1291.5	1300.5	1288.5
5°	1369.6	1366.6	1363.6	1363.6	1354.6	*1351.6*	1342.6	1336.6	1324.5	1315.5	1300.5
7.5°	1426.7	1408.6	1405.6	1411.6	1393.6	*1402.6*	1393.6	1384.6	1363.6	1339.6	1315.5
10°	1471.7	1462.7	1450.7	1447.7	1450.7	*1444.7*	1435.7	1426.7	1414.6	1384.6	1357.6
12.5°	1522.8	1516.8	1504.7	1498.7	1477.7	*1480.7*	1480.7	1468.7	1450.7	1432.7	1402.6
15°	1579.8	1555.8	1549.8	1534.8	1522.8	*1513.8*	1516.8	1519.8	1498.7	1480.7	1450.7
17.5°	1606.9	1600.9	1585.8	1567.8	1567.8	*1555.8*	1552.8	1552.8	1543.8	1537.8	1501.7
20°	1648.9	1642.9	1615.9	1600.9	1585.8	*1582.8*	1591.8	1591.8	1576.8	1573.8	1567.8
22.5°	1712.0	1694.0	1657.9	1633.9	1615.9	*1612.9*	1624.9	1621.9	1621.9	1624.9	1636.9
25°	1772.1	1751.0	1712.0	1672.9	1633.9	*1639.9*	1654.9	1657.9	1645.9	1663.9	1709.0
27.5°	1862.2	1859.2	1799.1	1721.0	1685.0	*1682.0*	1688.0	1682.0	1669.9	1691.0	1775.1
30°	2099.4	2072.4	1973.3	1829.1	1748.0	*1754.0*	1745.0	1709.0	1678.9	1703.0	1838.1
32.5°	2330.7	2267.6	2165.5	2000.3	1850.1	*1853.2*	1790.1	1721.0	1688.0	1715.0	1901.2
35°	2667.1	2601.0	2447.8	2159.5	2006.3	*1979.3*	1850.1	1766.0	1706.0	1736.0	1973.3
37.5°	3141.6	3045.5	2838.3	2474.9	2144.5	*2132.5*	1955.3	1805.1	1721.0	1733.0	2069.4
40°	3508.1	3415.0	3246.8	2808.3	2381.8	*2357.7*	2120.5	1880.2	1724.0	1748.0	2159.5
42.5°	3826.4	3778.4	3553.1	3102.6	2628.1	*2577.0*	2279.6	1973.3	1787.1	1787.1	2309.7
45°	4252.9	4162.8	3907.5	3378.9	2874.3	*2817.3*	2489.9	2120.5	1865.2	1832.1	2465.9
47.5°	4628.4	4553.3	4255.9	3640.2	3108.6	*3060.6*	2691.1	2279.6	1964.3	1913.2	2649.1
50°	5039.8	4961.8	4619.4	3952.6	3339.9	*3270.8*	2913.4	2426.8	2084.4	2039.4	2868.3
52.5°	5325.2	5259.1	4916.7	4234.9	3562.1	*3514.1*	3093.6	2577.0	2225.6	2180.5	3078.6
55°	5514.4	5409.3	5075.9	4481.2	3808.4	*3748.4*	3255.8	2745.2	2384.8	2369.8	3258.8
57.5°	5604.5	5499.4	5217.1	4697.5	4051.7	*3985.6*	3457.0	2928.4	2592.0	2604.0	3451.0
60°	5556.4	5478.4	5271.1	4901.7	4322.0	*4268.0*	3649.2	3138.6	2805.3	2856.3	3541.1
62.5°	5202.0	5220.1	5277.1	5205.0	4667.4	*4601.3*	3928.6	3406.0	3096.6	3105.6	3532.1
65°	4024.7	4099.8	4754.5	5556.4	5151.0	*5063.9*	4313.0	3742.3	3294.8	3192.7	3297.8
67.5°	2559.0	2718.2	3439.0	5751.7	5826.8	*5772.7*	4820.6	4018.7	3342.9	3321.9	3084.6
70°	*1742.0*	*1814.1*	*2273.6*	*5337.2*	*6484.5*	*6493.5*	*5523.4*	*4219.9*	*3493.1*	*3219.7*	*2577.0*
72.5°	1369.6	1375.6	1606.9	4808.6	6457.5	*6490.5*	5472.4	4430.1	3387.9	2868.3	1964.3
75°	919.1	943.1	1096.3	3922.6	5364.2	*5337.2*	4469.2	3402.9	3090.6	2267.6	1273.5
77.5°	258.3	267.3	456.5	2498.9	3760.4	*3874.5*	3243.8	1168.4	2150.5	1039.2	480.6
80°	78.1	84.1	186.2	717.8	1799.1	*2060.4*	1688.0	351.4	519.6	246.3	96.1
82.5°	33.0	36.0	111.1	165.2	411.5	*444.5*	396.5	93.1	162.2	78.1	33.0
85°	12.0	15.0	36.0	39.0	63.1	*57.1*	45.1	30.0	42.0	36.0	18.0
87.5°	0.0	3.0	3.0	6.0	9.0	*9.0*	12.0	12.0	12.0	12.0	12.0
90°	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1358821
CATALOG NUMBER: GSS-SB2C-730-U-SL4-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1276.5	1276.5	1276.5	1276.5	1276.5	1276.5	1276.5	1276.5	1276.5	1276.5	1276.5
2.5°	1279.5	1276.5	1264.5	1249.5	1240.4	1237.4	1228.4	1210.4	1216.4	1219.4	1204.4
5°	1291.5	1270.5	1246.4	1216.4	1183.4	1156.3	1120.3	1093.3	1075.2	1072.2	1069.2
7.5°	1303.5	1285.5	1243.4	1177.4	1111.3	1042.2	949.1	883.0	835.0	810.9	820.0
10°	1342.6	1312.5	1240.4	1138.3	997.2	847.0	711.8	633.7	588.7	567.7	558.6
12.5°	1381.6	1339.6	1240.4	1069.2	829.0	639.7	531.6	507.6	507.6	513.6	510.6
15°	1432.7	1384.6	1249.5	964.1	657.8	501.6	483.6	486.6	495.6	501.6	501.6
17.5°	1489.7	1453.7	1249.5	832.0	513.6	465.5	468.5	477.6	486.6	489.6	492.6
20°	1570.8	1519.8	1210.4	678.8	450.5	450.5	456.5	462.5	474.6	480.6	483.6
22.5°	1645.9	1588.8	1138.3	540.6	432.5	435.5	447.5	453.5	465.5	471.5	468.5
25°	1739.0	1685.0	1060.2	438.5	414.5	420.5	429.5	438.5	456.5	462.5	462.5
27.5°	1841.1	1793.1	1000.2	429.5	396.5	405.5	420.5	432.5	447.5	453.5	453.5
30°	1952.3	1904.2	964.1	462.5	387.4	384.4	402.5	411.5	429.5	444.5	447.5
32.5°	2069.4	1994.3	952.1	528.6	393.5	369.4	384.4	396.5	420.5	438.5	438.5
35°	2237.6	2129.5	952.1	600.7	417.5	354.4	366.4	381.4	408.5	426.5	426.5
37.5°	2444.8	2342.7	1045.2	651.8	438.5	342.4	348.4	363.4	384.4	408.5	411.5
40°	2691.1	2643.1	1291.5	684.8	450.5	330.4	336.4	342.4	354.4	378.4	384.4
42.5°	2955.4	2904.4	1642.9	717.8	444.5	321.4	318.4	318.4	324.4	339.4	342.4
45°	3210.7	3138.6	1958.3	705.8	417.5	303.4	297.3	288.3	288.3	300.3	300.3
47.5°	3436.0	3306.8	2111.5	624.7	384.4	285.3	273.3	258.3	258.3	264.3	264.3
50°	3580.2	3300.8	2015.3	495.6	336.4	267.3	249.3	237.3	234.3	237.3	234.3
52.5°	3601.2	3090.6	1657.9	384.4	291.3	246.3	225.3	219.3	216.3	216.3	216.3
55°	3460.0	2703.1	1165.4	294.3	255.3	222.3	207.2	204.2	201.2	198.2	195.2
57.5°	3216.7	2141.5	711.8	237.3	231.3	201.2	192.2	189.2	183.2	174.2	171.2
60°	2892.4	1576.8	375.4	201.2	201.2	177.2	177.2	177.2	162.2	150.2	144.2
62.5°	2531.9	1063.2	210.2	171.2	168.2	159.2	162.2	159.2	144.2	123.1	120.1
65°	2129.5	603.7	141.2	141.2	144.2	138.2	144.2	141.2	120.1	99.1	93.1
67.5°	1838.1	315.4	111.1	120.1	120.1	114.1	123.1	126.1	108.1	87.1	81.1
70°	*1438.7*	*159.2*	*90.1*	*99.1*	*99.1*	*90.1*	*108.1*	*117.1*	*99.1*	*75.1*	*72.1*
72.5°	1015.2	99.1	75.1	78.1	75.1	69.1	93.1	105.1	87.1	63.1	60.1
75°	618.7	66.1	57.1	63.1	54.1	54.1	81.1	93.1	75.1	51.1	48.1
77.5°	288.3	48.1	42.0	45.1	39.0	42.0	66.1	72.1	54.1	42.0	39.0
80°	72.1	33.0	33.0	30.0	30.0	33.0	48.1	45.1	39.0	36.0	33.0
82.5°	30.0	24.0	21.0	21.0	21.0	24.0	30.0	30.0	33.0	30.0	30.0
85°	15.0	15.0	15.0	15.0	18.0	18.0	24.0	27.0	27.0	27.0	24.0
87.5°	9.0	9.0	9.0	9.0	9.0	12.0	15.0	18.0	21.0	12.0	9.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)