Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1359205

Luminaire Tested: **GSS-SB2C-730-U-T2**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1359205
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2C-730-U-T2
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 102W 70CRI 3000K FIXTURE w/ TYPE II DISTRIBUTION OPTIC
Light Source:	(52) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	13451.9 lumens
Efficiency:	N/A
Efficacy:	131.9 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type II - Medium
BUG Rating:	B2 - U0 - G2


Input Watts (W):	102
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359205
CATALOG NUMBER: GSS-SB2C-730-U-T2

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 6 fc
Type II - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359205
CATALOG NUMBER: GSS-SB2C-730-U-T2

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1359205
CATALOG NUMBER: GSS-SB2C-730-U-T2

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3082.2	0.0	3082.2
	% Fixture	22.9	0.0	22.9
Street Side	Lumens	10369.8	0.0	10369.8
	% Fixture	77.1	0.0	77.1
Total	Lumens	13451.9	0.0	13451.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.7	1.4
10°-20°	577.2	4.3
20°-30°	975.2	7.2
30°-40°	1504.5	11.2
40°-50°	2297.6	17.1
50°-60°	3176.7	23.6
60°-70°	3210.3	23.9
70°-80°	1412.4	10.5
80°-90°	106.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	13451.9	100.0
0°-180°	13451.9	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1359205
CATALOG NUMBER: GSS-SB2C-730-U-T2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1049.5	7.8			
FM	(30°-60°)	5499.8	40.9			
FH	(60°-80°)	3766.6	28.0			G2/5000
FVH	(80°-90°)	53.9	0.4			G1/100
BL	(0°-30°)	694.6	5.2	B2/1000		
BM	(30°-60°)	1478.9	11.0	B2/2500		
BH	(60°-80°)	856.1	6.4	B2/1000		G2/1000
BVH	(80°-90°)	52.5	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2
Type II Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359205
CATALOG NUMBER: GSS-SB2C-730-U-T2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	79°	85°
0°	2006.4	2006.4	2006.4	2006.4	2006.4	2006.4	2006.4	2006.4	2006.4	*2006.4*	2006.4
2.5°	2099.5	2132.5	2132.5	2117.5	2111.5	2108.5	2087.5	2063.5	2054.4	*2039.4*	2030.4
5°	2228.7	2228.7	2234.7	2219.6	2228.7	2216.6	2186.6	2156.6	2120.5	*2093.5*	2081.5
7.5°	2240.7	2264.7	2279.7	2279.7	2297.7	2300.7	2285.7	2252.7	2207.6	*2165.6*	2144.6
10°	2252.7	2273.7	2273.7	2297.7	2336.8	2366.8	2375.8	2363.8	2291.7	*2261.7*	2219.6
12.5°	2225.7	2249.7	2258.7	2306.7	2360.8	2417.9	2459.9	2465.9	2420.9	*2366.8*	2303.7
15°	2132.5	2153.6	2189.6	2261.7	2357.8	2444.9	2526.0	2571.1	2520.0	*2481.0*	2393.9
17.5°	2006.4	2018.4	2078.5	2171.6	2303.7	2450.9	2592.1	2679.2	2667.2	*2616.1*	2514.0
20°	1994.4	2006.4	2024.4	2093.5	2246.7	2429.9	2634.1	2802.3	2835.4	*2757.3*	2631.1
22.5°	2096.5	2108.5	2108.5	2117.5	2213.6	2411.9	2676.2	2934.5	3009.6	*2943.5*	2781.3
25°	2237.7	2261.7	2234.7	2213.6	2246.7	2423.9	2700.2	3084.7	3231.9	*3150.8*	2949.5
27.5°	2438.9	2435.9	2411.9	2348.8	2339.8	2459.9	2766.3	3201.8	3445.1	*3361.0*	3123.7
30°	2718.2	2733.3	2679.2	2547.0	2487.0	2541.0	2856.4	3297.9	3670.4	*3601.3*	3288.9
32.5°	3033.6	3027.6	2961.5	2835.4	2688.2	2673.2	2940.5	3400.1	3928.7	*3841.6*	3496.2
35°	3373.0	3367.0	3346.0	3129.7	2937.5	2856.4	3075.7	3517.2	4229.0	*4157.0*	3739.5
37.5°	3679.4	3706.4	3769.5	3421.1	3216.8	3096.7	3249.9	3712.4	4613.5	*4508.4*	4033.8
40°	3940.7	3988.8	4048.8	3733.4	3478.1	3376.0	3481.1	4030.8	5025.0	*4961.9*	4388.2
42.5°	4181.0	4214.0	4208.0	4015.8	3796.5	3682.4	3772.5	4361.2	5556.6	*5511.6*	4823.7
45°	4475.3	4511.4	4496.4	4313.1	4093.9	3991.8	4153.9	4748.7	6061.2	*6067.2*	5235.2
47.5°	4763.7	4799.7	4790.7	4622.5	4412.3	4328.2	4550.4	5205.2	6547.8	*6628.9*	5682.8
50°	5034.0	5067.0	5085.1	4979.9	4796.7	4706.6	4937.9	5634.7	7019.4	*7202.6*	6109.3
52.5°	5109.1	5151.1	5274.3	5313.3	5232.2	5124.1	5292.3	6046.2	7424.8	*7698.2*	6520.8
55°	4862.8	4934.9	5199.2	5397.4	5637.7	5649.7	5661.7	6445.7	7779.3	*8145.7*	6896.2
57.5°	4433.3	4445.3	4754.7	5157.1	5727.8	6238.4	6298.5	6911.2	8124.7	*8581.2*	7268.7
60°	3481.1	3418.1	3919.7	4601.5	5403.4	6472.7	7313.7	7632.1	8554.2	*9106.8*	7716.2
62.5°	1865.2	1871.2	2285.7	3132.7	4475.3	6244.4	8184.8	8707.4	9181.9	*9788.7*	8380.0
65°	1171.4	1216.4	1450.7	1826.2	2709.2	4961.9	8238.8	10137.1	10176.1	*10779.8*	9212.0
67.5°	*856.0*	*868.0*	*1066.3*	*1339.6*	*1552.8*	*2910.5*	*6631.9*	*10155.1*	*10894.0*	*11476.7*	*9566.4*
70°	636.8	642.8	783.9	1009.2	1132.3	1363.6	4226.0	8788.5	10521.5	*10809.9*	8680.3
72.5°	465.6	468.6	543.6	741.9	892.1	811.0	1985.4	6331.5	9136.9	*9650.5*	7809.3
75°	327.4	333.4	387.5	513.6	600.7	564.7	756.9	3958.7	6559.8	*6502.7*	5454.5
77.5°	246.3	249.3	285.3	363.4	408.5	369.4	426.5	1850.2	2342.8	*2114.5*	1721.1
80°	180.2	189.2	207.2	228.3	273.3	237.3	240.3	519.6	564.7	*495.6*	444.5
82.5°	96.1	108.1	138.2	138.2	159.2	141.2	126.2	231.3	243.3	*228.3*	198.2
85°	30.0	30.0	33.0	42.1	63.1	63.1	63.1	78.1	81.1	*81.1*	69.1
87.5°	6.0	6.0	6.0	6.0	9.0	12.0	18.0	24.0	27.0	*30.0*	30.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359205
CATALOG NUMBER: GSS-SB2C-730-U-T2

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2006.4	2006.4	2006.4	2006.4	2006.4	2006.4	2006.4	2006.4	2006.4	2006.4	2006.4
2.5°	2024.4	2003.4	1982.4	1946.3	1928.3	1901.3	1877.2	1865.2	1856.2	1853.2	1853.2
5°	2063.5	2030.4	1964.3	1901.3	1844.2	1793.1	1754.1	1724.1	1706.0	1691.0	1691.0
7.5°	2102.5	2057.5	1958.3	1847.2	1766.1	1703.0	1649.0	1630.9	1624.9	1609.9	1600.9
10°	2168.6	2096.5	1949.3	1790.1	1676.0	1621.9	1597.9	1591.9	1594.9	1597.9	1597.9
12.5°	2219.6	2141.6	1925.3	1718.0	1606.9	1576.9	1579.9	1594.9	1618.9	1615.9	1609.9
15°	2291.7	2174.6	1877.2	1633.9	1552.8	1552.8	1582.9	1615.9	1640.0	1655.0	1646.0
17.5°	2375.8	2213.6	1805.2	1555.9	1507.8	1534.8	1597.9	1630.9	1673.0	1682.0	1676.0
20°	2481.0	2246.7	1724.1	1480.8	1477.8	1534.8	1588.9	1637.0	1670.0	1679.0	1685.0
22.5°	2583.1	2276.7	1618.9	1426.7	1444.7	1516.8	1567.9	1618.9	1633.9	1643.0	1646.0
25°	2688.2	2306.7	1522.8	1384.6	1420.7	1492.8	1534.8	1555.9	1558.9	1552.8	1552.8
27.5°	2802.3	2309.8	1426.7	1351.6	1393.7	1456.7	1480.8	1486.8	1474.8	1432.7	1420.7
30°	2922.5	2279.7	1348.6	1321.6	1363.6	1414.7	1432.7	1414.7	1372.6	1312.6	1306.6
32.5°	3021.6	2234.7	1291.5	1285.5	1330.6	1375.6	1375.6	1342.6	1279.5	1219.5	1216.4
35°	3171.8	2171.6	1234.5	1261.5	1300.5	1321.6	1327.6	1279.5	1210.4	1153.4	1147.4
37.5°	3319.0	2117.5	1210.4	1231.5	1267.5	1285.5	1267.5	1219.5	1174.4	1126.3	1126.3
40°	3547.2	2084.5	1180.4	1210.4	1240.5	1243.5	1210.4	1174.4	1180.4	1153.4	1150.4
42.5°	3796.5	2081.5	1168.4	1189.4	1210.4	1204.4	1156.4	1156.4	1165.4	1114.3	1102.3
45°	4081.9	2123.5	1168.4	1159.4	1171.4	1153.4	1126.3	1120.3	1099.3	1024.2	1021.2
47.5°	4379.2	2225.7	1174.4	1117.3	1114.3	1108.3	1096.3	1075.3	1012.2	949.1	940.1
50°	4613.5	2366.8	1192.4	1063.3	1051.3	1072.3	1051.3	1015.2	943.1	883.1	874.0
52.5°	4892.8	2508.0	1180.4	997.2	982.2	1036.2	1015.2	964.1	910.1	874.0	865.0
55°	5187.2	2655.2	1132.3	907.1	919.1	991.2	985.2	928.1	862.0	814.0	808.0
57.5°	5481.5	2841.4	1051.3	829.0	874.0	964.1	940.1	871.0	826.0	792.9	786.9
60°	5932.1	3108.7	934.1	747.9	829.0	907.1	868.0	847.0	799.0	771.9	756.9
62.5°	6514.8	3553.2	780.9	672.8	765.9	838.0	835.0	811.0	768.9	738.9	729.9
65°	7343.7	3976.7	639.8	600.7	684.8	753.9	789.9	768.9	726.9	693.8	690.8
67.5°	*7502.9*	*3553.2*	*531.6*	*525.6*	*594.7*	*672.8*	*741.9*	*726.9*	*660.8*	*618.7*	*612.7*
70°	6529.8	2538.0	447.5	453.5	519.6	588.7	663.8	627.7	573.7	549.7	546.7
72.5°	5796.9	2180.6	375.4	387.5	435.5	498.6	543.6	555.7	516.6	495.6	486.6
75°	4178.0	1633.9	303.4	318.4	351.4	387.5	471.6	492.6	456.5	435.5	420.5
77.5°	1549.8	681.8	225.3	240.3	264.3	315.4	381.5	426.5	399.5	414.5	372.4
80°	372.4	240.3	165.2	162.2	186.2	237.3	303.4	336.4	309.4	294.4	255.3
82.5°	162.2	117.1	108.1	108.1	114.1	156.2	201.2	237.3	231.3	192.2	183.2
85°	60.1	51.1	51.1	54.1	54.1	72.1	108.1	126.2	114.1	99.1	96.1
87.5°	27.0	27.0	21.0	18.0	15.0	15.0	18.0	12.0	9.0	6.0	6.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)