Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1365360

Luminaire Tested: **GSS-SB5B-730-U-SLL-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1365360
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB5B-730-U-SLL-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 5SQUARE 184W 70CRI 3000K FIXTURE w/ 90° Spill Light Eliminator LETT OPTIC OPTIC AND HOUSE SIDE SHIELD
Light Source:	(130) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	20724.8 lumens
Efficiency:	N/A
Efficacy:	112.6 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	184
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	11.1%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365360
CATALOG NUMBER: GSS-SB5B-730-U-SLL-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 13.1 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365360
CATALOG NUMBER: GSS-SB5B-730-U-SLL-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1365360
CATALOG NUMBER: GSS-SB5B-730-U-SLL-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4662.0	0.0	4662.0
	% Fixture	22.5	0.0	22.5
Street Side	Lumens	16062.8	0.0	16062.8
	% Fixture	77.5	0.0	77.5
Total	Lumens	20724.8	0.0	20724.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	344.1	1.7
10°-20°	951.7	4.6
20°-30°	1363.1	6.6
30°-40°	1709.9	8.3
40°-50°	2808.8	13.6
50°-60°	5071.3	24.5
60°-70°	5629.9	27.2
70°-80°	2544.8	12.3
80°-90°	301.2	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	20724.8	100.0
0°-180°	20724.8	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1365360
CATALOG NUMBER: GSS-SB5B-730-U-SLL-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1497.2	7.2			
FM	(30°-60°)	6981.4	33.7			
FH	(60°-80°)	7325.6	35.3			G3/7500
FVH	(80°-90°)	258.6	1.2			G3/500
BL	(0°-30°)	1161.8	5.6	B3/2500		
BM	(30°-60°)	2608.5	12.6	B3/5000		
BH	(60°-80°)	849.2	4.1	B2/1000		G2/1000
BVH	(80°-90°)	42.6	0.2			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365360
CATALOG NUMBER: GSS-SB5B-730-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5
2.5°	3943.0	3993.8	3987.5	4057.4	4121.0	4165.5	4203.7	4191.0	4159.2	4095.6	4051.1
5°	4356.3	4394.5	4458.1	4591.6	4693.4	4782.4	4769.7	4782.4	4687.0	4591.6	4477.2
7.5°	4712.5	4757.0	4846.0	5036.8	5164.0	5272.1	5259.4	5221.2	5113.1	4954.1	4782.4
10°	4935.0	4966.8	5062.2	5278.5	5424.7	5513.8	5482.0	5418.4	5278.5	5119.5	4916.0
12.5°	5030.4	5068.6	5151.3	5323.0	5418.4	5399.3	5386.6	5373.9	5303.9	5183.1	4998.6
15°	5043.2	5068.6	5132.2	5208.5	5170.4	5062.2	5036.8	5132.2	5221.2	5195.8	5043.2
17.5°	5043.2	5081.3	5094.0	5017.7	4820.6	4623.4	4598.0	4757.0	5005.0	5202.2	5113.1
20°	5062.2	5081.3	5055.9	4807.9	4439.0	4222.8	4178.3	4375.4	4744.3	5132.2	5183.1
22.5°	5087.7	5106.8	4998.6	4559.8	4127.4	3898.4	3873.0	4019.3	4451.7	5030.4	5259.4
25°	5138.6	5125.8	4960.5	4343.6	3853.9	3637.7	3599.5	3790.3	4210.1	4928.7	5386.6
27.5°	5202.2	5144.9	4909.6	4165.5	3656.8	3427.8	3402.4	3586.8	4006.5	4801.5	5494.7
30°	5284.8	5227.6	4903.3	4025.6	3510.5	3281.6	3249.8	3453.3	3866.6	4712.5	5647.3
32.5°	5399.3	5316.6	4909.6	3917.5	3427.8	3211.6	3192.5	3408.7	3809.4	4661.6	5806.3
35°	5551.9	5431.1	4935.0	3879.4	3453.3	3307.0	3351.5	3516.9	3866.6	4699.7	6067.1
37.5°	5742.7	5628.2	5062.2	3962.0	3733.1	3834.8	3949.3	4012.9	4140.1	4877.8	6486.8
40°	6060.7	5901.7	5253.0	4229.1	4483.5	4960.5	5183.1	5157.6	4865.1	5284.8	7078.2
42.5°	6505.9	6359.6	5641.0	4909.6	5736.4	6747.5	7122.7	6906.5	6022.5	5933.5	8051.3
45°	7186.3	6944.7	6162.5	5920.8	7249.9	8909.8	9755.6	9011.6	7491.6	6957.4	9437.6
47.5°	8057.6	7815.9	6976.5	6932.0	8941.6	11580.8	12585.6	11122.9	8948.0	8299.3	11097.5
50°	9456.7	9189.6	8172.1	7962.2	10811.3	14245.5	15587.4	13228.0	10429.7	9723.8	13145.3
52.5°	11377.3	11199.3	10067.2	9024.3	12483.9	17183.6	18341.1	15428.4	11574.5	11351.9	15377.5
55°	14054.7	13883.0	12534.8	10207.2	14067.4	20128.1	21063.0	17431.7	12572.9	13259.8	17711.5
57.5°	17088.2	17374.4	15911.7	11784.3	15733.6	22500.3	23804.0	19250.5	13921.2	15810.0	20306.2
60°	19066.1	19969.1	19784.7	14538.0	18322.0	25451.1	26869.3	21686.2	15892.6	17686.0	20249.0
62.5°	17349.0	18252.0	19663.9	17730.6	20815.0	28122.1	29317.7	24249.1	17851.4	16191.5	17005.6
65°	14722.5	15848.1	17336.3	15402.9	20376.2	28204.8	29432.2	24344.5	16655.8	11968.8	12057.8
67.5°	12687.4	13685.9	15517.4	13107.1	18061.3	25686.4	26653.1	21718.0	13768.5	7936.8	7866.8
70°	10588.7	11504.5	13819.4	11669.9	15822.7	22137.8	21304.7	18258.4	11638.1	5272.1	4369.0
72.5°	9024.3	9870.1	12280.4	10487.0	12553.8	17940.4	14684.3	15148.6	9469.4	3351.5	2976.3
75°	7466.2	8242.0	10442.5	9494.9	10385.2	11192.9	10149.9	10760.4	7803.2	2842.7	2295.8
77.5°	5240.3	5723.6	7326.3	7555.2	8083.0	6626.7	6435.9	7536.1	5551.9	1411.8	966.7
80°	2582.0	2880.9	3822.1	4496.2	3822.1	3758.5	4286.4	5017.7	2880.9	864.9	534.2
82.5°	1157.4	1373.7	1761.6	2721.9	1380.0	1500.9	1895.2	2671.0	1310.1	515.1	228.9
85°	184.4	203.5	343.4	457.9	375.2	578.7	553.3	521.5	279.8	139.9	63.6
87.5°	6.4	6.4	6.4	12.7	19.1	25.4	31.8	31.8	31.8	31.8	31.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365360
CATALOG NUMBER: GSS-SB5B-730-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5
2.5°	4038.3	4019.3	3923.9	3828.5	3745.8	3663.1	3580.5	3466.0	3376.9	3300.6	3268.8
5°	4419.9	4318.2	4171.9	4012.9	3873.0	3714.0	3561.4	3389.7	3249.8	3103.5	3027.2
7.5°	4680.7	4578.9	4337.2	4095.6	3923.9	3752.2	3593.2	3402.4	3218.0	3008.1	2893.6
10°	4801.5	4687.0	4426.3	4146.5	3936.6	3764.9	3618.6	3459.6	3275.2	3014.4	2861.8
12.5°	4884.2	4744.3	4445.4	4159.2	3949.3	3771.2	3631.3	3516.9	3408.7	3154.4	2976.3
15°	4935.0	4807.9	4496.2	4165.5	3930.2	3720.4	3586.8	3548.7	3567.7	3446.9	3230.7
17.5°	5011.4	4890.5	4559.8	4203.7	3898.4	3612.3	3466.0	3548.7	3720.4	3758.5	3586.8
20°	5113.1	4985.9	4642.5	4235.5	3803.0	3408.7	3268.8	3478.7	3764.9	3962.0	3866.6
22.5°	5227.6	5125.8	4737.9	4267.3	3663.1	3141.6	3078.0	3332.4	3637.7	3892.1	3898.4
25°	5367.5	5272.1	4871.5	4299.1	3472.3	2912.7	2925.4	3141.6	3383.3	3644.0	3688.6
27.5°	5558.3	5469.3	5036.8	4337.2	3275.2	2728.3	2791.9	2950.9	3116.2	3275.2	3338.8
30°	5768.2	5698.2	5233.9	4413.6	3090.8	2620.2	2658.3	2766.4	2900.0	2995.4	3027.2
32.5°	6054.3	5939.9	5418.4	4407.2	2950.9	2569.3	2531.1	2562.9	2671.0	2766.4	2772.8
35°	6410.5	6321.4	5609.2	4292.7	2823.7	2543.8	2410.3	2391.2	2454.8	2550.2	2543.8
37.5°	6932.0	6855.6	5920.8	4114.7	2664.7	2480.2	2283.1	2219.5	2264.0	2327.6	2346.7
40°	7714.2	7517.0	6276.9	3917.5	2505.7	2365.8	2130.5	2041.4	2073.2	2143.2	2155.9
42.5°	8776.2	8401.0	6753.9	3650.4	2353.1	2194.1	1977.8	1882.4	1901.5	1965.1	1977.8
45°	10137.2	9571.2	7408.9	3370.6	2232.2	2016.0	1818.8	1717.1	1736.2	1806.1	1837.9
47.5°	11727.1	10951.2	8095.8	3071.7	2162.3	1876.1	1659.9	1583.5	1628.1	1698.0	1710.7
50°	13603.2	12820.9	8534.6	2830.0	2117.7	1768.0	1513.6	1481.8	1539.0	1596.3	1609.0
52.5°	15651.0	14538.0	8254.8	2632.9	2079.6	1729.8	1411.8	1424.5	1469.1	1526.3	1545.4
55°	17641.5	15167.6	7326.3	2378.5	2035.1	1755.2	1335.5	1367.3	1424.5	1469.1	1481.8
57.5°	18938.9	14639.8	5901.7	2111.4	1984.2	1774.3	1297.4	1322.8	1386.4	1437.3	1443.6
60°	17806.9	13482.3	4419.9	1882.4	1876.1	1742.5	1284.6	1246.5	1335.5	1380.0	1386.4
62.5°	14588.9	11027.5	2823.7	1666.2	1672.6	1672.6	1278.3	1119.3	1233.8	1271.9	1265.6
65°	*10022.7*	*7796.9*	*1748.9*	*1361.0*	*1424.5*	*1519.9*	*1240.1*	*985.7*	*1119.3*	*1157.4*	*1144.7*
67.5°	6588.5	4954.1	1081.1	1049.3	1170.2	1316.4	1163.8	884.0	1004.8	1030.3	992.1
70°	3574.1	2334.0	712.3	686.8	915.8	1036.6	985.7	794.9	896.7	922.1	884.0
72.5°	2359.4	1341.9	502.4	502.4	718.6	725.0	807.7	712.3	794.9	820.4	782.2
75°	1774.3	864.9	349.8	387.9	457.9	566.0	578.7	597.8	674.1	705.9	667.8
77.5°	814.0	318.0	209.9	286.2	318.0	432.5	368.9	445.2	502.4	515.1	483.3
80°	470.6	178.1	139.9	184.4	203.5	356.1	216.2	267.1	356.1	375.2	337.1
82.5°	197.1	89.0	95.4	114.5	120.8	197.1	152.6	171.7	235.3	228.9	203.5
85°	57.2	57.2	63.6	70.0	70.0	114.5	108.1	101.8	108.1	108.1	89.0
87.5°	38.2	38.2	38.2	44.5	44.5	50.9	57.2	63.6	63.6	63.6	57.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365360
CATALOG NUMBER: GSS-SB5B-730-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5
2.5°	3224.3	3167.1	3084.4	3071.7	3027.2	2995.4	3027.2	3059.0	3116.2	3122.6	3148.0
5°	2957.2	2823.7	2721.9	2607.4	2550.2	2543.8	2531.1	2569.3	2652.0	2702.8	2741.0
7.5°	2779.1	2537.5	2359.4	2200.4	2143.2	2098.7	2136.8	2130.5	2238.6	2283.1	2321.3
10°	2683.8	2346.7	2079.6	1882.4	1806.1	1761.6	1755.2	1768.0	1831.6	1876.1	1920.6
12.5°	2747.3	2270.4	1876.1	1647.1	1564.5	1513.6	1469.1	1469.1	1481.8	1539.0	1558.1
15°	2957.2	2314.9	1780.7	1532.7	1424.5	1341.9	1284.6	1240.1	1246.5	1252.8	1271.9
17.5°	3262.5	2429.4	1748.9	1462.7	1348.2	1246.5	1189.2	1138.4	1125.6	1125.6	1119.3
20°	3555.0	2518.4	1723.5	1405.5	1259.2	1170.2	1119.3	1074.8	1055.7	1055.7	1055.7
22.5°	3675.8	2594.7	1691.7	1335.5	1170.2	1087.5	1043.0	1011.2	1004.8	1004.8	998.5
25°	3580.5	2569.3	1653.5	1265.6	1087.5	1023.9	985.7	953.9	947.6	953.9	947.6
27.5°	3281.6	2480.2	1602.6	1208.3	1023.9	966.7	934.9	903.1	896.7	903.1	903.1
30°	2963.6	2327.6	1519.9	1163.8	973.0	909.4	877.6	845.8	845.8	852.2	858.5
32.5°	2709.2	2175.0	1424.5	1106.6	915.8	858.5	826.7	794.9	794.9	807.7	807.7
35°	2493.0	2054.2	1329.2	1049.3	864.9	801.3	775.9	750.4	744.1	756.8	763.2
37.5°	2321.3	1946.0	1227.4	992.1	814.0	756.8	731.4	699.6	693.2	705.9	718.6
40°	2143.2	1825.2	1138.4	922.1	763.2	705.9	680.5	642.3	642.3	655.0	667.8
42.5°	1971.5	1717.1	1081.1	858.5	712.3	648.7	623.2	591.4	591.4	604.2	616.9
45°	1831.6	1615.3	1049.3	794.9	655.0	597.8	566.0	540.6	546.9	559.6	572.4
47.5°	1698.0	1507.2	1055.7	763.2	616.9	540.6	508.8	489.7	502.4	521.5	534.2
50°	1596.3	1430.9	1062.1	712.3	566.0	496.0	464.3	451.5	470.6	489.7	502.4
52.5°	1532.7	1354.6	1023.9	648.7	527.8	451.5	432.5	432.5	451.5	464.3	477.0
55°	1469.1	1227.4	941.2	578.7	489.7	419.7	407.0	407.0	426.1	438.8	445.2
57.5°	1418.2	1093.9	845.8	521.5	445.2	387.9	387.9	387.9	394.3	400.7	413.4
60°	1322.8	953.9	725.0	477.0	400.7	362.5	356.1	356.1	349.8	356.1	375.2
62.5°	1157.4	801.3	616.9	426.1	362.5	330.7	324.3	305.3	286.2	292.5	305.3
65°	*979.4*	*636.0*	*515.1*	*368.9*	*311.6*	*292.5*	*286.2*	*254.4*	*228.9*	*235.3*	*254.4*
67.5°	782.2	477.0	432.5	318.0	267.1	248.0	248.0	228.9	209.9	209.9	222.6
70°	610.5	400.7	324.3	254.4	209.9	209.9	222.6	203.5	178.1	178.1	197.1
72.5°	496.0	324.3	260.7	197.1	165.3	178.1	184.4	165.3	146.3	146.3	159.0
75°	387.9	254.4	203.5	146.3	127.2	133.6	146.3	133.6	114.5	120.8	127.2
77.5°	267.1	171.7	133.6	108.1	95.4	101.8	101.8	95.4	89.0	89.0	95.4
80°	178.1	114.5	89.0	76.3	70.0	70.0	63.6	63.6	70.0	70.0	76.3
82.5°	127.2	82.7	70.0	57.2	44.5	44.5	50.9	50.9	57.2	57.2	63.6
85°	76.3	57.2	50.9	38.2	31.8	38.2	38.2	44.5	50.9	50.9	57.2
87.5°	57.2	44.5	38.2	31.8	25.4	25.4	31.8	31.8	38.2	44.5	44.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365360
CATALOG NUMBER: GSS-SB5B-730-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5	3580.5
2.5°	3211.6	3287.9	3396.0	3491.4	3605.9	3720.4	3828.5	3930.2	3936.6	3943.0
5°	2861.8	3014.4	3192.5	3408.7	3637.7	3860.3	4095.6	4286.4	4330.9	4356.3
7.5°	2473.9	2696.5	2969.9	3275.2	3618.6	3962.0	4292.7	4578.9	4687.0	4712.5
10°	2066.9	2340.3	2671.0	3065.3	3529.6	3987.5	4432.6	4782.4	4909.6	4935.0
12.5°	1704.4	1927.0	2308.5	2785.5	3345.1	3949.3	4483.5	4871.5	4998.6	5030.4
15°	1392.8	1602.6	1958.8	2461.2	3090.8	3815.8	4445.4	4890.5	5017.7	5043.2
17.5°	1151.1	1284.6	1609.0	2155.9	2861.8	3644.0	4394.5	4903.3	5024.1	5043.2
20°	1055.7	1081.1	1252.8	1787.0	2620.2	3516.9	4362.7	4922.3	5043.2	5062.2
22.5°	1011.2	1011.2	1049.3	1361.0	2283.1	3383.3	4350.0	4979.6	5068.6	5087.7
25°	966.7	966.7	979.4	1068.4	1882.4	3218.0	4375.4	5081.3	5138.6	5138.6
27.5°	922.1	922.1	934.9	953.9	1399.1	2944.5	4381.8	5195.8	5221.2	5202.2
30°	877.6	890.3	890.3	903.1	1030.3	2601.1	4343.6	5323.0	5323.0	5284.8
32.5°	833.1	839.5	852.2	858.5	896.7	2155.9	4280.0	5482.0	5450.2	5399.3
35°	794.9	801.3	801.3	814.0	852.2	1723.5	4210.1	5698.2	5609.2	5551.9
37.5°	744.1	750.4	756.8	769.5	807.7	1367.3	4108.3	5882.6	5819.0	5742.7
40°	699.6	705.9	712.3	725.0	763.2	1176.5	3981.1	6162.5	6149.7	6060.7
42.5°	648.7	661.4	667.8	674.1	725.0	1074.8	3892.1	6614.0	6614.0	6505.9
45°	604.2	616.9	616.9	629.6	699.6	985.7	4089.2	7237.2	7288.1	7186.3
47.5°	566.0	572.4	572.4	578.7	661.4	909.4	4617.1	8191.2	8127.6	8057.6
50°	527.8	540.6	527.8	534.2	629.6	953.9	5488.3	9412.2	9577.6	9456.7
52.5°	502.4	508.8	483.3	483.3	585.1	1011.2	6200.6	10970.3	11523.6	11377.3
55°	470.6	477.0	445.2	445.2	515.1	877.6	6245.1	12744.6	13959.3	14054.7
57.5°	438.8	438.8	413.4	407.0	445.2	712.3	5539.2	14118.3	16872.0	17088.2
60°	400.7	394.3	381.6	368.9	407.0	655.0	4222.8	13933.9	18315.6	19066.1
62.5°	343.4	356.1	349.8	324.3	368.9	610.5	2753.7	12057.8	16687.6	17349.0
65°	*286.2*	*305.3*	*305.3*	*286.2*	*407.0*	*534.2*	*1450.0*	*9653.9*	*13927.5*	*14722.5*
67.5°	254.4	267.1	260.7	248.0	362.5	337.1	699.6	7402.6	11924.2	12687.4
70°	222.6	235.3	216.2	203.5	292.5	241.7	413.4	4954.1	9844.7	10588.7
72.5°	184.4	197.1	178.1	159.0	216.2	184.4	273.5	3224.3	8197.5	9024.3
75°	152.6	159.0	146.3	127.2	159.0	146.3	190.8	2105.0	6855.6	7466.2
77.5°	108.1	120.8	114.5	95.4	114.5	101.8	133.6	1202.0	4782.4	5240.3
80°	82.7	82.7	82.7	76.3	70.0	70.0	89.0	540.6	2321.3	2582.0
82.5°	70.0	70.0	63.6	57.2	50.9	44.5	50.9	159.0	1093.9	1157.4
85°	63.6	50.9	44.5	38.2	31.8	19.1	19.1	44.5	222.6	184.4
87.5°	38.2	31.8	25.4	12.7	6.4	6.4	0.0	6.4	6.4	6.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)