Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1363053

Luminaire Tested: **GSS-SB4C-730-U-SL2-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1363053
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4C-730-U-SL2-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 204W 70CRI 3000K FIXTURE w/ TYPE II SPILL CONTROL DISTRIBUTION OPTIC AND HOUSE SIDE SHIELD
Light Source:	(104) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	23963.7 lumens
Efficiency:	N/A
Efficacy:	117.5 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type II - Medium
BUG Rating:	B2 - U0 - G3


Input Watts (W):	204
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363053
CATALOG NUMBER: GSS-SB4C-730-U-SL2-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 13.7 fc
Type II - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363053
CATALOG NUMBER: GSS-SB4C-730-U-SL2-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1363053
CATALOG NUMBER: GSS-SB4C-730-U-SL2-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3223.2	0.0	3223.2
	% Fixture	13.5	0.0	13.5
Street Side	Lumens	20740.5	0.0	20740.5
	% Fixture	86.5	0.0	86.5
Total	Lumens	23963.7	0.0	23963.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	417.7	1.7
10°-20°	1034.8	4.3
20°-30°	1716.5	7.2
30°-40°	2736.3	11.4
40°-50°	4175.9	17.4
50°-60°	5560.2	23.2
60°-70°	5190.3	21.7
70°-80°	2935.1	12.2
80°-90°	196.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	23963.7	100.0
0°-180°	23963.7	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1363053
CATALOG NUMBER: GSS-SB4C-730-U-SL2-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2382.9	9.9			
FM	(30°-60°)	10977.3	45.8			
FH	(60°-80°)	7205.5	30.1			G3/7500
FVH	(80°-90°)	174.8	0.7			G2/225
BL	(0°-30°)	786.2	3.3	B2/1000		
BM	(30°-60°)	1495.0	6.2	B2/2500		
BH	(60°-80°)	920.0	3.8	B2/1000		G2/1000
BVH	(80°-90°)	22.0	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3
Type II Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363053
CATALOG NUMBER: GSS-SB4C-730-U-SL2-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	78°	85°
0°	4578.6	4578.6	4578.6	4578.6	4578.6	4578.6	4578.6	4578.6	4578.6	*4578.6*	4578.6
2.5°	5155.9	5082.1	5082.1	5048.5	5014.9	4954.5	4880.7	4800.1	4733.0	*4699.4*	4645.7
5°	5525.1	5505.0	5498.3	5444.6	5390.9	5303.6	5209.6	5055.2	4914.2	*4867.2*	4746.4
7.5°	5511.7	5498.3	5525.1	5592.3	5639.3	5605.7	5525.1	5337.2	5115.6	*5035.1*	4853.8
10°	5095.5	5055.2	5149.2	5296.9	5511.7	5733.3	5766.8	5585.6	5303.6	*5209.6*	4954.5
12.5°	4719.5	4719.5	4766.5	4900.8	5169.3	5565.4	5874.2	5813.8	5491.6	*5377.4*	5041.8
15°	4672.5	4639.0	4652.4	4712.8	4900.8	5290.2	5807.1	5988.4	5666.1	*5511.7*	5122.3
17.5°	4887.4	4847.1	4813.5	4786.7	4813.5	5068.6	5599.0	6136.1	5874.2	*5706.4*	5229.8
20°	5223.0	5223.0	5135.8	5028.3	4941.1	4988.1	5431.2	6230.1	6122.6	*5941.4*	5390.9
22.5°	5706.4	5646.0	5592.3	5424.4	5209.6	5108.9	5357.3	6330.8	6465.0	*6243.5*	5612.4
25°	6109.2	6129.4	6068.9	5860.8	5558.7	5337.2	5417.7	6371.0	6854.4	*6632.9*	5887.7
27.5°	6565.7	6545.6	6491.9	6283.8	5934.7	5619.1	5585.6	6451.6	7304.2	*7069.2*	6209.9
30°	6988.7	6988.7	6921.5	6686.6	6330.8	5988.4	5834.0	6585.9	7754.0	*7539.2*	6572.4
32.5°	7458.6	7465.3	7331.1	7082.7	6720.1	6330.8	6149.5	6787.3	8311.2	*8150.1*	7062.5
35°	7841.3	7854.7	7821.1	7552.6	7075.9	6686.6	6478.4	7102.8	8962.4	*8868.4*	7713.7
37.5°	8136.7	8156.8	8089.7	7968.8	7525.7	7028.9	6827.5	7492.2	9747.9	*9808.3*	8559.6
40°	8479.0	8479.0	8479.0	8297.8	7968.8	7404.9	7183.4	7975.5	10593.8	*10781.7*	9499.5
42.5°	8781.2	8801.3	8834.9	8693.9	8391.8	7942.0	7619.7	8519.3	11540.4	*11963.3*	10660.9
45°	8935.6	8975.8	9096.7	9036.3	8808.0	8371.6	8083.0	9049.7	12580.9	*13104.6*	11909.6
47.5°	9029.5	9076.5	9237.7	9311.5	9217.5	8700.6	8519.3	9680.7	13574.5	*14299.6*	13191.9
50°	9103.4	9170.5	9351.8	9492.8	9580.0	8975.8	8949.0	10325.2	14568.1	*15420.7*	14360.0
52.5°	8888.6	8955.7	9298.1	9747.9	9821.7	9392.1	9398.8	11023.4	15575.1	*16562.0*	15440.9
55°	8123.2	8170.2	8646.9	9553.2	10110.4	9875.4	10009.7	11929.7	16676.1	*17696.6*	16474.7
57.5°	5780.3	6068.9	6914.8	8351.5	9754.6	10566.9	10989.9	12930.0	17958.4	*18938.6*	17522.0
60°	2403.4	2611.5	3430.6	5961.5	8438.8	10660.9	12339.3	14574.8	19415.2	*20348.4*	18710.3
62.5°	1564.2	1584.4	1664.9	2557.8	5357.3	9351.8	12856.2	16904.4	21469.5	*21986.4*	19361.5
65°	1396.4	1423.2	1463.5	1591.1	1973.7	6310.6	11110.7	17689.9	23141.2	*23107.6*	18992.3
67.5°	1242.0	1275.5	1349.4	1362.8	1101.0	2322.8	7465.3	16535.1	24879.9	*25242.5*	19999.3
70°	*1060.7*	*1074.1*	*1208.4*	*1221.8*	*866.0*	*913.0*	*3759.5*	*14353.3*	*25524.4*	*26638.8*	*21288.2*
72.5°	738.5	778.8	1020.4	1074.1	691.5	590.8	1369.5	10446.1	23725.2	*25578.1*	21207.7
75°	436.4	456.5	584.1	731.8	537.1	416.2	617.6	6424.7	20415.5	*22154.3*	18871.4
77.5°	315.5	335.7	422.9	570.6	342.4	282.0	382.7	3356.7	14178.7	*14252.6*	10654.2
80°	100.7	114.1	261.8	382.7	248.4	181.3	235.0	1134.6	7163.2	*6760.4*	3256.0
82.5°	53.7	53.7	161.1	201.4	154.4	114.1	134.3	469.9	2296.0	*1470.2*	516.9
85°	26.9	26.9	67.1	80.6	60.4	53.7	67.1	167.8	241.7	*221.5*	147.7
87.5°	0.0	0.0	6.7	6.7	6.7	13.4	26.9	47.0	60.4	*60.4*	67.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363053
CATALOG NUMBER: GSS-SB4C-730-U-SL2-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	4578.6	4578.6	4578.6	4578.6	4578.6	4578.6	4578.6	4578.6	4578.6	4578.6	4578.6
2.5°	4585.3	4531.6	4451.0	4357.0	4289.9	4195.9	4115.3	4081.8	4021.3	4007.9	3994.5
5°	4632.3	4524.8	4343.6	4135.5	3954.2	3739.4	3564.8	3430.6	3336.6	3296.3	3276.1
7.5°	4706.1	4531.6	4236.2	3893.8	3564.8	3242.6	2920.3	2671.9	2531.0	2396.7	2403.4
10°	4746.4	4538.3	4095.2	3618.5	3128.5	2631.7	2148.3	1779.1	1584.4	1470.2	1443.4
12.5°	4780.0	4504.7	3934.1	3276.1	2578.0	1866.3	1383.0	1141.3	1040.6	1027.2	1020.4
15°	4800.1	4464.4	3732.7	2880.1	1953.6	1262.1	1027.2	960.0	933.2	926.5	926.5
17.5°	4847.1	4417.4	3524.5	2390.0	1356.1	1007.0	919.7	886.2	866.0	859.3	859.3
20°	4927.6	4424.1	3309.7	1852.9	1054.0	919.7	852.6	819.0	792.2	792.2	792.2
22.5°	5061.9	4451.0	3034.5	1389.7	926.5	839.2	778.8	738.5	725.0	731.8	731.8
25°	5243.2	4518.1	2752.5	1074.1	852.6	758.6	698.2	664.6	657.9	664.6	664.6
27.5°	5471.4	4592.0	2403.4	926.5	785.5	691.5	631.1	610.9	604.2	617.6	617.6
30°	5719.8	4679.3	1987.2	852.6	725.0	637.8	584.1	563.9	563.9	584.1	584.1
32.5°	6068.9	4820.2	1611.2	792.2	678.1	597.5	543.8	523.6	530.4	550.5	550.5
35°	6538.9	5001.5	1322.5	751.9	644.5	563.9	516.9	490.1	496.8	503.5	510.2
37.5°	7149.8	5249.9	1141.3	725.0	610.9	543.8	483.4	463.2	463.2	469.9	469.9
40°	7834.6	5545.3	1054.0	704.9	584.1	510.2	456.5	429.7	429.7	443.1	443.1
42.5°	8707.3	5860.8	986.9	678.1	550.5	483.4	422.9	402.8	396.1	409.5	409.5
45°	9714.3	6317.3	946.6	651.2	516.9	449.8	396.1	369.2	362.5	369.2	376.0
47.5°	10734.8	6800.7	906.3	617.6	496.8	422.9	376.0	342.4	335.7	335.7	335.7
50°	11694.8	7284.1	879.5	577.4	476.7	396.1	349.1	322.2	308.8	308.8	308.8
52.5°	12554.1	7733.9	866.0	543.8	456.5	376.0	335.7	302.1	282.0	282.0	282.0
55°	13373.1	8170.2	845.9	503.5	436.4	349.1	315.5	282.0	261.8	255.1	255.1
57.5°	14198.9	8573.0	792.2	463.2	396.1	329.0	295.4	261.8	241.7	228.3	228.3
60°	14876.9	8821.4	711.6	416.2	349.1	302.1	275.3	241.7	214.8	194.7	194.7
62.5°	14923.9	8566.3	590.8	369.2	308.8	275.3	248.4	214.8	181.3	154.4	154.4
65°	14125.0	7680.1	469.9	308.8	275.3	241.7	208.1	181.3	147.7	120.8	114.1
67.5°	14306.3	6968.5	362.5	261.8	241.7	194.7	167.8	147.7	120.8	100.7	100.7
70°	*14413.7*	*5484.9*	*288.7*	*214.8*	*201.4*	*154.4*	*134.3*	*127.6*	*100.7*	*80.6*	*80.6*
72.5°	13473.8	3397.0	235.0	181.3	154.4	107.4	107.4	100.7	80.6	60.4	53.7
75°	11882.7	2027.5	181.3	141.0	107.4	80.6	80.6	73.8	53.7	40.3	40.3
77.5°	7183.4	1067.4	141.0	107.4	73.8	60.4	53.7	47.0	33.6	26.9	20.1
80°	2222.1	376.0	107.4	73.8	53.7	47.0	33.6	20.1	13.4	13.4	6.7
82.5°	308.8	134.3	80.6	60.4	40.3	26.9	20.1	13.4	6.7	6.7	6.7
85°	107.4	73.8	53.7	40.3	26.9	20.1	13.4	6.7	6.7	0.0	0.0
87.5°	60.4	53.7	40.3	26.9	20.1	13.4	13.4	6.7	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)