Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360749

Luminaire Tested: **GSS-SB4C-730-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360749
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4C-730-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 204W 70CRI 3000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(104) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	28578.1 lumens
Efficiency:	N/A
Efficacy:	140.1 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	204
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360749
CATALOG NUMBER: GSS-SB4C-730-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 14.1 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360749
CATALOG NUMBER: GSS-SB4C-730-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360749
CATALOG NUMBER: GSS-SB4C-730-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	14289.1	0.0	14289.1
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	14289.1	0.0	14289.1
	% Fixture	50.0	0.0	50.0
Total	Lumens	28578.1	0.0	28578.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	545.0	1.9
10°-20°	1661.1	5.8
20°-30°	2776.3	9.7
30°-40°	3828.7	13.4
40°-50°	4693.5	16.4
50°-60°	5500.2	19.2
60°-70°	6107.8	21.4
70°-80°	3321.5	11.6
80°-90°	143.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	28578.1	100.0
0°-180°	28578.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360749
CATALOG NUMBER: GSS-SB4C-730-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2491.2	8.7			
FM	(30°-60°)	7011.2	24.5			
FH	(60°-80°)	4714.7	16.5			G2/5000
FVH	(80°-90°)	72.0	0.3			G1/100
BL	(0°-30°)	2491.2	8.7	B3/2500		
BM	(30°-60°)	7011.2	24.5	B4/8500		
BH	(60°-80°)	4714.7	16.5	B4/5000		G4/5000
BVH	(80°-90°)	72.0	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360749
CATALOG NUMBER: GSS-SB4C-730-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	5630.6	5630.6	5630.6	5630.6	5630.6	5630.6	5630.6	5630.6	5630.6	5630.6	5630.6
2.5°	5636.9	5636.9	5618.1	5643.1	5630.6	5636.9	5643.1	5636.9	5630.6	5636.9	5643.1
5°	5668.1	5655.6	5668.1	5680.6	5661.9	5674.4	5668.1	5636.9	5655.6	5655.6	5655.6
7.5°	5724.4	5737.0	5724.4	5755.7	5737.0	5774.5	5737.0	5711.9	5705.7	5699.4	5699.4
10°	5749.5	5749.5	5743.2	5799.5	5812.0	5849.6	5824.5	5787.0	5768.2	5743.2	5718.2
12.5°	5680.6	5693.2	5724.4	5830.8	5880.8	5955.9	5937.1	5862.1	5805.8	5787.0	5749.5
15°	5605.6	5618.1	5680.6	5812.0	5930.9	6043.5	6037.2	5943.4	5874.6	5824.5	5768.2
17.5°	5486.7	5505.5	5593.1	5793.3	6006.0	6131.1	6168.6	6074.8	5999.7	5918.4	5843.3
20°	5286.5	5286.5	5442.9	5699.4	5993.5	6275.0	6375.1	6300.0	6212.4	6081.0	5980.9
22.5°	5061.3	5073.8	5230.2	5568.0	5987.2	6400.1	6594.1	6512.7	6425.1	6281.2	6131.1
25°	4836.1	4836.1	5011.2	5392.9	5905.9	6487.7	6850.6	6806.8	6631.6	6500.2	6306.3
27.5°	4629.6	4629.6	4817.3	5217.7	5768.2	6512.7	7107.1	7107.1	6913.1	6719.2	6506.5
30°	4385.6	4448.2	4660.9	5080.0	5643.1	6468.9	7294.7	7413.6	7238.4	6988.2	6675.4
32.5°	4179.2	4222.9	4441.9	4886.1	5461.7	6418.9	7507.5	7801.5	7620.1	7276.0	6925.6
35°	3935.2	3928.9	4179.2	4617.1	5205.2	6306.3	7676.4	8264.5	8089.3	7720.2	7244.7
37.5°	3616.1	3616.1	3872.6	4298.0	4961.2	6112.3	7814.0	8777.5	8646.1	8226.9	7720.2
40°	3272.0	3309.5	3534.8	3966.4	4667.1	5880.8	7814.0	9196.6	9265.5	8833.8	8308.3
42.5°	3021.8	3034.3	3240.7	3647.4	4341.8	5580.5	7713.9	9559.5	9766.0	9403.1	8721.2
45°	2759.0	2790.3	2965.4	3340.8	4004.0	5223.9	7538.7	9966.2	10297.7	10047.5	9152.8
47.5°	2439.9	2471.2	2671.4	3053.0	3684.9	4836.1	7244.7	10391.6	11086.0	10904.6	9922.4
50°	2070.8	2095.8	2283.5	2690.2	3328.3	4391.9	6875.6	10710.6	11874.3	12055.7	11086.0
52.5°	1620.4	1639.1	1839.3	2233.5	2902.9	3966.4	6356.3	10904.6	12668.8	13307.0	12643.8
55°	1163.7	1194.9	1370.1	1695.4	2339.8	3397.1	5737.0	11004.7	13538.5	14789.7	14577.0
57.5°	838.3	850.8	969.7	1220.0	1739.2	2727.7	4942.4	10835.8	14320.5	16560.2	17004.4
60°	694.4	694.4	713.2	832.1	1188.7	1926.9	3991.5	10210.1	14989.9	18349.5	19719.6
62.5°	638.1	638.1	650.6	669.4	782.0	1251.2	2852.8	8940.1	15065.0	20069.9	22697.6
65°	581.8	581.8	594.3	606.9	631.9	813.3	1720.5	6544.0	13594.8	20088.7	24299.1
67.5°	531.8	531.8	538.0	544.3	556.8	594.3	944.7	3966.4	10879.6	19556.9	24912.3
70°	481.7	481.7	481.7	475.5	494.2	500.5	625.6	2014.5	7276.0	17661.3	24618.2
72.5°	*425.4*	*425.4*	*419.2*	*406.7*	*412.9*	*412.9*	*463.0*	*988.5*	*3778.8*	*14038.9*	*22228.3*
75°	362.9	369.1	344.1	331.6	325.3	331.6	369.1	563.1	1689.2	8514.7	16610.3
77.5°	306.6	319.1	281.5	256.5	250.2	250.2	287.8	350.3	725.7	3090.6	7444.9
80°	231.5	237.7	206.5	181.4	181.4	175.2	212.7	256.5	344.1	919.7	1670.4
82.5°	131.4	131.4	118.9	106.4	100.1	106.4	143.9	175.2	212.7	325.3	456.7
85°	31.3	31.3	37.5	43.8	43.8	56.3	81.3	93.8	112.6	131.4	175.2
87.5°	6.3	6.3	6.3	12.5	18.8	18.8	31.3	43.8	56.3	68.8	75.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360749
CATALOG NUMBER: GSS-SB4C-730-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	5630.6	5630.6	*5630.6*
2.5°	5643.1	5649.4	*5643.1*
5°	5680.6	5668.1	*5649.4*
7.5°	5686.9	5693.2	*5699.4*
10°	5711.9	5737.0	*5699.4*
12.5°	5737.0	5718.2	*5705.7*
15°	5755.7	5749.5	*5711.9*
17.5°	5824.5	5799.5	*5793.3*
20°	5930.9	5924.6	*5905.9*
22.5°	6056.0	6043.5	*6037.2*
25°	6237.4	6193.7	*6168.6*
27.5°	6387.6	6350.1	*6337.5*
30°	6537.7	6462.7	*6462.7*
32.5°	6669.1	6650.4	*6637.8*
35°	6981.9	6888.1	*6900.6*
37.5°	7363.6	7269.7	*7188.4*
40°	7901.6	7776.5	*7726.4*
42.5°	8245.7	8120.6	*8133.1*
45°	8439.6	8220.7	*8164.4*
47.5°	8965.2	8689.9	*8614.8*
50°	9816.0	9478.2	*9384.3*
52.5°	11192.4	10648.1	*10523.0*
55°	12919.1	12249.7	*12124.5*
57.5°	15283.9	14395.6	*14126.5*
60°	18161.8	17060.7	*16654.0*
62.5°	21621.5	20263.9	*19876.0*
65°	24224.1	23091.7	*22491.1*
67.5°	26307.4	25375.2	*25087.4*
70°	27546.1	27589.9	*27665.0*
72.5°	*26113.4*	*27314.6*	*27890.2*
75°	19137.8	20069.9	*20964.6*
77.5°	7394.8	6669.1	*6456.4*
80°	1194.9	1119.9	*1157.4*
82.5°	538.0	569.3	*600.6*
85°	350.3	406.7	*431.7*
87.5°	81.3	81.3	*81.3*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)