Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1358061

Luminaire Tested: **GSS-SB4C-730-U-T4FT-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1358061
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4C-730-U-T4FT-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 204W 70CRI 3000K FIXTURE w/ TYPE IV FORWARD THROW DISTRIBUTION OPTIC AND HOUSE SIDE SHIELD
Light Source:	(104) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	20041.1 lumens
Efficiency:	N/A
Efficacy:	98.2 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type IV - Short
BUG Rating:	B2 - U0 - G4


Input Watts (W):	204
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1358061
CATALOG NUMBER: GSS-SB4C-730-U-T4FT-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 8 fc
Type IV - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1358061
CATALOG NUMBER: GSS-SB4C-730-U-T4FT-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1358061
CATALOG NUMBER: GSS-SB4C-730-U-T4FT-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2496.3	0.0	2496.3
	% Fixture	12.5	0.0	12.5
Street Side	Lumens	17544.8	0.0	17544.8
	% Fixture	87.5	0.0	87.5
Total	Lumens	20041.1	0.0	20041.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	270.3	1.3
10°-20°	638.8	3.2
20°-30°	1043.5	5.2
30°-40°	1865.0	9.3
40°-50°	3339.0	16.7
50°-60°	4849.1	24.2
60°-70°	5408.0	27.0
70°-80°	2489.3	12.4
80°-90°	138.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	20041.1	100.0
0°-180°	20041.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1358061
CATALOG NUMBER: GSS-SB4C-730-U-T4FT-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1266.7	6.3			
FM	(30°-60°)	8593.7	42.9			
FH	(60°-80°)	7566.3	37.8			G4/12000
FVH	(80°-90°)	118.1	0.6			G2/225
BL	(0°-30°)	685.9	3.4	B2/1000		
BM	(30°-60°)	1459.4	7.3	B2/2500		
BH	(60°-80°)	331.0	1.7	B1/500		G1/500
BVH	(80°-90°)	20.1	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G4
Type IV Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1358061
CATALOG NUMBER: GSS-SB4C-730-U-T4FT-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	36°	45°	55°	65°	75°	85°
0°	3201.9	3201.9	3201.9	3201.9	3201.9	*3201.9*	3201.9	3201.9	3201.9	3201.9	3201.9
2.5°	3164.2	3151.6	3151.6	3164.2	3195.6	*3176.8*	3164.2	3183.0	3189.3	3208.2	3214.5
5°	2975.5	2981.7	2962.9	3006.9	3038.4	*3044.7*	3088.7	3145.3	3176.8	3239.7	3246.0
7.5°	2730.1	2755.3	2767.9	2830.8	2893.7	*2900.0*	2981.7	3069.8	3164.2	3252.2	3296.3
10°	2535.1	2541.4	2554.0	2623.2	2736.4	*2749.0*	2862.2	3006.9	3145.3	3290.0	3340.3
12.5°	2409.3	2421.9	2421.9	2478.5	2591.7	*2604.3*	2736.4	2931.4	3132.7	3302.6	3396.9
15°	2409.3	2396.7	2396.7	2440.8	2528.8	*2541.4*	2667.2	2874.8	3101.3	3340.3	3491.3
17.5°	2421.9	2428.2	2415.6	2447.0	2522.5	*2535.1*	2648.3	2843.4	3107.6	3396.9	3566.8
20°	2472.2	2472.2	2459.6	2510.0	2579.1	*2598.0*	2692.4	2855.9	3132.7	3478.7	3673.7
22.5°	2541.4	2522.5	2516.2	2572.9	2660.9	*2692.4*	2774.2	2918.8	3170.5	3579.4	3786.9
25°	2642.1	2623.2	2610.6	2673.5	2755.3	*2767.9*	2912.6	3025.8	3271.1	3711.5	3975.7
27.5°	2830.8	2805.6	2742.7	2786.7	2887.4	*2900.0*	3044.7	3183.0	3409.5	3862.4	4189.5
30°	3409.5	3371.8	3189.3	3006.9	3044.7	*3063.5*	3208.2	3384.3	3598.2	4095.2	4510.4
32.5°	4095.2	4107.8	3875.0	3529.0	3302.6	*3308.9*	3403.2	3648.6	3875.0	4422.3	4906.7
35°	4975.9	4938.1	4623.6	4221.0	3793.2	*3774.4*	3749.2	4019.7	4277.6	4831.2	5403.6
37.5°	5818.8	5806.2	5548.3	5045.1	4548.1	*4472.6*	4296.5	4510.4	4749.4	5347.0	5957.2
40°	6447.9	6385.0	6234.0	5900.6	5479.1	*5435.1*	5063.9	5114.3	5340.7	6039.0	6535.9
42.5°	6856.8	6844.2	6668.0	6567.4	6372.4	*6353.5*	5913.2	5938.3	6064.1	6825.3	7215.3
45°	7259.4	7227.9	7076.9	7014.0	7026.6	*7070.6*	7007.7	6863.1	6957.4	7699.7	7945.0
47.5°	7662.0	7586.5	7473.2	7498.4	7762.6	*7819.2*	8026.8	7913.6	7794.1	8699.9	8630.7
50°	7812.9	7819.2	7850.7	8001.7	8435.7	*8567.8*	9052.2	8825.7	8637.0	9750.4	9423.3
52.5°	7869.6	7901.0	8114.9	8379.1	9071.1	*9234.6*	10178.2	9895.1	9373.0	10769.5	9939.2
55°	7932.5	7913.6	8341.3	8681.0	9737.9	*9914.0*	11209.9	10750.7	10065.0	11537.0	10379.5
57.5°	8253.3	8259.6	8593.0	8957.8	10360.6	*10599.7*	12153.5	11581.0	10448.7	12115.7	10505.3
60°	8762.8	8882.3	9108.8	9505.1	11102.9	*11442.6*	13084.5	12184.9	10838.7	12128.3	9958.0
62.5°	9058.5	9127.7	9769.3	10543.1	12373.6	*12713.3*	14072.1	12656.7	10637.4	11008.6	8555.2
65°	8039.4	8096.0	9536.6	12115.7	14355.2	*14638.2*	15160.4	12694.4	9574.3	9146.5	6642.9
67.5°	6001.2	6152.2	7869.6	13770.1	17393.5	*17531.9*	16481.4	11763.4	7869.6	6397.5	3900.2
70°	*4327.9*	*4554.4*	*5869.1*	*14279.7*	*19551.2*	*19664.4*	*16229.8*	*9756.7*	*5296.7*	*3283.7*	*1836.9*
72.5°	3132.7	3252.2	4189.5	13392.7	18400.0	*17833.9*	11448.9	6101.9	2793.0	1673.3	842.9
75°	2164.0	2252.0	2667.2	10077.6	12537.2	*12424.0*	5774.8	2214.3	1358.8	968.8	509.5
77.5°	893.3	893.3	1195.2	5674.1	7014.0	*7127.3*	2623.2	603.9	717.1	559.9	295.7
80°	289.4	289.4	478.1	2013.0	3246.0	*3283.7*	943.6	295.7	383.7	339.7	157.3
82.5°	106.9	100.6	245.3	666.8	805.2	*855.5*	257.9	144.7	232.8	201.3	75.5
85°	37.7	37.7	88.1	138.4	151.0	*132.1*	69.2	69.2	113.2	94.4	31.5
87.5°	0.0	0.0	6.3	12.6	18.9	*18.9*	18.9	18.9	25.2	18.9	18.9
90°	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1358061
CATALOG NUMBER: GSS-SB4C-730-U-T4FT-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3201.9	3201.9	3201.9	3201.9	3201.9	3201.9	3201.9	3201.9	3201.9	3201.9	3201.9
2.5°	3201.9	3214.5	3189.3	3164.2	3157.9	3126.4	3107.6	3082.4	3076.1	3069.8	3082.4
5°	3239.7	3239.7	3176.8	3107.6	3025.8	2912.6	2793.0	2686.1	2642.1	2591.7	2598.0
7.5°	3283.7	3252.2	3157.9	2975.5	2730.1	2459.6	2233.2	2063.3	1962.7	1874.6	1899.8
10°	3321.4	3290.0	3095.0	2742.7	2333.8	1969.0	1641.8	1453.1	1333.6	1264.4	1295.9
12.5°	3378.1	3315.2	2988.0	2447.0	1887.2	1440.5	1188.9	1088.3	1056.8	1038.0	1038.0
15°	3441.0	3334.0	2824.5	2113.6	1459.4	1088.3	1019.1	1019.1	1025.4	1025.4	1031.7
17.5°	3503.9	3340.3	2648.3	1729.9	1132.3	993.9	1000.2	1006.5	1019.1	1006.5	1006.5
20°	3579.4	3384.3	2421.9	1390.2	993.9	975.0	981.3	993.9	1006.5	993.9	1000.2
22.5°	3705.2	3428.4	2226.9	1170.1	975.0	962.5	962.5	981.3	987.6	968.8	975.0
25°	3849.9	3485.0	2019.3	1082.0	987.6	943.6	956.2	968.8	975.0	962.5	962.5
27.5°	4032.3	3579.4	1818.0	1082.0	1000.2	931.0	937.3	956.2	968.8	949.9	962.5
30°	4296.5	3692.6	1692.2	1113.4	1012.8	905.8	912.1	937.3	956.2	943.6	949.9
32.5°	4623.6	3887.6	1585.2	1138.6	1006.5	880.7	874.4	912.1	943.6	937.3	949.9
35°	5026.2	4114.1	1516.0	1163.8	993.9	861.8	836.7	887.0	937.3	937.3	943.6
37.5°	5428.8	4353.1	1547.5	1157.5	962.5	849.2	805.2	849.2	905.8	924.7	937.3
40°	5906.9	4617.3	1623.0	1119.7	943.6	811.5	780.0	811.5	868.1	899.6	912.1
42.5°	6334.6	4868.9	1698.5	1075.7	918.4	773.7	754.9	780.0	811.5	842.9	861.8
45°	6837.9	5063.9	1673.3	1025.4	893.3	742.3	736.0	742.3	754.9	767.5	780.0
47.5°	7196.5	5126.8	1560.1	981.3	836.7	717.1	704.5	698.3	685.7	685.7	692.0
50°	7586.5	4950.7	1333.6	931.0	754.9	685.7	660.5	641.6	622.8	610.2	616.5
52.5°	7756.3	4497.8	1119.7	842.9	660.5	641.6	610.2	585.0	559.9	553.6	547.3
55°	7687.1	3875.0	924.7	710.8	591.3	591.3	559.9	534.7	509.5	490.7	484.4
57.5°	7422.9	3233.4	742.3	528.4	522.1	534.7	509.5	484.4	459.2	434.1	434.1
60°	6806.4	2478.5	572.4	427.8	452.9	471.8	465.5	446.6	402.6	364.9	364.9
62.5°	5743.3	1679.6	408.9	346.0	383.7	415.2	421.5	402.6	352.3	308.2	301.9
65°	4365.7	987.6	314.5	295.7	327.1	358.6	371.1	352.3	295.7	245.3	232.8
67.5°	2654.6	534.7	245.3	251.6	283.1	301.9	320.8	308.2	257.9	207.6	201.3
70°	*1132.3*	*270.5*	*201.3*	*207.6*	*226.5*	*232.8*	*270.5*	*276.8*	*232.8*	*182.4*	*176.1*
72.5°	522.1	201.3	163.6	176.1	169.8	176.1	232.8	245.3	201.3	144.7	144.7
75°	301.9	151.0	125.8	138.4	113.2	132.1	188.7	201.3	169.8	119.5	113.2
77.5°	163.6	106.9	88.1	94.4	81.8	100.6	151.0	157.3	125.8	94.4	94.4
80°	94.4	69.2	62.9	56.6	56.6	69.2	106.9	100.6	81.8	81.8	81.8
82.5°	50.3	37.7	37.7	37.7	37.7	44.0	56.6	62.9	69.2	69.2	69.2
85°	25.2	18.9	18.9	18.9	25.2	31.5	44.0	50.3	56.6	56.6	56.6
87.5°	12.6	12.6	12.6	12.6	12.6	18.9	31.5	37.7	44.0	25.2	12.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)