Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1362677

Luminaire Tested: **GSS-SB6C-730-U-SL2**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1362677
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6C-730-U-SL2
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 300W 70CRI 3000K FIXTURE w/ TYPE II SPILL CONTROL DISTRIBUTION OPTIC
Light Source:	(156) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	42560.7 lumens
Efficiency:	N/A
Efficacy:	141.9 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type II - Medium
BUG Rating:	B4 - U0 - G4


Input Watts (W):	300
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.3%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1362677
CATALOG NUMBER: GSS-SB6C-730-U-SL2

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 23.7 fc
Type II - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1362677
CATALOG NUMBER: GSS-SB6C-730-U-SL2

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1362677
CATALOG NUMBER: GSS-SB6C-730-U-SL2

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	9349.2	0.0	9349.2
	% Fixture	22.0	0.0	22.0
Street Side	Lumens	33211.5	0.0	33211.5
	% Fixture	78.0	0.0	78.0
Total	Lumens	42560.7	0.0	42560.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	875.0	2.1
10°-20°	2173.0	5.1
20°-30°	3421.3	8.0
30°-40°	5105.7	12.0
40°-50°	7259.6	17.1
50°-60°	9170.2	21.5
60°-70°	8583.5	20.2
70°-80°	5452.3	12.8
80°-90°	520.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	42560.7	100.0
0°-180°	42560.7	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1362677
CATALOG NUMBER: GSS-SB6C-730-U-SL2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	4028.5	9.5			
FM	(30°-60°)	17347.8	40.8			
FH	(60°-80°)	11447.7	26.9			G4/12000
FVH	(80°-90°)	387.4	0.9			G3/500
BL	(0°-30°)	2440.8	5.7	B3/2500		
BM	(30°-60°)	4187.7	9.8	B3/5000		
BH	(60°-80°)	2588.0	6.1	B4/5000		G4/5000
BVH	(80°-90°)	132.7	0.3			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type II Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1362677
CATALOG NUMBER: GSS-SB6C-730-U-SL2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	79°	85°
0°	9425.5	9425.5	9425.5	9425.5	9425.5	9425.5	9425.5	9425.5	9425.5	*9425.5*	9425.5
2.5°	9647.1	9657.2	9616.9	9616.9	9626.9	9586.7	9536.3	9526.2	9486.0	*9486.0*	9486.0
5°	9697.4	9697.4	9687.4	9737.7	9757.9	9788.1	9747.8	9717.6	9657.2	*9657.2*	9576.6
7.5°	9163.7	9143.6	9224.1	9455.8	9697.4	9828.3	9908.9	9908.9	9878.7	*9828.3*	9757.9
10°	8156.7	8186.9	8307.8	8619.9	9063.0	9657.2	9979.4	10110.3	10060.0	*10039.8*	9919.0
12.5°	7623.0	7612.9	7703.6	7935.2	8317.8	9042.9	9838.4	10251.3	10261.4	*10211.0*	10070.0
15°	7562.6	7532.4	7572.7	7653.2	7905.0	8489.0	9415.5	10301.6	10402.3	*10382.2*	10221.1
17.5°	7905.0	7894.9	7834.5	7814.3	7804.3	8126.5	9002.6	10261.4	10593.7	*10573.5*	10392.3
20°	8499.1	8448.8	8338.0	8237.3	8025.8	8056.0	8680.4	10211.0	10855.5	*10825.3*	10644.0
22.5°	9133.5	9153.7	9053.0	8811.3	8438.7	8267.5	8579.7	10140.5	11207.9	*11187.8*	10946.1
25°	9908.9	9888.8	9767.9	9496.0	9002.6	8630.0	8690.4	10120.4	11610.7	*11630.9*	11338.9
27.5°	10704.4	10684.3	10533.2	10190.9	9616.9	9073.1	8942.2	10200.9	12124.3	*12114.2*	11751.7
30°	11590.6	11600.7	11409.3	10946.1	10251.3	9626.9	9345.0	10412.4	12637.9	*12668.1*	12225.0
32.5°	12386.1	12436.5	12325.7	11892.7	11026.7	10200.9	9838.4	10754.8	13322.6	*13373.0*	12829.2
35°	12889.6	12919.8	12909.8	12708.4	11852.4	10855.5	10331.8	11187.8	14148.4	*14339.7*	13634.8
37.5°	13373.0	13443.5	13453.6	13302.5	12658.0	11630.9	10915.9	11792.0	15205.7	*15517.9*	14692.2
40°	13896.6	13876.5	14017.5	13836.2	13383.1	12456.6	11520.1	12476.8	16373.9	*16887.4*	15930.8
42.5°	14208.8	14259.2	14440.4	14400.1	13947.0	13221.9	12204.9	13242.1	17834.0	*18589.3*	17431.2
45°	14410.2	14460.6	14722.4	14762.7	14521.0	13745.6	12849.4	13977.2	19173.3	*20351.5*	19042.4
47.5°	14480.7	14510.9	14853.3	15014.4	14913.7	14077.9	13352.9	14813.0	20492.5	*22013.1*	20653.6
50°	14198.7	14309.5	14752.6	15115.1	15185.6	14249.1	13785.9	15699.2	21912.4	*23624.3*	22274.9
52.5°	13765.7	13826.1	14359.9	15135.3	15356.8	14531.0	14319.6	16635.7	23251.7	*25235.5*	23664.6
55°	12919.8	13040.7	13705.3	14802.9	15457.5	14903.6	15014.4	17693.0	24641.4	*26645.3*	25175.1
57.5°	10523.2	10734.6	11832.3	13383.1	15185.6	15638.8	16051.6	19002.1	26161.9	*28276.6*	26524.5
60°	6595.9	6877.8	8025.8	10533.2	13644.9	16071.8	17703.1	20704.0	27974.5	*29988.5*	28024.9
62.5°	3574.9	3564.8	3907.2	5387.5	9838.4	14943.9	19123.0	23654.5	30310.8	*31579.6*	28901.0
65°	3101.6	3101.6	3141.8	3131.8	4249.6	11026.7	17713.2	25416.7	31922.0	*32002.5*	28155.8
67.5°	2789.4	2789.4	2849.8	2698.8	2316.1	4934.3	12960.1	24369.5	34590.5	*34540.2*	29112.4
70°	2457.1	2467.2	2567.9	2477.2	1863.0	2003.9	7089.3	22194.3	36584.4	*37661.9*	31015.7
72.5°	*1802.5*	*1863.0*	*2155.0*	*2155.0*	*1530.6*	*1349.4*	*2880.0*	*17209.7*	*35335.7*	*38588.3*	*32596.7*
75°	1268.8	1278.9	1429.9	1540.7	1208.4	1017.1	1399.7	11520.1	32415.4	*36000.3*	31186.9
77.5°	966.7	976.8	1027.1	1228.5	825.7	745.2	966.7	6293.8	23382.6	*24309.0*	20230.7
80°	644.5	634.4	704.9	866.0	584.1	503.5	624.3	2104.6	13121.2	*12517.0*	8448.8
82.5°	322.2	332.3	382.7	453.2	342.4	302.1	362.5	1087.6	5145.8	*2990.8*	1228.5
85°	90.6	110.8	130.9	181.3	141.0	130.9	171.2	382.7	654.6	*483.4*	332.3
87.5°	10.1	10.1	20.1	20.1	20.1	30.2	50.4	80.6	110.8	*110.8*	110.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1362677
CATALOG NUMBER: GSS-SB6C-730-U-SL2

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	9425.5	9425.5	9425.5	9425.5	9425.5	9425.5	9425.5	9425.5	9425.5	9425.5	9425.5
2.5°	9465.8	9435.6	9395.3	9334.9	9334.9	9264.4	9224.1	9143.6	9173.8	9133.5	9113.4
5°	9556.5	9516.2	9425.5	9324.8	9224.1	9073.1	8952.3	8781.1	8760.9	8720.6	8660.2
7.5°	9717.6	9616.9	9506.1	9274.5	9083.2	8740.8	8468.9	8126.5	7935.2	7814.3	7824.4
10°	9878.7	9747.8	9516.2	9214.1	8801.2	8237.3	7532.4	6857.7	6344.1	6052.1	6112.5
12.5°	9989.5	9848.5	9536.3	9053.0	8287.6	7159.8	5850.7	4894.0	4521.4	4330.1	4330.1
15°	10100.2	9919.0	9506.1	8710.6	7320.9	5397.5	4360.3	3997.8	3897.1	3836.7	3816.5
17.5°	10241.2	10029.7	9415.5	8076.2	5770.1	4219.3	3856.8	3746.0	3746.0	3736.0	3715.8
20°	10412.4	10160.7	9304.7	7069.2	4430.8	3786.3	3685.6	3665.5	3685.6	3675.6	3665.5
22.5°	10674.2	10321.8	9022.7	5679.5	3806.5	3584.9	3574.9	3474.2	3494.3	3514.4	3504.4
25°	11006.5	10523.2	8489.0	4340.2	3494.3	3454.0	3353.3	3262.7	3252.6	3262.7	3262.7
27.5°	11318.7	10674.2	7623.0	3574.9	3272.8	3262.7	3172.1	3091.5	3091.5	3101.6	3101.6
30°	11661.1	10764.9	6293.8	3182.1	3141.8	3091.5	3061.3	3031.1	3041.1	3071.4	3071.4
32.5°	12114.2	10855.5	4994.7	2960.6	3010.9	2940.4	2960.6	2950.5	2970.7	3021.0	3031.1
35°	12668.1	10895.8	3997.8	2829.7	2829.7	2769.3	2779.3	2739.0	2739.0	2769.3	2789.4
37.5°	13403.2	10915.9	3363.4	2759.2	2688.7	2658.5	2638.3	2588.0	2517.5	2467.2	2477.2
40°	14198.7	10966.3	3021.0	2708.8	2628.3	2618.2	2577.9	2507.4	2306.0	2144.9	2134.8
42.5°	15256.1	11107.2	2849.8	2628.3	2628.3	2628.3	2567.9	2255.7	2094.6	1983.8	1973.7
45°	16323.5	11479.8	2759.2	2557.8	2618.2	2628.3	2356.4	2165.1	2034.1	1913.3	1883.1
47.5°	17511.8	12013.5	2718.9	2517.5	2547.7	2567.9	2215.4	2124.8	1973.7	1832.7	1802.5
50°	18690.0	12577.5	2678.6	2447.0	2447.0	2316.1	2185.2	2084.5	1933.4	1782.4	1762.3
52.5°	19938.7	13232.0	2638.3	2326.2	2316.1	2175.1	2155.0	2074.4	1913.3	1722.0	1681.7
55°	21026.2	13826.1	2567.9	2185.2	2175.1	2034.1	2134.8	2034.1	1792.5	1570.9	1530.6
57.5°	22063.4	14309.5	2477.2	2034.1	2054.3	1923.4	2054.3	1953.6	1681.7	1460.2	1440.0
60°	23050.3	14813.0	2356.4	1903.2	1903.2	1822.7	1953.6	1822.7	1570.9	1349.4	1319.2
62.5°	23342.3	14651.9	2155.0	1762.3	1752.2	1691.8	1822.7	1671.6	1429.9	1228.5	1198.3
65°	22335.3	13826.1	1913.3	1621.3	1591.1	1540.7	1631.3	1490.4	1268.8	1107.7	1097.6
67.5°	22476.3	13503.9	1641.4	1440.0	1409.8	1369.5	1399.7	1289.0	1117.8	996.9	986.9
70°	22657.6	13151.5	1389.7	1268.8	1198.3	1127.8	1198.3	1107.7	986.9	886.2	876.1
72.5°	*22516.6*	*12174.7*	*1148.0*	*1067.4*	*1017.1*	*936.5*	*1027.1*	*956.7*	*856.0*	*775.4*	*755.3*
75°	20482.4	9788.1	936.5	876.1	815.7	765.3	825.7	805.6	725.0	715.0	644.5
77.5°	13775.8	6273.6	725.0	674.7	654.6	604.2	644.5	614.3	574.0	533.7	503.5
80°	5971.5	2809.5	523.6	473.3	453.2	422.9	463.2	453.2	433.0	402.8	392.7
82.5°	856.0	664.6	352.5	322.2	271.9	251.8	271.9	292.0	422.9	513.6	503.5
85°	241.7	201.4	171.2	151.1	120.8	100.7	110.8	181.3	241.7	151.1	130.9
87.5°	110.8	100.7	80.6	50.4	30.2	30.2	20.1	10.1	10.1	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)