Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360779

Luminaire Tested: **GSS-SB6A-735-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360779
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6A-735-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 170W 70CRI 3500K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(156) 3500K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	25800.7 lumens
Efficiency:	N/A
Efficacy:	151.8 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	170
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	12.0%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360779
CATALOG NUMBER: GSS-SB6A-735-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 12.7 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360779
CATALOG NUMBER: GSS-SB6A-735-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360779
CATALOG NUMBER: GSS-SB6A-735-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	12900.3	0.0	12900.3
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	12900.3	0.0	12900.3
	% Fixture	50.0	0.0	50.0
Total	Lumens	25800.7	0.0	25800.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	492.0	1.9
10°-20°	1499.6	5.8
20°-30°	2506.5	9.7
30°-40°	3456.6	13.4
40°-50°	4237.4	16.4
50°-60°	4965.6	19.2
60°-70°	5514.3	21.4
70°-80°	2998.7	11.6
80°-90°	129.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	25800.7	100.0
0°-180°	25800.7	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360779
CATALOG NUMBER: GSS-SB6A-735-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2249.1	8.7			
FM	(30°-60°)	6329.8	24.5			
FH	(60°-80°)	4256.5	16.5			G2/5000
FVH	(80°-90°)	65.0	0.3			G1/100
BL	(0°-30°)	2249.1	8.7	B3/2500		
BM	(30°-60°)	6329.8	24.5	B4/8500		
BH	(60°-80°)	4256.5	16.5	B4/5000		G4/5000
BVH	(80°-90°)	65.0	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360779
CATALOG NUMBER: GSS-SB6A-735-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	5083.4	5083.4	5083.4	5083.4	5083.4	5083.4	5083.4	5083.4	5083.4	5083.4	5083.4
2.5°	5089.0	5089.0	5072.1	5094.7	5083.4	5089.0	5094.7	5089.0	5083.4	5089.0	5094.7
5°	5117.3	5106.0	5117.3	5128.6	5111.6	5122.9	5117.3	5089.0	5106.0	5106.0	5106.0
7.5°	5168.1	5179.4	5168.1	5196.3	5179.4	5213.3	5179.4	5156.8	5151.2	5145.5	5145.5
10°	5190.7	5190.7	5185.0	5235.9	5247.2	5281.1	5258.5	5224.6	5207.6	5185.0	5162.5
12.5°	5128.6	5139.9	5168.1	5264.1	5309.3	5377.1	5360.1	5292.4	5241.5	5224.6	5190.7
15°	5060.8	5072.1	5128.6	5247.2	5354.5	5456.2	5450.5	5365.8	5303.7	5258.5	5207.6
17.5°	4953.5	4970.4	5049.5	5230.2	5422.3	5535.2	5569.1	5484.4	5416.6	5343.2	5275.4
20°	4772.7	4772.7	4913.9	5145.5	5411.0	5665.1	5755.5	5687.7	5608.7	5490.0	5399.7
22.5°	4569.4	4580.7	4721.9	5026.9	5405.3	5778.1	5953.2	5879.8	5800.7	5670.8	5535.2
25°	4366.1	4366.1	4524.2	4868.7	5331.9	5857.2	6184.8	6145.2	5987.1	5868.5	5693.4
27.5°	4179.7	4179.7	4349.1	4710.6	5207.6	5879.8	6416.4	6416.4	6241.3	6066.2	5874.1
30°	3959.4	4015.9	4207.9	4586.3	5094.7	5840.2	6585.8	6693.1	6535.0	6309.0	6026.6
32.5°	3773.0	3812.5	4010.2	4411.2	4930.9	5795.0	6777.8	7043.3	6879.5	6568.9	6252.6
35°	3552.7	3547.1	3773.0	4168.4	4699.3	5693.4	6930.3	7461.3	7303.1	6969.9	6540.6
37.5°	3264.7	3264.7	3496.2	3880.3	4479.0	5518.3	7054.6	7924.4	7805.8	7427.4	6969.9
40°	2954.0	2987.9	3191.2	3581.0	4213.6	5309.3	7054.6	8302.8	8365.0	7975.3	7500.8
42.5°	2728.1	2739.4	2925.8	3292.9	3919.8	5038.2	6964.2	8630.4	8816.8	8489.2	7873.6
45°	2490.9	2519.1	2677.2	3016.1	3614.8	4716.2	6806.1	8997.6	9296.9	9071.0	8263.3
47.5°	2202.8	2231.0	2411.8	2756.3	3326.8	4366.1	6540.6	9381.7	10008.6	9844.8	8958.0
50°	1869.6	1892.1	2061.6	2428.7	3004.8	3965.0	6207.4	9669.7	10720.3	10884.1	10008.6
52.5°	1462.9	1479.8	1660.6	2016.4	2620.8	3581.0	5738.6	9844.8	11437.6	12013.7	11415.0
55°	1050.6	1078.8	1237.0	1530.7	2112.4	3067.0	5179.4	9935.2	12222.7	13352.3	13160.3
57.5°	756.9	768.2	875.5	1101.4	1570.2	2462.6	4462.1	9782.7	12928.7	14950.8	15351.8
60°	626.9	626.9	643.9	751.2	1073.2	1739.6	3603.5	9217.9	13533.1	16566.2	17803.1
62.5°	576.1	576.1	587.4	604.4	706.0	1129.6	2575.6	8071.3	13600.9	18119.4	20491.7
65°	525.3	525.3	536.6	547.9	570.5	734.3	1553.3	5908.0	12273.5	18136.4	21937.6
67.5°	480.1	480.1	485.7	491.4	502.7	536.6	852.9	3581.0	9822.2	17656.3	22491.1
70°	434.9	434.9	434.9	429.3	446.2	451.9	564.8	1818.7	6568.9	15944.9	22225.7
72.5°	*384.1*	*384.1*	*378.4*	*367.1*	*372.8*	*372.8*	*418.0*	*892.4*	*3411.5*	*12674.6*	*20068.0*
75°	327.6	333.2	310.7	299.4	293.7	299.4	333.2	508.3	1525.0	7687.2	14996.0
77.5°	276.8	288.1	254.2	231.6	225.9	225.9	259.8	316.3	655.2	2790.2	6721.4
80°	209.0	214.6	186.4	163.8	163.8	158.1	192.0	231.6	310.7	830.3	1508.1
82.5°	118.6	118.6	107.3	96.0	90.4	96.0	129.9	158.1	192.0	293.7	412.3
85°	28.2	28.2	33.9	39.5	39.5	50.8	73.4	84.7	101.7	118.6	158.1
87.5°	5.6	5.6	5.6	11.3	16.9	16.9	28.2	39.5	50.8	62.1	67.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360779
CATALOG NUMBER: GSS-SB6A-735-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	5083.4	5083.4	*5083.4*
2.5°	5094.7	5100.3	*5094.7*
5°	5128.6	5117.3	*5100.3*
7.5°	5134.2	5139.9	*5145.5*
10°	5156.8	5179.4	*5145.5*
12.5°	5179.4	5162.5	*5151.2*
15°	5196.3	5190.7	*5156.8*
17.5°	5258.5	5235.9	*5230.2*
20°	5354.5	5348.8	*5331.9*
22.5°	5467.5	5456.2	*5450.5*
25°	5631.3	5591.7	*5569.1*
27.5°	5766.8	5732.9	*5721.6*
30°	5902.4	5834.6	*5834.6*
32.5°	6021.0	6004.0	*5992.7*
35°	6303.4	6218.7	*6230.0*
37.5°	6647.9	6563.2	*6489.8*
40°	7133.7	7020.7	*6975.5*
42.5°	7444.3	7331.4	*7342.7*
45°	7619.4	7421.7	*7370.9*
47.5°	8093.9	7845.3	*7777.6*
50°	8862.0	8557.0	*8472.3*
52.5°	10104.6	9613.2	*9500.3*
55°	11663.5	11059.2	*10946.2*
57.5°	13798.5	12996.5	*12753.6*
60°	16396.7	15402.6	*15035.5*
62.5°	19520.2	18294.5	*17944.3*
65°	21869.8	20847.5	*20305.3*
67.5°	23750.7	22909.1	*22649.3*
70°	24869.0	24908.5	*24976.3*
72.5°	*23575.6*	*24660.0*	*25179.7*
75°	17277.8	18119.4	*18927.1*
77.5°	6676.2	6021.0	*5828.9*
80°	1078.8	1011.0	*1044.9*
82.5°	485.7	514.0	*542.2*
85°	316.3	367.1	*389.7*
87.5°	73.4	73.4	*73.4*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ

Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-735-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369
CIE u':	0.2386
CIE v':	0.5156
Duv:	0.0013
CIE x:	0.4143
CIE y:	0.3980
CIE z:	0.1877
Peak Wavelength (nm):	590
Dominant Wavelength (nm):	580
Purity:	43.80166
Rf:	71.4
Rg:	96

CRI (Ra):	70.1
R1:	66.6
R2:	77.6
R3:	88.5
R4:	69.5
R5:	66.4
R6:	69.6
R7:	77.5
R8:	44.9
R9:	-40.2
R10:	49.1
R11:	66.3
R12:	45.7
R13:	68.0
R14:	93.4
R15:	57.6



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3369K
CIE x = 0.4143
CIE y = 0.3980
Duv = 0.0013

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.36**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-5

TM-30-18


Summary


R_f = 71.4
R_g = 96
CIE R_a = 70.1
R_9 = -40.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	





REPORT NUMBER: SP1-2407-184-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-5

TM-30-18

Measure Comparisons





(END OF REPORT)