Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1359221

Luminaire Tested: **GSS-SB6C-730-U-T2**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1359221
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6C-730-U-T2
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 300W 70CRI 3000K FIXTURE w/ TYPE II DISTRIBUTION OPTIC
Light Source:	(156) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	42255.7 lumens
Efficiency:	N/A
Efficacy:	140.9 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type II - Medium
BUG Rating:	B4 - U0 - G4


Input Watts (W):	300
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.3%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359221
CATALOG NUMBER: GSS-SB6C-730-U-T2

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 18.8 fc
Type II - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359221
CATALOG NUMBER: GSS-SB6C-730-U-T2

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1359221
CATALOG NUMBER: GSS-SB6C-730-U-T2

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	9681.8	0.0	9681.8
	% Fixture	22.9	0.0	22.9
Street Side	Lumens	32573.9	0.0	32573.9
	% Fixture	77.1	0.0	77.1
Total	Lumens	42255.7	0.0	42255.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	602.2	1.4
10°-20°	1813.1	4.3
20°-30°	3063.3	7.2
30°-40°	4725.8	11.2
40°-50°	7217.2	17.1
50°-60°	9978.7	23.6
60°-70°	10084.3	23.9
70°-80°	4436.7	10.5
80°-90°	334.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	42255.7	100.0
0°-180°	42255.7	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1359221
CATALOG NUMBER: GSS-SB6C-730-U-T2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	3296.7	7.8			
FM	(30°-60°)	17276.1	40.9			
FH	(60°-80°)	11831.7	28.0			G4/12000
FVH	(80°-90°)	169.3	0.4			G2/225
BL	(0°-30°)	2181.9	5.2	B3/2500		
BM	(30°-60°)	4645.6	11.0	B3/5000		
BH	(60°-80°)	2689.3	6.4	B4/5000		G4/5000
BVH	(80°-90°)	164.9	0.4			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type II Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359221
CATALOG NUMBER: GSS-SB6C-730-U-T2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	79°	85°
0°	6302.5	6302.5	6302.5	6302.5	6302.5	6302.5	6302.5	6302.5	6302.5	*6302.5*	6302.5
2.5°	6595.0	6698.8	6698.8	6651.6	6632.8	6623.3	6557.3	6481.8	6453.5	*6406.3*	6378.0
5°	7000.7	7000.7	7019.6	6972.4	7000.7	6963.0	6868.6	6774.3	6661.1	*6576.1*	6538.4
7.5°	7038.5	7113.9	7161.1	7161.1	7217.7	7227.2	7180.0	7076.2	6934.7	*6802.6*	6736.5
10°	7076.2	7142.2	7142.2	7217.7	7340.4	7434.7	7463.0	7425.3	7198.9	*7104.5*	6972.4
12.5°	6991.3	7066.8	7095.1	7246.0	7415.9	7595.1	7727.2	7746.1	7604.6	*7434.7*	7236.6
15°	6698.8	6764.8	6878.1	7104.5	7406.4	7680.0	7934.8	8076.3	7915.9	*7793.3*	7519.6
17.5°	6302.5	6340.3	6529.0	6821.5	7236.6	7698.9	8142.3	8416.0	8378.2	*8217.8*	7897.0
20°	6264.8	6302.5	6359.1	6576.1	7057.3	7632.9	8274.4	8802.8	8906.6	*8661.3*	8265.0
22.5°	6585.6	6623.3	6623.3	6651.6	6953.5	7576.3	8406.5	9217.9	9453.8	*9246.2*	8736.7
25°	7029.0	7104.5	7019.6	6953.5	7057.3	7614.0	8482.0	9689.7	10152.0	*9897.2*	9265.1
27.5°	7661.2	7651.7	7576.3	7378.1	7349.8	7727.2	8689.6	10057.6	10821.9	*10557.7*	9812.3
30°	8538.6	8585.8	8416.0	8000.8	7812.1	7982.0	8972.6	10359.6	11529.5	*11312.5*	10331.3
32.5°	9529.3	9510.4	9302.8	8906.6	8444.3	8397.1	9236.8	10680.3	12340.9	*12067.3*	10982.3
35°	10595.4	10576.6	10510.5	9831.2	9227.4	8972.6	9661.4	11048.3	13284.4	*13057.9*	11746.5
37.5°	11557.8	11642.7	11840.8	10746.4	10104.8	9727.4	10208.6	11661.6	14492.1	*14161.8*	12671.1
40°	12378.6	12529.6	12718.3	11727.6	10925.7	10604.9	10935.1	12661.7	15784.6	*15586.5*	13784.4
42.5°	13133.4	13237.2	13218.3	12614.5	11925.8	11567.2	11850.3	13699.5	17454.6	*17313.1*	15152.5
45°	14058.0	14171.3	14124.1	13548.6	12859.8	12539.0	13048.5	14916.6	19039.7	*19058.6*	16445.1
47.5°	14963.8	15077.0	15048.7	14520.4	13859.9	13595.7	14293.9	16350.7	20568.2	*20822.9*	17850.9
50°	15812.9	15916.7	15973.3	15643.1	15067.6	14784.5	15511.0	17699.9	22049.4	*22625.0*	19190.7
52.5°	16048.8	16180.9	16567.7	16690.4	16435.7	16096.0	16624.4	18992.5	23323.2	*24181.7*	20483.2
55°	15275.2	15501.6	16331.9	16954.6	17709.4	17747.1	17784.8	20247.4	24436.5	*25587.5*	21662.6
57.5°	13926.0	13963.7	14935.5	16199.8	17992.4	19596.4	19785.1	21709.8	25521.5	*26955.6*	22832.5
60°	10935.1	10737.0	12312.6	14454.3	16973.4	20332.3	22974.1	23974.2	26870.7	*28606.7*	24238.3
62.5°	5859.1	5878.0	7180.0	9840.6	14058.0	19615.2	25710.2	27351.9	28842.6	*30748.4*	26323.5
65°	3679.6	3821.1	4557.1	5736.4	8510.3	15586.5	25880.0	31842.9	31965.6	*33862.0*	28936.9
67.5°	*2689.0*	*2726.7*	*3349.4*	*4208.0*	*4877.9*	*9142.4*	*20832.3*	*31899.5*	*34220.5*	*36050.9*	*30050.3*
70°	2000.2	2019.1	2462.5	3170.1	3557.0	4283.5	13274.9	27606.6	33050.6	*33956.3*	27267.0
72.5°	1462.4	1471.8	1707.7	2330.4	2802.2	2547.4	6236.5	19888.8	28701.1	*30314.4*	24530.8
75°	1028.4	1047.3	1217.1	1613.4	1887.0	1773.8	2377.6	12435.2	20605.9	*20426.6*	17133.8
77.5°	773.7	783.1	896.3	1141.6	1283.2	1160.5	1339.8	5811.9	7359.2	*6642.2*	5406.2
80°	566.1	594.4	651.0	717.1	858.6	745.4	754.8	1632.2	1773.8	*1556.8*	1396.4
82.5°	301.9	339.7	434.0	434.0	500.1	443.4	396.3	726.5	764.2	*717.1*	622.7
85°	94.3	94.3	103.8	132.1	198.1	198.1	198.1	245.3	254.7	*254.7*	217.0
87.5°	18.9	18.9	18.9	18.9	28.3	37.7	56.6	75.5	84.9	*94.3*	94.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359221
CATALOG NUMBER: GSS-SB6C-730-U-T2

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	6302.5	6302.5	6302.5	6302.5	6302.5	6302.5	6302.5	6302.5	6302.5	6302.5	6302.5
2.5°	6359.1	6293.1	6227.1	6113.8	6057.2	5972.3	5896.8	5859.1	5830.8	5821.4	5821.4
5°	6481.8	6378.0	6170.4	5972.3	5793.0	5632.7	5510.0	5415.7	5359.0	5311.9	5311.9
7.5°	6604.5	6462.9	6151.6	5802.5	5547.7	5349.6	5179.8	5123.2	5104.3	5057.1	5028.8
10°	6812.0	6585.6	6123.3	5623.2	5264.7	5094.9	5019.4	5000.5	5009.9	5019.4	5019.4
12.5°	6972.4	6727.1	6047.8	5396.8	5047.7	4953.3	4962.8	5009.9	5085.4	5076.0	5057.1
15°	7198.9	6830.9	5896.8	5132.6	4877.9	4877.9	4972.2	5076.0	5151.5	5198.6	5170.3
17.5°	7463.0	6953.5	5670.4	4887.3	4736.3	4821.3	5019.4	5123.2	5255.3	5283.6	5264.7
20°	7793.3	7057.3	5415.7	4651.4	4642.0	4821.3	4991.1	5142.0	5245.8	5274.1	5293.0
22.5°	8114.0	7151.7	5085.4	4481.6	4538.2	4764.6	4925.0	5085.4	5132.6	5160.9	5170.3
25°	8444.3	7246.0	4783.5	4349.5	4462.7	4689.2	4821.3	4887.3	4896.7	4877.9	4877.9
27.5°	8802.8	7255.5	4481.6	4245.7	4377.8	4575.9	4651.4	4670.3	4632.6	4500.5	4462.7
30°	9180.2	7161.1	4236.3	4151.4	4283.5	4443.9	4500.5	4443.9	4311.8	4123.1	4104.2
32.5°	9491.5	7019.6	4057.0	4038.2	4179.7	4321.2	4321.2	4217.4	4019.3	3830.6	3821.1
35°	9963.3	6821.5	3877.8	3962.7	4085.3	4151.4	4170.2	4019.3	3802.3	3623.0	3604.1
37.5°	10425.6	6651.6	3802.3	3868.3	3981.5	4038.2	3981.5	3830.6	3689.1	3538.1	3538.1
40°	11142.7	6547.8	3707.9	3802.3	3896.6	3906.1	3802.3	3689.1	3707.9	3623.0	3613.6
42.5°	11925.8	6538.4	3670.2	3736.2	3802.3	3783.4	3632.4	3632.4	3660.8	3500.4	3462.6
45°	12822.1	6670.5	3670.2	3641.9	3679.6	3623.0	3538.1	3519.2	3453.2	3217.3	3207.9
47.5°	13756.1	6991.3	3689.1	3509.8	3500.4	3481.5	3443.8	3377.7	3179.6	2981.4	2953.1
50°	14492.1	7434.7	3745.7	3340.0	3302.2	3368.3	3302.2	3189.0	2962.6	2773.9	2745.6
52.5°	15369.5	7878.2	3707.9	3132.4	3085.2	3255.1	3189.0	3028.6	2858.8	2745.6	2717.3
55°	16294.1	8340.5	3557.0	2849.3	2887.1	3113.5	3094.7	2915.4	2707.8	2556.9	2538.0
57.5°	17218.8	8925.4	3302.2	2604.0	2745.6	3028.6	2953.1	2736.1	2594.6	2490.8	2472.0
60°	18634.0	9765.2	2934.3	2349.3	2604.0	2849.3	2726.7	2660.7	2509.7	2424.8	2377.6
62.5°	20464.4	11161.5	2453.1	2113.4	2405.9	2632.3	2622.9	2547.4	2415.3	2321.0	2292.7
65°	23068.4	12491.9	2009.6	1887.0	2151.2	2368.2	2481.4	2415.3	2283.3	2179.5	2170.0
67.5°	*23568.5*	*11161.5*	*1670.0*	*1651.1*	*1868.1*	*2113.4*	*2330.4*	*2283.3*	*2075.7*	*1943.6*	*1924.7*
70°	20511.5	7972.5	1405.8	1424.7	1632.2	1849.2	2085.1	1971.9	1802.1	1726.6	1717.2
72.5°	18209.4	6849.8	1179.4	1217.1	1368.1	1566.2	1707.7	1745.5	1622.8	1556.8	1528.5
75°	13124.0	5132.6	952.9	1000.1	1103.9	1217.1	1481.3	1547.3	1434.1	1368.1	1320.9
77.5°	4868.4	2141.7	707.6	754.8	830.3	990.7	1198.2	1339.8	1254.8	1302.0	1169.9
80°	1169.9	754.8	518.9	509.5	585.0	745.4	952.9	1056.7	971.8	924.6	802.0
82.5°	509.5	368.0	339.7	339.7	358.5	490.6	632.1	745.4	726.5	603.8	575.5
85°	188.7	160.4	160.4	169.8	169.8	226.4	339.7	396.3	358.5	311.4	301.9
87.5°	84.9	84.9	66.0	56.6	47.2	47.2	56.6	37.7	28.3	18.9	18.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)