Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360738

Luminaire Tested: **GSS-SB1D-730-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360738
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB1D-730-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 1SQUARE 76W 70CRI 3000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(26) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	9186.1 lumens
Efficiency:	N/A
Efficacy:	120.9 lumens/watt
Luminous Opening:	Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	76
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360738
CATALOG NUMBER: GSS-SB1D-730-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 4.5 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360738
CATALOG NUMBER: GSS-SB1D-730-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360738
CATALOG NUMBER: GSS-SB1D-730-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4593.1	0.0	4593.1
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	4593.1	0.0	4593.1
	% Fixture	50.0	0.0	50.0
Total	Lumens	9186.1	0.0	9186.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.2	1.9
10°-20°	533.9	5.8
20°-30°	892.4	9.7
30°-40°	1230.7	13.4
40°-50°	1508.7	16.4
50°-60°	1768.0	19.2
60°-70°	1963.3	21.4
70°-80°	1067.6	11.6
80°-90°	46.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9186.1	100.0
0°-180°	9186.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360738
CATALOG NUMBER: GSS-SB1D-730-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	800.8	8.7			
FM	(30°-60°)	2253.7	24.5			
FH	(60°-80°)	1515.5	16.5			G1/1800
FVH	(80°-90°)	23.1	0.3			G1/100
BL	(0°-30°)	800.8	8.7	B2/1000		
BM	(30°-60°)	2253.7	24.5	B2/2500		
BH	(60°-80°)	1515.5	16.5	B3/2500		G3/2500
BVH	(80°-90°)	23.1	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360738
CATALOG NUMBER: GSS-SB1D-730-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1809.9	1809.9	1809.9	1809.9	1809.9	1809.9	1809.9	1809.9	1809.9	1809.9	1809.9
2.5°	1811.9	1811.9	1805.9	1813.9	1809.9	1811.9	1813.9	1811.9	1809.9	1811.9	1813.9
5°	1822.0	1817.9	1822.0	1826.0	1820.0	1824.0	1822.0	1811.9	1817.9	1817.9	1817.9
7.5°	1840.1	1844.1	1840.1	1850.1	1844.1	1856.2	1844.1	1836.0	1834.0	1832.0	1832.0
10°	1848.1	1848.1	1846.1	1864.2	1868.2	1880.3	1872.2	1860.2	1854.1	1846.1	1838.1
12.5°	1826.0	1830.0	1840.1	1874.3	1890.3	1914.5	1908.4	1884.3	1866.2	1860.2	1848.1
15°	1801.9	1805.9	1826.0	1868.2	1906.4	1942.6	1940.6	1910.5	1888.3	1872.2	1854.1
17.5°	1763.6	1769.7	1797.8	1862.2	1930.6	1970.8	1982.8	1952.7	1928.5	1902.4	1878.3
20°	1699.3	1699.3	1749.6	1832.0	1926.5	2017.0	2049.2	2025.1	1996.9	1954.7	1922.5
22.5°	1626.9	1630.9	1681.2	1789.8	1924.5	2057.3	2119.6	2093.5	2065.3	2019.0	1970.8
25°	1554.5	1554.5	1610.8	1733.5	1898.4	2085.4	2202.0	2188.0	2131.7	2089.4	2027.1
27.5°	1488.1	1488.1	1548.5	1677.2	1854.1	2093.5	2284.5	2284.5	2222.2	2159.8	2091.4
30°	1409.7	1429.8	1498.2	1632.9	1813.9	2079.4	2344.8	2383.0	2326.7	2246.3	2145.7
32.5°	1343.3	1357.4	1427.8	1570.6	1755.6	2063.3	2413.2	2507.7	2449.4	2338.8	2226.2
35°	1264.9	1262.9	1343.3	1484.1	1673.2	2027.1	2467.5	2656.5	2600.2	2481.6	2328.7
37.5°	1162.4	1162.4	1244.8	1381.6	1594.7	1964.7	2511.7	2821.4	2779.2	2644.5	2481.6
40°	1051.8	1063.8	1136.2	1275.0	1500.2	1890.3	2511.7	2956.2	2978.3	2839.5	2670.6
42.5°	971.3	975.3	1041.7	1172.4	1395.6	1793.8	2479.6	3072.8	3139.2	3022.5	2803.3
45°	886.9	896.9	953.2	1073.9	1287.0	1679.2	2423.3	3203.5	3310.1	3229.7	2942.1
47.5°	784.3	794.3	858.7	981.4	1184.5	1554.5	2328.7	3340.3	3563.5	3505.2	3189.4
50°	665.6	673.7	734.0	864.7	1069.9	1411.7	2210.1	3442.8	3816.9	3875.2	3563.5
52.5°	520.8	526.9	591.2	717.9	933.1	1275.0	2043.2	3505.2	4072.3	4277.4	4064.2
55°	374.0	384.1	440.4	545.0	752.1	1092.0	1844.1	3537.3	4351.8	4754.0	4685.6
57.5°	269.5	273.5	311.7	392.1	559.1	876.8	1588.7	3483.1	4603.2	5323.1	5465.9
60°	223.2	223.2	229.3	267.5	382.1	619.4	1283.0	3282.0	4818.4	5898.3	6338.7
62.5°	205.1	205.1	209.1	215.2	251.4	402.2	917.0	2873.7	4842.5	6451.3	7295.9
65°	187.0	187.0	191.0	195.1	203.1	261.4	553.0	2103.5	4369.9	6457.3	7810.7
67.5°	170.9	170.9	172.9	175.0	179.0	191.0	303.7	1275.0	3497.1	6286.4	8007.8
70°	154.8	154.8	154.8	152.8	158.9	160.9	201.1	647.5	2338.8	5677.1	7913.3
72.5°	*136.7*	*136.7*	*134.7*	*130.7*	*132.7*	*132.7*	*148.8*	*317.7*	*1214.6*	*4512.7*	*7145.1*
75°	116.6	118.6	110.6	106.6	104.6	106.6	118.6	181.0	543.0	2737.0	5339.2
77.5°	98.5	102.6	90.5	82.5	80.4	80.4	92.5	112.6	233.3	993.4	2393.1
80°	74.4	76.4	66.4	58.3	58.3	56.3	68.4	82.5	110.6	295.6	536.9
82.5°	42.2	42.2	38.2	34.2	32.2	34.2	46.3	56.3	68.4	104.6	146.8
85°	10.1	10.1	12.1	14.1	14.1	18.1	26.1	30.2	36.2	42.2	56.3
87.5°	2.0	2.0	2.0	4.0	6.0	6.0	10.1	14.1	18.1	22.1	24.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360738
CATALOG NUMBER: GSS-SB1D-730-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1809.9	1809.9	*1809.9*
2.5°	1813.9	1815.9	*1813.9*
5°	1826.0	1822.0	*1815.9*
7.5°	1828.0	1830.0	*1832.0*
10°	1836.0	1844.1	*1832.0*
12.5°	1844.1	1838.1	*1834.0*
15°	1850.1	1848.1	*1836.0*
17.5°	1872.2	1864.2	*1862.2*
20°	1906.4	1904.4	*1898.4*
22.5°	1946.6	1942.6	*1940.6*
25°	2005.0	1990.9	*1982.8*
27.5°	2053.2	2041.2	*2037.1*
30°	2101.5	2077.4	*2077.4*
32.5°	2143.7	2137.7	*2133.7*
35°	2244.3	2214.1	*2218.1*
37.5°	2366.9	2336.8	*2310.6*
40°	2539.9	2499.7	*2483.6*
42.5°	2650.5	2610.3	*2614.3*
45°	2712.8	2642.5	*2624.4*
47.5°	2881.8	2793.3	*2769.1*
50°	3155.3	3046.7	*3016.5*
52.5°	3597.7	3422.7	*3382.5*
55°	4152.7	3937.5	*3897.3*
57.5°	4912.9	4627.3	*4540.8*
60°	5837.9	5484.0	*5353.3*
62.5°	6950.0	6513.6	*6388.9*
65°	7786.6	7422.6	*7229.5*
67.5°	8456.3	8156.6	*8064.1*
70°	8854.4	8868.5	*8892.6*
72.5°	*8393.9*	*8780.0*	*8965.0*
75°	6151.7	6451.3	*6738.9*
77.5°	2377.0	2143.7	*2075.4*
80°	384.1	360.0	*372.0*
82.5°	172.9	183.0	*193.1*
85°	112.6	130.7	*138.8*
87.5°	26.1	26.1	*26.1*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)