Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360742

Luminaire Tested: **GSS-SB2D-730-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360742
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2D-730-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 147W 70CRI 3000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(52) 3000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	18756.4 lumens
Efficiency:	N/A
Efficacy:	127.6 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	147
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	3.1%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360742
CATALOG NUMBER: GSS-SB2D-730-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 9.2 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360742
CATALOG NUMBER: GSS-SB2D-730-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360742
CATALOG NUMBER: GSS-SB2D-730-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	9378.2	0.0	9378.2
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	9378.2	0.0	9378.2
	% Fixture	50.0	0.0	50.0
Total	Lumens	18756.4	0.0	18756.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	357.7	1.9
10°-20°	1090.2	5.8
20°-30°	1822.2	9.7
30°-40°	2512.9	13.4
40°-50°	3080.5	16.4
50°-60°	3609.9	19.2
60°-70°	4008.7	21.4
70°-80°	2179.9	11.6
80°-90°	94.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	18756.4	100.0
0°-180°	18756.4	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360742
CATALOG NUMBER: GSS-SB2D-730-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1635.0	8.7			
FM	(30°-60°)	4601.6	24.5			
FH	(60°-80°)	3094.3	16.5			G2/5000
FVH	(80°-90°)	47.2	0.3			G1/100
BL	(0°-30°)	1635.0	8.7	B3/2500		
BM	(30°-60°)	4601.6	24.5	B3/5000		
BH	(60°-80°)	3094.3	16.5	B4/5000		G4/5000
BVH	(80°-90°)	47.2	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360742
CATALOG NUMBER: GSS-SB2D-730-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3695.5	3695.5	3695.5	3695.5	3695.5	3695.5	3695.5	3695.5	3695.5	3695.5	3695.5
2.5°	3699.6	3699.6	3687.3	3703.7	3695.5	3699.6	3703.7	3699.6	3695.5	3699.6	3703.7
5°	3720.1	3711.9	3720.1	3728.3	3716.0	3724.2	3720.1	3699.6	3711.9	3711.9	3711.9
7.5°	3757.1	3765.3	3757.1	3777.6	3765.3	3789.9	3765.3	3748.9	3744.8	3740.7	3740.7
10°	3773.5	3773.5	3769.4	3806.3	3814.6	3839.2	3822.8	3798.1	3785.8	3769.4	3753.0
12.5°	3728.3	3736.5	3757.1	3826.9	3859.7	3909.0	3896.7	3847.4	3810.5	3798.1	3773.5
15°	3679.1	3687.3	3728.3	3814.6	3892.6	3966.5	3962.4	3900.8	3855.6	3822.8	3785.8
17.5°	3601.0	3613.4	3670.8	3802.2	3941.8	4024.0	4048.6	3987.0	3937.7	3884.4	3835.1
20°	3469.6	3469.6	3572.3	3740.7	3933.6	4118.4	4184.1	4134.8	4077.4	3991.1	3925.4
22.5°	3321.8	3330.0	3432.7	3654.4	3929.5	4200.5	4327.8	4274.4	4217.0	4122.5	4024.0
25°	3174.0	3174.0	3289.0	3539.5	3876.2	4258.0	4496.2	4467.4	4352.5	4266.2	4138.9
27.5°	3038.5	3038.5	3161.7	3424.5	3785.8	4274.4	4664.5	4664.5	4537.2	4409.9	4270.3
30°	2878.4	2919.4	3059.0	3334.1	3703.7	4245.7	4787.7	4865.7	4750.7	4586.5	4381.2
32.5°	2742.9	2771.6	2915.3	3206.9	3584.6	4212.9	4927.3	5120.3	5001.2	4775.4	4545.4
35°	2582.7	2578.6	2742.9	3030.3	3416.3	4138.9	5038.2	5424.1	5309.2	5066.9	4754.9
37.5°	2373.3	2373.3	2541.7	2820.9	3256.1	4011.7	5128.5	5760.8	5674.6	5399.5	5066.9
40°	2147.5	2172.1	2319.9	2603.3	3063.1	3859.7	5128.5	6036.0	6081.1	5797.8	5452.9
42.5°	1983.2	1991.5	2127.0	2393.9	2849.6	3662.6	5062.8	6274.1	6409.6	6171.5	5723.9
45°	1810.8	1831.3	1946.3	2192.7	2627.9	3428.6	4947.8	6541.0	6758.6	6594.4	6007.2
47.5°	1601.4	1621.9	1753.3	2003.8	2418.5	3174.0	4754.9	6820.2	7276.0	7156.9	6512.3
50°	1359.1	1375.5	1498.7	1765.6	2184.4	2882.5	4512.6	7029.6	7793.4	7912.4	7276.0
52.5°	1063.5	1075.8	1207.2	1465.9	1905.2	2603.3	4171.8	7156.9	8314.8	8733.7	8298.4
55°	763.7	784.3	899.2	1112.8	1535.7	2229.6	3765.3	7222.6	8885.6	9706.8	9567.2
57.5°	550.2	558.4	636.4	800.7	1141.5	1790.3	3243.8	7111.8	9398.8	10868.8	11160.4
60°	455.8	455.8	468.1	546.1	780.2	1264.7	2619.7	6701.1	9838.2	12043.2	12942.4
62.5°	418.8	418.8	427.0	439.4	513.3	821.2	1872.4	5867.6	9887.5	13172.3	14896.9
65°	381.9	381.9	390.1	398.3	414.7	533.8	1129.2	4295.0	8922.5	13184.7	15948.1
67.5°	349.0	349.0	353.1	357.2	365.4	390.1	620.0	2603.3	7140.5	12835.6	16350.5
70°	316.2	316.2	316.2	312.1	324.4	328.5	410.6	1322.2	4775.4	11591.5	16157.5
72.5°	*279.2*	*279.2*	*275.1*	*266.9*	*271.0*	*271.0*	*303.9*	*648.8*	*2480.1*	*9214.1*	*14588.9*
75°	238.2	242.3	225.8	217.6	213.5	217.6	242.3	369.5	1108.6	5588.4	10901.7
77.5°	201.2	209.4	184.8	168.3	164.2	164.2	188.9	229.9	476.3	2028.4	4886.3
80°	151.9	156.0	135.5	119.1	119.1	115.0	139.6	168.3	225.8	603.6	1096.3
82.5°	86.2	86.2	78.0	69.8	65.7	69.8	94.4	115.0	139.6	213.5	299.7
85°	20.5	20.5	24.6	28.7	28.7	37.0	53.4	61.6	73.9	86.2	115.0
87.5°	4.1	4.1	4.1	8.2	12.3	12.3	20.5	28.7	37.0	45.2	49.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360742
CATALOG NUMBER: GSS-SB2D-730-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3695.5	3695.5	*3695.5*
2.5°	3703.7	3707.8	*3703.7*
5°	3728.3	3720.1	*3707.8*
7.5°	3732.4	3736.5	*3740.7*
10°	3748.9	3765.3	*3740.7*
12.5°	3765.3	3753.0	*3744.8*
15°	3777.6	3773.5	*3748.9*
17.5°	3822.8	3806.3	*3802.2*
20°	3892.6	3888.5	*3876.2*
22.5°	3974.7	3966.5	*3962.4*
25°	4093.8	4065.0	*4048.6*
27.5°	4192.3	4167.7	*4159.5*
30°	4290.9	4241.6	*4241.6*
32.5°	4377.1	4364.8	*4356.6*
35°	4582.4	4520.8	*4529.0*
37.5°	4832.9	4771.3	*4717.9*
40°	5186.0	5103.9	*5071.0*
42.5°	5411.8	5329.7	*5337.9*
45°	5539.1	5395.4	*5358.5*
47.5°	5884.0	5703.4	*5654.1*
50°	6442.5	6220.7	*6159.1*
52.5°	7345.8	6988.6	*6906.4*
55°	8479.1	8039.7	*7957.6*
57.5°	10031.2	9448.1	*9271.6*
60°	11920.0	11197.3	*10930.4*
62.5°	14190.7	13299.6	*13045.1*
65°	15898.8	15155.6	*14761.4*
67.5°	17266.1	16654.3	*16465.4*
70°	18079.1	18107.9	*18157.1*
72.5°	*17138.8*	*17927.2*	*18305.0*
75°	12560.5	13172.3	*13759.5*
77.5°	4853.4	4377.1	*4237.5*
80°	784.3	735.0	*759.6*
82.5°	353.1	373.7	*394.2*
85°	229.9	266.9	*283.3*
87.5°	53.4	53.4	*53.4*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-730-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

Spectral Parameters

CCT (K):	2985
CIE u':	0.2504
CIE v':	0.5243
Duv:	0.0019
CIE x:	0.4408
CIE y:	0.4101
CIE z:	0.1491
Peak Wavelength (nm):	595
Dominant Wavelength (nm):	582
Purity:	55.41818
Rf:	73.8
Rg:	94.4

CRI (Ra):	70.8
R1:	66.3
R2:	80.6
R3:	94.5
R4:	68.2
R5:	66.5
R6:	74.7
R7:	76.2
R8:	39.6
R9:	-43.2
R10:	57.6
R11:	64.8
R12:	53.5
R13:	68.7
R14:	97.0
R15:	56.4



Test Conditions


Stabilization Time:	36M
Operation Time:	1H 36M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2985K
CIE x = 0.4408
CIE y = 0.4101
Duv = 0.0019

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.19**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.13**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-4

TM-30-18


Summary


R_f = 73.8
R_g = 94.4
CIE R_a = 70.8
R_9 = -43.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	





REPORT NUMBER: SP1-2407-184-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-4

TM-30-18

Measure Comparisons





(END OF REPORT)