Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1365388

Luminaire Tested: **GSS-SB6B-735-U-SLL-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1365388
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6B-735-U-SLL-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 219W 70CRI 3500K FIXTURE w/ 90° Spill Light Eliminator LETT OPTIC OPTIC AND HOUSE SIDE SHIELD
Light Source:	(156) 3500K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	24882.5 lumens
Efficiency:	N/A
Efficacy:	113.6 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B3 - U0 - G4


Input Watts (W):	219
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365388
CATALOG NUMBER: GSS-SB6B-735-U-SLL-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 15.7 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365388
CATALOG NUMBER: GSS-SB6B-735-U-SLL-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1365388
CATALOG NUMBER: GSS-SB6B-735-U-SLL-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5597.2	0.0	5597.2
	% Fixture	22.5	0.0	22.5
Street Side	Lumens	19285.3	0.0	19285.3
	% Fixture	77.5	0.0	77.5
Total	Lumens	24882.5	0.0	24882.5
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	413.2	1.7
10°-20°	1142.6	4.6
20°-30°	1636.6	6.6
30°-40°	2052.9	8.3
40°-50°	3372.2	13.6
50°-60°	6088.7	24.5
60°-70°	6759.4	27.2
70°-80°	3055.4	12.3
80°-90°	361.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	24882.5	100.0
0°-180°	24882.5	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1365388
CATALOG NUMBER: GSS-SB6B-735-U-SLL-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1797.5	7.2			
FM	(30°-60°)	8382.0	33.7			
FH	(60°-80°)	8795.2	35.3			G4/12000
FVH	(80°-90°)	310.5	1.2			G3/500
BL	(0°-30°)	1394.8	5.6	B3/2500		
BM	(30°-60°)	3131.8	12.6	B3/5000		
BH	(60°-80°)	1019.6	4.1	B3/2500		G3/2500
BVH	(80°-90°)	51.1	0.2			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365388
CATALOG NUMBER: GSS-SB6B-735-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8	*4298.8*	4298.8	4298.8	4298.8	4298.8
2.5°	4734.0	4795.1	4787.4	4871.4	4947.8	5001.2	*5047.0*	5031.8	4993.6	4917.2	4863.8
5°	5230.3	5276.1	5352.5	5512.8	5635.0	5741.9	*5726.6*	5741.9	5627.3	5512.8	5375.4
7.5°	5657.9	5711.3	5818.2	6047.3	6200.0	6329.8	*6314.5*	6268.7	6138.9	5948.0	5741.9
10°	5925.1	5963.3	6077.8	6337.4	6513.0	6619.9	*6581.8*	6505.4	6337.4	6146.5	5902.2
12.5°	6039.6	6085.5	6184.7	6390.9	6505.4	6482.5	*6467.2*	6452.0	6368.0	6222.9	6001.5
15°	6054.9	6085.5	6161.8	6253.4	6207.6	6077.8	*6047.3*	6161.8	6268.7	6238.2	6054.9
17.5°	6054.9	6100.7	6116.0	6024.4	5787.7	5551.0	*5520.4*	5711.3	6009.1	6245.8	6138.9
20°	6077.8	6100.7	6070.2	5772.4	5329.5	5069.9	*5016.5*	5253.2	5696.0	6161.8	6222.9
22.5°	6108.4	6131.3	6001.5	5474.6	4955.4	4680.5	*4650.0*	4825.6	5344.8	6039.6	6314.5
25°	6169.4	6154.2	5955.7	5215.0	4627.1	4367.5	*4321.7*	4550.7	5054.7	5917.5	6467.2
27.5°	6245.8	6177.1	5894.6	5001.2	4390.4	4115.5	*4085.0*	4306.4	4810.3	5764.8	6597.0
30°	6345.1	6276.3	5886.9	4833.2	4214.8	3939.9	*3901.7*	4146.1	4642.4	5657.9	6780.3
32.5°	6482.5	6383.2	5894.6	4703.4	4115.5	3855.9	*3833.0*	4092.6	4573.6	5596.8	6971.2
35°	6665.8	6520.7	5925.1	4657.6	4146.1	3970.4	*4023.9*	4222.4	4642.4	5642.6	7284.2
37.5°	6894.8	6757.4	6077.8	4756.9	4482.0	4604.2	*4741.6*	4818.0	4970.7	5856.4	7788.2
40°	7276.6	7085.7	6306.9	5077.6	5383.0	5955.7	*6222.9*	6192.4	5841.1	6345.1	8498.3
42.5°	7811.1	7635.5	6772.6	5894.6	6887.2	8101.2	*8551.7*	8292.1	7230.8	7123.9	9666.5
45°	8628.1	8337.9	7398.8	7108.6	8704.4	10697.3	*11712.8*	10819.4	8994.6	8353.2	11331.0
47.5°	9674.1	9384.0	8376.1	8322.6	10735.4	13904.2	*15110.6*	13354.4	10743.1	9964.3	13323.9
50°	11353.9	11033.2	9811.6	9559.6	12980.3	17103.4	*18714.5*	15881.7	12522.1	11674.6	15782.5
52.5°	13659.8	13446.0	12086.9	10834.7	14988.4	20631.0	*22020.7*	18523.6	13896.5	13629.3	18462.5
55°	16874.4	16668.2	15049.5	12254.9	16889.6	24166.2	*25288.6*	20928.8	15095.3	15919.9	21264.7
57.5°	20516.5	20860.1	19103.9	14148.5	18890.1	27014.2	*28579.5*	23112.5	16714.0	18981.7	24380.0
60°	22891.1	23975.3	23753.9	17454.6	21997.7	30557.1	*32259.8*	26036.9	19081.0	21234.2	24311.3
62.5°	20829.5	21913.8	23608.8	21287.6	24990.8	33764.0	*35199.4*	29114.0	21432.7	19439.9	20417.2
65°	*17676.1*	*19027.6*	*20814.2*	*18493.1*	*24464.0*	*33863.2*	*35336.9*	*29228.5*	*19997.3*	*14369.9*	*14476.8*
67.5°	15232.7	16431.5	18630.5	15736.7	21684.7	30839.6	*32000.2*	26075.1	16530.8	9529.0	9445.1
70°	12713.0	13812.5	16591.8	14011.1	18997.0	26579.0	*25578.8*	21921.4	13972.9	6329.8	5245.6
72.5°	10834.7	11850.2	14744.1	12590.9	15072.4	21539.6	*17630.3*	18187.7	11369.2	4023.9	3573.4
75°	8964.0	9895.5	12537.4	11399.7	12468.7	13438.4	*12186.2*	12919.2	9368.7	3413.0	2756.4
77.5°	6291.6	6871.9	8796.0	9070.9	9704.7	7956.1	*7727.1*	9048.0	6665.8	1695.1	1160.6
80°	3100.0	3458.9	4588.9	5398.3	4588.9	4512.6	*5146.3*	6024.4	3458.9	1038.4	641.4
82.5°	1389.7	1649.3	2115.0	3268.0	1656.9	1802.0	*2275.4*	3206.9	1572.9	618.5	274.9
85°	221.4	244.3	412.3	549.8	450.5	694.8	*664.3*	626.1	336.0	168.0	76.4
87.5°	7.6	7.6	7.6	15.3	22.9	30.5	*38.2*	38.2	38.2	38.2	38.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365388
CATALOG NUMBER: GSS-SB6B-735-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8
2.5°	4848.5	4825.6	4711.1	4596.5	4497.3	4398.0	4298.8	4161.3	4054.4	3962.8	3924.6
5°	5306.6	5184.5	5008.9	4818.0	4650.0	4459.1	4275.9	4069.7	3901.7	3726.1	3634.5
7.5°	5619.7	5497.5	5207.4	4917.2	4711.1	4504.9	4314.0	4085.0	3863.5	3611.6	3474.1
10°	5764.8	5627.3	5314.3	4978.3	4726.3	4520.2	4344.6	4153.7	3932.3	3619.2	3436.0
12.5°	5864.0	5696.0	5337.2	4993.6	4741.6	4527.8	4359.8	4222.4	4092.6	3787.2	3573.4
15°	5925.1	5772.4	5398.3	5001.2	4718.7	4466.7	4306.4	4260.6	4283.5	4138.4	3878.8
17.5°	6016.7	5871.7	5474.6	5047.0	4680.5	4336.9	4161.3	4260.6	4466.7	4512.6	4306.4
20°	6138.9	5986.2	5573.9	5085.2	4566.0	4092.6	3924.6	4176.6	4520.2	4756.9	4642.4
22.5°	6276.3	6154.2	5688.4	5123.4	4398.0	3771.9	3695.6	4001.0	4367.5	4672.9	4680.5
25°	6444.3	6329.8	5848.8	5161.6	4169.0	3497.0	3512.3	3771.9	4062.1	4375.1	4428.6
27.5°	6673.4	6566.5	6047.3	5207.4	3932.3	3275.6	3352.0	3542.9	3741.4	3932.3	4008.6
30°	6925.4	6841.4	6284.0	5299.0	3710.8	3145.8	3191.6	3321.4	3481.8	3596.3	3634.5
32.5°	7269.0	7131.5	6505.4	5291.4	3542.9	3084.7	3038.9	3077.1	3206.9	3321.4	3329.1
35°	7696.5	7589.6	6734.5	5153.9	3390.1	3054.2	2893.8	2870.9	2947.3	3061.8	3054.2
37.5°	8322.6	8231.0	7108.6	4940.1	3199.3	2977.8	2741.1	2664.8	2718.2	2794.6	2817.5
40°	9261.8	9025.1	7536.2	4703.4	3008.4	2840.4	2557.9	2451.0	2489.2	2573.1	2588.4
42.5°	10536.9	10086.4	8108.9	4382.8	2825.1	2634.2	2374.6	2260.1	2283.0	2359.4	2374.6
45°	12170.9	11491.4	8895.3	4046.8	2680.0	2420.4	2183.7	2061.6	2084.5	2168.5	2206.6
47.5°	14079.8	13148.3	9719.9	3687.9	2596.1	2252.5	1992.9	1901.2	1954.7	2038.7	2053.9
50°	16332.2	15393.1	10246.8	3397.8	2542.6	2122.7	1817.2	1779.1	1847.8	1916.5	1931.8
52.5°	18790.9	17454.6	9910.8	3161.1	2496.8	2076.8	1695.1	1710.3	1763.8	1832.5	1855.4
55°	21180.8	18210.6	8796.0	2855.7	2443.3	2107.4	1603.4	1641.6	1710.3	1763.8	1779.1
57.5°	22738.4	17576.8	7085.7	2535.0	2382.3	2130.3	1557.6	1588.2	1664.5	1725.6	1733.2
60°	21379.3	16187.2	5306.6	2260.1	2252.5	2092.1	1542.4	1496.5	1603.4	1656.9	1664.5
62.5°	17515.7	13239.9	3390.1	2000.5	2008.1	2008.1	1534.7	1343.8	1481.3	1527.1	1519.5
65°	*12033.5*	*9361.1*	*2099.7*	*1634.0*	*1710.3*	*1824.9*	*1488.9*	*1183.5*	*1343.8*	*1389.7*	*1374.4*
67.5°	7910.3	5948.0	1298.0	1259.8	1404.9	1580.5	1397.3	1061.3	1206.4	1236.9	1191.1
70°	4291.1	2802.2	855.2	824.6	1099.5	1244.6	1183.5	954.4	1076.6	1107.1	1061.3
72.5°	2832.8	1611.1	603.2	603.2	862.8	870.4	969.7	855.2	954.4	985.0	939.2
75°	2130.3	1038.4	419.9	465.8	549.8	679.6	694.8	717.7	809.4	847.5	801.7
77.5°	977.3	381.8	252.0	343.6	381.8	519.2	442.9	534.5	603.2	618.5	580.3
80°	565.0	213.8	168.0	221.4	244.3	427.6	259.6	320.7	427.6	450.5	404.7
82.5°	236.7	106.9	114.5	137.4	145.1	236.7	183.3	206.2	282.5	274.9	244.3
85°	68.7	68.7	76.4	84.0	84.0	137.4	129.8	122.2	129.8	129.8	106.9
87.5°	45.8	45.8	45.8	53.4	53.4	61.1	68.7	76.4	76.4	76.4	68.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365388
CATALOG NUMBER: GSS-SB6B-735-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8
2.5°	3871.2	3802.5	3703.2	3687.9	3634.5	3596.3	3634.5	3672.7	3741.4	3749.0	3779.5
5°	3550.5	3390.1	3268.0	3130.5	3061.8	3054.2	3038.9	3084.7	3184.0	3245.1	3290.9
7.5°	3336.7	3046.5	2832.8	2641.9	2573.1	2519.7	2565.5	2557.9	2687.7	2741.1	2786.9
10°	3222.2	2817.5	2496.8	2260.1	2168.5	2115.0	2107.4	2122.7	2199.0	2252.5	2305.9
12.5°	3298.5	2725.9	2252.5	1977.6	1878.3	1817.2	1763.8	1763.8	1779.1	1847.8	1870.7
15°	3550.5	2779.3	2137.9	1840.1	1710.3	1611.1	1542.4	1488.9	1496.5	1504.2	1527.1
17.5°	3917.0	2916.7	2099.7	1756.2	1618.7	1496.5	1427.8	1366.7	1351.5	1351.5	1343.8
20°	4268.2	3023.6	2069.2	1687.4	1511.8	1404.9	1343.8	1290.4	1267.5	1267.5	1267.5
22.5°	4413.3	3115.3	2031.0	1603.4	1404.9	1305.7	1252.2	1214.0	1206.4	1206.4	1198.8
25°	4298.8	3084.7	1985.2	1519.5	1305.7	1229.3	1183.5	1145.3	1137.7	1145.3	1137.7
27.5°	3939.9	2977.8	1924.1	1450.7	1229.3	1160.6	1122.4	1084.2	1076.6	1084.2	1084.2
30°	3558.1	2794.6	1824.9	1397.3	1168.2	1091.9	1053.7	1015.5	1015.5	1023.2	1030.8
32.5°	3252.7	2611.3	1710.3	1328.6	1099.5	1030.8	992.6	954.4	954.4	969.7	969.7
35°	2993.1	2466.3	1595.8	1259.8	1038.4	962.1	931.5	901.0	893.3	908.6	916.3
37.5°	2786.9	2336.4	1473.6	1191.1	977.3	908.6	878.1	839.9	832.3	847.5	862.8
40°	2573.1	2191.4	1366.7	1107.1	916.3	847.5	817.0	771.2	771.2	786.5	801.7
42.5°	2367.0	2061.6	1298.0	1030.8	855.2	778.8	748.3	710.1	710.1	725.4	740.6
45°	2199.0	1939.4	1259.8	954.4	786.5	717.7	679.6	649.0	656.6	671.9	687.2
47.5°	2038.7	1809.6	1267.5	916.3	740.6	649.0	610.8	587.9	603.2	626.1	641.4
50°	1916.5	1718.0	1275.1	855.2	679.6	595.6	557.4	542.1	565.0	587.9	603.2
52.5°	1840.1	1626.4	1229.3	778.8	633.7	542.1	519.2	519.2	542.1	557.4	572.7
55°	1763.8	1473.6	1130.0	694.8	587.9	503.9	488.7	488.7	511.6	526.8	534.5
57.5°	1702.7	1313.3	1015.5	626.1	534.5	465.8	465.8	465.8	473.4	481.0	496.3
60°	1588.2	1145.3	870.4	572.7	481.0	435.2	427.6	427.6	419.9	427.6	450.5
62.5°	1389.7	962.1	740.6	511.6	435.2	397.0	389.4	366.5	343.6	351.2	366.5
65°	*1175.9*	*763.5*	*618.5*	*442.9*	*374.1*	*351.2*	*343.6*	*305.4*	*274.9*	*282.5*	*305.4*
67.5°	939.2	572.7	519.2	381.8	320.7	297.8	297.8	274.9	252.0	252.0	267.2
70°	733.0	481.0	389.4	305.4	252.0	252.0	267.2	244.3	213.8	213.8	236.7
72.5°	595.6	389.4	313.1	236.7	198.5	213.8	221.4	198.5	175.6	175.6	190.9
75°	465.8	305.4	244.3	175.6	152.7	160.3	175.6	160.3	137.4	145.1	152.7
77.5°	320.7	206.2	160.3	129.8	114.5	122.2	122.2	114.5	106.9	106.9	114.5
80°	213.8	137.4	106.9	91.6	84.0	84.0	76.4	76.4	84.0	84.0	91.6
82.5°	152.7	99.3	84.0	68.7	53.4	53.4	61.1	61.1	68.7	68.7	76.4
85°	91.6	68.7	61.1	45.8	38.2	45.8	45.8	53.4	61.1	61.1	68.7
87.5°	68.7	53.4	45.8	38.2	30.5	30.5	38.2	38.2	45.8	53.4	53.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1365388
CATALOG NUMBER: GSS-SB6B-735-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8	4298.8
2.5°	3855.9	3947.5	4077.3	4191.9	4329.3	4466.7	4596.5	4718.7	4726.3	4734.0
5°	3436.0	3619.2	3833.0	4092.6	4367.5	4634.7	4917.2	5146.3	5199.7	5230.3
7.5°	2970.2	3237.4	3565.8	3932.3	4344.6	4756.9	5153.9	5497.5	5627.3	5657.9
10°	2481.5	2809.8	3206.9	3680.3	4237.7	4787.4	5321.9	5741.9	5894.6	5925.1
12.5°	2046.3	2313.5	2771.7	3344.3	4016.2	4741.6	5383.0	5848.8	6001.5	6039.6
15°	1672.2	1924.1	2351.7	2954.9	3710.8	4581.3	5337.2	5871.7	6024.4	6054.9
17.5°	1382.0	1542.4	1931.8	2588.4	3436.0	4375.1	5276.1	5886.9	6032.0	6054.9
20°	1267.5	1298.0	1504.2	2145.6	3145.8	4222.4	5237.9	5909.8	6054.9	6077.8
22.5°	1214.0	1214.0	1259.8	1634.0	2741.1	4062.1	5222.7	5978.6	6085.5	6108.4
25°	1160.6	1160.6	1175.9	1282.8	2260.1	3863.5	5253.2	6100.7	6169.4	6169.4
27.5°	1107.1	1107.1	1122.4	1145.3	1679.8	3535.2	5260.8	6238.2	6268.7	6245.8
30°	1053.7	1069.0	1069.0	1084.2	1236.9	3122.9	5215.0	6390.9	6390.9	6345.1
32.5°	1000.2	1007.9	1023.2	1030.8	1076.6	2588.4	5138.7	6581.8	6543.6	6482.5
35°	954.4	962.1	962.1	977.3	1023.2	2069.2	5054.7	6841.4	6734.5	6665.8
37.5°	893.3	901.0	908.6	923.9	969.7	1641.6	4932.5	7062.8	6986.4	6894.8
40°	839.9	847.5	855.2	870.4	916.3	1412.6	4779.8	7398.8	7383.5	7276.6
42.5°	778.8	794.1	801.7	809.4	870.4	1290.4	4672.9	7940.9	7940.9	7811.1
45°	725.4	740.6	740.6	755.9	839.9	1183.5	4909.6	8689.1	8750.2	8628.1
47.5°	679.6	687.2	687.2	694.8	794.1	1091.9	5543.3	9834.5	9758.1	9674.1
50°	633.7	649.0	633.7	641.4	755.9	1145.3	6589.4	11300.5	11499.0	11353.9
52.5°	603.2	610.8	580.3	580.3	702.5	1214.0	7444.6	13171.2	13835.4	13659.8
55°	565.0	572.7	534.5	534.5	618.5	1053.7	7498.0	15301.5	16759.8	16874.4
57.5°	526.8	526.8	496.3	488.7	534.5	855.2	6650.5	16950.7	20256.9	20516.5
60°	481.0	473.4	458.1	442.9	488.7	786.5	5069.9	16729.3	21990.1	22891.1
62.5°	412.3	427.6	419.9	389.4	442.9	733.0	3306.2	14476.8	20035.4	20829.5
65°	*343.6*	*366.5*	*366.5*	*343.6*	*488.7*	*641.4*	*1740.9*	*11590.6*	*16721.6*	*17676.1*
67.5°	305.4	320.7	313.1	297.8	435.2	404.7	839.9	8887.7	14316.5	15232.7
70°	267.2	282.5	259.6	244.3	351.2	290.1	496.3	5948.0	11819.7	12713.0
72.5°	221.4	236.7	213.8	190.9	259.6	221.4	328.3	3871.2	9842.1	10834.7
75°	183.3	190.9	175.6	152.7	190.9	175.6	229.1	2527.3	8231.0	8964.0
77.5°	129.8	145.1	137.4	114.5	137.4	122.2	160.3	1443.1	5741.9	6291.6
80°	99.3	99.3	99.3	91.6	84.0	84.0	106.9	649.0	2786.9	3100.0
82.5°	84.0	84.0	76.4	68.7	61.1	53.4	61.1	190.9	1313.3	1389.7
85°	76.4	61.1	53.4	45.8	38.2	22.9	22.9	53.4	267.2	221.4
87.5°	45.8	38.2	30.5	15.3	7.6	7.6	0.0	7.6	7.6	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ

Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-735-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369
CIE u':	0.2386
CIE v':	0.5156
Duv:	0.0013
CIE x:	0.4143
CIE y:	0.3980
CIE z:	0.1877
Peak Wavelength (nm):	590
Dominant Wavelength (nm):	580
Purity:	43.80166
Rf:	71.4
Rg:	96

CRI (Ra):	70.1
R1:	66.6
R2:	77.6
R3:	88.5
R4:	69.5
R5:	66.4
R6:	69.6
R7:	77.5
R8:	44.9
R9:	-40.2
R10:	49.1
R11:	66.3
R12:	45.7
R13:	68.0
R14:	93.4
R15:	57.6



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3369K
CIE x = 0.4143
CIE y = 0.3980
Duv = 0.0013

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.36**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-5

TM-30-18


Summary


R_f = 71.4
R_g = 96
CIE R_a = 70.1
R_9 = -40.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	





REPORT NUMBER: SP1-2407-184-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-5

TM-30-18

Measure Comparisons





(END OF REPORT)