Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360771

Luminaire Tested: **GSS-SB4A-735-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360771
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4A-735-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 114W 70CRI 3500K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(104) 3500K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	17201.1 lumens
Efficiency:	N/A
Efficacy:	150.9 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	114
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.2%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360771
CATALOG NUMBER: GSS-SB4A-735-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 8.5 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360771
CATALOG NUMBER: GSS-SB4A-735-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360771
CATALOG NUMBER: GSS-SB4A-735-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	8600.5	0.0	8600.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	8600.5	0.0	8600.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	17201.1	0.0	17201.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.0	1.9
10°-20°	999.8	5.8
20°-30°	1671.1	9.7
30°-40°	2304.5	13.4
40°-50°	2825.0	16.4
50°-60°	3310.5	19.2
60°-70°	3676.3	21.4
70°-80°	1999.2	11.6
80°-90°	86.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	17201.1	100.0
0°-180°	17201.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360771
CATALOG NUMBER: GSS-SB4A-735-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1499.4	8.7			
FM	(30°-60°)	4220.0	24.5			
FH	(60°-80°)	2837.7	16.5			G2/5000
FVH	(80°-90°)	43.3	0.3			G1/100
BL	(0°-30°)	1499.4	8.7	B3/2500		
BM	(30°-60°)	4220.0	24.5	B3/5000		
BH	(60°-80°)	2837.7	16.5	B4/5000		G4/5000
BVH	(80°-90°)	43.3	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360771
CATALOG NUMBER: GSS-SB4A-735-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3389.0	3389.0	3389.0	3389.0	3389.0	3389.0	3389.0	3389.0	3389.0	3389.0	3389.0
2.5°	3392.8	3392.8	3381.5	3396.6	3389.0	3392.8	3396.6	3392.8	3389.0	3392.8	3396.6
5°	3411.6	3404.1	3411.6	3419.2	3407.9	3415.4	3411.6	3392.8	3404.1	3404.1	3404.1
7.5°	3445.5	3453.1	3445.5	3464.4	3453.1	3475.7	3453.1	3438.0	3434.2	3430.5	3430.5
10°	3460.6	3460.6	3456.8	3490.7	3498.2	3520.8	3505.8	3483.2	3471.9	3456.8	3441.8
12.5°	3419.2	3426.7	3445.5	3509.5	3539.7	3584.9	3573.6	3528.4	3494.5	3483.2	3460.6
15°	3374.0	3381.5	3419.2	3498.2	3569.8	3637.6	3633.8	3577.3	3535.9	3505.8	3471.9
17.5°	3302.4	3313.7	3366.4	3486.9	3615.0	3690.3	3712.9	3656.4	3611.2	3562.3	3517.1
20°	3181.9	3181.9	3276.1	3430.5	3607.4	3776.9	3837.1	3792.0	3739.2	3660.2	3599.9
22.5°	3046.4	3053.9	3148.0	3351.4	3603.7	3852.2	3968.9	3920.0	3867.3	3780.7	3690.3
25°	2910.8	2910.8	3016.2	3245.9	3554.7	3904.9	4123.3	4097.0	3991.5	3912.5	3795.7
27.5°	2786.5	2786.5	2899.5	3140.5	3471.9	3920.0	4277.7	4277.7	4161.0	4044.3	3916.2
30°	2639.7	2677.3	2805.4	3057.7	3396.6	3893.6	4390.7	4462.2	4356.8	4206.2	4017.9
32.5°	2515.4	2541.8	2673.6	2940.9	3287.4	3863.5	4518.7	4695.7	4586.5	4379.4	4168.5
35°	2368.6	2364.8	2515.4	2779.0	3133.0	3795.7	4620.4	4974.4	4868.9	4646.8	4360.6
37.5°	2176.5	2176.5	2330.9	2587.0	2986.1	3679.0	4703.2	5283.1	5204.1	4951.8	4646.8
40°	1969.4	1992.0	2127.6	2387.4	2809.1	3539.7	4703.2	5535.4	5576.9	5317.0	5000.7
42.5°	1818.8	1826.3	1950.6	2195.3	2613.3	3358.9	4643.0	5753.8	5878.1	5659.7	5249.2
45°	1660.6	1679.5	1784.9	2010.8	2410.0	3144.3	4537.6	5998.6	6198.2	6047.6	5509.1
47.5°	1468.6	1487.4	1607.9	1837.6	2217.9	2910.8	4360.6	6254.7	6672.6	6563.4	5972.2
50°	1246.4	1261.5	1374.4	1619.2	2003.3	2643.5	4138.4	6446.7	7147.1	7256.3	6672.6
52.5°	975.3	986.6	1107.1	1344.3	1747.2	2387.4	3825.9	6563.4	7625.3	8009.4	7610.3
55°	700.4	719.2	824.7	1020.5	1408.3	2044.7	3453.1	6623.7	8148.8	8901.9	8773.9
57.5°	504.6	512.1	583.7	734.3	1046.8	1641.8	2974.8	6522.0	8619.5	9967.5	10234.9
60°	418.0	418.0	429.3	500.8	715.5	1159.8	2402.5	6145.5	9022.4	11044.5	11869.2
62.5°	384.1	384.1	391.6	402.9	470.7	753.1	1717.1	5381.0	9067.6	12080.1	13661.6
65°	350.2	350.2	357.7	365.3	380.3	489.5	1035.5	3938.8	8182.7	12091.3	14625.6
67.5°	320.1	320.1	323.8	327.6	335.1	357.7	568.6	2387.4	6548.4	11771.3	14994.6
70°	290.0	290.0	290.0	286.2	297.5	301.2	376.6	1212.5	4379.4	10630.3	14817.6
72.5°	*256.1*	*256.1*	*252.3*	*244.8*	*248.5*	*248.5*	*278.7*	*595.0*	*2274.4*	*8450.0*	*13379.2*
75°	218.4	222.2	207.1	199.6	195.8	199.6	222.2	338.9	1016.7	5125.0	9997.7
77.5°	184.5	192.0	169.5	154.4	150.6	150.6	173.2	210.9	436.8	1860.2	4481.1
80°	139.3	143.1	124.3	109.2	109.2	105.4	128.0	154.4	207.1	553.5	1005.4
82.5°	79.1	79.1	71.5	64.0	60.2	64.0	86.6	105.4	128.0	195.8	274.9
85°	18.8	18.8	22.6	26.4	26.4	33.9	49.0	56.5	67.8	79.1	105.4
87.5°	3.8	3.8	3.8	7.5	11.3	11.3	18.8	26.4	33.9	41.4	45.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360771
CATALOG NUMBER: GSS-SB4A-735-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3389.0	3389.0	*3389.0*
2.5°	3396.6	3400.3	*3396.6*
5°	3419.2	3411.6	*3400.3*
7.5°	3422.9	3426.7	*3430.5*
10°	3438.0	3453.1	*3430.5*
12.5°	3453.1	3441.8	*3434.2*
15°	3464.4	3460.6	*3438.0*
17.5°	3505.8	3490.7	*3486.9*
20°	3569.8	3566.0	*3554.7*
22.5°	3645.1	3637.6	*3633.8*
25°	3754.3	3727.9	*3712.9*
27.5°	3844.7	3822.1	*3814.6*
30°	3935.1	3889.9	*3889.9*
32.5°	4014.1	4002.8	*3995.3*
35°	4202.4	4145.9	*4153.5*
37.5°	4432.1	4375.6	*4326.7*
40°	4756.0	4680.6	*4650.5*
42.5°	4963.1	4887.8	*4895.3*
45°	5079.8	4948.0	*4914.1*
47.5°	5396.1	5230.4	*5185.2*
50°	5908.2	5704.9	*5648.4*
52.5°	6736.7	6409.1	*6333.7*
55°	7776.0	7373.0	*7297.7*
57.5°	9199.4	8664.6	*8502.7*
60°	10931.5	10268.8	*10024.0*
62.5°	13013.9	12196.8	*11963.3*
65°	14580.4	13898.8	*13537.3*
67.5°	15834.4	15273.3	*15100.1*
70°	16579.9	16606.3	*16651.5*
72.5°	*15717.6*	*16440.6*	*16787.1*
75°	11519.0	12080.1	*12618.5*
77.5°	4450.9	4014.1	*3886.1*
80°	719.2	674.0	*696.6*
82.5°	323.8	342.7	*361.5*
85°	210.9	244.8	*259.8*
87.5°	49.0	49.0	*49.0*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ

Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-735-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369
CIE u':	0.2386
CIE v':	0.5156
Duv:	0.0013
CIE x:	0.4143
CIE y:	0.3980
CIE z:	0.1877
Peak Wavelength (nm):	590
Dominant Wavelength (nm):	580
Purity:	43.80166
Rf:	71.4
Rg:	96

CRI (Ra):	70.1
R1:	66.6
R2:	77.6
R3:	88.5
R4:	69.5
R5:	66.4
R6:	69.6
R7:	77.5
R8:	44.9
R9:	-40.2
R10:	49.1
R11:	66.3
R12:	45.7
R13:	68.0
R14:	93.4
R15:	57.6



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3369K
CIE x = 0.4143
CIE y = 0.3980
Duv = 0.0013

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.36**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-5

TM-30-18


Summary


R_f = 71.4
R_g = 96
CIE R_a = 70.1
R_9 = -40.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	





REPORT NUMBER: SP1-2407-184-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-5

TM-30-18

Measure Comparisons





(END OF REPORT)