Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360395

Luminaire Tested: **GSS-SB6A-735-U-T3-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360395
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6A-735-U-T3-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 170W 70CRI 3500K FIXTURE w/ TYPE III DISTRIBUTION OPTIC AND HOUSE SIDE SHIELD
Light Source:	(156) 3500K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	18956.8 lumens
Efficiency:	N/A
Efficacy:	111.5 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B2 - U0 - G3


Input Watts (W):	170
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	12.0%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360395
CATALOG NUMBER: GSS-SB6A-735-U-T3-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 8.6 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360395
CATALOG NUMBER: GSS-SB6A-735-U-T3-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360395
CATALOG NUMBER: GSS-SB6A-735-U-T3-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2266.6	0.0	2266.6
	% Fixture	12.0	0.0	12.0
Street Side	Lumens	16690.2	0.0	16690.2
	% Fixture	88.0	0.0	88.0
Total	Lumens	18956.8	0.0	18956.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.8	1.3
10°-20°	631.9	3.3
20°-30°	1126.5	5.9
30°-40°	2016.1	10.6
40°-50°	3175.9	16.8
50°-60°	4619.2	24.4
60°-70°	5025.8	26.5
70°-80°	2030.3	10.7
80°-90°	85.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	18956.8	100.0
0°-180°	18956.8	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360395
CATALOG NUMBER: GSS-SB6A-735-U-T3-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1336.7	7.1			
FM	(30°-60°)	8557.6	45.1			
FH	(60°-80°)	6726.6	35.5			G3/7500
FVH	(80°-90°)	69.2	0.4			G1/100
BL	(0°-30°)	667.5	3.5	B2/1000		
BM	(30°-60°)	1253.6	6.6	B2/2500		
BH	(60°-80°)	329.5	1.7	B1/500		G1/500
BVH	(80°-90°)	16.1	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360395
CATALOG NUMBER: GSS-SB6A-735-U-T3-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	51°	55°	65°	75°	85°
0°	2691.8	2691.8	2691.8	2691.8	2691.8	2691.8	*2691.8*	2691.8	2691.8	2691.8	2691.8
2.5°	2714.6	2708.9	2714.6	2691.8	2703.2	2708.9	*2720.2*	2703.2	2697.5	2703.2	2697.5
5°	2703.2	2697.5	2703.2	2708.9	2720.2	2737.3	*2731.6*	2731.6	2742.9	2720.2	2720.2
7.5°	2606.7	2601.0	2635.0	2646.4	2691.8	2731.6	*2777.0*	2760.0	2782.7	2777.0	2760.0
10°	2487.4	2470.4	2504.4	2566.9	2635.0	2737.3	*2782.7*	2794.1	2845.2	2867.9	2856.5
12.5°	2419.2	2402.2	2447.6	2493.1	2601.0	2725.9	*2805.4*	2833.8	2890.6	2936.0	2947.4
15°	2368.1	2385.2	2430.6	2515.8	2618.0	2748.6	*2816.8*	2873.6	2992.8	3038.3	3038.3
17.5°	2402.2	2396.5	2436.3	2521.5	2646.4	2777.0	*2879.2*	2936.0	3078.0	3140.5	3134.8
20°	2737.3	2703.2	2697.5	2652.1	2691.8	2845.2	*2970.1*	3026.9	3163.2	3248.4	3242.7
22.5°	3168.9	3202.9	3112.1	3009.9	2884.9	2936.0	*3066.7*	3146.2	3282.5	3373.3	3339.2
25°	3753.8	3736.8	3674.3	3469.9	3242.7	3134.8	*3202.9*	3282.5	3452.8	3526.6	3469.9
27.5°	4372.8	4299.0	4219.5	3935.5	3634.5	3435.8	*3447.1*	3498.3	3697.0	3742.4	3611.8
30°	5037.3	5048.6	4918.0	4531.8	4117.3	3816.3	*3793.6*	3816.3	3975.3	3969.6	3787.9
32.5°	5798.2	5769.8	5644.9	5230.3	4770.3	4276.3	*4219.5*	4179.7	4247.9	4185.4	3975.3
35°	6332.1	6360.5	6224.2	5951.6	5491.6	4878.2	*4742.0*	4645.4	4577.3	4509.1	4282.0
37.5°	6809.1	6775.0	6695.5	6542.2	6093.5	5531.3	*5270.1*	5184.9	5037.3	4849.9	4639.7
40°	6917.0	6900.0	6860.2	6865.9	6576.3	6139.0	*5951.6*	5798.2	5542.7	5389.4	5116.8
42.5°	6900.0	6956.8	6968.1	7013.5	6848.9	6741.0	*6547.9*	6400.2	6161.7	5974.3	5690.3
45°	6990.8	7087.4	7166.9	7206.6	7098.7	7087.4	*7110.1*	7041.9	6877.2	6684.2	6360.5
47.5°	7172.6	7337.2	7462.2	7547.4	7524.7	7712.1	*7592.8*	7575.8	7643.9	7456.5	7132.8
50°	7513.3	7558.7	7854.0	7979.0	8189.1	8461.7	*8228.8*	8285.6	8421.9	8439.0	7842.7
52.5°	7768.8	7808.6	8103.9	8473.0	8938.7	9239.7	*9029.6*	9023.9	9268.1	9336.2	8529.8
55°	7837.0	7927.9	8308.4	8950.1	9824.6	10131.3	*9983.7*	9932.5	10256.2	10375.5	9137.5
57.5°	7740.5	7774.5	8319.7	9245.4	10466.4	11130.8	*11176.2*	11017.2	11312.5	11340.9	9586.1
60°	6695.5	6843.2	7797.2	9432.8	11011.5	12215.5	*12454.0*	12363.1	12385.9	12334.7	9921.2
62.5°	4628.4	4656.8	6059.5	9234.0	11460.2	13311.5	*13709.1*	13640.9	13447.8	12965.1	9750.8
65°	2203.4	2356.8	3254.1	7814.3	11522.7	14146.3	*14918.7*	14964.1	14066.8	12970.8	9092.1
67.5°	*1516.3*	*1522.0*	*1732.1*	*5514.3*	*9773.5*	*14384.9*	*15566.1*	*15356.0*	*14010.0*	*12851.5*	*8285.6*
70°	959.7	891.6	999.5	3146.2	6604.7	11295.5	*13885.1*	14623.4	13771.5	12073.5	7002.2
72.5°	380.5	408.9	471.4	1033.6	3237.0	6434.3	*9069.3*	11130.8	12419.9	10443.6	5468.9
75°	170.4	181.7	238.5	431.6	834.8	2623.7	*3509.6*	4918.0	9938.2	8245.9	3873.1
77.5°	113.6	119.3	153.3	249.9	380.5	732.6	*1283.5*	1504.9	5957.3	4509.1	1817.3
80°	68.1	73.8	102.2	153.3	210.1	261.2	*391.8*	454.3	1573.1	1493.6	499.8
82.5°	45.4	39.8	68.1	85.2	124.9	107.9	*124.9*	147.7	431.6	380.5	136.3
85°	17.0	17.0	28.4	34.1	45.4	56.8	*51.1*	62.5	102.2	102.2	62.5
87.5°	0.0	0.0	5.7	5.7	17.0	22.7	*28.4*	28.4	39.8	39.8	34.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360395
CATALOG NUMBER: GSS-SB6A-735-U-T3-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2691.8	2691.8	2691.8	2691.8	2691.8	2691.8	2691.8	2691.8	2691.8	2691.8	2691.8
2.5°	2703.2	2686.2	2691.8	2680.5	2686.2	2674.8	2652.1	2674.8	2657.8	2657.8	2674.8
5°	2720.2	2714.6	2697.5	2669.1	2652.1	2612.3	2549.9	2521.5	2493.1	2476.0	2487.4
7.5°	2777.0	2754.3	2725.9	2657.8	2566.9	2447.6	2322.7	2180.7	2072.8	2061.5	2021.7
10°	2850.8	2828.1	2765.7	2612.3	2424.9	2084.2	1811.6	1624.2	1510.6	1436.8	1408.4
12.5°	2947.4	2919.0	2805.4	2544.2	2084.2	1607.2	1283.5	1147.2	1107.4	1090.4	1084.7
15°	3038.3	3004.2	2805.4	2322.7	1686.7	1209.6	1044.9	1010.9	1005.2	1010.9	1005.2
17.5°	3123.4	3078.0	2777.0	2021.7	1294.8	1022.2	982.5	965.4	959.7	954.1	954.1
20°	3225.7	3151.8	2697.5	1692.3	1067.6	971.1	954.1	931.4	931.4	908.6	914.3
22.5°	3322.2	3220.0	2544.2	1363.0	982.5	942.7	925.7	903.0	891.6	874.6	874.6
25°	3418.7	3288.1	2362.5	1130.1	931.4	914.3	897.3	874.6	846.2	823.5	823.5
27.5°	3560.7	3379.0	2146.7	1033.6	903.0	874.6	857.5	829.1	795.1	766.7	766.7
30°	3719.7	3503.9	1970.6	1016.5	891.6	823.5	795.1	749.6	726.9	704.2	704.2
32.5°	3912.8	3674.3	1840.0	1044.9	863.2	755.3	709.9	664.4	647.4	647.4	647.4
35°	4196.8	3924.2	1698.0	1050.6	829.1	687.2	613.3	567.9	567.9	590.6	590.6
37.5°	4577.3	4196.8	1624.2	1039.3	800.7	619.0	533.8	499.8	494.1	516.8	516.8
40°	5014.5	4497.8	1652.6	999.5	761.0	550.9	471.4	443.0	437.3	443.0	448.6
42.5°	5491.6	4821.5	1720.7	942.7	692.8	494.1	425.9	408.9	403.2	403.2	403.2
45°	5997.0	5042.9	1788.9	885.9	624.7	448.6	397.5	386.2	380.5	380.5	380.5
47.5°	6479.7	5219.0	1743.4	834.8	567.9	420.2	374.8	374.8	369.1	369.1	369.1
50°	6894.3	5201.9	1550.4	783.7	505.4	397.5	363.5	357.8	357.8	352.1	352.1
52.5°	7127.1	4855.5	1249.4	726.9	448.6	374.8	352.1	346.4	340.7	335.1	335.1
55°	7218.0	4395.5	971.1	641.7	408.9	357.8	340.7	335.1	323.7	318.0	312.3
57.5°	7059.0	3719.7	749.6	511.1	374.8	335.1	323.7	318.0	306.7	289.6	283.9
60°	6735.3	2981.5	562.2	391.8	335.1	306.7	306.7	301.0	278.3	249.9	244.2
62.5°	6167.4	2141.0	425.9	318.0	289.6	278.3	289.6	278.3	244.2	204.4	198.8
65°	5366.6	1323.2	329.4	272.6	255.6	244.2	261.2	249.9	210.1	164.7	153.3
67.5°	*4486.4*	*675.8*	*255.6*	*232.8*	*215.8*	*204.4*	*221.5*	*221.5*	*181.7*	*136.3*	*130.6*
70°	3464.2	374.8	204.4	193.1	176.0	159.0	187.4	193.1	159.0	119.3	113.6
72.5°	2572.6	238.5	164.7	159.0	136.3	113.6	153.3	164.7	136.3	90.9	85.2
75°	1681.0	187.4	124.9	124.9	96.5	90.9	130.6	142.0	119.3	68.1	68.1
77.5°	806.4	142.0	96.5	85.2	68.1	68.1	113.6	119.3	85.2	51.1	51.1
80°	266.9	96.5	68.1	56.8	45.4	45.4	90.9	68.1	45.4	39.8	39.8
82.5°	90.9	62.5	45.4	39.8	34.1	28.4	28.4	34.1	34.1	28.4	28.4
85°	45.4	39.8	34.1	28.4	22.7	22.7	22.7	22.7	28.4	28.4	28.4
87.5°	28.4	28.4	22.7	17.0	17.0	17.0	17.0	17.0	22.7	11.4	11.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ

Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-735-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369
CIE u':	0.2386
CIE v':	0.5156
Duv:	0.0013
CIE x:	0.4143
CIE y:	0.3980
CIE z:	0.1877
Peak Wavelength (nm):	590
Dominant Wavelength (nm):	580
Purity:	43.80166
Rf:	71.4
Rg:	96

CRI (Ra):	70.1
R1:	66.6
R2:	77.6
R3:	88.5
R4:	69.5
R5:	66.4
R6:	69.6
R7:	77.5
R8:	44.9
R9:	-40.2
R10:	49.1
R11:	66.3
R12:	45.7
R13:	68.0
R14:	93.4
R15:	57.6



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3369K
CIE x = 0.4143
CIE y = 0.3980
Duv = 0.0013

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.36**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-5

TM-30-18


Summary


R_f = 71.4
R_g = 96
CIE R_a = 70.1
R_9 = -40.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	





REPORT NUMBER: SP1-2407-184-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-5

TM-30-18

Measure Comparisons





(END OF REPORT)