Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1359992

Luminaire Tested: **GSS-SB1B-735-U-T3**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1359992
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB1B-735-U-T3
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 1SQUARE 40W 70CRI 3500K FIXTURE w/ TYPE III DISTRIBUTION OPTIC
Light Source:	(26) 3500K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	5010.2 lumens
Efficiency:	N/A
Efficacy:	125.3 lumens/watt
Luminous Opening:	Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B1 - U0 - G1


Input Watts (W):	40
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	5.3%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359992
CATALOG NUMBER: GSS-SB1B-735-U-T3

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 2.2 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359992
CATALOG NUMBER: GSS-SB1B-735-U-T3

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1359992
CATALOG NUMBER: GSS-SB1B-735-U-T3

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1185.3	0.0	1185.3
	% Fixture	23.7	0.0	23.7
Street Side	Lumens	3824.9	0.0	3824.9
	% Fixture	76.3	0.0	76.3
Total	Lumens	5010.2	0.0	5010.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.0	1.5
10°-20°	239.8	4.8
20°-30°	410.0	8.2
30°-40°	594.7	11.9
40°-50°	772.6	15.4
50°-60°	1046.8	20.9
60°-70°	1221.1	24.4
70°-80°	602.0	12.0
80°-90°	47.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5010.2	100.0
0°-180°	5010.2	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1359992
CATALOG NUMBER: GSS-SB1B-735-U-T3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	427.4	8.5			
FM	(30°-60°)	1829.9	36.5			
FH	(60°-80°)	1542.8	30.8			G1/1800
FVH	(80°-90°)	24.8	0.5			G1/100
BL	(0°-30°)	298.4	6.0	B1/500		
BM	(30°-60°)	584.2	11.7	B1/1000		
BH	(60°-80°)	280.3	5.6	B1/500		G1/500
BVH	(80°-90°)	22.5	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359992
CATALOG NUMBER: GSS-SB1B-735-U-T3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	52°	55°	65°	75°	85°
0°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3
2.5°	798.8	797.6	796.5	792.1	792.1	793.2	791.0	792.1	791.0	785.4	780.9
5°	843.4	833.3	831.1	828.9	831.1	824.4	818.8	815.5	803.2	799.9	786.5
7.5°	862.4	863.5	862.4	857.9	854.5	854.5	845.6	841.2	833.3	820.0	797.6
10°	889.1	888.0	884.7	886.9	893.6	882.4	875.7	872.4	859.0	840.0	818.8
12.5°	937.1	929.3	927.1	923.7	922.6	915.9	908.1	909.2	893.6	864.6	842.3
15°	978.4	969.4	979.5	972.8	963.9	953.8	946.0	939.3	921.5	894.7	866.8
17.5°	1017.4	1013.0	1017.4	1017.4	1016.3	999.6	984.0	978.4	957.2	927.1	890.2
20°	1047.5	1047.5	1055.3	1055.3	1052.0	1042.0	1031.9	1025.2	995.1	956.1	913.7
22.5°	1086.6	1068.7	1085.5	1086.6	1087.7	1079.9	1073.2	1064.3	1033.0	986.2	932.6
25°	1123.4	1108.9	1118.9	1112.2	1116.7	1120.1	1116.7	1113.4	1078.8	1025.2	960.5
27.5°	1181.4	1166.9	1173.6	1158.0	1158.0	1154.6	1160.2	1164.7	1126.7	1063.2	985.1
30°	1268.4	1251.7	1246.1	1227.2	1208.2	1200.4	1202.6	1210.4	1184.8	1100.0	1009.6
32.5°	1343.2	1334.2	1329.8	1314.2	1290.7	1255.0	1260.6	1260.6	1233.8	1126.7	1021.9
35°	1404.5	1402.3	1403.4	1382.2	1377.8	1319.7	1319.7	1317.5	1268.4	1162.4	1054.2
37.5°	1444.7	1432.4	1438.0	1445.8	1431.3	1392.3	1382.2	1376.6	1316.4	1200.4	1096.6
40°	1435.8	1426.8	1448.0	1462.5	1451.4	1443.6	1442.5	1431.3	1364.4	1248.3	1159.1
42.5°	1434.7	1426.8	1452.5	1468.1	1462.5	1474.8	1478.2	1486.0	1425.7	1324.2	1248.3
45°	1439.1	1435.8	1478.2	1498.2	1484.9	1501.6	1520.6	1527.2	1503.8	1416.8	1359.9
47.5°	1475.9	1471.5	1520.6	1544.0	1555.1	1584.1	1571.9	1583.0	1596.4	1548.4	1488.2
50°	1511.6	1516.1	1581.9	1604.2	1658.9	1699.0	1656.7	1674.5	1719.1	1701.3	1660.0
52.5°	1568.5	1569.6	1634.3	1690.1	1795.0	1832.9	1791.6	1793.9	1854.1	1887.6	1832.9
55°	1583.0	1595.3	1682.3	1798.3	1948.9	1975.7	1956.7	1948.9	2020.3	2066.1	2006.9
57.5°	1581.9	1575.2	1683.4	1844.1	2066.1	2160.9	2172.1	2150.9	2211.1	2230.1	2197.7
60°	1540.6	1554.0	1672.3	1876.4	2175.4	2386.3	2413.0	2385.1	2414.1	2419.7	2329.4
62.5°	1414.6	1419.0	1580.8	1877.5	2261.3	2573.7	2652.9	2621.6	2594.9	2525.7	2358.4
65°	1209.3	1201.5	1356.6	1722.5	2276.9	2754.4	2868.2	2868.2	2694.2	2561.4	2297.0
67.5°	1008.5	996.2	1112.2	1404.5	2027.0	2833.6	3015.4	2956.3	2715.4	2585.9	2150.9
70°	486.4	521.0	698.4	994.0	1549.6	2392.9	2906.1	2928.4	2698.6	2509.0	1867.5
72.5°	174.0	166.2	251.0	426.2	857.9	1561.8	2433.1	2629.4	2581.5	2288.1	1529.5
75°	80.3	81.4	104.9	148.4	277.8	761.9	1547.3	1810.6	2211.1	1902.1	1144.6
77.5°	62.5	62.5	71.4	84.8	114.9	246.5	791.0	1016.3	1429.1	1178.1	545.5
80°	45.7	46.9	48.0	55.8	70.3	92.6	235.4	352.5	521.0	378.2	177.4
82.5°	32.4	32.4	31.2	31.2	37.9	41.3	63.6	89.2	152.8	103.8	46.9
85°	13.4	15.6	13.4	13.4	13.4	16.7	20.1	23.4	33.5	29.0	20.1
87.5°	2.2	2.2	2.2	3.3	4.5	5.6	6.7	7.8	8.9	8.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359992
CATALOG NUMBER: GSS-SB1B-735-U-T3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3
2.5°	778.7	778.7	775.3	769.8	767.5	764.2	763.1	761.9	759.7	764.2	761.9
5°	783.1	778.7	774.2	765.3	764.2	758.6	753.0	751.9	748.6	751.9	751.9
7.5°	793.2	786.5	776.5	767.5	759.7	758.6	748.6	739.6	739.6	740.8	739.6
10°	811.0	803.2	793.2	776.5	761.9	748.6	731.8	720.7	721.8	721.8	719.6
12.5°	834.5	823.3	805.5	780.9	758.6	737.4	717.3	714.0	712.9	715.1	708.4
15°	852.3	842.3	813.3	785.4	750.8	729.6	708.4	700.6	701.7	699.5	693.9
17.5°	874.6	859.0	823.3	782.0	741.9	721.8	697.2	680.5	671.6	672.7	671.6
20°	895.8	873.5	831.1	782.0	739.6	703.9	672.7	650.4	631.4	628.1	627.0
22.5°	911.4	889.1	840.0	783.1	726.3	683.9	638.1	609.1	581.2	576.8	575.6
25°	933.8	904.7	850.1	775.3	708.4	650.4	593.5	561.1	536.6	532.1	532.1
27.5°	952.7	921.5	863.5	767.5	679.4	604.7	551.1	518.8	503.1	495.3	495.3
30°	972.8	938.2	874.6	744.1	640.3	558.9	517.6	496.4	478.6	470.8	467.4
32.5°	995.1	966.1	876.9	720.7	601.3	528.8	494.2	476.4	457.4	446.2	445.1
35°	1023.0	1001.8	869.0	686.1	562.3	505.4	471.9	451.8	432.8	421.7	423.9
37.5°	1067.6	1043.1	845.6	637.0	529.9	490.9	454.0	425.0	402.7	384.9	386.0
40°	1133.4	1093.3	811.0	577.9	506.5	474.1	432.8	399.4	367.0	340.3	340.3
42.5°	1208.2	1137.9	768.6	523.2	488.6	452.9	410.5	368.1	322.4	294.5	293.4
45°	1291.9	1176.9	719.6	478.6	459.6	427.3	381.5	321.3	291.2	276.7	275.6
47.5°	1403.4	1219.3	661.5	439.5	426.2	401.6	338.0	294.5	276.7	265.5	264.4
50°	1508.3	1265.1	613.6	401.6	390.5	371.5	307.9	283.4	268.9	259.9	257.7
52.5°	1629.9	1311.9	560.0	364.8	350.3	324.6	301.2	277.8	264.4	257.7	255.5
55°	1750.4	1377.8	500.9	331.3	314.6	303.4	294.5	274.4	261.0	256.6	253.2
57.5°	1887.6	1441.3	428.4	295.6	288.9	287.8	293.4	273.3	262.2	254.4	249.9
60°	1959.0	1469.2	352.5	263.3	264.4	271.1	288.9	273.3	255.5	242.1	236.5
62.5°	1934.4	1412.3	278.9	230.9	241.0	253.2	281.1	263.3	241.0	230.9	224.2
65°	1836.3	1315.3	217.5	203.0	219.8	230.9	262.2	248.8	226.5	216.4	215.3
67.5°	*1694.6*	*1146.8*	*176.3*	*178.5*	*195.2*	*209.7*	*245.4*	*239.9*	*214.2*	*207.5*	*207.5*
70°	1424.6	921.5	145.0	156.2	170.7	186.3	233.2	225.3	198.6	195.2	195.2
72.5°	1113.4	650.4	123.8	137.2	141.7	164.0	216.4	208.6	193.0	200.8	201.9
75°	785.4	396.0	106.0	116.0	120.5	135.0	200.8	204.2	189.7	215.3	219.8
77.5°	357.0	174.0	82.6	91.5	97.1	114.9	172.9	189.7	164.0	164.0	155.1
80°	124.9	73.6	65.8	65.8	70.3	89.2	143.9	156.2	131.6	116.0	111.6
82.5°	45.7	40.2	49.1	49.1	44.6	54.7	95.9	103.8	94.8	82.6	81.4
85°	17.8	19.0	30.1	30.1	22.3	26.8	53.5	55.8	53.5	46.9	46.9
87.5°	7.8	7.8	8.9	8.9	7.8	6.7	10.0	10.0	6.7	4.5	2.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ

Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-735-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369
CIE u':	0.2386
CIE v':	0.5156
Duv:	0.0013
CIE x:	0.4143
CIE y:	0.3980
CIE z:	0.1877
Peak Wavelength (nm):	590
Dominant Wavelength (nm):	580
Purity:	43.80166
Rf:	71.4
Rg:	96

CRI (Ra):	70.1
R1:	66.6
R2:	77.6
R3:	88.5
R4:	69.5
R5:	66.4
R6:	69.6
R7:	77.5
R8:	44.9
R9:	-40.2
R10:	49.1
R11:	66.3
R12:	45.7
R13:	68.0
R14:	93.4
R15:	57.6



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3369K
CIE x = 0.4143
CIE y = 0.3980
Duv = 0.0013

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.36**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-5

TM-30-18


Summary


R_f = 71.4
R_g = 96
CIE R_a = 70.1
R_9 = -40.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	





REPORT NUMBER: SP1-2407-184-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-5

TM-30-18

Measure Comparisons





(END OF REPORT)