Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1363836

Luminaire Tested: **GSS-SB2B-735-U-SL3-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1363836
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2B-735-U-SL3-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 74W 70CRI 3500K FIXTURE w/ TYPE III SPILL CONTROL DISTRIBUTION OPTIC AND HOUSE SIDE SHIELD
Light Source:	(52) 3500K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	7464.4 lumens
Efficiency:	N/A
Efficacy:	100.9 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type III - Medium
BUG Rating:	B1 - U0 - G2


Input Watts (W):	74
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	13.6%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363836
CATALOG NUMBER: GSS-SB2B-735-U-SL3-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 4.4 fc
Type III - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363836
CATALOG NUMBER: GSS-SB2B-735-U-SL3-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1363836
CATALOG NUMBER: GSS-SB2B-735-U-SL3-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	668.6	0.0	668.6
	% Fixture	9.0	0.0	9.0
Street Side	Lumens	6795.8	0.0	6795.8
	% Fixture	91.0	0.0	91.0
Total	Lumens	7464.4	0.0	7464.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.3	1.5
10°-20°	319.3	4.3
20°-30°	484.5	6.5
30°-40°	701.7	9.4
40°-50°	1047.9	14.0
50°-60°	1517.4	20.3
60°-70°	1838.2	24.6
70°-80°	1327.6	17.8
80°-90°	116.4	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7464.4	100.0
0°-180°	7464.4	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1363836
CATALOG NUMBER: GSS-SB2B-735-U-SL3-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	708.4	9.5			
FM	(30°-60°)	2952.6	39.6			
FH	(60°-80°)	3028.5	40.6			G2/5000
FVH	(80°-90°)	106.3	1.4			G2/225
BL	(0°-30°)	206.7	2.8	B1/500		
BM	(30°-60°)	314.5	4.2	B1/1000		
BH	(60°-80°)	137.4	1.8	B1/500		G1/500
BVH	(80°-90°)	10.1	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2
Type III Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363836
CATALOG NUMBER: GSS-SB2B-735-U-SL3-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	57°	65°	75°	85°
0°	1200.8	1200.8	1200.8	1200.8	1200.8	1200.8	1200.8	*1200.8*	1200.8	1200.8	1200.8
2.5°	1443.9	1448.7	1431.7	1422.0	1402.5	1370.9	1339.3	*1339.3*	1302.9	1268.8	1225.1
5°	1657.8	1643.2	1635.9	1611.6	1575.1	1536.2	1480.3	*1465.7*	1407.4	1334.5	1247.0
7.5°	1820.6	1803.6	1796.3	1774.4	1733.1	1682.1	1606.7	*1594.6*	1509.5	1402.5	1276.1
10°	1920.3	1908.1	1908.1	1891.1	1859.5	1806.0	1730.7	*1713.7*	1611.6	1465.7	1295.6
12.5°	1876.5	1871.7	1900.8	1939.7	1954.3	1922.7	1842.5	*1820.6*	1703.9	1536.2	1319.9
15°	1677.2	1672.3	1725.8	1827.9	1951.9	2005.4	1944.6	*1925.1*	1803.6	1609.1	1344.2
17.5°	1485.2	1477.9	1528.9	1631.0	1815.8	2015.1	2051.5	*2027.2*	1903.3	1682.1	1370.9
20°	1375.8	1368.5	1402.5	1485.2	1652.9	1937.3	2107.4	*2112.3*	2012.6	1762.3	1397.7
22.5°	1336.9	1334.5	1351.5	1407.4	1526.5	1803.6	2129.3	*2158.5*	2131.8	1854.6	1436.6
25°	1353.9	1344.2	1349.1	1370.9	1456.0	1696.7	2117.2	*2173.1*	2231.4	1966.5	1487.6
27.5°	1397.7	1390.4	1383.1	1383.1	1426.8	1618.9	2085.6	*2177.9*	2333.5	2088.0	1531.4
30°	1470.6	1460.9	1439.0	1412.3	1426.8	1570.3	2049.1	*2165.8*	2421.0	2219.3	1592.1
32.5°	1635.9	1628.6	1565.4	1480.3	1460.9	1558.1	2007.8	*2143.9*	2515.8	2374.8	1662.6
35°	1798.7	1791.4	1747.7	1626.2	1519.2	1567.8	1981.0	*2129.3*	2632.5	2564.4	1745.3
37.5°	1871.7	1859.5	1825.5	1759.8	1655.3	1623.7	1988.3	*2146.3*	2800.2	2773.5	1847.4
40°	1964.0	1944.6	1893.5	1832.8	1786.6	1752.6	2046.7	*2204.7*	2987.4	3014.1	1959.2
42.5°	2100.2	2078.3	2002.9	1917.8	1864.4	1932.4	2158.5	*2309.2*	3218.3	3281.5	2095.3
45°	2287.3	2258.1	2160.9	2049.1	1983.5	2022.4	2309.2	*2457.5*	3475.9	3585.3	2253.3
47.5°	2457.5	2450.2	2340.8	2212.0	2134.2	2083.1	2472.1	*2630.1*	3748.2	3925.6	2416.1
50°	2617.9	2591.2	2484.2	2357.8	2292.2	2207.1	2651.9	*2822.1*	4020.4	4236.8	2591.2
52.5°	2792.9	2763.7	2617.9	2474.5	2408.9	2389.4	2885.3	*3050.6*	4258.6	4564.9	2768.6
55°	2929.0	2887.7	2727.3	2608.2	2503.7	2569.3	3135.6	*3325.2*	4470.1	4861.5	2948.5
57.5°	3099.2	3045.7	2817.2	2729.7	2649.5	2751.6	3417.6	*3599.9*	4691.3	5111.8	3128.4
60°	3247.5	3206.1	2984.9	2875.6	2800.2	2958.2	3692.3	*3852.7*	4863.9	5325.7	3293.6
62.5°	2795.3	2790.5	2848.8	3177.0	3065.2	3271.8	3986.4	*4127.4*	4968.4	5469.1	3361.7
65°	1983.5	1998.1	2160.9	3181.8	3580.5	3796.8	4372.9	*4465.3*	4973.3	5306.3	3228.0
67.5°	1261.5	1247.0	1448.7	2664.1	3599.9	4832.3	4961.1	*4868.8*	4749.6	5131.3	3245.0
70°	756.0	760.8	828.9	1932.4	2967.9	5068.1	5782.7	*5544.5*	4883.3	5260.1	3259.6
72.5°	410.8	420.5	517.7	948.0	1966.5	4032.6	6652.9	*6686.9*	5340.3	5320.9	3203.7
73°	*374.3*	*376.8*	*464.3*	*792.4*	*1701.5*	*3833.3*	*6611.6*	*6750.1*	*5432.7*	*5337.9*	*3167.2*
75°	247.9	247.9	316.0	449.7	746.2	2980.1	5488.6	*6101.1*	5746.2	5162.9	2882.8
77.5°	153.1	162.9	218.8	311.1	272.2	1499.8	3228.0	*3733.6*	5124.0	3884.3	1810.9
80°	55.9	60.8	136.1	204.2	158.0	568.8	1353.9	*1553.2*	2374.8	1971.3	653.9
82.5°	29.2	31.6	85.1	104.5	85.1	148.3	605.3	*646.6*	957.7	512.9	121.5
85°	14.6	17.0	36.5	43.8	34.0	48.6	150.7	*141.0*	216.3	68.1	34.0
87.5°	0.0	0.0	2.4	4.9	7.3	9.7	14.6	*14.6*	17.0	19.4	19.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363836
CATALOG NUMBER: GSS-SB2B-735-U-SL3-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1200.8	1200.8	1200.8	1200.8	1200.8	1200.8	1200.8	1200.8	1200.8	1200.8	1200.8
2.5°	1198.4	1178.9	1132.7	1086.5	1052.5	1016.0	982.0	952.8	935.8	928.5	935.8
5°	1200.8	1159.5	1064.7	969.9	877.5	802.1	731.6	680.6	644.1	632.0	627.1
7.5°	1200.8	1132.7	984.4	828.9	692.8	593.1	522.6	491.0	474.0	471.6	471.6
10°	1198.4	1101.1	894.5	690.3	534.8	466.7	444.8	440.0	440.0	440.0	442.4
12.5°	1195.9	1072.0	792.4	556.6	449.7	427.8	420.5	420.5	422.9	425.4	427.8
15°	1191.1	1028.2	685.5	464.3	418.1	410.8	405.9	405.9	408.4	413.2	413.2
17.5°	1186.2	984.4	580.9	422.9	403.5	396.2	393.8	391.3	396.2	401.1	401.1
20°	1176.5	928.5	493.4	401.1	388.9	384.1	381.6	379.2	381.6	386.5	388.9
22.5°	1164.3	858.0	435.1	386.5	376.8	369.5	367.0	364.6	364.6	374.3	374.3
25°	1152.2	780.3	401.1	371.9	362.2	354.9	350.0	347.6	350.0	357.3	357.3
27.5°	1127.9	695.2	379.2	359.7	350.0	340.3	335.4	330.6	333.0	340.3	340.3
30°	1091.4	605.3	367.0	347.6	335.4	323.3	316.0	311.1	313.6	320.9	323.3
32.5°	1037.9	527.5	362.2	337.9	323.3	306.3	296.5	289.3	291.7	301.4	301.4
35°	982.0	471.6	359.7	328.1	308.7	291.7	274.7	264.9	269.8	279.5	282.0
37.5°	923.7	440.0	359.7	323.3	299.0	277.1	252.8	243.1	245.5	255.2	257.7
40°	872.6	425.4	362.2	318.4	286.8	260.1	233.4	221.2	226.1	238.2	235.8
42.5°	853.2	422.9	362.2	306.3	274.7	243.1	213.9	201.8	206.6	213.9	216.3
45°	875.1	432.7	357.3	294.1	257.7	223.6	199.3	187.2	189.6	194.5	199.3
47.5°	950.4	444.8	350.0	279.5	243.1	209.0	184.7	175.0	170.2	177.4	179.9
50°	1054.9	452.1	337.9	264.9	230.9	194.5	172.6	160.4	155.6	158.0	160.4
52.5°	1174.0	452.1	325.7	250.4	218.8	179.9	162.9	150.7	141.0	143.4	143.4
55°	1293.1	447.3	294.1	238.2	206.6	170.2	153.1	136.1	128.8	128.8	126.4
57.5°	1417.1	440.0	255.2	221.2	192.0	158.0	141.0	126.4	116.7	111.8	111.8
60°	1538.7	430.2	233.4	204.2	175.0	148.3	128.8	116.7	104.5	97.2	94.8
62.5°	1601.9	403.5	209.0	182.3	158.0	133.7	116.7	104.5	89.9	80.2	77.8
65°	1567.8	347.6	179.9	162.9	143.4	119.1	104.5	92.4	75.4	63.2	63.2
67.5°	1604.3	291.7	153.1	138.6	124.0	102.1	87.5	80.2	65.6	55.9	55.9
70°	1616.4	228.5	128.8	119.1	107.0	85.1	75.4	70.5	58.3	48.6	46.2
72.5°	1526.5	170.2	104.5	99.7	87.5	65.6	63.2	58.3	48.6	38.9	38.9
73°	*1490.0*	*158.0*	*99.7*	*94.8*	*82.6*	*63.2*	*60.8*	*55.9*	*46.2*	*38.9*	*36.5*
75°	1312.6	121.5	82.6	77.8	65.6	53.5	51.0	46.2	38.9	31.6	31.6
77.5°	870.2	87.5	63.2	58.3	48.6	41.3	38.9	34.0	29.2	24.3	24.3
80°	320.9	58.3	46.2	41.3	36.5	34.0	29.2	24.3	19.4	19.4	17.0
82.5°	65.6	38.9	34.0	29.2	26.7	24.3	19.4	17.0	14.6	14.6	14.6
85°	26.7	24.3	19.4	19.4	19.4	17.0	14.6	14.6	12.2	12.2	9.7
87.5°	17.0	14.6	14.6	12.2	12.2	9.7	9.7	9.7	9.7	9.7	9.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ

Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-735-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369
CIE u':	0.2386
CIE v':	0.5156
Duv:	0.0013
CIE x:	0.4143
CIE y:	0.3980
CIE z:	0.1877
Peak Wavelength (nm):	590
Dominant Wavelength (nm):	580
Purity:	43.80166
Rf:	71.4
Rg:	96

CRI (Ra):	70.1
R1:	66.6
R2:	77.6
R3:	88.5
R4:	69.5
R5:	66.4
R6:	69.6
R7:	77.5
R8:	44.9
R9:	-40.2
R10:	49.1
R11:	66.3
R12:	45.7
R13:	68.0
R14:	93.4
R15:	57.6



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3369K
CIE x = 0.4143
CIE y = 0.3980
Duv = 0.0013

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.36**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-5

TM-30-18


Summary


R_f = 71.4
R_g = 96
CIE R_a = 70.1
R_9 = -40.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	





REPORT NUMBER: SP1-2407-184-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-5

TM-30-18

Measure Comparisons





(END OF REPORT)