Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1363837

Luminaire Tested: **GSS-SB2C-735-U-SL3-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1363837
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2C-735-U-SL3-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 102W 70CRI 3500K FIXTURE w/ TYPE III SPILL CONTROL DISTRIBUTION OPTIC AND HOUSE SIDE SHIELD
Light Source:	(52) 3500K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	9843.5 lumens
Efficiency:	N/A
Efficacy:	96.5 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type III - Medium
BUG Rating:	B1 - U0 - G2


Input Watts (W):	102
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363837
CATALOG NUMBER: GSS-SB2C-735-U-SL3-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 5.8 fc
Type III - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363837
CATALOG NUMBER: GSS-SB2C-735-U-SL3-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1363837
CATALOG NUMBER: GSS-SB2C-735-U-SL3-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	881.7	0.0	881.7
	% Fixture	9.0	0.0	9.0
Street Side	Lumens	8961.8	0.0	8961.8
	% Fixture	91.0	0.0	91.0
Total	Lumens	9843.5	0.0	9843.5
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.8	1.5
10°-20°	421.0	4.3
20°-30°	639.0	6.5
30°-40°	925.4	9.4
40°-50°	1381.9	14.0
50°-60°	2001.0	20.3
60°-70°	2424.1	24.6
70°-80°	1750.8	17.8
80°-90°	153.5	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9843.5	100.0
0°-180°	9843.5	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1363837
CATALOG NUMBER: GSS-SB2C-735-U-SL3-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	934.2	9.5			
FM	(30°-60°)	3893.6	39.6			
FH	(60°-80°)	3993.8	40.6			G2/5000
FVH	(80°-90°)	140.2	1.4			G2/225
BL	(0°-30°)	272.6	2.8	B1/500		
BM	(30°-60°)	414.7	4.2	B1/1000		
BH	(60°-80°)	181.1	1.8	B1/500		G1/500
BVH	(80°-90°)	13.3	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2
Type III Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363837
CATALOG NUMBER: GSS-SB2C-735-U-SL3-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	57°	65°	75°	85°
0°	1583.5	1583.5	1583.5	1583.5	1583.5	1583.5	1583.5	*1583.5*	1583.5	1583.5	1583.5
2.5°	1904.0	1910.4	1888.0	1875.2	1849.5	1807.9	1766.2	*1766.2*	1718.1	1673.2	1615.5
5°	2186.1	2166.9	2157.3	2125.2	2077.1	2025.8	1952.1	*1932.9*	1856.0	1759.8	1644.4
7.5°	2400.9	2378.4	2368.8	2340.0	2285.5	2218.2	2118.8	*2102.8*	1990.6	1849.5	1682.9
10°	2532.3	2516.3	2516.3	2493.8	2452.2	2381.6	2282.3	*2259.8*	2125.2	1932.9	1708.5
12.5°	2474.6	2468.2	2506.7	2557.9	2577.2	2535.5	2429.7	*2400.9*	2247.0	2025.8	1740.6
15°	2211.8	2205.3	2275.9	2410.5	2574.0	2644.5	2564.4	*2538.7*	2378.4	2122.0	1772.6
17.5°	1958.5	1948.9	2016.2	2150.9	2394.5	2657.3	2705.4	*2673.3*	2509.9	2218.2	1807.9
20°	1814.3	1804.7	1849.5	1958.5	2179.7	2554.7	2779.1	*2785.5*	2654.1	2323.9	1843.1
22.5°	1763.0	1759.8	1782.2	1856.0	2013.0	2378.4	2808.0	*2846.4*	2811.2	2445.8	1894.4
25°	1785.4	1772.6	1779.0	1807.9	1920.1	2237.4	2791.9	*2865.7*	2942.6	2593.2	1961.7
27.5°	1843.1	1833.5	1823.9	1823.9	1881.6	2134.8	2750.3	*2872.1*	3077.2	2753.5	2019.4
30°	1939.3	1926.5	1897.6	1862.4	1881.6	2070.7	2702.2	*2856.0*	3192.6	2926.6	2099.6
32.5°	2157.3	2147.6	2064.3	1952.1	1926.5	2054.7	2647.7	*2827.2*	3317.6	3131.7	2192.5
35°	2372.0	2362.4	2304.7	2144.4	2003.4	2067.5	2612.4	*2808.0*	3471.5	3381.7	2301.5
37.5°	2468.2	2452.2	2407.3	2320.7	2182.9	2141.2	2622.1	*2830.4*	3692.7	3657.4	2436.1
40°	2590.0	2564.4	2497.0	2416.9	2356.0	2311.1	2699.0	*2907.3*	3939.5	3974.7	2583.6
42.5°	2769.5	2740.7	2641.3	2529.1	2458.6	2548.3	2846.4	*3045.2*	4244.0	4327.3	2763.1
45°	3016.3	2977.9	2849.6	2702.2	2615.6	2666.9	3045.2	*3240.7*	4583.8	4728.0	2971.4
47.5°	3240.7	3231.1	3086.8	2917.0	2814.4	2747.1	3259.9	*3468.3*	4942.8	5176.8	3186.2
50°	3452.3	3417.0	3276.0	3109.3	3022.7	2910.5	3497.1	*3721.5*	5301.8	5587.1	3417.0
52.5°	3683.1	3644.6	3452.3	3263.1	3176.6	3150.9	3804.9	*4022.8*	5615.9	6019.8	3651.0
55°	3862.6	3808.1	3596.5	3439.4	3301.6	3388.2	4135.0	*4385.0*	5894.8	6410.9	3888.2
57.5°	4086.9	4016.4	3715.1	3599.7	3493.9	3628.6	4506.9	*4747.3*	6186.5	6741.0	4125.4
60°	4282.5	4228.0	3936.3	3792.0	3692.7	3901.0	4869.1	*5080.6*	6414.1	7023.1	4343.4
62.5°	3686.3	3679.8	3756.8	4189.5	4042.1	4314.5	5256.9	*5442.8*	6551.9	7212.2	4433.1
65°	2615.6	2634.9	2849.6	4195.9	4721.6	5006.9	5766.6	*5888.4*	6558.3	6997.5	4256.8
67.5°	1663.6	1644.4	1910.4	3513.2	4747.3	6372.4	6542.3	*6420.5*	6263.4	6766.7	4279.3
70°	996.9	1003.3	1093.1	2548.3	3913.8	6683.3	7625.7	*7311.6*	6439.7	6936.6	4298.5
72.5°	541.7	554.5	682.8	1250.1	2593.2	5317.8	8773.3	*8818.2*	7042.4	7016.7	4224.8
73°	*493.6*	*496.8*	*612.2*	*1045.0*	*2243.8*	*5055.0*	*8718.8*	*8901.5*	*7164.2*	*7039.2*	*4176.7*
75°	327.0	327.0	416.7	593.0	984.1	3929.9	7237.9	*8045.7*	7577.7	6808.4	3801.7
77.5°	201.9	214.8	288.5	410.3	359.0	1977.8	4256.8	*4923.6*	6757.1	5122.3	2388.1
80°	73.7	80.1	179.5	269.3	208.4	750.1	1785.4	*2048.3*	3131.7	2599.6	862.3
82.5°	38.5	41.7	112.2	137.8	112.2	195.5	798.2	*852.6*	1262.9	676.3	160.3
85°	19.2	22.4	48.1	57.7	44.9	64.1	198.7	*185.9*	285.3	89.8	44.9
87.5°	0.0	0.0	3.2	6.4	9.6	12.8	19.2	*19.2*	22.4	25.6	25.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363837
CATALOG NUMBER: GSS-SB2C-735-U-SL3-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1583.5	1583.5	1583.5	1583.5	1583.5	1583.5	1583.5	1583.5	1583.5	1583.5	1583.5
2.5°	1580.3	1554.6	1493.7	1432.8	1388.0	1339.9	1295.0	1256.5	1234.1	1224.5	1234.1
5°	1583.5	1529.0	1404.0	1279.0	1157.2	1057.8	964.8	897.5	849.4	833.4	827.0
7.5°	1583.5	1493.7	1298.2	1093.1	913.6	782.1	689.2	647.5	625.1	621.9	621.9
10°	1580.3	1452.1	1179.6	910.3	705.2	615.4	586.6	580.2	580.2	580.2	583.4
12.5°	1577.1	1413.6	1045.0	734.0	593.0	564.2	554.5	554.5	557.7	561.0	564.2
15°	1570.7	1355.9	903.9	612.2	551.3	541.7	535.3	535.3	538.5	544.9	544.9
17.5°	1564.3	1298.2	766.1	557.7	532.1	522.5	519.3	516.1	522.5	528.9	528.9
20°	1551.4	1224.5	650.7	528.9	512.9	506.5	503.3	500.0	503.3	509.7	512.9
22.5°	1535.4	1131.5	573.8	509.7	496.8	487.2	484.0	480.8	480.8	493.6	493.6
25°	1519.4	1028.9	528.9	490.4	477.6	468.0	461.6	458.4	461.6	471.2	471.2
27.5°	1487.3	916.8	500.0	474.4	461.6	448.8	442.4	435.9	439.1	448.8	448.8
30°	1439.2	798.2	484.0	458.4	442.4	426.3	416.7	410.3	413.5	423.1	426.3
32.5°	1368.7	695.6	477.6	445.6	426.3	403.9	391.1	381.4	384.7	397.5	397.5
35°	1295.0	621.9	474.4	432.7	407.1	384.7	362.2	349.4	355.8	368.6	371.8
37.5°	1218.1	580.2	474.4	426.3	394.3	365.4	333.4	320.5	323.7	336.6	339.8
40°	1150.8	561.0	477.6	419.9	378.2	343.0	307.7	291.7	298.1	314.1	310.9
42.5°	1125.1	557.7	477.6	403.9	362.2	320.5	282.1	266.1	272.5	282.1	285.3
45°	1154.0	570.6	471.2	387.9	339.8	294.9	262.8	246.8	250.0	256.4	262.8
47.5°	1253.3	586.6	461.6	368.6	320.5	275.7	243.6	230.8	224.4	234.0	237.2
50°	1391.2	596.2	445.6	349.4	304.5	256.4	227.6	211.6	205.1	208.4	211.6
52.5°	1548.2	596.2	429.5	330.2	288.5	237.2	214.8	198.7	185.9	189.1	189.1
55°	1705.3	589.8	387.9	314.1	272.5	224.4	201.9	179.5	169.9	169.9	166.7
57.5°	1868.8	580.2	336.6	291.7	253.2	208.4	185.9	166.7	153.9	147.5	147.5
60°	2029.0	567.4	307.7	269.3	230.8	195.5	169.9	153.9	137.8	128.2	125.0
62.5°	2112.4	532.1	275.7	240.4	208.4	176.3	153.9	137.8	118.6	105.8	102.6
65°	2067.5	458.4	237.2	214.8	189.1	157.1	137.8	121.8	99.4	83.3	83.3
67.5°	2115.6	384.7	201.9	182.7	163.5	134.6	115.4	105.8	86.5	73.7	73.7
70°	2131.6	301.3	169.9	157.1	141.0	112.2	99.4	93.0	76.9	64.1	60.9
72.5°	2013.0	224.4	137.8	131.4	115.4	86.5	83.3	76.9	64.1	51.3	51.3
73°	*1964.9*	*208.4*	*131.4*	*125.0*	*109.0*	*83.3*	*80.1*	*73.7*	*60.9*	*51.3*	*48.1*
75°	1730.9	160.3	109.0	102.6	86.5	70.5	67.3	60.9	51.3	41.7	41.7
77.5°	1147.5	115.4	83.3	76.9	64.1	54.5	51.3	44.9	38.5	32.1	32.1
80°	423.1	76.9	60.9	54.5	48.1	44.9	38.5	32.1	25.6	25.6	22.4
82.5°	86.5	51.3	44.9	38.5	35.3	32.1	25.6	22.4	19.2	19.2	19.2
85°	35.3	32.1	25.6	25.6	25.6	22.4	19.2	19.2	16.0	16.0	12.8
87.5°	22.4	19.2	19.2	16.0	16.0	12.8	12.8	12.8	12.8	12.8	12.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ

Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-735-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369
CIE u':	0.2386
CIE v':	0.5156
Duv:	0.0013
CIE x:	0.4143
CIE y:	0.3980
CIE z:	0.1877
Peak Wavelength (nm):	590
Dominant Wavelength (nm):	580
Purity:	43.80166
Rf:	71.4
Rg:	96

CRI (Ra):	70.1
R1:	66.6
R2:	77.6
R3:	88.5
R4:	69.5
R5:	66.4
R6:	69.6
R7:	77.5
R8:	44.9
R9:	-40.2
R10:	49.1
R11:	66.3
R12:	45.7
R13:	68.0
R14:	93.4
R15:	57.6



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3369K
CIE x = 0.4143
CIE y = 0.3980
Duv = 0.0013

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.36**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-5

TM-30-18


Summary


R_f = 71.4
R_g = 96
CIE R_a = 70.1
R_9 = -40.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	





REPORT NUMBER: SP1-2407-184-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-5

TM-30-18

Measure Comparisons





(END OF REPORT)