Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1364605

Luminaire Tested: **GSS-SB2C-735-U-SLR-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1364605
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2C-735-U-SLR-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 102W 70CRI 3500K FIXTURE w/ 90° Spill Light Eliminator RIGHT OPTIC AND HOUSE SIDE SHIELD
Light Source:	(52) 3500K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	10438.9 lumens
Efficiency:	N/A
Efficacy:	102.3 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B1 - U0 - G2


Input Watts (W):	102
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364605
CATALOG NUMBER: GSS-SB2C-735-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 5.7 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364605
CATALOG NUMBER: GSS-SB2C-735-U-SLR-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1364605
CATALOG NUMBER: GSS-SB2C-735-U-SLR-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1687.5	0.0	1687.5
	% Fixture	16.2	0.0	16.2
Street Side	Lumens	8751.4	0.0	8751.4
	% Fixture	83.8	0.0	83.8
Total	Lumens	10438.9	0.0	10438.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.4	1.7
10°-20°	479.7	4.6
20°-30°	687.0	6.6
30°-40°	861.7	8.3
40°-50°	1415.5	13.6
50°-60°	2554.4	24.5
60°-70°	2834.9	27.2
70°-80°	1280.8	12.3
80°-90°	151.4	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10438.9	100.0
0°-180°	10438.9	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1364605
CATALOG NUMBER: GSS-SB2C-735-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	894.2	8.6			
FM	(30°-60°)	3963.9	38.0			
FH	(60°-80°)	3757.3	36.0			G2/5000
FVH	(80°-90°)	136.0	1.3			G2/225
BL	(0°-30°)	445.9	4.3	B1/500		
BM	(30°-60°)	867.7	8.3	B1/1000		
BH	(60°-80°)	358.4	3.4	B1/500		G1/500
BVH	(80°-90°)	15.5	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364605
CATALOG NUMBER: GSS-SB2C-735-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7
2.5°	2035.5	2033.5	2025.8	1977.8	1929.7	1888.0	1846.3	1804.7	1747.0	1702.1	1663.6
5°	2227.8	2217.5	2176.5	2102.8	2022.6	1952.1	1872.0	1795.1	1708.5	1638.0	1564.3
7.5°	2359.2	2349.0	2307.9	2186.1	2064.3	1977.8	1891.2	1811.1	1714.9	1622.0	1516.2
10°	2420.1	2408.6	2362.4	2231.0	2090.0	1984.2	1897.6	1823.9	1743.8	1650.8	1519.4
12.5°	2461.8	2447.7	2391.3	2240.6	2096.4	1990.6	1900.8	1830.3	1772.6	1718.1	1589.9
15°	2487.4	2474.6	2423.3	2266.3	2099.6	1981.0	1875.2	1807.9	1788.6	1798.3	1737.4
17.5°	2525.9	2513.7	2465.0	2298.3	2118.8	1964.9	1820.7	1747.0	1788.6	1875.2	1894.4
20°	2577.2	2564.4	2513.1	2340.0	2134.8	1916.9	1718.1	1647.6	1753.4	1897.6	1997.0
22.5°	2634.9	2624.6	2583.6	2388.1	2150.9	1846.3	1583.5	1551.4	1679.7	1833.5	1961.7
25°	2705.4	2695.8	2657.3	2455.4	2166.9	1750.2	1468.1	1474.5	1583.5	1705.3	1836.7
27.5°	2801.6	2792.6	2756.7	2538.7	2186.1	1650.8	1375.1	1407.2	1487.3	1570.7	1650.8
30°	2907.3	2900.3	2872.1	2638.1	2224.6	1557.9	1320.6	1339.9	1394.4	1461.7	1509.8
32.5°	3051.6	3040.1	2993.9	2731.0	2221.4	1487.3	1295.0	1275.8	1291.8	1346.3	1394.4
35°	3231.1	3222.1	3186.2	2827.2	2163.7	1423.2	1282.2	1214.9	1205.3	1237.3	1285.4
37.5°	3493.9	3486.3	3455.5	2984.3	2073.9	1343.1	1250.1	1150.8	1118.7	1141.1	1173.2
40°	3888.2	3868.3	3788.8	3163.8	1974.6	1262.9	1192.4	1073.8	1029.0	1045.0	1080.2
42.5°	4423.5	4385.7	4234.4	3404.2	1839.9	1186.0	1105.9	996.9	948.8	958.4	990.5
45°	5109.5	5052.4	4824.2	3734.4	1698.9	1125.1	1016.1	916.8	865.5	875.1	910.3
47.5°	5910.9	5832.6	5519.8	4080.5	1548.2	1089.9	945.6	836.6	798.2	820.6	855.9
50°	6856.5	6777.6	6462.2	4301.7	1426.4	1067.4	891.1	762.9	746.9	775.7	804.6
52.5°	7888.6	7776.4	7327.7	4160.7	1327.1	1048.2	871.9	711.6	718.0	740.5	769.3
55°	8891.9	8642.5	7645.0	3692.7	1198.8	1025.7	884.7	673.1	689.2	718.0	740.5
57.5°	9545.8	9112.5	7379.0	2974.7	1064.2	1000.1	894.3	653.9	666.7	698.8	724.4
60°	8975.3	8539.3	6795.6	2227.8	948.8	945.6	878.3	647.5	628.3	673.1	695.6
62.5°	7353.3	6994.3	5558.3	1423.2	839.8	843.0	843.0	644.3	564.2	621.9	641.1
65°	*5051.8*	*4827.4*	*3929.9*	*881.5*	*686.0*	*718.0*	*766.1*	*625.1*	*496.8*	*564.2*	*583.4*
67.5°	3320.8	3156.1	2497.0	544.9	528.9	589.8	663.5	586.6	445.6	506.5	519.3
70°	1801.5	1676.5	1176.4	359.0	346.2	461.6	522.5	496.8	400.7	452.0	464.8
72.5°	1189.2	1086.6	676.4	253.2	253.2	362.2	365.4	407.1	359.0	400.7	413.5
75°	894.3	802.6	435.9	176.3	195.5	230.8	285.3	291.7	301.3	339.8	355.8
77.5°	410.3	360.3	160.3	105.8	144.2	160.3	218.0	185.9	224.4	253.2	259.6
80°	237.2	207.7	89.8	70.5	93.0	102.6	179.5	109.0	134.6	179.5	189.1
82.5°	99.4	88.5	44.9	48.1	57.7	60.9	99.4	76.9	86.5	118.6	115.4
85°	28.8	28.8	28.8	32.1	35.3	35.3	57.7	54.5	51.3	54.5	54.5
87.5°	19.2	19.2	19.2	19.2	22.4	22.4	25.6	28.8	32.1	32.1	32.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364605
CATALOG NUMBER: GSS-SB2C-735-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7
2.5°	1647.6	1625.2	1596.3	1554.6	1548.2	1525.8	1509.8	1525.8	1541.8	1570.7	1573.9
5°	1525.8	1490.5	1423.2	1371.9	1314.2	1285.4	1282.2	1275.8	1295.0	1336.7	1362.3
7.5°	1458.5	1400.8	1279.0	1189.2	1109.1	1080.2	1057.8	1077.0	1073.8	1128.3	1150.8
10°	1442.5	1352.7	1182.8	1048.2	948.8	910.3	887.9	884.7	891.1	923.2	945.6
12.5°	1500.2	1384.8	1144.3	945.6	830.2	788.5	762.9	740.5	740.5	746.9	775.7
15°	1628.4	1490.5	1166.8	897.5	772.5	718.0	676.4	647.5	625.1	628.3	631.5
17.5°	1807.9	1644.4	1224.5	881.5	737.3	679.6	628.3	599.4	573.8	567.4	567.4
20°	1948.9	1791.8	1269.4	868.7	708.4	634.7	589.8	564.2	541.7	532.1	532.1
22.5°	1964.9	1852.8	1307.8	852.7	673.1	589.8	548.1	525.7	509.7	506.5	506.5
25°	1859.2	1804.7	1295.0	833.4	637.9	548.1	516.1	496.8	480.8	477.6	480.8
27.5°	1682.9	1654.0	1250.1	807.8	609.0	516.1	487.2	471.2	455.2	452.0	455.2
30°	1525.8	1493.7	1173.2	766.1	586.6	490.4	458.4	442.4	426.3	426.3	429.5
32.5°	1397.6	1365.5	1096.3	718.0	557.7	461.6	432.7	416.7	400.7	400.7	407.1
35°	1282.2	1256.5	1035.4	669.9	528.9	435.9	403.9	391.1	378.2	375.0	381.4
37.5°	1182.8	1170.0	980.9	618.7	500.1	410.3	381.4	368.6	352.6	349.4	355.8
40°	1086.6	1080.2	920.0	573.8	464.8	384.7	355.8	343.0	323.8	323.8	330.2
42.5°	996.9	993.7	865.5	544.9	432.7	359.0	327.0	314.1	298.1	298.1	304.5
45°	926.4	923.2	814.2	528.9	400.7	330.2	301.3	285.3	272.5	275.7	282.1
47.5°	862.3	855.9	759.7	532.1	384.7	310.9	272.5	256.4	246.8	253.2	262.8
50°	811.0	804.6	721.2	535.3	359.0	285.3	250.0	234.0	227.6	237.2	246.8
52.5°	778.9	772.5	682.8	516.1	327.0	266.1	227.6	218.0	218.0	227.6	234.0
55°	746.9	740.5	618.7	474.4	291.7	246.8	211.6	205.1	205.1	214.8	221.2
57.5°	727.6	714.8	551.3	426.3	262.8	224.4	195.5	195.5	195.5	198.7	201.9
60°	698.8	666.7	480.8	365.4	240.4	201.9	182.7	179.5	179.5	176.3	179.5
62.5°	637.9	583.4	403.9	310.9	214.8	182.7	166.7	163.5	153.9	144.2	147.5
65°	*577.0*	*493.6*	*320.5*	*259.6*	*185.9*	*157.1*	*147.5*	*144.2*	*128.2*	*115.4*	*118.6*
67.5°	500.1	394.3	240.4	218.0	160.3	134.6	125.0	125.0	115.4	105.8	105.8
70°	445.6	307.7	201.9	163.5	128.2	105.8	105.8	112.2	102.6	89.8	89.8
72.5°	394.3	250.0	163.5	131.4	99.4	83.3	89.8	93.0	83.3	73.7	73.7
75°	336.6	195.5	128.2	102.6	73.7	64.1	67.3	73.7	67.3	57.7	60.9
77.5°	243.6	134.6	86.5	67.3	54.5	48.1	51.3	51.3	48.1	44.9	44.9
80°	169.9	89.8	57.7	44.9	38.5	35.3	35.3	32.1	32.1	35.3	35.3
82.5°	102.6	64.1	41.7	35.3	28.8	22.4	22.4	25.6	25.6	28.8	28.8
85°	44.9	38.5	28.8	25.6	19.2	16.0	19.2	19.2	22.4	25.6	25.6
87.5°	28.8	28.8	22.4	19.2	16.0	12.8	12.8	16.0	16.0	19.2	22.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364605
CATALOG NUMBER: GSS-SB2C-735-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7
2.5°	1586.7	1618.8	1657.2	1711.7	1759.8	1817.5	1875.2	1929.7	1981.0	1987.4	2009.8
5°	1381.6	1442.5	1519.4	1609.1	1718.1	1833.5	1945.7	2064.3	2160.5	2195.7	2247.0
7.5°	1170.0	1246.9	1359.1	1496.9	1650.8	1823.9	1997.0	2163.7	2307.9	2375.2	2442.6
10°	968.0	1041.8	1179.6	1346.3	1545.0	1779.0	2009.8	2234.2	2410.5	2487.4	2551.5
12.5°	785.3	859.1	971.3	1163.6	1404.0	1686.1	1990.6	2259.8	2455.4	2535.5	2596.4
15°	641.1	702.0	807.8	987.3	1240.5	1557.9	1923.3	2240.6	2465.0	2541.9	2586.8
17.5°	564.2	580.2	647.5	811.0	1086.6	1442.5	1836.7	2215.0	2471.4	2541.9	2567.6
20°	532.1	532.1	544.9	631.5	900.7	1320.6	1772.6	2198.9	2481.0	2551.5	2548.3
22.5°	503.3	509.7	509.7	528.9	686.0	1150.8	1705.3	2192.5	2509.9	2564.4	2519.5
25°	477.6	487.2	487.2	493.6	538.5	948.8	1622.0	2205.4	2561.2	2590.0	2500.3
27.5°	455.2	464.8	464.8	471.2	480.8	705.2	1484.1	2208.6	2618.9	2622.1	2474.6
30°	432.7	442.4	448.8	448.8	455.2	519.3	1311.0	2189.3	2683.0	2663.7	2471.4
32.5°	407.1	419.9	423.1	429.5	432.7	452.0	1086.6	2157.3	2763.1	2721.4	2474.6
35°	384.7	400.7	403.9	403.9	410.3	429.5	868.7	2122.0	2872.1	2798.4	2487.4
37.5°	362.2	375.0	378.2	381.4	387.9	407.1	689.2	2070.7	2965.0	2894.5	2551.5
40°	336.6	352.6	355.8	359.0	365.4	384.7	593.0	2006.6	3106.1	3054.8	2647.7
42.5°	310.9	327.0	333.4	336.6	339.8	365.4	541.7	1961.7	3333.7	3279.2	2843.2
45°	288.5	304.5	310.9	310.9	317.3	352.6	496.8	2061.1	3647.8	3622.2	3106.1
47.5°	269.3	285.3	288.5	288.5	291.7	333.4	458.4	2327.2	4128.6	4061.3	3516.4
50°	253.2	266.1	272.5	266.1	269.3	317.3	480.8	2766.3	4744.1	4766.5	4119.0
52.5°	240.4	253.2	256.4	243.6	243.6	294.9	509.7	3125.3	5529.4	5734.6	5074.2
55°	224.4	237.2	240.4	224.4	224.4	259.6	442.4	3147.8	6423.7	7084.1	6317.9
57.5°	208.4	221.2	221.2	208.4	205.1	224.4	359.0	2791.9	7116.1	8613.1	8020.0
60°	189.1	201.9	198.7	192.3	185.9	205.1	330.2	2128.4	7023.1	9609.9	9972.2
62.5°	153.9	173.1	179.5	176.3	163.5	185.9	307.7	1388.0	6077.5	8744.5	9911.3
65°	*128.2*	*144.2*	*153.9*	*153.9*	*144.2*	*205.1*	*269.3*	*730.8*	*4865.9*	*7420.6*	*8738.1*
67.5°	112.2	128.2	134.6	131.4	125.0	182.7	169.9	352.6	3731.1	6394.9	7821.3
70°	99.4	112.2	118.6	109.0	102.6	147.5	121.8	208.4	2497.0	5337.1	6965.4
72.5°	80.1	93.0	99.4	89.8	80.1	109.0	93.0	137.8	1625.2	4548.5	6189.7
75°	64.1	76.9	80.1	73.7	64.1	80.1	73.7	96.2	1061.0	3763.2	5263.4
77.5°	48.1	54.5	60.9	57.7	48.1	57.7	51.3	67.3	605.8	2641.3	3692.7
80°	38.5	41.7	41.7	41.7	38.5	35.3	35.3	44.9	272.5	1301.4	1926.5
82.5°	32.1	35.3	35.3	32.1	28.8	25.6	22.4	25.6	80.1	583.4	887.9
85°	28.8	32.1	25.6	22.4	19.2	16.0	9.6	9.6	22.4	93.0	173.1
87.5°	22.4	19.2	16.0	12.8	6.4	3.2	3.2	0.0	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364605
CATALOG NUMBER: GSS-SB2C-735-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	1804.7	1804.7	1804.7	*1804.7*	1804.7	1804.7	1804.7	1804.7	1804.7	1804.7
2.5°	2045.1	2077.1	2099.6	*2118.8*	2112.4	2096.4	2064.3	2041.9	2036.7	2035.5
5°	2314.3	2365.6	2410.5	*2404.1*	2410.5	2362.4	2314.3	2256.6	2233.6	2227.8
7.5°	2538.7	2602.8	2657.3	*2650.9*	2631.7	2577.2	2497.0	2410.5	2369.5	2359.2
10°	2660.5	2734.3	2779.1	*2763.1*	2731.0	2660.5	2580.4	2477.8	2431.7	2420.1
12.5°	2683.0	2731.0	2721.4	*2715.0*	2708.6	2673.3	2612.4	2519.5	2473.3	2461.8
15°	2625.3	2606.0	2551.5	*2538.7*	2586.8	2631.7	2618.9	2541.9	2498.3	2487.4
17.5°	2529.1	2429.7	2330.4	*2317.5*	2397.7	2522.7	2622.1	2577.2	2536.2	2525.9
20°	2423.3	2237.4	2128.4	*2106.0*	2205.4	2391.3	2586.8	2612.4	2584.2	2577.2
22.5°	2298.3	2080.3	1964.9	*1952.1*	2025.8	2243.8	2535.5	2650.9	2638.1	2634.9
25°	2189.3	1942.5	1833.5	*1814.3*	1910.5	2122.0	2484.2	2715.0	2707.3	2705.4
27.5°	2099.6	1843.1	1727.7	*1714.9*	1807.9	2019.4	2420.1	2769.5	2795.2	2801.6
30°	2029.1	1769.4	1654.0	*1638.0*	1740.6	1948.9	2375.2	2846.4	2895.2	2907.3
32.5°	1974.6	1727.7	1618.8	*1609.1*	1718.1	1920.1	2349.6	2926.6	3026.6	3051.6
35°	1955.3	1740.6	1666.8	*1689.3*	1772.6	1948.9	2368.8	3058.0	3196.5	3231.1
37.5°	1997.0	1881.6	1932.9	*1990.6*	2022.6	2086.8	2458.6	3269.6	3449.1	3493.9
40°	2131.6	2259.8	2500.3	*2612.4*	2599.6	2452.2	2663.7	3567.7	3824.1	3888.2
42.5°	2474.6	2891.3	3401.0	*3590.1*	3481.1	3035.6	2990.7	4058.1	4350.4	4423.5
45°	2984.3	3654.2	4490.8	*4917.2*	4542.1	3776.0	3506.8	4756.9	5039.0	5109.5
47.5°	3493.9	4506.9	5837.1	*6343.6*	5606.3	4510.1	4183.1	5593.5	5847.4	5910.9
50°	4013.2	5449.3	7180.2	*7856.6*	6667.3	5256.9	4901.1	6625.7	6810.3	6856.5
52.5°	4548.5	6292.3	8661.1	*9244.5*	7776.4	5833.9	5721.7	7750.8	7861.1	7888.6
55°	5144.8	7090.5	10145.3	*10616.5*	8786.1	6337.2	6683.4	8927.2	8899.0	8891.9
57.5°	5939.7	7930.3	11340.9	*11998.0*	9702.9	7016.7	7968.8	10235.0	9683.7	9545.8
60°	7327.7	9234.9	12828.2	*13543.0*	10930.6	8010.4	8914.4	10206.2	9221.4	8975.3
62.5°	8936.8	10491.4	14174.5	*14777.1*	12222.4	8997.7	8161.1	8571.4	7596.9	7353.3
65°	*7763.6*	*10270.3*	*14216.2*	*14834.8*	*12270.5*	*8395.1*	*6032.7*	*6077.5*	*5256.9*	*5051.8*
67.5°	6606.4	9103.5	12946.8	*13434.1*	10946.6	6939.8	4000.4	3965.1	3449.7	3320.8
70°	5882.0	7975.2	11158.2	*10738.3*	9202.9	5866.0	2657.3	2202.1	1881.6	1801.5
72.5°	5285.8	6327.6	9042.6	*7401.4*	7635.4	4772.9	1689.3	1500.2	1251.4	1189.2
75°	4785.7	5234.5	5641.6	*5115.9*	5423.6	3933.1	1432.8	1157.2	946.9	894.3
77.5°	3808.1	4074.1	3340.1	*3243.9*	3798.5	2798.4	711.6	487.2	425.7	410.3
80°	2266.3	1926.5	1894.4	*2160.5*	2529.1	1452.1	435.9	269.3	243.6	237.2
82.5°	1371.9	695.6	756.5	*955.2*	1346.3	660.3	259.6	115.4	102.6	99.4
85°	230.8	189.1	291.7	*278.9*	262.8	141.0	70.5	32.1	29.5	28.8
87.5°	6.4	9.6	12.8	*16.0*	16.0	16.0	16.0	16.0	18.6	19.2
90°	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ

Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-735-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369
CIE u':	0.2386
CIE v':	0.5156
Duv:	0.0013
CIE x:	0.4143
CIE y:	0.3980
CIE z:	0.1877
Peak Wavelength (nm):	590
Dominant Wavelength (nm):	580
Purity:	43.80166
Rf:	71.4
Rg:	96

CRI (Ra):	70.1
R1:	66.6
R2:	77.6
R3:	88.5
R4:	69.5
R5:	66.4
R6:	69.6
R7:	77.5
R8:	44.9
R9:	-40.2
R10:	49.1
R11:	66.3
R12:	45.7
R13:	68.0
R14:	93.4
R15:	57.6



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3369K
CIE x = 0.4143
CIE y = 0.3980
Duv = 0.0013

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.36**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-5

TM-30-18


Summary


R_f = 71.4
R_g = 96
CIE R_a = 70.1
R_9 = -40.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	





REPORT NUMBER: SP1-2407-184-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-5

TM-30-18

Measure Comparisons





(END OF REPORT)