Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360765

Luminaire Tested: **GSS-SB2C-735-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360765
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2C-735-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 102W 70CRI 3500K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(52) 3500K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	13646 lumens
Efficiency:	N/A
Efficacy:	133.8 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	102
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360765
CATALOG NUMBER: GSS-SB2C-735-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 6.7 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360765
CATALOG NUMBER: GSS-SB2C-735-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360765
CATALOG NUMBER: GSS-SB2C-735-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6823.0	0.0	6823.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	6823.0	0.0	6823.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	13646.0	0.0	13646.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	260.2	1.9
10°-20°	793.2	5.8
20°-30°	1325.7	9.7
30°-40°	1828.2	13.4
40°-50°	2241.2	16.4
50°-60°	2626.3	19.2
60°-70°	2916.5	21.4
70°-80°	1586.0	11.6
80°-90°	68.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	13646.0	100.0
0°-180°	13646.0	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360765
CATALOG NUMBER: GSS-SB2C-735-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1189.5	8.7			
FM	(30°-60°)	3347.9	24.5			
FH	(60°-80°)	2251.2	16.5			G2/5000
FVH	(80°-90°)	34.4	0.3			G1/100
BL	(0°-30°)	1189.5	8.7	B3/2500		
BM	(30°-60°)	3347.9	24.5	B3/5000		
BH	(60°-80°)	2251.2	16.5	B3/2500		G3/2500
BVH	(80°-90°)	34.4	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360765
CATALOG NUMBER: GSS-SB2C-735-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	2688.6	2688.6	2688.6	2688.6	2688.6	2688.6	2688.6	2688.6	2688.6	2688.6	2688.6
2.5°	2691.6	2691.6	2682.6	2694.6	2688.6	2691.6	2694.6	2691.6	2688.6	2691.6	2694.6
5°	2706.5	2700.6	2706.5	2712.5	2703.5	2709.5	2706.5	2691.6	2700.6	2700.6	2700.6
7.5°	2733.4	2739.4	2733.4	2748.3	2739.4	2757.3	2739.4	2727.4	2724.5	2721.5	2721.5
10°	2745.4	2745.4	2742.4	2769.3	2775.2	2793.2	2781.2	2763.3	2754.3	2742.4	2730.4
12.5°	2712.5	2718.5	2733.4	2784.2	2808.1	2843.9	2835.0	2799.1	2772.2	2763.3	2745.4
15°	2676.7	2682.6	2712.5	2775.2	2832.0	2885.8	2882.8	2838.0	2805.1	2781.2	2754.3
17.5°	2619.9	2628.9	2670.7	2766.3	2867.8	2927.6	2945.5	2900.7	2864.9	2826.0	2790.2
20°	2524.3	2524.3	2599.0	2721.5	2861.9	2996.3	3044.1	3008.2	2966.4	2903.7	2855.9
22.5°	2416.8	2422.7	2497.4	2658.7	2858.9	3056.0	3148.7	3109.8	3068.0	2999.3	2927.6
25°	2309.2	2309.2	2392.9	2575.1	2820.0	3097.9	3271.1	3250.2	3166.6	3103.8	3011.2
27.5°	2210.6	2210.6	2300.2	2491.4	2754.3	3109.8	3393.6	3393.6	3301.0	3208.4	3106.8
30°	2094.1	2124.0	2225.6	2425.7	2694.6	3088.9	3483.2	3540.0	3456.3	3336.9	3187.5
32.5°	1995.5	2016.5	2121.0	2333.1	2607.9	3065.0	3584.8	3725.2	3638.6	3474.3	3307.0
35°	1879.0	1876.0	1995.5	2204.7	2485.5	3011.2	3665.5	3946.3	3862.6	3686.4	3459.3
37.5°	1726.7	1726.7	1849.2	2052.3	2369.0	2918.6	3731.2	4191.2	4128.5	3928.3	3686.4
40°	1562.4	1580.3	1687.8	1894.0	2228.6	2808.1	3731.2	4391.4	4424.2	4218.1	3967.2
42.5°	1442.9	1448.9	1547.4	1741.6	2073.2	2664.7	3683.4	4564.6	4663.2	4490.0	4164.3
45°	1317.4	1332.4	1416.0	1595.2	1911.9	2494.4	3599.7	4758.8	4917.2	4797.7	4370.5
47.5°	1165.1	1180.0	1275.6	1457.8	1759.5	2309.2	3459.3	4962.0	5293.6	5206.9	4737.9
50°	988.8	1000.8	1090.4	1284.6	1589.3	2097.1	3283.1	5114.3	5670.0	5756.6	5293.6
52.5°	773.7	782.7	878.3	1066.5	1386.1	1894.0	3035.1	5206.9	6049.4	6354.1	6037.4
55°	555.6	570.6	654.2	809.6	1117.3	1622.1	2739.4	5254.7	6464.6	7062.1	6960.5
57.5°	400.3	406.3	463.0	582.5	830.5	1302.5	2360.0	5174.1	6838.0	7907.5	8119.6
60°	331.6	331.6	340.6	397.3	567.6	920.1	1905.9	4875.3	7157.7	8761.9	9416.1
62.5°	304.7	304.7	310.7	319.6	373.4	597.5	1362.2	4268.9	7193.5	9583.4	10838.1
65°	277.8	277.8	283.8	289.8	301.7	388.4	821.5	3124.8	6491.5	9592.3	11602.8
67.5°	253.9	253.9	256.9	259.9	265.9	283.8	451.1	1894.0	5195.0	9338.4	11895.6
70°	230.0	230.0	230.0	227.0	236.0	239.0	298.7	961.9	3474.3	8433.3	11755.2
72.5°	*203.1*	*203.1*	*200.2*	*194.2*	*197.2*	*197.2*	*221.1*	*472.0*	*1804.4*	*6703.6*	*10614.0*
75°	173.3	176.3	164.3	158.3	155.3	158.3	176.3	268.9	806.6	4065.8	7931.4
77.5°	146.4	152.4	134.4	122.5	119.5	119.5	137.4	167.3	346.5	1475.7	3554.9
80°	110.5	113.5	98.6	86.6	86.6	83.6	101.6	122.5	164.3	439.1	797.6
82.5°	62.7	62.7	56.8	50.8	47.8	50.8	68.7	83.6	101.6	155.3	218.1
85°	14.9	14.9	17.9	20.9	20.9	26.9	38.8	44.8	53.8	62.7	83.6
87.5°	3.0	3.0	3.0	6.0	9.0	9.0	14.9	20.9	26.9	32.9	35.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360765
CATALOG NUMBER: GSS-SB2C-735-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	2688.6	2688.6	*2688.6*
2.5°	2694.6	2697.6	*2694.6*
5°	2712.5	2706.5	*2697.6*
7.5°	2715.5	2718.5	*2721.5*
10°	2727.4	2739.4	*2721.5*
12.5°	2739.4	2730.4	*2724.5*
15°	2748.3	2745.4	*2727.4*
17.5°	2781.2	2769.3	*2766.3*
20°	2832.0	2829.0	*2820.0*
22.5°	2891.7	2885.8	*2882.8*
25°	2978.4	2957.5	*2945.5*
27.5°	3050.1	3032.1	*3026.2*
30°	3121.8	3085.9	*3085.9*
32.5°	3184.5	3175.5	*3169.6*
35°	3333.9	3289.1	*3295.0*
37.5°	3516.1	3471.3	*3432.4*
40°	3773.0	3713.3	*3689.4*
42.5°	3937.3	3877.6	*3883.5*
45°	4029.9	3925.4	*3898.5*
47.5°	4280.9	4149.4	*4113.6*
50°	4687.1	4525.8	*4481.0*
52.5°	5344.3	5084.4	*5024.7*
55°	6168.8	5849.2	*5789.5*
57.5°	7298.1	6873.9	*6745.4*
60°	8672.2	8146.5	*7952.3*
62.5°	10324.2	9676.0	*9490.8*
65°	11567.0	11026.3	*10739.5*
67.5°	12561.7	12116.6	*11979.2*
70°	13153.2	13174.2	*13210.0*
72.5°	*12469.1*	*13042.7*	*13317.5*
75°	9138.3	9583.4	*10010.6*
77.5°	3531.0	3184.5	*3082.9*
80°	570.6	534.7	*552.7*
82.5°	256.9	271.8	*286.8*
85°	167.3	194.2	*206.1*
87.5°	38.8	38.8	*38.8*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ

Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-735-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369
CIE u':	0.2386
CIE v':	0.5156
Duv:	0.0013
CIE x:	0.4143
CIE y:	0.3980
CIE z:	0.1877
Peak Wavelength (nm):	590
Dominant Wavelength (nm):	580
Purity:	43.80166
Rf:	71.4
Rg:	96

CRI (Ra):	70.1
R1:	66.6
R2:	77.6
R3:	88.5
R4:	69.5
R5:	66.4
R6:	69.6
R7:	77.5
R8:	44.9
R9:	-40.2
R10:	49.1
R11:	66.3
R12:	45.7
R13:	68.0
R14:	93.4
R15:	57.6



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3369K
CIE x = 0.4143
CIE y = 0.3980
Duv = 0.0013

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.36**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-5

TM-30-18


Summary


R_f = 71.4
R_g = 96
CIE R_a = 70.1
R_9 = -40.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	





REPORT NUMBER: SP1-2407-184-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-5

TM-30-18

Measure Comparisons





(END OF REPORT)