Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360679

Luminaire Tested: **GSS-SB5A-740-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360679
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB5A-740-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 5SQUARE 143W 70CRI 4000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(130) 4000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	22740.3 lumens
Efficiency:	N/A
Efficacy:	159.0 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	143
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	10.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360679
CATALOG NUMBER: GSS-SB5A-740-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 11.2 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360679
CATALOG NUMBER: GSS-SB5A-740-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360679
CATALOG NUMBER: GSS-SB5A-740-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	11370.2	0.0	11370.2
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	11370.2	0.0	11370.2
	% Fixture	50.0	0.0	50.0
Total	Lumens	22740.3	0.0	22740.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	433.7	1.9
10°-20°	1321.7	5.8
20°-30°	2209.2	9.7
30°-40°	3046.6	13.4
40°-50°	3734.8	16.4
50°-60°	4376.6	19.2
60°-70°	4860.2	21.4
70°-80°	2643.0	11.6
80°-90°	114.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	22740.3	100.0
0°-180°	22740.3	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360679
CATALOG NUMBER: GSS-SB5A-740-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1982.3	8.7			
FM	(30°-60°)	5579.0	24.5			
FH	(60°-80°)	3751.6	16.5			G2/5000
FVH	(80°-90°)	57.3	0.3			G1/100
BL	(0°-30°)	1982.3	8.7	B3/2500		
BM	(30°-60°)	5579.0	24.5	B4/8500		
BH	(60°-80°)	3751.6	16.5	B4/5000		G4/5000
BVH	(80°-90°)	57.3	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360679
CATALOG NUMBER: GSS-SB5A-740-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	4480.4	4480.4	4480.4	4480.4	4480.4	4480.4	4480.4	4480.4	4480.4	4480.4	4480.4
2.5°	4485.4	4485.4	4470.4	4490.4	4480.4	4485.4	4490.4	4485.4	4480.4	4485.4	4490.4
5°	4510.3	4500.3	4510.3	4520.2	4505.3	4515.3	4510.3	4485.4	4500.3	4500.3	4500.3
7.5°	4555.1	4565.0	4555.1	4580.0	4565.0	4594.9	4565.0	4545.1	4540.1	4535.2	4535.2
10°	4575.0	4575.0	4570.0	4614.8	4624.8	4654.6	4634.7	4604.9	4589.9	4570.0	4550.1
12.5°	4520.2	4530.2	4555.1	4639.7	4679.5	4739.3	4724.3	4664.6	4619.8	4604.9	4575.0
15°	4460.5	4470.4	4520.2	4624.8	4719.4	4809.0	4804.0	4729.3	4674.6	4634.7	4589.9
17.5°	4365.9	4380.8	4450.5	4609.8	4779.1	4878.7	4908.5	4833.9	4774.1	4709.4	4649.7
20°	4206.6	4206.6	4331.1	4535.2	4769.1	4993.2	5072.8	5013.1	4943.4	4838.8	4759.2
22.5°	4027.4	4037.3	4161.8	4430.6	4764.2	5092.7	5247.1	5182.3	5112.6	4998.1	4878.7
25°	3848.2	3848.2	3987.6	4291.2	4699.4	5162.4	5451.2	5416.3	5276.9	5172.4	5018.1
27.5°	3683.9	3683.9	3833.2	4151.8	4589.9	5182.3	5655.3	5655.3	5500.9	5346.6	5177.4
30°	3489.7	3539.5	3708.8	4042.3	4490.4	5147.5	5804.6	5899.2	5759.8	5560.7	5311.8
32.5°	3325.5	3360.3	3534.5	3888.0	4346.0	5107.7	5973.9	6207.9	6063.5	5789.7	5510.9
35°	3131.3	3126.3	3325.5	3673.9	4141.9	5018.1	6108.3	6576.2	6436.8	6143.1	5764.8
37.5°	2877.4	2877.4	3081.5	3420.0	3947.7	4863.7	6217.8	6984.5	6879.9	6546.4	6143.1
40°	2603.6	2633.5	2812.7	3156.2	3713.8	4679.5	6217.8	7318.0	7372.8	7029.3	6611.1
42.5°	2404.5	2414.4	2578.7	2902.3	3454.9	4440.6	6138.2	7606.7	7771.0	7482.3	6939.7
45°	2195.4	2220.3	2359.7	2658.4	3186.1	4156.8	5998.8	7930.3	8194.2	7995.0	7283.1
47.5°	1941.5	1966.4	2125.7	2429.4	2932.2	3848.2	5764.8	8268.8	8821.4	8677.1	7895.5
50°	1647.8	1667.7	1817.1	2140.6	2648.4	3494.7	5471.1	8522.7	9448.7	9593.0	8821.4
52.5°	1289.4	1304.3	1463.6	1777.2	2309.9	3156.2	5057.9	8677.1	10080.9	10588.7	10061.0
55°	926.0	950.8	1090.2	1349.1	1861.9	2703.2	4565.0	8756.7	10772.9	11768.5	11599.3
57.5°	667.1	677.0	771.6	970.8	1383.9	2170.5	3932.8	8622.3	11395.2	13177.4	13530.8
60°	552.6	552.6	567.5	662.1	945.9	1533.3	3176.1	8124.5	11927.8	14601.1	15691.4
62.5°	507.8	507.8	517.7	532.7	622.3	995.6	2270.1	7113.9	11987.6	15970.2	18061.0
65°	463.0	463.0	472.9	482.9	502.8	647.2	1369.0	5207.2	10817.7	15985.1	19335.4
67.5°	423.1	423.1	428.1	433.1	443.1	472.9	751.7	3156.2	8657.1	15561.9	19823.3
70°	383.3	383.3	383.3	378.3	393.3	398.3	497.8	1603.0	5789.7	14053.5	19589.3
72.5°	*338.5*	*338.5*	*333.5*	*323.6*	*328.6*	*328.6*	*368.4*	*786.6*	*3006.8*	*11171.1*	*17687.6*
75°	288.7	293.7	273.8	263.8	258.9	263.8	293.7	448.0	1344.1	6775.4	13217.2
77.5°	243.9	253.9	224.0	204.1	199.1	199.1	229.0	278.8	577.5	2459.2	5924.1
80°	184.2	189.2	164.3	144.4	144.4	139.4	169.3	204.1	273.8	731.8	1329.2
82.5°	104.5	104.5	94.6	84.6	79.7	84.6	114.5	139.4	169.3	258.9	363.4
85°	24.9	24.9	29.9	34.8	34.8	44.8	64.7	74.7	89.6	104.5	139.4
87.5°	5.0	5.0	5.0	10.0	14.9	14.9	24.9	34.8	44.8	54.8	59.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360679
CATALOG NUMBER: GSS-SB5A-740-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	4480.4	4480.4	*4480.4*
2.5°	4490.4	4495.3	*4490.4*
5°	4520.2	4510.3	*4495.3*
7.5°	4525.2	4530.2	*4535.2*
10°	4545.1	4565.0	*4535.2*
12.5°	4565.0	4550.1	*4540.1*
15°	4580.0	4575.0	*4545.1*
17.5°	4634.7	4614.8	*4609.8*
20°	4719.4	4714.4	*4699.4*
22.5°	4818.9	4809.0	*4804.0*
25°	4963.3	4928.4	*4908.5*
27.5°	5082.8	5052.9	*5042.9*
30°	5202.2	5142.5	*5142.5*
32.5°	5306.8	5291.9	*5281.9*
35°	5555.7	5481.0	*5491.0*
37.5°	5859.4	5784.7	*5720.0*
40°	6287.5	6187.9	*6148.1*
42.5°	6561.3	6461.7	*6471.7*
45°	6715.6	6541.4	*6496.6*
47.5°	7133.8	6914.8	*6855.0*
50°	7810.8	7542.0	*7467.3*
52.5°	8906.1	8472.9	*8373.4*
55°	10280.0	9747.4	*9647.8*
57.5°	12161.8	11454.9	*11240.8*
60°	14451.8	13575.6	*13252.0*
62.5°	17204.8	16124.5	*15815.8*
65°	19275.7	18374.6	*17896.7*
67.5°	20933.5	20191.7	*19962.7*
70°	21919.1	21954.0	*22013.7*
72.5°	*20779.1*	*21734.9*	*22192.9*
75°	15228.4	15970.2	*16682.0*
77.5°	5884.3	5306.8	*5137.5*
80°	950.8	891.1	*921.0*
82.5°	428.1	453.0	*477.9*
85°	278.8	323.6	*343.5*
87.5°	64.7	64.7	*64.7*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ

Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-740-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 4000K CCT 26 LEDS

Spectral Parameters

CCT (K):	3949
CIE u':	0.2248
CIE v':	0.5053
Duv:	0.0022
CIE x:	0.3844
CIE y:	0.3840
CIE z:	0.2316
Peak Wavelength (nm):	440
Dominant Wavelength (nm):	578
Purity:	30.60026
Rf:	71.8
Rg:	96.5

CRI (Ra):	70.7
R1:	68.0
R2:	76.0
R3:	84.3
R4:	72.0
R5:	68.6
R6:	68.3
R7:	77.9
R8:	50.3
R9:	-36.7
R10:	45.1
R11:	70.7
R12:	47.1
R13:	68.5
R14:	91.1
R15:	58.7



Test Conditions


Stabilization Time:	34M
Operation Time:	1H 34M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3949K
CIE x = 0.3844
CIE y = 0.3840
Duv = 0.0022

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.78**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-1

TM-30-18


Summary


R_f = 71.8
R_g = 96.5
CIE R_a = 70.7
R_9 = -36.7


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 56	CES51 = 86	CES76 = 48
CES02 = 61	CES27 = 79	CES52 = 88	CES77 = 71
CES03 = 30	CES28 = 80	CES53 = 73	CES78 = 52
CES04 = 70	CES29 = 49	CES54 = 79	CES79 = 79
CES05 = 47	CES30 = 53	CES55 = 77	CES80 = 77
CES06 = 50	CES31 = 55	CES56 = 67	CES81 = 75
CES07 = 40	CES32 = 53	CES57 = 64	CES82 = 90
CES08 = 39	CES33 = 59	CES58 = 67	CES83 = 84
CES09 = 29	CES34 = 67	CES59 = 87	CES84 = 89
CES10 = 74	CES35 = 82	CES60 = 91	CES85 = 86
CES11 = 57	CES36 = 86	CES61 = 87	CES86 = 71
CES12 = 63	CES37 = 76	CES62 = 76	CES87 = 78
CES13 = 42	CES38 = 62	CES63 = 73	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 71	CES89 = 72
CES15 = 71	CES40 = 84	CES65 = 64	CES90 = 72
CES16 = 46	CES41 = 81	CES66 = 67	CES91 = 97
CES17 = 49	CES42 = 76	CES67 = 65	CES92 = 66
CES18 = 56	CES43 = 71	CES68 = 72	CES93 = 81
CES19 = 72	CES44 = 98	CES69 = 82	CES94 = 55
CES20 = 65	CES45 = 80	CES70 = 61	CES95 = 73
CES21 = 86	CES46 = 76	CES71 = 59	CES96 = 78
CES22 = 78	CES47 = 71	CES72 = 86	CES97 = 83
CES23 = 92	CES48 = 61	CES73 = 52	CES98 = 72
CES24 = 91	CES49 = 76	CES74 = 93	CES99 = 60
CES25 = 72	CES50 = 84	CES75 = 56	





REPORT NUMBER: SP1-2407-184-1

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-1

TM-30-18

Measure Comparisons





(END OF REPORT)