Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360006

Luminaire Tested: **GSS-SB4D-735-U-T3**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360006
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4D-735-U-T3
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 238W 70CRI 3500K FIXTURE w/ TYPE III DISTRIBUTION OPTIC
Light Source:	(104) 3500K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	31269.6 lumens
Efficiency:	N/A
Efficacy:	131.4 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B3 - U0 - G4


Input Watts (W):	238
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	--
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360006
CATALOG NUMBER: GSS-SB4D-735-U-T3

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 13.7 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360006
CATALOG NUMBER: GSS-SB4D-735-U-T3

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360006
CATALOG NUMBER: GSS-SB4D-735-U-T3

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	7397.9	0.0	7397.9
	% Fixture	23.7	0.0	23.7
Street Side	Lumens	23871.7	0.0	23871.7
	% Fixture	76.3	0.0	76.3
Total	Lumens	31269.6	0.0	31269.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	474.5	1.5
10°-20°	1496.6	4.8
20°-30°	2558.7	8.2
30°-40°	3711.9	11.9
40°-50°	4821.7	15.4
50°-60°	6533.1	20.9
60°-70°	7620.8	24.4
70°-80°	3757.4	12.0
80°-90°	294.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	31269.6	100.0
0°-180°	31269.6	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360006
CATALOG NUMBER: GSS-SB4D-735-U-T3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2667.6	8.5			
FM	(30°-60°)	11420.6	36.5			
FH	(60°-80°)	9628.7	30.8			G4/12000
FVH	(80°-90°)	154.8	0.5			G2/225
BL	(0°-30°)	1862.2	6.0	B3/2500		
BM	(30°-60°)	3646.1	11.7	B3/5000		
BH	(60°-80°)	1749.4	5.6	B3/2500		G3/2500
BVH	(80°-90°)	140.1	0.4			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360006
CATALOG NUMBER: GSS-SB4D-735-U-T3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	52°	55°	65°	75°	85°
0°	4839.0	4839.0	4839.0	4839.0	4839.0	4839.0	*4839.0*	4839.0	4839.0	4839.0	4839.0
2.5°	4985.2	4978.2	4971.3	4943.4	4943.4	4950.4	*4936.4*	4943.4	4936.4	4901.6	4873.8
5°	5263.7	5201.0	5187.1	5173.2	5187.1	5145.3	*5110.5*	5089.6	5013.0	4992.1	4908.6
7.5°	5382.1	5389.0	5382.1	5354.2	5333.3	5333.3	*5277.6*	5249.8	5201.0	5117.5	4978.2
10°	5549.2	5542.2	5521.3	5535.2	5577.0	5507.4	*5465.6*	5444.7	5361.2	5242.8	5110.5
12.5°	5848.5	5799.8	5785.9	5765.0	5758.0	5716.3	*5667.5*	5674.5	5577.0	5396.0	5256.7
15°	6106.2	6050.5	6113.1	6071.3	6015.6	5953.0	*5904.2*	5862.5	5751.1	5584.0	5409.9
17.5°	6349.8	6322.0	6349.8	6349.8	6342.9	6238.4	*6141.0*	6106.2	5973.9	5785.9	5556.1
20°	6537.8	6537.8	6586.6	6586.6	6565.7	6503.0	*6440.4*	6398.6	6210.6	5966.9	5702.3
22.5°	6781.5	6670.1	6774.6	6781.5	6788.5	6739.8	*6698.0*	6642.3	6447.3	6154.9	5820.7
25°	7011.3	6920.8	6983.4	6941.7	6969.5	6990.4	*6969.5*	6948.6	6732.8	6398.6	5994.8
27.5°	7373.3	7282.8	7324.6	7227.1	7227.1	7206.2	*7241.1*	7268.9	7032.2	6635.3	6147.9
30°	7916.4	7812.0	7777.2	7658.8	7540.4	7491.7	*7505.6*	7554.4	7394.2	6865.1	6301.1
32.5°	8382.9	8327.2	8299.4	8201.9	8055.7	7832.9	*7867.7*	7867.7	7700.6	7032.2	6377.7
35°	8765.9	8751.9	8758.9	8626.6	8598.8	8236.7	*8236.7*	8222.8	7916.4	7255.0	6579.6
37.5°	9016.5	8939.9	8974.7	9023.5	8933.0	8689.3	*8626.6*	8591.8	8215.8	7491.7	6844.2
40°	8960.8	8905.1	9037.4	9127.9	9058.3	9009.5	*9002.6*	8933.0	8515.2	7791.1	7234.1
42.5°	8953.8	8905.1	9065.2	9162.7	9127.9	9204.5	*9225.4*	9274.1	8898.1	8264.5	7791.1
45°	8981.7	8960.8	9225.4	9350.7	9267.2	9371.6	*9490.0*	9531.7	9385.5	8842.4	8487.4
47.5°	9211.5	9183.6	9490.0	9636.2	9705.8	9886.8	*9810.2*	9879.9	9963.4	9664.0	9288.0
50°	9434.3	9462.1	9872.9	10012.2	10353.3	10604.0	*10339.4*	10450.8	10729.3	10617.9	10360.3
52.5°	9789.3	9796.3	10200.1	10548.3	11202.7	11439.5	*11181.9*	11195.8	11571.8	11780.6	11439.5
55°	9879.9	9956.4	10499.5	11223.6	12163.6	12330.7	*12212.3*	12163.6	12609.2	12894.6	12525.6
57.5°	9872.9	9831.1	10506.5	11509.1	12894.6	13486.5	*13556.1*	13423.8	13799.8	13918.1	13716.2
60°	9615.3	9698.8	10436.9	11711.0	13577.0	14892.9	*15060.0*	14885.9	15067.0	15101.8	14537.8
62.5°	8828.5	8856.4	9865.9	11718.0	14113.1	16062.6	*16556.9*	16362.0	16194.9	15763.2	14718.8
65°	7547.4	7498.7	8466.5	10750.2	14210.6	17190.5	*17900.7*	17900.7	16814.6	15986.0	14335.9
67.5°	*6294.1*	*6217.6*	*6941.7*	*8765.9*	*12651.0*	*17684.9*	*18819.8*	*18450.8*	*16946.9*	*16139.2*	*13423.8*
70°	3035.7	3251.5	4358.6	6203.6	9671.0	14934.7	*18137.4*	18276.7	16842.4	15658.8	11655.3
72.5°	1086.2	1037.4	1566.6	2659.7	5354.2	9747.6	*15185.3*	16410.7	16111.3	14280.2	9545.7
75°	501.3	508.3	654.5	926.0	1733.7	4755.4	*9657.1*	11300.2	13799.8	11871.2	7143.6
77.5°	389.9	389.9	445.6	529.2	717.1	1538.7	*4936.4*	6342.9	8919.0	7352.5	3404.7
80°	285.5	292.4	299.4	348.1	438.6	577.9	*1469.1*	2200.2	3251.5	2360.3	1107.0
82.5°	201.9	201.9	195.0	195.0	236.7	257.6	*396.9*	557.0	953.9	647.5	292.4
85°	83.6	97.5	83.6	83.6	83.6	104.4	*125.3*	146.2	208.9	181.0	125.3
87.5°	13.9	13.9	13.9	20.9	27.9	34.8	*41.8*	48.7	55.7	55.7	55.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360006
CATALOG NUMBER: GSS-SB4D-735-U-T3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	4839.0	4839.0	4839.0	4839.0	4839.0	4839.0	4839.0	4839.0	4839.0	4839.0	4839.0
2.5°	4859.9	4859.9	4839.0	4804.2	4790.2	4769.3	4762.4	4755.4	4741.5	4769.3	4755.4
5°	4887.7	4859.9	4832.0	4776.3	4769.3	4734.5	4699.7	4692.8	4671.9	4692.8	4692.8
7.5°	4950.4	4908.6	4845.9	4790.2	4741.5	4734.5	4671.9	4616.2	4616.2	4623.1	4616.2
10°	5061.8	5013.0	4950.4	4845.9	4755.4	4671.9	4567.4	4497.8	4504.8	4504.8	4490.8
12.5°	5208.0	5138.4	5027.0	4873.8	4734.5	4602.2	4476.9	4456.0	4449.1	4463.0	4421.2
15°	5319.4	5256.7	5075.7	4901.6	4685.8	4553.5	4421.2	4372.5	4379.4	4365.5	4330.7
17.5°	5458.6	5361.2	5138.4	4880.7	4630.1	4504.8	4351.6	4247.2	4191.5	4198.4	4191.5
20°	5590.9	5451.7	5187.1	4880.7	4616.2	4393.4	4198.4	4059.2	3940.8	3919.9	3913.0
22.5°	5688.4	5549.2	5242.8	4887.7	4532.6	4268.0	3982.6	3801.6	3627.5	3599.6	3592.7
25°	5827.7	5646.6	5305.5	4839.0	4421.2	4059.2	3704.1	3502.2	3349.0	3321.1	3321.1
27.5°	5946.0	5751.1	5389.0	4790.2	4240.2	3773.7	3439.5	3237.6	3140.1	3091.4	3091.4
30°	6071.3	5855.5	5458.6	4644.0	3996.5	3488.2	3230.6	3098.3	2986.9	2938.2	2917.3
32.5°	6210.6	6029.6	5472.6	4497.8	3752.8	3300.2	3084.4	2973.0	2854.6	2785.0	2778.1
35°	6384.7	6252.4	5423.8	4282.0	3509.1	3154.0	2945.2	2819.8	2701.5	2631.8	2645.8
37.5°	6663.2	6510.0	5277.6	3975.6	3307.2	3063.5	2833.8	2652.7	2513.5	2402.1	2409.0
40°	7074.0	6823.3	5061.8	3606.6	3161.0	2959.1	2701.5	2492.6	2290.7	2123.6	2123.6
42.5°	7540.4	7101.8	4797.2	3265.4	3049.6	2826.8	2562.2	2297.6	2012.2	1838.1	1831.2
45°	8062.6	7345.5	4490.8	2986.9	2868.6	2666.7	2381.2	2005.2	1817.2	1726.7	1719.8
47.5°	8758.9	7610.1	4128.8	2743.2	2659.7	2506.5	2109.7	1838.1	1726.7	1657.1	1650.1
50°	9413.4	7895.5	3829.4	2506.5	2436.9	2318.5	1921.7	1768.5	1678.0	1622.3	1608.3
52.5°	10172.3	8188.0	3495.2	2276.8	2186.2	2026.1	1879.9	1733.7	1650.1	1608.3	1594.4
55°	10924.2	8598.8	3126.2	2067.9	1963.4	1893.8	1838.1	1712.8	1629.2	1601.4	1580.5
57.5°	11780.6	8995.6	2673.6	1845.1	1803.3	1796.3	1831.2	1705.8	1636.2	1587.5	1559.6
60°	12226.2	9169.7	2200.2	1643.2	1650.1	1691.9	1803.3	1705.8	1594.4	1510.9	1476.1
62.5°	12073.1	8814.6	1740.6	1441.2	1503.9	1580.5	1754.6	1643.2	1503.9	1441.2	1399.5
65°	11460.4	8208.8	1357.7	1267.2	1371.6	1441.2	1636.2	1552.6	1413.4	1350.7	1343.8
67.5°	*10576.1*	*7157.5*	*1100.1*	*1114.0*	*1218.4*	*1309.0*	*1531.8*	*1496.9*	*1336.8*	*1295.0*	*1295.0*
70°	8891.2	5751.1	905.1	974.8	1065.3	1162.7	1455.2	1406.4	1239.3	1218.4	1218.4
72.5°	6948.6	4059.2	772.8	856.4	884.2	1023.5	1350.7	1302.0	1204.5	1253.3	1260.2
75°	4901.6	2471.7	661.4	724.1	752.0	842.5	1253.3	1274.1	1183.6	1343.8	1371.6
77.5°	2228.0	1086.2	515.2	570.9	605.7	717.1	1079.2	1183.6	1023.5	1023.5	967.8
80°	779.8	459.5	410.8	410.8	438.6	557.0	898.2	974.8	821.6	724.1	696.3
82.5°	285.5	250.7	306.4	306.4	278.5	341.2	598.8	647.5	591.8	515.2	508.3
85°	111.4	118.4	188.0	188.0	139.3	167.1	334.2	348.1	334.2	292.4	292.4
87.5°	48.7	48.7	55.7	55.7	48.7	41.8	62.7	62.7	41.8	27.9	13.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ

Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-5
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-735-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369
CIE u':	0.2386
CIE v':	0.5156
Duv:	0.0013
CIE x:	0.4143
CIE y:	0.3980
CIE z:	0.1877
Peak Wavelength (nm):	590
Dominant Wavelength (nm):	580
Purity:	43.80166
Rf:	71.4
Rg:	96

CRI (Ra):	70.1
R1:	66.6
R2:	77.6
R3:	88.5
R4:	69.5
R5:	66.4
R6:	69.6
R7:	77.5
R8:	44.9
R9:	-40.2
R10:	49.1
R11:	66.3
R12:	45.7
R13:	68.0
R14:	93.4
R15:	57.6



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3369K
CIE x = 0.4143
CIE y = 0.3980
Duv = 0.0013

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.36**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-5

TM-30-18


Summary


R_f = 71.4
R_g = 96
CIE R_a = 70.1
R_9 = -40.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	





REPORT NUMBER: SP1-2407-184-5

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-5

TM-30-18

Measure Comparisons





(END OF REPORT)