Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360663

Luminaire Tested: **GSS-SB1A-740-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360663
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB1A-740-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 1SQUARE 31W 70CRI 4000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(26) 4000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	4257.2 lumens
Efficiency:	N/A
Efficacy:	137.3 lumens/watt
Luminous Opening:	Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B2 - U0 - G2


Input Watts (W):	31
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.4%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360663
CATALOG NUMBER: GSS-SB1A-740-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 2.1 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360663
CATALOG NUMBER: GSS-SB1A-740-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360663
CATALOG NUMBER: GSS-SB1A-740-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2128.6	0.0	2128.6
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2128.6	0.0	2128.6
	% Fixture	50.0	0.0	50.0
Total	Lumens	4257.2	0.0	4257.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	1.9
10°-20°	247.4	5.8
20°-30°	413.6	9.7
30°-40°	570.4	13.4
40°-50°	699.2	16.4
50°-60°	819.3	19.2
60°-70°	909.9	21.4
70°-80°	494.8	11.6
80°-90°	21.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4257.2	100.0
0°-180°	4257.2	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360663
CATALOG NUMBER: GSS-SB1A-740-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	371.1	8.7			
FM	(30°-60°)	1044.4	24.5			
FH	(60°-80°)	702.3	16.5			G1/1800
FVH	(80°-90°)	10.7	0.3			G1/100
BL	(0°-30°)	371.1	8.7	B1/500		
BM	(30°-60°)	1044.4	24.5	B2/2500		
BH	(60°-80°)	702.3	16.5	B2/1000		G2/1000
BVH	(80°-90°)	10.7	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360663
CATALOG NUMBER: GSS-SB1A-740-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	838.8	838.8	838.8	838.8	838.8	838.8	838.8	838.8	838.8	838.8	838.8
2.5°	839.7	839.7	836.9	840.6	838.8	839.7	840.6	839.7	838.8	839.7	840.6
5°	844.4	842.5	844.4	846.2	843.4	845.3	844.4	839.7	842.5	842.5	842.5
7.5°	852.7	854.6	852.7	857.4	854.6	860.2	854.6	850.9	849.9	849.0	849.0
10°	856.5	856.5	855.5	863.9	865.8	871.4	867.7	862.1	859.3	855.5	851.8
12.5°	846.2	848.1	852.7	868.6	876.0	887.2	884.4	873.2	864.9	862.1	856.5
15°	835.0	836.9	846.2	865.8	883.5	900.3	899.3	885.4	875.1	867.7	859.3
17.5°	817.3	820.1	833.2	863.0	894.7	913.3	918.9	904.9	893.7	881.6	870.4
20°	787.5	787.5	810.8	849.0	892.8	934.8	949.7	938.5	925.4	905.9	891.0
22.5°	754.0	755.8	779.1	829.4	891.9	953.4	982.3	970.2	957.1	935.7	913.3
25°	720.4	720.4	746.5	803.3	879.8	966.4	1020.5	1014.0	987.9	968.3	939.4
27.5°	689.6	689.6	717.6	777.3	859.3	970.2	1058.7	1058.7	1029.8	1000.9	969.2
30°	653.3	662.6	694.3	756.8	840.6	963.6	1086.7	1104.4	1078.3	1041.0	994.4
32.5°	622.5	629.1	661.7	727.9	813.6	956.2	1118.4	1162.2	1135.1	1083.9	1031.7
35°	586.2	585.3	622.5	687.8	775.4	939.4	1143.5	1231.1	1205.0	1150.0	1079.2
37.5°	538.7	538.7	576.9	640.3	739.0	910.5	1164.0	1307.5	1288.0	1225.5	1150.0
40°	487.4	493.0	526.6	590.9	695.2	876.0	1164.0	1370.0	1380.2	1315.9	1237.6
42.5°	450.1	452.0	482.8	543.3	646.8	831.3	1149.1	1424.0	1454.8	1400.7	1299.2
45°	411.0	415.7	441.7	497.7	596.5	778.2	1123.0	1484.6	1534.0	1496.7	1363.5
47.5°	363.5	368.1	397.9	454.8	548.9	720.4	1079.2	1548.0	1651.4	1624.4	1478.1
50°	308.5	312.2	340.2	400.7	495.8	654.2	1024.2	1595.5	1768.9	1795.9	1651.4
52.5°	241.4	244.2	274.0	332.7	432.4	590.9	946.9	1624.4	1887.2	1982.3	1883.5
55°	173.3	178.0	204.1	252.6	348.6	506.1	854.6	1639.3	2016.8	2203.2	2171.5
57.5°	124.9	126.7	144.5	181.7	259.1	406.3	736.2	1614.2	2133.3	2466.9	2533.1
60°	103.4	103.4	106.2	124.0	177.1	287.0	594.6	1521.0	2233.0	2733.4	2937.5
62.5°	95.1	95.1	96.9	99.7	116.5	186.4	425.0	1331.8	2244.2	2989.7	3381.1
65°	86.7	86.7	88.5	90.4	94.1	121.2	256.3	974.8	2025.1	2992.5	3619.7
67.5°	79.2	79.2	80.1	81.1	82.9	88.5	140.7	590.9	1620.7	2913.3	3711.1
70°	71.8	71.8	71.8	70.8	73.6	74.6	93.2	300.1	1083.9	2630.9	3667.3
72.5°	*63.4*	*63.4*	*62.4*	*60.6*	*61.5*	*61.5*	*69.0*	*147.2*	*562.9*	*2091.3*	*3311.3*
75°	54.1	55.0	51.3	49.4	48.5	49.4	55.0	83.9	251.6	1268.4	2474.4
77.5°	45.7	47.5	41.9	38.2	37.3	37.3	42.9	52.2	108.1	460.4	1109.0
80°	34.5	35.4	30.8	27.0	27.0	26.1	31.7	38.2	51.3	137.0	248.8
82.5°	19.6	19.6	17.7	15.8	14.9	15.8	21.4	26.1	31.7	48.5	68.0
85°	4.7	4.7	5.6	6.5	6.5	8.4	12.1	14.0	16.8	19.6	26.1
87.5°	0.9	0.9	0.9	1.9	2.8	2.8	4.7	6.5	8.4	10.3	11.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360663
CATALOG NUMBER: GSS-SB1A-740-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	838.8	838.8	*838.8*
2.5°	840.6	841.6	*840.6*
5°	846.2	844.4	*841.6*
7.5°	847.2	848.1	*849.0*
10°	850.9	854.6	*849.0*
12.5°	854.6	851.8	*849.9*
15°	857.4	856.5	*850.9*
17.5°	867.7	863.9	*863.0*
20°	883.5	882.6	*879.8*
22.5°	902.1	900.3	*899.3*
25°	929.2	922.6	*918.9*
27.5°	951.5	945.9	*944.1*
30°	973.9	962.7	*962.7*
32.5°	993.5	990.7	*988.8*
35°	1040.1	1026.1	*1028.0*
37.5°	1096.9	1082.9	*1070.8*
40°	1177.1	1158.4	*1151.0*
42.5°	1228.3	1209.7	*1211.5*
45°	1257.2	1224.6	*1216.2*
47.5°	1335.5	1294.5	*1283.3*
50°	1462.2	1411.9	*1397.9*
52.5°	1667.3	1586.2	*1567.6*
55°	1924.5	1824.8	*1806.1*
57.5°	2276.8	2144.4	*2104.4*
60°	2705.5	2541.5	*2480.9*
62.5°	3220.9	3018.6	*2960.8*
65°	3608.5	3439.9	*3350.4*
67.5°	3918.9	3780.0	*3737.2*
70°	4103.4	4109.9	*4121.1*
72.5°	*3890.0*	*4068.9*	*4154.7*
75°	2850.9	2989.7	*3123.0*
77.5°	1101.6	993.5	*961.8*
80°	178.0	166.8	*172.4*
82.5°	80.1	84.8	*89.5*
85°	52.2	60.6	*64.3*
87.5°	12.1	12.1	*12.1*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ

Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-740-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 4000K CCT 26 LEDS

Spectral Parameters

CCT (K):	3949
CIE u':	0.2248
CIE v':	0.5053
Duv:	0.0022
CIE x:	0.3844
CIE y:	0.3840
CIE z:	0.2316
Peak Wavelength (nm):	440
Dominant Wavelength (nm):	578
Purity:	30.60026
Rf:	71.8
Rg:	96.5

CRI (Ra):	70.7
R1:	68.0
R2:	76.0
R3:	84.3
R4:	72.0
R5:	68.6
R6:	68.3
R7:	77.9
R8:	50.3
R9:	-36.7
R10:	45.1
R11:	70.7
R12:	47.1
R13:	68.5
R14:	91.1
R15:	58.7



Test Conditions


Stabilization Time:	34M
Operation Time:	1H 34M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3949K
CIE x = 0.3844
CIE y = 0.3840
Duv = 0.0022

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.78**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-1

TM-30-18


Summary


R_f = 71.8
R_g = 96.5
CIE R_a = 70.7
R_9 = -36.7


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 56	CES51 = 86	CES76 = 48
CES02 = 61	CES27 = 79	CES52 = 88	CES77 = 71
CES03 = 30	CES28 = 80	CES53 = 73	CES78 = 52
CES04 = 70	CES29 = 49	CES54 = 79	CES79 = 79
CES05 = 47	CES30 = 53	CES55 = 77	CES80 = 77
CES06 = 50	CES31 = 55	CES56 = 67	CES81 = 75
CES07 = 40	CES32 = 53	CES57 = 64	CES82 = 90
CES08 = 39	CES33 = 59	CES58 = 67	CES83 = 84
CES09 = 29	CES34 = 67	CES59 = 87	CES84 = 89
CES10 = 74	CES35 = 82	CES60 = 91	CES85 = 86
CES11 = 57	CES36 = 86	CES61 = 87	CES86 = 71
CES12 = 63	CES37 = 76	CES62 = 76	CES87 = 78
CES13 = 42	CES38 = 62	CES63 = 73	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 71	CES89 = 72
CES15 = 71	CES40 = 84	CES65 = 64	CES90 = 72
CES16 = 46	CES41 = 81	CES66 = 67	CES91 = 97
CES17 = 49	CES42 = 76	CES67 = 65	CES92 = 66
CES18 = 56	CES43 = 71	CES68 = 72	CES93 = 81
CES19 = 72	CES44 = 98	CES69 = 82	CES94 = 55
CES20 = 65	CES45 = 80	CES70 = 61	CES95 = 73
CES21 = 86	CES46 = 76	CES71 = 59	CES96 = 78
CES22 = 78	CES47 = 71	CES72 = 86	CES97 = 83
CES23 = 92	CES48 = 61	CES73 = 52	CES98 = 72
CES24 = 91	CES49 = 76	CES74 = 93	CES99 = 60
CES25 = 72	CES50 = 84	CES75 = 56	





REPORT NUMBER: SP1-2407-184-1

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-1

TM-30-18

Measure Comparisons





(END OF REPORT)