Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360675

Luminaire Tested: **GSS-SB4A-740-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360675
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4A-740-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 114W 70CRI 4000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(104) 4000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	18202.2 lumens
Efficiency:	N/A
Efficacy:	159.7 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	114
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.2%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360675
CATALOG NUMBER: GSS-SB4A-740-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 9 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360675
CATALOG NUMBER: GSS-SB4A-740-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360675
CATALOG NUMBER: GSS-SB4A-740-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	9101.1	0.0	9101.1
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	9101.1	0.0	9101.1
	% Fixture	50.0	0.0	50.0
Total	Lumens	18202.2	0.0	18202.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.1	1.9
10°-20°	1058.0	5.8
20°-30°	1768.3	9.7
30°-40°	2438.6	13.4
40°-50°	2989.4	16.4
50°-60°	3503.2	19.2
60°-70°	3890.3	21.4
70°-80°	2115.5	11.6
80°-90°	91.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	18202.2	100.0
0°-180°	18202.2	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360675
CATALOG NUMBER: GSS-SB4A-740-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1586.7	8.7			
FM	(30°-60°)	4465.7	24.5			
FH	(60°-80°)	3002.9	16.5			G2/5000
FVH	(80°-90°)	45.8	0.3			G1/100
BL	(0°-30°)	1586.7	8.7	B3/2500		
BM	(30°-60°)	4465.7	24.5	B3/5000		
BH	(60°-80°)	3002.9	16.5	B4/5000		G4/5000
BVH	(80°-90°)	45.8	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360675
CATALOG NUMBER: GSS-SB4A-740-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3586.3	3586.3	3586.3	3586.3	3586.3	3586.3	3586.3	3586.3	3586.3	3586.3	3586.3
2.5°	3590.3	3590.3	3578.3	3594.3	3586.3	3590.3	3594.3	3590.3	3586.3	3590.3	3594.3
5°	3610.2	3602.2	3610.2	3618.2	3606.2	3614.2	3610.2	3590.3	3602.2	3602.2	3602.2
7.5°	3646.1	3654.0	3646.1	3666.0	3654.0	3677.9	3654.0	3638.1	3634.1	3630.1	3630.1
10°	3662.0	3662.0	3658.0	3693.9	3701.8	3725.8	3709.8	3685.9	3674.0	3658.0	3642.1
12.5°	3618.2	3626.1	3646.1	3713.8	3745.7	3793.5	3781.5	3733.7	3697.9	3685.9	3662.0
15°	3570.3	3578.3	3618.2	3701.8	3777.6	3849.3	3845.3	3785.5	3741.7	3709.8	3674.0
17.5°	3494.6	3506.6	3562.4	3689.9	3825.4	3905.1	3929.0	3869.2	3821.4	3769.6	3721.8
20°	3367.1	3367.1	3466.7	3630.1	3817.4	3996.7	4060.5	4012.7	3956.9	3873.2	3809.4
22.5°	3223.7	3231.6	3331.3	3546.4	3813.4	4076.4	4199.9	4148.1	4092.4	4000.7	3905.1
25°	3080.2	3080.2	3191.8	3434.9	3761.6	4132.2	4363.3	4335.4	4223.8	4140.2	4016.6
27.5°	2948.7	2948.7	3068.3	3323.3	3674.0	4148.1	4526.7	4526.7	4403.2	4279.6	4144.2
30°	2793.3	2833.2	2968.6	3235.6	3594.3	4120.2	4646.2	4721.9	4610.4	4451.0	4251.7
32.5°	2661.8	2689.7	2829.2	3112.1	3478.7	4088.4	4781.7	4969.0	4853.4	4634.3	4411.1
35°	2506.4	2502.4	2661.8	2940.8	3315.3	4016.6	4889.3	5263.9	5152.3	4917.2	4614.4
37.5°	2303.2	2303.2	2466.6	2737.5	3159.9	3893.1	4977.0	5590.6	5506.9	5240.0	4917.2
40°	2084.0	2107.9	2251.4	2526.3	2972.6	3745.7	4977.0	5857.6	5901.4	5626.5	5291.8
42.5°	1924.6	1932.6	2064.1	2323.1	2765.4	3554.4	4913.2	6088.7	6220.2	5989.1	5554.8
45°	1757.3	1777.2	1888.8	2127.9	2550.2	3327.3	4801.6	6347.7	6558.9	6399.5	5829.7
47.5°	1554.1	1574.0	1701.5	1944.6	2347.0	3080.2	4614.4	6618.7	7061.0	6945.4	6319.8
50°	1319.0	1334.9	1454.4	1713.4	2119.9	2797.3	4379.3	6821.9	7563.1	7678.6	7061.0
52.5°	1032.1	1044.0	1171.5	1422.6	1848.9	2526.3	4048.5	6945.4	8069.1	8475.6	8053.2
55°	741.2	761.1	872.7	1079.9	1490.3	2163.7	3654.0	7009.2	8623.0	9420.0	9284.5
57.5°	534.0	541.9	617.6	777.0	1107.8	1737.4	3148.0	6901.6	9121.1	10547.7	10830.6
60°	442.3	442.3	454.3	530.0	757.1	1227.3	2542.3	6503.1	9547.5	11687.3	12560.0
62.5°	406.4	406.4	414.4	426.4	498.1	797.0	1817.1	5694.2	9595.3	12783.1	14456.7
65°	370.6	370.6	378.6	386.5	402.5	518.0	1095.8	4168.1	8658.9	12795.1	15476.8
67.5°	338.7	338.7	342.7	346.7	354.6	378.6	601.7	2526.3	6929.5	12456.4	15867.3
70°	306.8	306.8	306.8	302.8	314.8	318.8	398.5	1283.1	4634.3	11249.0	15680.0
72.5°	*271.0*	*271.0*	*267.0*	*259.0*	*263.0*	*263.0*	*294.9*	*629.6*	*2406.8*	*8941.8*	*14157.9*
75°	231.1	235.1	219.2	211.2	207.2	211.2	235.1	358.6	1075.9	5423.3	10579.5
77.5°	195.3	203.2	179.3	163.4	159.4	159.4	183.3	223.1	462.2	1968.5	4741.9
80°	147.4	151.4	131.5	115.6	115.6	111.6	135.5	163.4	219.2	585.8	1063.9
82.5°	83.7	83.7	75.7	67.7	63.8	67.7	91.6	111.6	135.5	207.2	290.9
85°	19.9	19.9	23.9	27.9	27.9	35.9	51.8	59.8	71.7	83.7	111.6
87.5°	4.0	4.0	4.0	8.0	12.0	12.0	19.9	27.9	35.9	43.8	47.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360675
CATALOG NUMBER: GSS-SB4A-740-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3586.3	3586.3	*3586.3*
2.5°	3594.3	3598.2	*3594.3*
5°	3618.2	3610.2	*3598.2*
7.5°	3622.2	3626.1	*3630.1*
10°	3638.1	3654.0	*3630.1*
12.5°	3654.0	3642.1	*3634.1*
15°	3666.0	3662.0	*3638.1*
17.5°	3709.8	3693.9	*3689.9*
20°	3777.6	3773.6	*3761.6*
22.5°	3857.3	3849.3	*3845.3*
25°	3972.8	3944.9	*3929.0*
27.5°	4068.4	4044.5	*4036.6*
30°	4164.1	4116.3	*4116.3*
32.5°	4247.8	4235.8	*4227.8*
35°	4447.0	4387.2	*4395.2*
37.5°	4690.1	4630.3	*4578.5*
40°	5032.8	4953.1	*4921.2*
42.5°	5251.9	5172.2	*5180.2*
45°	5375.4	5236.0	*5200.1*
47.5°	5710.2	5534.8	*5487.0*
50°	6252.1	6036.9	*5977.1*
52.5°	7128.7	6782.1	*6702.4*
55°	8228.5	7802.2	*7722.5*
57.5°	9734.8	9168.9	*8997.6*
60°	11567.8	10866.5	*10607.4*
62.5°	13771.3	12906.6	*12659.6*
65°	15429.0	14707.8	*14325.2*
67.5°	16755.9	16162.2	*15978.9*
70°	17544.9	17572.8	*17620.6*
72.5°	*16632.4*	*17397.5*	*17764.1*
75°	12189.4	12783.1	*13352.9*
77.5°	4710.0	4247.8	*4112.3*
80°	761.1	713.3	*737.2*
82.5°	342.7	362.6	*382.5*
85°	223.1	259.0	*274.9*
87.5°	51.8	51.8	*51.8*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ

Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-740-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 4000K CCT 26 LEDS

Spectral Parameters

CCT (K):	3949
CIE u':	0.2248
CIE v':	0.5053
Duv:	0.0022
CIE x:	0.3844
CIE y:	0.3840
CIE z:	0.2316
Peak Wavelength (nm):	440
Dominant Wavelength (nm):	578
Purity:	30.60026
Rf:	71.8
Rg:	96.5

CRI (Ra):	70.7
R1:	68.0
R2:	76.0
R3:	84.3
R4:	72.0
R5:	68.6
R6:	68.3
R7:	77.9
R8:	50.3
R9:	-36.7
R10:	45.1
R11:	70.7
R12:	47.1
R13:	68.5
R14:	91.1
R15:	58.7



Test Conditions


Stabilization Time:	34M
Operation Time:	1H 34M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3949K
CIE x = 0.3844
CIE y = 0.3840
Duv = 0.0022

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.78**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-1

TM-30-18


Summary


R_f = 71.8
R_g = 96.5
CIE R_a = 70.7
R_9 = -36.7


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 56	CES51 = 86	CES76 = 48
CES02 = 61	CES27 = 79	CES52 = 88	CES77 = 71
CES03 = 30	CES28 = 80	CES53 = 73	CES78 = 52
CES04 = 70	CES29 = 49	CES54 = 79	CES79 = 79
CES05 = 47	CES30 = 53	CES55 = 77	CES80 = 77
CES06 = 50	CES31 = 55	CES56 = 67	CES81 = 75
CES07 = 40	CES32 = 53	CES57 = 64	CES82 = 90
CES08 = 39	CES33 = 59	CES58 = 67	CES83 = 84
CES09 = 29	CES34 = 67	CES59 = 87	CES84 = 89
CES10 = 74	CES35 = 82	CES60 = 91	CES85 = 86
CES11 = 57	CES36 = 86	CES61 = 87	CES86 = 71
CES12 = 63	CES37 = 76	CES62 = 76	CES87 = 78
CES13 = 42	CES38 = 62	CES63 = 73	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 71	CES89 = 72
CES15 = 71	CES40 = 84	CES65 = 64	CES90 = 72
CES16 = 46	CES41 = 81	CES66 = 67	CES91 = 97
CES17 = 49	CES42 = 76	CES67 = 65	CES92 = 66
CES18 = 56	CES43 = 71	CES68 = 72	CES93 = 81
CES19 = 72	CES44 = 98	CES69 = 82	CES94 = 55
CES20 = 65	CES45 = 80	CES70 = 61	CES95 = 73
CES21 = 86	CES46 = 76	CES71 = 59	CES96 = 78
CES22 = 78	CES47 = 71	CES72 = 86	CES97 = 83
CES23 = 92	CES48 = 61	CES73 = 52	CES98 = 72
CES24 = 91	CES49 = 76	CES74 = 93	CES99 = 60
CES25 = 72	CES50 = 84	CES75 = 56	





REPORT NUMBER: SP1-2407-184-1

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-1

TM-30-18

Measure Comparisons





(END OF REPORT)