Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360672

Luminaire Tested: **GSS-SB3B-740-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360672
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB3B-740-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 3SQUARE 109W 70CRI 4000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(78) 4000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	16495.6 lumens
Efficiency:	N/A
Efficacy:	151.3 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	109
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360672
CATALOG NUMBER: GSS-SB3B-740-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 8.1 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360672
CATALOG NUMBER: GSS-SB3B-740-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360672
CATALOG NUMBER: GSS-SB3B-740-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	8247.8	0.0	8247.8
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	8247.8	0.0	8247.8
	% Fixture	50.0	0.0	50.0
Total	Lumens	16495.6	0.0	16495.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	314.6	1.9
10°-20°	958.8	5.8
20°-30°	1602.5	9.7
30°-40°	2210.0	13.4
40°-50°	2709.2	16.4
50°-60°	3174.8	19.2
60°-70°	3525.5	21.4
70°-80°	1917.2	11.6
80°-90°	83.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	16495.6	100.0
0°-180°	16495.6	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360672
CATALOG NUMBER: GSS-SB3B-740-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1437.9	8.7			
FM	(30°-60°)	4046.9	24.5			
FH	(60°-80°)	2721.3	16.5			G2/5000
FVH	(80°-90°)	41.5	0.3			G1/100
BL	(0°-30°)	1437.9	8.7	B3/2500		
BM	(30°-60°)	4046.9	24.5	B3/5000		
BH	(60°-80°)	2721.3	16.5	B4/5000		G4/5000
BVH	(80°-90°)	41.5	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360672
CATALOG NUMBER: GSS-SB3B-740-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3250.0	3250.0	3250.0	3250.0	3250.0	3250.0	3250.0	3250.0	3250.0	3250.0	3250.0
2.5°	3253.6	3253.6	3242.8	3257.3	3250.0	3253.6	3257.3	3253.6	3250.0	3253.6	3257.3
5°	3271.7	3264.5	3271.7	3278.9	3268.1	3275.3	3271.7	3253.6	3264.5	3264.5	3264.5
7.5°	3304.2	3311.4	3304.2	3322.3	3311.4	3333.1	3311.4	3297.0	3293.4	3289.8	3289.8
10°	3318.6	3318.6	3315.0	3347.5	3354.8	3376.4	3362.0	3340.3	3329.5	3315.0	3300.6
12.5°	3278.9	3286.1	3304.2	3365.6	3394.5	3437.8	3427.0	3383.6	3351.1	3340.3	3318.6
15°	3235.6	3242.8	3278.9	3354.8	3423.4	3488.4	3484.8	3430.6	3390.9	3362.0	3329.5
17.5°	3167.0	3177.8	3228.4	3343.9	3466.7	3538.9	3560.6	3506.4	3463.1	3416.1	3372.8
20°	3051.4	3051.4	3141.7	3289.8	3459.5	3622.0	3679.8	3636.4	3585.9	3510.0	3452.3
22.5°	2921.4	2928.6	3018.9	3213.9	3455.9	3694.2	3806.2	3759.2	3708.7	3625.6	3538.9
25°	2791.4	2791.4	2892.5	3112.8	3408.9	3744.8	3954.2	3928.9	3827.8	3752.0	3640.0
27.5°	2672.3	2672.3	2780.6	3011.7	3329.5	3759.2	4102.3	4102.3	3990.3	3878.4	3755.6
30°	2531.4	2567.5	2690.3	2932.3	3257.3	3733.9	4210.6	4279.2	4178.1	4033.7	3853.1
32.5°	2412.2	2437.5	2563.9	2820.3	3152.5	3705.0	4333.4	4503.1	4398.4	4199.8	3997.5
35°	2271.4	2267.8	2412.2	2665.0	3004.5	3640.0	4430.9	4770.3	4669.2	4456.2	4181.7
37.5°	2087.2	2087.2	2235.3	2480.9	2863.6	3528.1	4510.3	5066.4	4990.6	4748.7	4456.2
40°	1888.6	1910.3	2040.3	2289.5	2693.9	3394.5	4510.3	5308.4	5348.1	5098.9	4795.6
42.5°	1744.2	1751.4	1870.6	2105.3	2506.1	3221.1	4452.5	5517.8	5637.0	5427.6	5033.9
45°	1592.5	1610.6	1711.7	1928.4	2311.1	3015.3	4351.4	5752.6	5944.0	5799.5	5283.1
47.5°	1408.3	1426.4	1542.0	1762.2	2127.0	2791.4	4181.7	5998.1	6399.0	6294.2	5727.3
50°	1195.3	1209.7	1318.1	1552.8	1921.1	2535.0	3968.7	6182.3	6854.0	6958.7	6399.0
52.5°	935.3	946.1	1061.7	1289.2	1675.6	2289.5	3668.9	6294.2	7312.6	7680.9	7298.1
55°	671.7	689.7	790.8	978.6	1350.6	1960.9	3311.4	6352.0	7814.5	8536.8	8414.0
57.5°	483.9	491.1	559.7	704.2	1003.9	1574.5	2852.8	6254.5	8265.9	9558.7	9815.1
60°	400.8	400.8	411.7	480.3	686.1	1112.2	2303.9	5893.4	8652.3	10591.5	11382.3
62.5°	368.3	368.3	375.6	386.4	451.4	722.2	1646.7	5160.3	8695.7	11584.6	13101.3
65°	335.8	335.8	343.1	350.3	364.7	469.4	993.1	3777.3	7847.0	11595.4	14025.7
67.5°	306.9	306.9	310.6	314.2	321.4	343.1	545.3	2289.5	6279.8	11288.5	14379.6
70°	278.1	278.1	278.1	274.4	285.3	288.9	361.1	1162.8	4199.8	10194.3	14209.9
72.5°	*245.6*	*245.6*	*241.9*	*234.7*	*238.3*	*238.3*	*267.2*	*570.6*	*2181.1*	*8103.4*	*12830.4*
75°	209.4	213.1	198.6	191.4	187.8	191.4	213.1	325.0	975.0	4914.8	9587.6
77.5°	176.9	184.2	162.5	148.1	144.4	144.4	166.1	202.2	418.9	1783.9	4297.3
80°	133.6	137.2	119.2	104.7	104.7	101.1	122.8	148.1	198.6	530.8	964.2
82.5°	75.8	75.8	68.6	61.4	57.8	61.4	83.1	101.1	122.8	187.8	263.6
85°	18.1	18.1	21.7	25.3	25.3	32.5	46.9	54.2	65.0	75.8	101.1
87.5°	3.6	3.6	3.6	7.2	10.8	10.8	18.1	25.3	32.5	39.7	43.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360672
CATALOG NUMBER: GSS-SB3B-740-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3250.0	3250.0	*3250.0*
2.5°	3257.3	3260.9	*3257.3*
5°	3278.9	3271.7	*3260.9*
7.5°	3282.5	3286.1	*3289.8*
10°	3297.0	3311.4	*3289.8*
12.5°	3311.4	3300.6	*3293.4*
15°	3322.3	3318.6	*3297.0*
17.5°	3362.0	3347.5	*3343.9*
20°	3423.4	3419.8	*3408.9*
22.5°	3495.6	3488.4	*3484.8*
25°	3600.3	3575.0	*3560.6*
27.5°	3687.0	3665.3	*3658.1*
30°	3773.7	3730.3	*3730.3*
32.5°	3849.5	3838.7	*3831.4*
35°	4030.0	3975.9	*3983.1*
37.5°	4250.3	4196.2	*4149.2*
40°	4560.9	4488.7	*4459.8*
42.5°	4759.5	4687.3	*4694.5*
45°	4871.4	4745.1	*4712.6*
47.5°	5174.8	5015.9	*4972.6*
50°	5665.9	5470.9	*5416.7*
52.5°	6460.3	6146.2	*6074.0*
55°	7457.0	7070.6	*6998.4*
57.5°	8822.0	8309.3	*8154.0*
60°	10483.2	9847.6	*9612.9*
62.5°	12480.1	11696.5	*11472.6*
65°	13982.4	13328.8	*12982.1*
67.5°	15184.9	14646.8	*14480.7*
70°	15899.9	15925.2	*15968.5*
72.5°	*15072.9*	*15766.3*	*16098.5*
75°	11046.5	11584.6	*12101.0*
77.5°	4268.4	3849.5	*3726.7*
80°	689.7	646.4	*668.1*
82.5°	310.6	328.6	*346.7*
85°	202.2	234.7	*249.2*
87.5°	46.9	46.9	*46.9*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ

Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-740-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 4000K CCT 26 LEDS

Spectral Parameters

CCT (K):	3949
CIE u':	0.2248
CIE v':	0.5053
Duv:	0.0022
CIE x:	0.3844
CIE y:	0.3840
CIE z:	0.2316
Peak Wavelength (nm):	440
Dominant Wavelength (nm):	578
Purity:	30.60026
Rf:	71.8
Rg:	96.5

CRI (Ra):	70.7
R1:	68.0
R2:	76.0
R3:	84.3
R4:	72.0
R5:	68.6
R6:	68.3
R7:	77.9
R8:	50.3
R9:	-36.7
R10:	45.1
R11:	70.7
R12:	47.1
R13:	68.5
R14:	91.1
R15:	58.7



Test Conditions


Stabilization Time:	34M
Operation Time:	1H 34M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3949K
CIE x = 0.3844
CIE y = 0.3840
Duv = 0.0022

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.78**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-1

TM-30-18


Summary


R_f = 71.8
R_g = 96.5
CIE R_a = 70.7
R_9 = -36.7


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 56	CES51 = 86	CES76 = 48
CES02 = 61	CES27 = 79	CES52 = 88	CES77 = 71
CES03 = 30	CES28 = 80	CES53 = 73	CES78 = 52
CES04 = 70	CES29 = 49	CES54 = 79	CES79 = 79
CES05 = 47	CES30 = 53	CES55 = 77	CES80 = 77
CES06 = 50	CES31 = 55	CES56 = 67	CES81 = 75
CES07 = 40	CES32 = 53	CES57 = 64	CES82 = 90
CES08 = 39	CES33 = 59	CES58 = 67	CES83 = 84
CES09 = 29	CES34 = 67	CES59 = 87	CES84 = 89
CES10 = 74	CES35 = 82	CES60 = 91	CES85 = 86
CES11 = 57	CES36 = 86	CES61 = 87	CES86 = 71
CES12 = 63	CES37 = 76	CES62 = 76	CES87 = 78
CES13 = 42	CES38 = 62	CES63 = 73	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 71	CES89 = 72
CES15 = 71	CES40 = 84	CES65 = 64	CES90 = 72
CES16 = 46	CES41 = 81	CES66 = 67	CES91 = 97
CES17 = 49	CES42 = 76	CES67 = 65	CES92 = 66
CES18 = 56	CES43 = 71	CES68 = 72	CES93 = 81
CES19 = 72	CES44 = 98	CES69 = 82	CES94 = 55
CES20 = 65	CES45 = 80	CES70 = 61	CES95 = 73
CES21 = 86	CES46 = 76	CES71 = 59	CES96 = 78
CES22 = 78	CES47 = 71	CES72 = 86	CES97 = 83
CES23 = 92	CES48 = 61	CES73 = 52	CES98 = 72
CES24 = 91	CES49 = 76	CES74 = 93	CES99 = 60
CES25 = 72	CES50 = 84	CES75 = 56	





REPORT NUMBER: SP1-2407-184-1

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-1

TM-30-18

Measure Comparisons





(END OF REPORT)