Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360680

Luminaire Tested: **GSS-SB5B-740-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360680
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB5B-740-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 5SQUARE 184W 70CRI 4000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(130) 4000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	28649.3 lumens
Efficiency:	N/A
Efficacy:	155.7 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	184
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	11.1%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360680
CATALOG NUMBER: GSS-SB5B-740-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 14.1 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360680
CATALOG NUMBER: GSS-SB5B-740-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360680
CATALOG NUMBER: GSS-SB5B-740-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	14324.6	0.0	14324.6
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	14324.6	0.0	14324.6
	% Fixture	50.0	0.0	50.0
Total	Lumens	28649.3	0.0	28649.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	546.4	1.9
10°-20°	1665.2	5.8
20°-30°	2783.2	9.7
30°-40°	3838.3	13.4
40°-50°	4705.2	16.4
50°-60°	5513.9	19.2
60°-70°	6123.1	21.4
70°-80°	3329.7	11.6
80°-90°	144.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	28649.3	100.0
0°-180°	28649.3	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360680
CATALOG NUMBER: GSS-SB5B-740-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2497.4	8.7			
FM	(30°-60°)	7028.7	24.5			
FH	(60°-80°)	4726.4	16.5			G2/5000
FVH	(80°-90°)	72.1	0.3			G1/100
BL	(0°-30°)	2497.4	8.7	B3/2500		
BM	(30°-60°)	7028.7	24.5	B4/8500		
BH	(60°-80°)	4726.4	16.5	B4/5000		G4/5000
BVH	(80°-90°)	72.1	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360680
CATALOG NUMBER: GSS-SB5B-740-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	5644.6	5644.6	5644.6	5644.6	5644.6	5644.6	5644.6	5644.6	5644.6	5644.6	5644.6
2.5°	5650.9	5650.9	5632.1	5657.2	5644.6	5650.9	5657.2	5650.9	5644.6	5650.9	5657.2
5°	5682.3	5669.7	5682.3	5694.8	5676.0	5688.5	5682.3	5650.9	5669.7	5669.7	5669.7
7.5°	5738.7	5751.2	5738.7	5770.1	5751.2	5788.9	5751.2	5726.2	5719.9	5713.6	5713.6
10°	5763.8	5763.8	5757.5	5814.0	5826.5	5864.1	5839.0	5801.4	5782.6	5757.5	5732.4
12.5°	5694.8	5707.3	5738.7	5845.3	5895.5	5970.8	5951.9	5876.7	5820.2	5801.4	5763.8
15°	5619.5	5632.1	5694.8	5826.5	5945.7	6058.6	6052.3	5958.2	5889.2	5839.0	5782.6
17.5°	5500.4	5519.2	5607.0	5807.7	6020.9	6146.4	6184.0	6089.9	6014.7	5933.1	5857.9
20°	5299.7	5299.7	5456.5	5713.6	6008.4	6290.6	6391.0	6315.7	6227.9	6096.2	5995.8
22.5°	5073.9	5086.4	5243.2	5581.9	6002.1	6416.1	6610.5	6528.9	6441.1	6296.9	6146.4
25°	4848.1	4848.1	5023.7	5406.3	5920.6	6503.9	6867.6	6823.7	6648.1	6516.4	6322.0
27.5°	4641.1	4641.1	4829.3	5230.7	5782.6	6528.9	7124.8	7124.8	6930.3	6735.9	6522.7
30°	4396.5	4459.3	4672.5	5092.7	5657.2	6485.0	7312.9	7432.1	7256.5	7005.6	6692.0
32.5°	4189.6	4233.5	4453.0	4898.3	5475.3	6434.9	7526.2	7820.9	7639.1	7294.1	6942.9
35°	3945.0	3938.7	4189.6	4628.6	5218.1	6322.0	7695.5	8285.1	8109.4	7739.4	7262.7
37.5°	3625.1	3625.1	3882.2	4308.7	4973.5	6127.6	7833.5	8799.3	8667.6	8247.4	7739.4
40°	3280.2	3317.8	3543.6	3976.3	4678.8	5895.5	7833.5	9219.6	9288.5	8855.8	8329.0
42.5°	3029.3	3041.8	3248.8	3656.5	4352.6	5594.4	7733.1	9583.3	9790.3	9426.5	8742.9
45°	2765.9	2797.2	2972.8	3349.1	4014.0	5237.0	7557.5	9991.0	10323.4	10072.5	9175.6
47.5°	2446.0	2477.4	2678.1	3060.6	3694.1	4848.1	7262.7	10417.5	11113.6	10931.8	9947.1
50°	2076.0	2101.1	2289.2	2696.9	3336.6	4402.8	6892.7	10737.3	11903.9	12085.8	11113.6
52.5°	1624.4	1643.2	1843.9	2239.0	2910.1	3976.3	6372.2	10931.8	12700.4	13340.1	12675.3
55°	1166.6	1197.9	1373.5	1699.7	2345.7	3405.6	5751.2	11032.1	13572.2	14826.5	14613.3
57.5°	840.4	853.0	972.1	1223.0	1743.6	2734.5	4954.7	10862.8	14356.2	16601.5	17046.8
60°	696.2	696.2	715.0	834.1	1191.6	1931.7	4001.4	10235.6	15027.2	18395.2	19768.7
62.5°	639.7	639.7	652.3	671.1	784.0	1254.4	2859.9	8962.4	15102.5	20119.9	22754.1
65°	583.3	583.3	595.8	608.4	633.5	815.3	1724.7	6560.3	13628.6	20138.8	24359.7
67.5°	533.1	533.1	539.4	545.6	558.2	595.8	947.0	3976.3	10906.7	19605.7	24974.3
70°	482.9	482.9	482.9	476.7	495.5	501.7	627.2	2019.5	7294.1	17705.3	24679.6
72.5°	*426.5*	*426.5*	*420.2*	*407.7*	*413.9*	*413.9*	*464.1*	*990.9*	*3788.2*	*14073.9*	*22283.7*
75°	363.8	370.0	344.9	332.4	326.1	332.4	370.0	564.5	1693.4	8535.9	16651.6
77.5°	307.3	319.9	282.2	257.1	250.9	250.9	288.5	351.2	727.5	3098.3	7463.4
80°	232.1	238.3	207.0	181.9	181.9	175.6	213.2	257.1	344.9	922.0	1674.6
82.5°	131.7	131.7	119.2	106.6	100.3	106.6	144.3	175.6	213.2	326.1	457.8
85°	31.4	31.4	37.6	43.9	43.9	56.4	81.5	94.1	112.9	131.7	175.6
87.5°	6.3	6.3	6.3	12.5	18.8	18.8	31.4	43.9	56.4	69.0	75.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360680
CATALOG NUMBER: GSS-SB5B-740-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	5644.6	5644.6	*5644.6*
2.5°	5657.2	5663.4	*5657.2*
5°	5694.8	5682.3	*5663.4*
7.5°	5701.1	5707.3	*5713.6*
10°	5726.2	5751.2	*5713.6*
12.5°	5751.2	5732.4	*5719.9*
15°	5770.1	5763.8	*5726.2*
17.5°	5839.0	5814.0	*5807.7*
20°	5945.7	5939.4	*5920.6*
22.5°	6071.1	6058.6	*6052.3*
25°	6253.0	6209.1	*6184.0*
27.5°	6403.5	6365.9	*6353.3*
30°	6554.0	6478.8	*6478.8*
32.5°	6685.7	6666.9	*6654.4*
35°	6999.3	6905.3	*6917.8*
37.5°	7381.9	7287.8	*7206.3*
40°	7921.3	7795.9	*7745.7*
42.5°	8266.2	8140.8	*8153.3*
45°	8460.7	8241.2	*8184.7*
47.5°	8987.5	8711.5	*8636.3*
50°	9840.5	9501.8	*9407.7*
52.5°	11220.3	10674.6	*10549.2*
55°	12951.3	12280.2	*12154.8*
57.5°	15322.0	14431.4	*14161.7*
60°	18207.0	17103.2	*16695.5*
62.5°	21675.4	20314.4	*19925.5*
65°	24284.4	23149.2	*22547.1*
67.5°	26372.9	25438.4	*25149.9*
70°	27614.8	27658.7	*27733.9*
72.5°	*26178.5*	*27382.7*	*27959.7*
75°	19185.4	20119.9	*21016.8*
77.5°	7413.3	6685.7	*6472.5*
80°	1197.9	1122.7	*1160.3*
82.5°	539.4	570.7	*602.1*
85°	351.2	407.7	*432.8*
87.5°	81.5	81.5	*81.5*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ

Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-740-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 4000K CCT 26 LEDS

Spectral Parameters

CCT (K):	3949
CIE u':	0.2248
CIE v':	0.5053
Duv:	0.0022
CIE x:	0.3844
CIE y:	0.3840
CIE z:	0.2316
Peak Wavelength (nm):	440
Dominant Wavelength (nm):	578
Purity:	30.60026
Rf:	71.8
Rg:	96.5

CRI (Ra):	70.7
R1:	68.0
R2:	76.0
R3:	84.3
R4:	72.0
R5:	68.6
R6:	68.3
R7:	77.9
R8:	50.3
R9:	-36.7
R10:	45.1
R11:	70.7
R12:	47.1
R13:	68.5
R14:	91.1
R15:	58.7



Test Conditions


Stabilization Time:	34M
Operation Time:	1H 34M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3949K
CIE x = 0.3844
CIE y = 0.3840
Duv = 0.0022

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.78**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-1

TM-30-18


Summary


R_f = 71.8
R_g = 96.5
CIE R_a = 70.7
R_9 = -36.7


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 56	CES51 = 86	CES76 = 48
CES02 = 61	CES27 = 79	CES52 = 88	CES77 = 71
CES03 = 30	CES28 = 80	CES53 = 73	CES78 = 52
CES04 = 70	CES29 = 49	CES54 = 79	CES79 = 79
CES05 = 47	CES30 = 53	CES55 = 77	CES80 = 77
CES06 = 50	CES31 = 55	CES56 = 67	CES81 = 75
CES07 = 40	CES32 = 53	CES57 = 64	CES82 = 90
CES08 = 39	CES33 = 59	CES58 = 67	CES83 = 84
CES09 = 29	CES34 = 67	CES59 = 87	CES84 = 89
CES10 = 74	CES35 = 82	CES60 = 91	CES85 = 86
CES11 = 57	CES36 = 86	CES61 = 87	CES86 = 71
CES12 = 63	CES37 = 76	CES62 = 76	CES87 = 78
CES13 = 42	CES38 = 62	CES63 = 73	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 71	CES89 = 72
CES15 = 71	CES40 = 84	CES65 = 64	CES90 = 72
CES16 = 46	CES41 = 81	CES66 = 67	CES91 = 97
CES17 = 49	CES42 = 76	CES67 = 65	CES92 = 66
CES18 = 56	CES43 = 71	CES68 = 72	CES93 = 81
CES19 = 72	CES44 = 98	CES69 = 82	CES94 = 55
CES20 = 65	CES45 = 80	CES70 = 61	CES95 = 73
CES21 = 86	CES46 = 76	CES71 = 59	CES96 = 78
CES22 = 78	CES47 = 71	CES72 = 86	CES97 = 83
CES23 = 92	CES48 = 61	CES73 = 52	CES98 = 72
CES24 = 91	CES49 = 76	CES74 = 93	CES99 = 60
CES25 = 72	CES50 = 84	CES75 = 56	





REPORT NUMBER: SP1-2407-184-1

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-1

TM-30-18

Measure Comparisons





(END OF REPORT)