Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360684

Luminaire Tested: **GSS-SB6B-740-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360684
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6B-740-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 219W 70CRI 4000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(156) 4000K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	34396.9 lumens
Efficiency:	N/A
Efficacy:	157.1 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B5 - U0 - G5


Input Watts (W):	219
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360684
CATALOG NUMBER: GSS-SB6B-740-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 16.9 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360684
CATALOG NUMBER: GSS-SB6B-740-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360684
CATALOG NUMBER: GSS-SB6B-740-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	17198.5	0.0	17198.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	17198.5	0.0	17198.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	34396.9	0.0	34396.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	656.0	1.9
10°-20°	1999.3	5.8
20°-30°	3341.6	9.7
30°-40°	4608.3	13.4
40°-50°	5649.2	16.4
50°-60°	6620.1	19.2
60°-70°	7351.5	21.4
70°-80°	3997.7	11.6
80°-90°	173.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	34396.9	100.0
0°-180°	34396.9	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360684
CATALOG NUMBER: GSS-SB6B-740-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2998.4	8.7			
FM	(30°-60°)	8438.8	24.5			
FH	(60°-80°)	5674.6	16.5			G3/7500
FVH	(80°-90°)	86.6	0.3			G1/100
BL	(0°-30°)	2998.4	8.7	B4/5000		
BM	(30°-60°)	8438.8	24.5	B4/8500		
BH	(60°-80°)	5674.6	16.5	B5		G5
BVH	(80°-90°)	86.6	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G5
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360684
CATALOG NUMBER: GSS-SB6B-740-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	6777.0	6777.0	6777.0	6777.0	6777.0	6777.0	6777.0	6777.0	6777.0	6777.0	6777.0
2.5°	6784.6	6784.6	6762.0	6792.1	6777.0	6784.6	6792.1	6784.6	6777.0	6784.6	6792.1
5°	6822.2	6807.2	6822.2	6837.3	6814.7	6829.8	6822.2	6784.6	6807.2	6807.2	6807.2
7.5°	6890.0	6905.1	6890.0	6927.6	6905.1	6950.2	6905.1	6874.9	6867.4	6859.9	6859.9
10°	6920.1	6920.1	6912.6	6980.4	6995.4	7040.6	7010.5	6965.3	6942.7	6912.6	6882.5
12.5°	6837.3	6852.3	6890.0	7018.0	7078.2	7168.6	7146.0	7055.7	6987.9	6965.3	6920.1
15°	6746.9	6762.0	6837.3	6995.4	7138.5	7274.0	7266.5	7153.5	7070.7	7010.5	6942.7
17.5°	6603.9	6626.4	6731.9	6972.8	7228.8	7379.4	7424.6	7311.7	7221.3	7123.4	7033.1
20°	6362.9	6362.9	6551.1	6859.9	7213.8	7552.6	7673.1	7582.8	7477.3	7319.2	7198.7
22.5°	6091.8	6106.9	6295.1	6701.7	7206.3	7703.2	7936.7	7838.8	7733.4	7560.2	7379.4
25°	5820.7	5820.7	6031.6	6490.9	7108.4	7808.7	8245.4	8192.7	7981.9	7823.7	7590.3
27.5°	5572.2	5572.2	5798.1	6280.1	6942.7	7838.8	8554.1	8554.1	8320.7	8087.3	7831.2
30°	5278.6	5353.9	5609.9	6114.4	6792.1	7786.1	8780.0	8923.1	8712.3	8411.1	8034.6
32.5°	5030.1	5082.8	5346.3	5881.0	6573.7	7725.8	9036.1	9390.0	9171.6	8757.4	8335.8
35°	4736.4	4728.9	5030.1	5557.2	6265.0	7590.3	9239.4	9947.2	9736.4	9292.1	8719.8
37.5°	4352.4	4352.4	4661.1	5173.1	5971.3	7356.9	9405.0	10564.7	10406.5	9902.0	9292.1
40°	3938.2	3983.4	4254.5	4774.1	5617.4	7078.2	9405.0	11069.2	11152.0	10632.4	9999.9
42.5°	3637.0	3652.1	3900.6	4390.0	5225.9	6716.8	9284.5	11505.9	11754.4	11317.7	10496.9
45°	3320.8	3358.4	3569.2	4021.0	4819.2	6287.6	9073.7	11995.4	12394.5	12093.3	11016.5
47.5°	2936.7	2974.4	3215.3	3674.7	4435.2	5820.7	8719.8	12507.4	13343.2	13124.9	11942.7
50°	2492.4	2522.6	2748.5	3237.9	4006.0	5286.1	8275.5	12891.4	14292.0	14510.4	13343.2
52.5°	1950.3	1972.9	2213.8	2688.2	3493.9	4774.1	7650.5	13124.9	15248.3	16016.4	15218.2
55°	1400.6	1438.2	1649.1	2040.6	2816.2	4088.8	6905.1	13245.4	16295.0	17801.0	17545.0
57.5°	1009.0	1024.1	1167.2	1468.4	2093.4	3283.1	5948.7	13042.0	17236.3	19932.0	20466.7
60°	835.8	835.8	858.4	1001.5	1430.7	2319.3	4804.2	12289.0	18042.0	22085.6	23734.7
62.5°	768.1	768.1	783.1	805.7	941.3	1506.0	3433.7	10760.4	18132.4	24156.4	27319.0
65°	700.3	700.3	715.4	730.4	760.5	978.9	2070.8	7876.4	16362.8	24179.0	29246.7
67.5°	640.1	640.1	647.6	655.1	670.2	715.4	1137.0	4774.1	13094.8	23538.9	29984.6
70°	579.8	579.8	579.8	572.3	594.9	602.4	753.0	2424.7	8757.4	21257.3	29630.7
72.5°	*512.0*	*512.0*	*504.5*	*489.5*	*497.0*	*497.0*	*557.2*	*1189.7*	*4548.1*	*16897.4*	*26754.3*
75°	436.7	444.3	414.2	399.1	391.6	399.1	444.3	677.7	2033.1	10248.4	19992.3
77.5°	369.0	384.0	338.9	308.7	301.2	301.2	346.4	421.7	873.5	3719.8	8960.8
80°	278.6	286.1	248.5	218.4	218.4	210.8	256.0	308.7	414.2	1106.9	2010.5
82.5°	158.1	158.1	143.1	128.0	120.5	128.0	173.2	210.8	256.0	391.6	549.7
85°	37.7	37.7	45.2	52.7	52.7	67.8	97.9	113.0	135.5	158.1	210.8
87.5°	7.5	7.5	7.5	15.1	22.6	22.6	37.7	52.7	67.8	82.8	90.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360684
CATALOG NUMBER: GSS-SB6B-740-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	6777.0	6777.0	*6777.0*
2.5°	6792.1	6799.6	*6792.1*
5°	6837.3	6822.2	*6799.6*
7.5°	6844.8	6852.3	*6859.9*
10°	6874.9	6905.1	*6859.9*
12.5°	6905.1	6882.5	*6867.4*
15°	6927.6	6920.1	*6874.9*
17.5°	7010.5	6980.4	*6972.8*
20°	7138.5	7131.0	*7108.4*
22.5°	7289.1	7274.0	*7266.5*
25°	7507.5	7454.7	*7424.6*
27.5°	7688.2	7643.0	*7627.9*
30°	7868.9	7778.5	*7778.5*
32.5°	8027.0	8004.4	*7989.4*
35°	8403.5	8290.6	*8305.6*
37.5°	8862.9	8749.9	*8652.0*
40°	9510.5	9359.8	*9299.6*
42.5°	9924.6	9774.0	*9789.1*
45°	10158.0	9894.5	*9826.7*
47.5°	10790.6	10459.2	*10368.9*
50°	11814.6	11408.0	*11295.1*
52.5°	13471.3	12816.1	*12665.5*
55°	15549.5	14743.8	*14593.2*
57.5°	18395.9	17326.6	*17002.8*
60°	21859.7	20534.4	*20045.0*
62.5°	26023.8	24389.8	*23923.0*
65°	29156.3	27793.4	*27070.5*
67.5°	31663.9	30541.9	*30195.5*
70°	33154.8	33207.5	*33297.9*
72.5°	*31430.4*	*32876.2*	*33569.0*
75°	23034.4	24156.4	*25233.2*
77.5°	8900.5	8027.0	*7771.0*
80°	1438.2	1347.9	*1393.1*
82.5°	647.6	685.2	*722.9*
85°	421.7	489.5	*519.6*
87.5°	97.9	97.9	*97.9*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ

Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-740-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 4000K CCT 26 LEDS

Spectral Parameters

CCT (K):	3949
CIE u':	0.2248
CIE v':	0.5053
Duv:	0.0022
CIE x:	0.3844
CIE y:	0.3840
CIE z:	0.2316
Peak Wavelength (nm):	440
Dominant Wavelength (nm):	578
Purity:	30.60026
Rf:	71.8
Rg:	96.5

CRI (Ra):	70.7
R1:	68.0
R2:	76.0
R3:	84.3
R4:	72.0
R5:	68.6
R6:	68.3
R7:	77.9
R8:	50.3
R9:	-36.7
R10:	45.1
R11:	70.7
R12:	47.1
R13:	68.5
R14:	91.1
R15:	58.7



Test Conditions


Stabilization Time:	34M
Operation Time:	1H 34M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3949K
CIE x = 0.3844
CIE y = 0.3840
Duv = 0.0022

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.47**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.78**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	139	NR	620	607	NR	750	15	NR	880	0	NR
365	0	NR	495	198	NR	625	554	NR	755	13	NR	885	0	NR
370	0	NR	500	267	NR	630	504	NR	760	11	NR	890	0	NR
375	0	NR	505	343	NR	635	452	NR	765	10	NR	895	0	NR
380	0	NR	510	410	NR	640	403	NR	770	8	NR	900	0	NR
385	2	NR	515	470	NR	645	357	NR	775	7	NR	905	0	NR
390	4	NR	520	516	NR	650	314	NR	780	6	NR	910	0	NR
395	7	NR	525	550	NR	655	275	NR	785	5	NR	915	0	NR
400	10	NR	530	578	NR	660	240	NR	790	5	NR	920	0	NR
405	17	NR	535	601	NR	665	208	NR	795	4	NR	925	0	NR
410	35	NR	540	620	NR	670	179	NR	800	4	NR	930	0	NR
415	70	NR	545	641	NR	675	155	NR	805	3	NR	935	0	NR
420	147	NR	550	664	NR	680	133	NR	810	3	NR	940	0	NR
425	285	NR	555	689	NR	685	114	NR	815	2	NR	945	0	NR
430	487	NR	560	715	NR	690	98	NR	820	2	NR	950	0	NR
435	787	NR	565	743	NR	695	84	NR	825	2	NR	955	0	NR
440	1000	NR	570	771	NR	700	72	NR	830	2	NR	960	0	NR
445	783	NR	575	794	NR	705	61	NR	835	1	NR	965	0	NR
450	417	NR	580	811	NR	710	52	NR	840	1	NR	970	0	NR
455	261	NR	585	817	NR	715	45	NR	845	1	NR	975	0	NR
460	167	NR	590	815	NR	720	39	NR	850	1	NR	980	0	NR
465	104	NR	595	801	NR	725	33	NR	855	1	NR	985	0	NR
470	79	NR	600	777	NR	730	28	NR	860	1	NR	990	0	NR
475	73	NR	605	744	NR	735	24	NR	865	1	NR	995	0	NR
480	76	NR	610	704	NR	740	21	NR	870	1	NR	1000	0	NR
485	98	NR	615	657	NR	745	18	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-1

TM-30-18


Summary


R_f = 71.8
R_g = 96.5
CIE R_a = 70.7
R_9 = -36.7


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 56	CES51 = 86	CES76 = 48
CES02 = 61	CES27 = 79	CES52 = 88	CES77 = 71
CES03 = 30	CES28 = 80	CES53 = 73	CES78 = 52
CES04 = 70	CES29 = 49	CES54 = 79	CES79 = 79
CES05 = 47	CES30 = 53	CES55 = 77	CES80 = 77
CES06 = 50	CES31 = 55	CES56 = 67	CES81 = 75
CES07 = 40	CES32 = 53	CES57 = 64	CES82 = 90
CES08 = 39	CES33 = 59	CES58 = 67	CES83 = 84
CES09 = 29	CES34 = 67	CES59 = 87	CES84 = 89
CES10 = 74	CES35 = 82	CES60 = 91	CES85 = 86
CES11 = 57	CES36 = 86	CES61 = 87	CES86 = 71
CES12 = 63	CES37 = 76	CES62 = 76	CES87 = 78
CES13 = 42	CES38 = 62	CES63 = 73	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 71	CES89 = 72
CES15 = 71	CES40 = 84	CES65 = 64	CES90 = 72
CES16 = 46	CES41 = 81	CES66 = 67	CES91 = 97
CES17 = 49	CES42 = 76	CES67 = 65	CES92 = 66
CES18 = 56	CES43 = 71	CES68 = 72	CES93 = 81
CES19 = 72	CES44 = 98	CES69 = 82	CES94 = 55
CES20 = 65	CES45 = 80	CES70 = 61	CES95 = 73
CES21 = 86	CES46 = 76	CES71 = 59	CES96 = 78
CES22 = 78	CES47 = 71	CES72 = 86	CES97 = 83
CES23 = 92	CES48 = 61	CES73 = 52	CES98 = 72
CES24 = 91	CES49 = 76	CES74 = 93	CES99 = 60
CES25 = 72	CES50 = 84	CES75 = 56	





REPORT NUMBER: SP1-2407-184-1

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-1

TM-30-18

Measure Comparisons





(END OF REPORT)